

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001614

Luminaire Tested: SA4XXDIP-B575D590UB35-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001614
REPORT IS A COMBINATION OF REPORTS P996236 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D590UB35-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4431.0 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001614

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001614

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49		
1	97	92	88	84	89	85	81	78	71	69	66	59	57	55	48	46	45	40		
2	88	80	73	68	80	73	68	63	62	58	54	51	48	45	41	39	37	32		
3	80	70	62	56	73	64	58	52	54	49	45	45	41	38	36	33	31	27		
4	73	61	53	47	67	57	49	44	48	42	38	40	36	32	32	29	26	23		
5	67	55	46	40	61	50	43	37	43	37	32	36	31	28	29	26	23	20		
6	61	49	40	34	56	45	38	32	38	33	28	32	27	24	26	23	20	17		
7	57	44	36	30	52	41	33	28	35	29	25	29	25	21	24	20	18	15		
8	52	40	32	26	48	37	30	25	32	26	22	27	22	19	22	18	16	13		
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	17	14	12		
10	46	33	26	21	42	31	24	20	27	21	17	22	18	15	19	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5668	5668	5668
5°	5684	5521	5531
10°	5647	5412	5397
15°	5594	5290	5246
20°	5516	5157	5098
25°	5428	5012	4940
30°	5333	4868	4779
35°	5224	4720	4635
40°	5137	4578	4486
45°	5010	4445	4354
50°	4901	4294	4216
55°	4787	4148	4055
60°	4611	3967	3905
65°	4419	3772	3724
70°	4185	3547	3514
75°	3859	3300	3315
80°	3488	3046	3106
85°	3005	2793	2937

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5010 cd/sqm

TEST NUMBER: P1001614

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	1.5
10°-20°	188.7	4.3
20°-30°	285.3	6.4
30°-40°	345.2	7.8
40°-50°	364.9	8.2
50°-60°	343.5	7.8
60°-70°	285.0	6.4
70°-80°	200.0	4.5
80°-90°	114.3	2.6
90°-100°	115.5	2.6
100°-110°	194.6	4.4
110°-120°	279.5	6.3
120°-130°	343.4	7.8
130°-140°	372.8	8.4
140°-150°	360.0	8.1
150°-160°	301.4	6.8
160°-170°	200.6	4.5
170°-180°	70.2	1.6
0°-30°	539.9	12.2
0°-40°	885.1	20.0
0°-60°	1593.5	36.0
0°-90°	2192.9	49.5
90°-120°	589.7	13.3
90°-150°	1665.9	37.6
90°-180°	2238.0	50.5
0°-180°	4431.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	695	695	695	695	695	
5°	696	694	688	694	694	66
15°	667	668	666	673	672	188
25°	610	615	617	626	627	281
35°	534	543	551	562	564	334
45°	445	460	475	488	492	344
55°	349	365	388	404	409	311
65°	241	266	293	312	318	239
75°	134	163	195	217	224	142
85°	41	74	109	132	140	43
90°	14	52	90	116	123	11
95°	44	75	111	134	141	45
105°	141	157	188	209	217	150
115°	255	262	286	302	307	252
125°	368	367	386	399	403	328
135°	472	475	481	492	495	365
145°	572	574	574	578	580	358
155°	654	654	654	656	654	301
165°	712	711	710	713	711	201
175°	741	738	738	742	738	70
180°	742	742	742	742	742	

TEST NUMBER: P1001614

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	695.1	695.1	695.1	695.1	695.1
2.5°	698.2	695.9	689.7	695.1	694.4
5°	695.9	693.6	688.1	694.4	693.6
7.5°	691.2	689.7	685.0	692.0	691.2
10°	685.0	684.2	680.3	687.4	686.6
12.5°	676.5	676.5	674.1	680.3	680.3
15°	667.1	667.9	665.6	672.6	671.8
17.5°	654.7	657.0	656.2	663.2	662.4
20°	641.4	643.8	644.5	652.3	652.3
22.5°	626.6	629.7	631.3	639.1	640.6
25°	610.3	615.0	617.3	625.9	626.6
27.5°	592.4	599.4	602.5	610.3	611.1
30°	574.5	580.7	586.2	594.7	596.3
32.5°	555.0	562.8	569.0	579.1	580.7
35°	534.0	543.3	551.1	562.0	564.4
37.5°	513.0	523.9	533.2	544.1	546.5
40°	492.7	502.9	513.8	525.4	528.6
42.5°	469.4	481.1	494.3	507.5	509.9
45°	445.3	460.1	474.8	488.1	492.0
47.5°	422.7	437.5	454.6	467.8	472.5
50°	397.8	414.9	432.0	447.6	452.3
52.5°	372.9	390.0	410.2	425.8	430.5
55°	348.7	365.1	388.4	404.0	408.7
57.5°	321.5	341.7	364.3	383.0	386.9
60°	295.0	315.3	341.0	358.9	365.1
62.5°	269.3	291.9	317.6	335.5	341.7
65°	241.3	266.2	292.7	312.1	318.4
67.5°	214.8	241.3	269.3	288.8	295.0
70°	187.6	214.1	243.6	264.7	270.1
72.5°	161.1	188.4	220.3	240.5	246.8
75°	133.9	162.7	195.4	217.2	224.2
77.5°	108.2	138.6	172.8	194.6	202.4
80°	84.8	116.0	150.2	173.6	179.8
82.5°	61.5	94.2	128.4	152.6	159.6
85°	41.3	74.0	109.0	132.3	140.1
87.5°	25.7	57.6	91.9	114.4	121.4
90°	14.2	51.6	89.7	115.7	123.1
92.5°	26.6	61.3	97.7	121.2	128.0
95°	44.5	75.4	111.3	134.0	141.0
97.5°	64.4	91.6	128.1	150.7	157.7
100°	89.0	111.5	147.0	169.2	174.6
102.5°	115.4	133.0	167.2	189.2	195.9
105°	140.8	156.9	188.0	209.1	217.2
107.5°	168.9	182.7	210.5	232.2	237.1
110°	196.8	208.8	235.6	252.3	260.2

TEST NUMBER: P1001614

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	225.8	235.2	259.8	276.9	283.1
115°	255.0	262.0	285.7	302.3	307.2
117.5°	283.1	287.7	310.5	325.1	329.7
120°	310.4	315.0	335.9	348.6	356.0
122.5°	339.7	340.3	360.7	374.6	377.1
125°	367.6	366.8	385.7	399.4	402.9
127.5°	393.4	394.4	408.8	421.7	426.6
130°	420.2	421.2	433.6	446.5	448.9
132.5°	448.3	448.8	457.5	469.6	473.7
135°	471.7	475.2	480.6	491.9	494.8
137.5°	498.7	499.6	503.9	513.9	518.3
140°	525.7	526.0	526.8	536.4	539.7
142.5°	549.6	550.7	549.4	558.0	561.1
145°	572.0	573.5	574.0	578.2	579.5
147.5°	594.9	597.0	596.4	596.6	599.2
150°	615.6	617.1	617.1	617.1	616.5
152.5°	634.3	635.5	636.0	637.8	636.0
155°	654.4	654.4	653.8	656.1	653.8
157.5°	671.6	670.5	670.5	672.2	670.5
160°	686.5	686.0	685.4	687.1	684.3
162.5°	700.3	698.6	698.0	701.5	698.6
165°	712.4	710.7	709.5	713.0	710.7
167.5°	722.1	719.8	719.8	723.3	719.8
170°	730.2	727.3	727.9	731.3	727.3
172.5°	735.9	733.6	733.6	737.6	733.6
175°	741.1	738.2	737.6	741.7	737.6
177.5°	743.4	740.5	740.5	744.5	739.9
180°	742.2	742.2	742.2	742.2	742.2

(END OF REPORT)