

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001618

Luminaire Tested: SA4XXDIP-B575D590UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001618
REPORT IS A COMBINATION OF REPORTS P996240 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D590UB35-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4626.3 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001618

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001618

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	94	90	87	91	88	84	81	75	72	70	63	62	60	53	52	50
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	41	46	40	36	39	35	31	33	30	27
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7920	7920	7920
5°	7927	7692	7702
10°	7860	7479	7426
15°	7747	7225	7116
20°	7603	6951	6794
25°	7441	6660	6449
30°	7246	6347	6069
35°	7043	6026	5701
40°	6832	5680	5310
45°	6611	5333	4946
50°	6367	4997	4541
55°	6100	4605	4140
60°	5828	4175	3721
65°	5516	3730	3249
70°	5156	3196	2744
75°	4619	2575	2199
80°	3936	1862	1546
85°	3056	1038	832

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6611 cd/sqm

TEST NUMBER: P1001618

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	2.0
10°-20°	257.9	5.6
20°-30°	379.6	8.2
30°-40°	441.2	9.5
40°-50°	441.2	9.5
50°-60°	385.9	8.3
60°-70°	286.5	6.2
70°-80°	162.5	3.5
80°-90°	47.7	1.0
90°-100°	217.0	4.7
100°-110°	441.4	9.5
110°-120°	393.4	8.5
120°-130°	330.5	7.1
130°-140°	275.8	6.0
140°-150°	210.6	4.6
150°-160°	148.0	3.2
160°-170°	87.1	1.9
170°-180°	28.3	0.6
0°-30°	729.1	15.8
0°-40°	1170.3	25.3
0°-60°	1997.4	43.2
0°-90°	2494.1	53.9
90°-120°	1051.9	22.7
90°-150°	1868.7	40.4
90°-180°	2132.0	46.1
0°-180°	4626.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	921	909	914	911	260
25°	837	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	149	149	170
85°	42	42	40	40	40	45
90°	1	5	10	12	12	4
95°	19	60	468	232	140	21
105°	67	97	376	811	808	72
115°	118	148	336	645	775	117
125°	165	196	334	549	619	147
135°	196	233	331	487	553	151
145°	226	258	330	411	452	142
155°	257	277	320	363	378	118
165°	280	288	307	325	330	79
175°	292	292	294	298	297	28
180°	292	292	292	292	292	

TEST NUMBER: P1001618

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	971.3	971.3	971.3	971.3	971.3
2.5°	974.4	972.1	963.5	971.3	970.5
5°	970.5	967.4	958.8	967.4	965.8
7.5°	963.5	960.4	951.1	958.1	957.3
10°	953.4	950.3	940.2	946.4	944.8
12.5°	940.2	937.0	926.1	933.2	930.8
15°	923.8	920.7	909.0	913.7	911.4
17.5°	905.1	901.2	890.3	893.5	891.9
20°	884.1	880.2	868.6	870.9	869.3
22.5°	861.6	856.1	844.4	849.1	846.0
25°	836.6	831.2	820.3	821.1	818.0
27.5°	808.6	803.2	793.1	791.5	787.6
30°	780.6	774.4	764.3	761.2	757.3
32.5°	751.0	745.6	734.7	730.8	726.9
35°	719.9	714.5	703.6	698.1	694.2
37.5°	687.2	682.5	670.9	665.4	660.0
40°	655.3	649.1	637.4	629.6	625.7
42.5°	621.1	618.0	604.7	595.4	593.0
45°	587.6	582.2	569.7	561.1	558.8
47.5°	552.6	548.7	537.0	527.7	521.4
50°	516.8	513.7	502.8	491.9	487.2
52.5°	481.8	477.9	466.2	456.8	450.6
55°	444.4	442.1	431.2	421.8	417.2
57.5°	409.4	407.0	396.1	386.8	382.1
60°	372.8	368.9	358.8	351.8	347.9
62.5°	337.0	333.9	323.0	316.8	312.9
65°	301.2	297.3	289.5	281.7	277.8
67.5°	264.6	261.5	253.7	245.9	245.2
70°	231.1	225.7	219.5	213.2	210.9
72.5°	195.3	189.9	185.2	180.6	178.2
75°	160.3	156.4	152.5	149.4	148.7
77.5°	126.1	124.5	120.6	119.9	117.5
80°	95.7	93.4	91.8	90.3	89.5
82.5°	66.2	65.4	65.4	64.6	63.8
85°	42.0	42.0	40.5	40.5	39.7
87.5°	20.2	19.5	18.7	18.7	18.7
90°	0.6	4.6	10.3	11.5	12.1
92.5°	8.0	44.2	225.0	74.4	52.2
95°	18.9	59.6	467.8	231.6	140.1
97.5°	31.6	66.0	500.5	473.0	336.4
100°	43.6	74.6	461.5	654.4	526.3
102.5°	55.1	84.9	412.7	768.0	691.6
105°	67.2	97.3	376.5	810.8	807.6
107.5°	80.4	109.9	353.0	797.8	862.7
110°	93.6	122.6	342.1	751.9	863.8

TEST NUMBER: P1001618

CATALOG NUMBER: SA4XXDIP-B575D590UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	106.2	135.2	336.9	695.7	830.0
115°	118.2	148.4	335.8	645.2	775.4
117.5°	130.9	160.8	335.2	605.6	722.1
120°	143.5	172.8	335.2	578.8	678.4
122.5°	155.0	184.6	334.6	561.4	644.0
125°	164.7	195.8	334.1	549.0	618.8
127.5°	173.9	206.0	332.9	537.2	602.7
130°	181.4	216.1	332.3	523.2	588.9
132.5°	188.8	224.8	331.8	506.5	573.4
135°	195.7	233.0	331.2	487.4	553.3
137.5°	202.6	240.2	331.2	466.6	529.8
140°	210.1	246.8	330.6	446.6	504.0
142.5°	218.1	252.8	330.6	427.9	476.4
145°	225.6	258.3	329.5	411.0	451.7
147.5°	234.2	263.4	327.7	396.9	428.8
150°	242.2	268.4	326.0	384.0	409.8
152.5°	249.7	272.9	323.2	373.1	392.6
155°	256.6	277.0	320.3	362.8	378.3
157.5°	263.5	280.6	317.4	353.0	365.1
160°	269.8	283.8	314.0	343.2	353.0
162.5°	275.5	286.4	310.5	333.8	341.5
165°	279.5	288.2	307.1	325.2	330.0
167.5°	284.1	289.6	303.6	317.7	320.9
170°	287.0	290.8	300.2	310.2	312.2
172.5°	289.9	291.6	296.7	303.6	303.6
175°	291.6	292.2	294.5	298.5	297.3
177.5°	292.7	292.2	292.7	294.8	292.7
180°	292.2	292.2	292.2	292.2	292.2

(END OF REPORT)