

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001632

Luminaire Tested: SA4XXDIP-B575D590UB50-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001632
REPORT IS A COMBINATION OF REPORTS P996254 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D590UB50-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4242.0 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001632

CATALOG NUMBER: SA4XXDIP-B575D590UB50-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001632

CATALOG NUMBER: SA4XXDIP-B575D590UB50-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	97	92	88	84	89	85	81	78	71	69	66	59	57	55	48	46	45
2	88	80	73	68	80	73	68	63	62	58	54	51	48	45	41	39	37
3	80	70	62	56	73	64	58	52	54	49	45	45	41	38	36	33	31
4	73	61	53	47	67	57	49	44	48	42	38	40	36	32	32	29	26
5	67	55	46	40	61	50	43	37	43	37	32	36	31	28	29	26	23
6	61	49	40	34	56	45	38	32	38	33	28	32	27	24	26	23	20
7	57	44	36	30	52	41	33	28	35	29	25	29	25	21	24	20	18
8	52	40	32	26	48	37	30	25	32	26	22	27	22	19	22	18	16
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	17	14
10	46	33	26	21	42	31	24	20	27	21	17	22	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5427	5427	5427
5°	5442	5285	5295
10°	5406	5182	5167
15°	5356	5065	5022
20°	5281	4938	4881
25°	5197	4798	4729
30°	5105	4660	4575
35°	5001	4518	4437
40°	4918	4383	4294
45°	4796	4255	4168
50°	4691	4111	4036
55°	4583	3972	3883
60°	4416	3798	3738
65°	4230	3611	3565
70°	4007	3397	3364
75°	3694	3160	3173
80°	3340	2916	2975
85°	2874	2673	2811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4796 cd/sqm

TEST NUMBER: P1001632

CATALOG NUMBER: SA4XXDIP-B575D590UB50-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	1.5
10°-20°	180.7	4.3
20°-30°	273.2	6.4
30°-40°	330.5	7.8
40°-50°	349.4	8.2
50°-60°	328.8	7.8
60°-70°	272.9	6.4
70°-80°	191.5	4.5
80°-90°	109.5	2.6
90°-100°	110.6	2.6
100°-110°	186.3	4.4
110°-120°	267.6	6.3
120°-130°	328.8	7.8
130°-140°	356.9	8.4
140°-150°	344.6	8.1
150°-160°	288.6	6.8
160°-170°	192.0	4.5
170°-180°	67.2	1.6
0°-30°	516.9	12.2
0°-40°	847.4	20.0
0°-60°	1525.6	36.0
0°-90°	2099.4	49.5
90°-120°	564.5	13.3
90°-150°	1594.8	37.6
90°-180°	2143.0	50.5
0°-180°	4242.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	666	666	666	666	666	
5°	666	664	659	665	664	63
15°	639	639	637	644	643	180
25°	584	589	591	599	600	269
35°	511	520	528	538	540	320
45°	426	440	455	467	471	329
55°	334	350	372	387	391	298
65°	231	255	280	299	305	229
75°	128	156	187	208	215	136
85°	40	71	104	127	134	41
90°	14	49	86	111	118	11
95°	43	72	107	128	135	43
105°	135	150	180	200	208	143
115°	244	251	274	289	294	241
125°	352	351	369	382	386	314
135°	452	455	460	471	474	350
145°	548	549	550	554	555	343
155°	626	626	626	628	626	288
165°	682	680	679	682	680	192
175°	709	707	706	710	706	67
180°	710	710	710	710	710	

TEST NUMBER: P1001632

CATALOG NUMBER: SA4XXDIP-B575D590UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	665.5	665.5	665.5	665.5	665.5
2.5°	668.5	666.3	660.3	665.5	664.8
5°	666.3	664.0	658.8	664.8	664.0
7.5°	661.8	660.3	655.8	662.5	661.8
10°	655.8	655.1	651.4	658.1	657.3
12.5°	647.6	647.6	645.4	651.4	651.4
15°	638.7	639.4	637.2	643.9	643.2
17.5°	626.8	629.0	628.2	635.0	634.2
20°	614.1	616.3	617.1	624.5	624.5
22.5°	599.9	602.9	604.4	611.9	613.3
25°	584.3	588.7	591.0	599.2	599.9
27.5°	567.1	573.8	576.8	584.3	585.0
30°	550.0	556.0	561.2	569.4	570.9
32.5°	531.4	538.8	544.8	554.5	556.0
35°	511.2	520.2	527.6	538.1	540.3
37.5°	491.1	501.6	510.5	520.9	523.2
40°	471.7	481.4	491.9	503.0	506.0
42.5°	449.4	460.6	473.2	485.9	488.1
45°	426.3	440.4	454.6	467.3	471.0
47.5°	404.7	418.8	435.2	447.9	452.4
50°	380.8	397.2	413.6	428.5	433.0
52.5°	357.0	373.4	392.7	407.7	412.1
55°	333.9	349.5	371.9	386.8	391.3
57.5°	307.8	327.2	348.8	366.7	370.4
60°	282.5	301.8	326.4	343.6	349.5
62.5°	257.9	279.5	304.1	321.2	327.2
65°	231.0	254.9	280.2	298.8	304.8
67.5°	205.7	231.0	257.9	276.5	282.5
70°	179.6	204.9	233.3	253.4	258.6
72.5°	154.3	180.4	210.9	230.3	236.2
75°	128.2	155.8	187.1	207.9	214.6
77.5°	103.6	132.7	165.4	186.3	193.8
80°	81.2	111.0	143.8	166.2	172.2
82.5°	58.9	90.2	123.0	146.1	152.8
85°	39.5	70.8	104.3	126.7	134.1
87.5°	24.6	55.1	87.9	109.6	116.3
90°	13.5	49.4	85.9	110.8	117.9
92.5°	25.5	58.7	93.5	116.0	122.5
95°	42.7	72.2	106.6	128.4	135.1
97.5°	61.7	87.8	122.6	144.2	150.9
100°	85.1	106.7	140.7	162.0	167.2
102.5°	110.4	127.4	160.1	181.1	187.7
105°	134.7	150.2	180.0	200.2	207.9
107.5°	161.7	174.9	201.6	222.4	227.0
110°	188.4	199.9	225.5	241.5	249.1

TEST NUMBER: P1001632

CATALOG NUMBER: SA4XXDIP-B575D590UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	216.2	225.2	248.7	265.0	271.0
115°	244.1	250.8	273.5	289.3	294.0
117.5°	271.0	275.4	297.3	311.3	315.6
120°	297.1	301.6	321.6	333.7	340.7
122.5°	325.2	325.7	345.3	358.6	361.1
125°	351.9	351.1	369.3	382.3	385.7
127.5°	376.7	377.5	391.3	403.7	408.4
130°	402.3	403.2	415.1	427.4	429.7
132.5°	429.2	429.6	437.9	449.5	453.5
135°	451.6	454.9	460.1	470.9	473.7
137.5°	477.4	478.2	482.3	491.9	496.1
140°	503.2	503.5	504.3	513.5	516.6
142.5°	526.0	527.1	525.9	534.1	537.1
145°	547.5	549.0	549.5	553.5	554.8
147.5°	569.5	571.5	571.0	571.1	573.6
150°	589.2	590.7	590.7	590.7	590.2
152.5°	607.2	608.3	608.9	610.5	608.9
155°	626.5	626.5	625.9	628.1	625.9
157.5°	642.9	641.8	641.8	643.5	641.8
160°	657.2	656.7	656.1	657.8	655.0
162.5°	670.4	668.8	668.2	671.5	668.8
165°	682.0	680.3	679.2	682.5	680.3
167.5°	691.3	689.1	689.1	692.4	689.1
170°	699.0	696.3	696.8	700.1	696.3
172.5°	704.5	702.3	702.3	706.1	702.3
175°	709.4	706.7	706.1	710.0	706.1
177.5°	711.6	708.9	708.9	712.7	708.3
180°	710.5	710.5	710.5	710.5	710.5

(END OF REPORT)