

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001644

Luminaire Tested: SA4XXDIP-B575D810UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001644
REPORT IS A COMBINATION OF REPORTS P996266 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D810UB27-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5179.0 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001644

CATALOG NUMBER: SA4XXDIP-B575D810UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001644

CATALOG NUMBER: SA4XXDIP-B575D810UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	85	89	86	82	79	72	69	67	59	58	56	48	46	45
2	88	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	55	51	47	46	42	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	24
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21
7	58	45	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	47	35	27	23	43	32	26	21	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7826	7594	7603
10°	7759	7383	7331
15°	7648	7133	7025
20°	7506	6861	6708
25°	7345	6575	6366
30°	7153	6265	5990
35°	6953	5948	5628
40°	6745	5607	5242
45°	6527	5265	4882
50°	6284	4933	4482
55°	6022	4545	4086
60°	5753	4121	3673
65°	5445	3683	3208
70°	5091	3156	2709
75°	4562	2543	2169
80°	3887	1839	1527
85°	3020	1025	822

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6527 cd/sqm

TEST NUMBER: P1001644

CATALOG NUMBER: SA4XXDIP-B575D810UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.4	1.7
10°-20°	254.6	4.9
20°-30°	374.7	7.2
30°-40°	435.6	8.4
40°-50°	435.5	8.4
50°-60°	380.9	7.4
60°-70°	282.8	5.5
70°-80°	160.5	3.1
80°-90°	48.0	0.9
90°-100°	63.8	1.2
100°-110°	191.1	3.7
110°-120°	324.7	6.3
120°-130°	428.2	8.3
130°-140°	480.9	9.3
140°-150°	472.7	9.1
150°-160°	397.5	7.7
160°-170°	264.5	5.1
170°-180°	92.6	1.8
0°-30°	719.7	13.9
0°-40°	1155.3	22.3
0°-60°	1971.8	38.1
0°-90°	2463.1	47.6
90°-120°	579.5	11.2
90°-150°	1961.2	37.9
90°-180°	2716.0	52.4
0°-180°	5179.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	959	959	959	959	959	
5°	958	955	946	955	953	91
15°	912	909	897	902	900	257
25°	826	820	810	810	808	380
35°	711	705	694	689	685	444
45°	580	575	562	554	552	447
55°	439	436	426	416	412	393
65°	297	294	286	278	274	294
75°	158	154	151	148	147	168
85°	42	42	40	40	39	45
90°	2	11	17	21	23	6
95°	45	52	58	60	60	49
105°	176	177	180	182	185	187
115°	330	330	328	328	327	326
125°	481	481	480	478	477	429
135°	620	624	624	623	621	480
145°	753	756	757	756	754	471
155°	863	863	862	865	862	397
165°	940	937	936	940	937	265
175°	977	974	973	978	973	93
180°	979	979	979	979	979	

TEST NUMBER: P1001644

CATALOG NUMBER: SA4XXDIP-B575D810UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	958.8	958.8	958.8	958.8	958.8
2.5°	961.9	959.6	951.1	958.8	958.1
5°	958.1	955.0	946.5	955.0	953.4
7.5°	951.1	948.1	938.8	945.8	945.0
10°	941.2	938.1	928.1	934.2	932.7
12.5°	928.1	925.0	914.3	921.2	918.9
15°	912.0	908.9	897.4	902.0	899.7
17.5°	893.5	889.7	878.9	882.0	880.5
20°	872.8	868.9	857.4	859.7	858.2
22.5°	850.5	845.1	833.6	838.2	835.1
25°	825.9	820.5	809.8	810.5	807.5
27.5°	798.2	792.9	782.9	781.3	777.5
30°	770.6	764.4	754.5	751.4	747.5
32.5°	741.4	736.0	725.3	721.4	717.6
35°	710.7	705.3	694.5	689.2	685.3
37.5°	678.4	673.8	662.3	656.9	651.5
40°	646.9	640.8	629.2	621.5	617.7
42.5°	613.1	610.0	597.0	587.7	585.4
45°	580.1	574.7	562.4	553.9	551.6
47.5°	545.5	541.6	530.1	520.9	514.8
50°	510.1	507.1	496.3	485.6	480.9
52.5°	475.6	471.7	460.2	451.0	444.8
55°	438.7	436.4	425.6	416.4	411.8
57.5°	404.1	401.8	391.1	381.8	377.2
60°	368.0	364.2	354.2	347.3	343.4
62.5°	332.7	329.6	318.8	312.7	308.9
65°	297.3	293.5	285.8	278.1	274.3
67.5°	261.2	258.1	250.5	242.8	242.0
70°	228.2	222.8	216.7	210.5	208.2
72.5°	192.8	187.5	182.9	178.2	175.9
75°	158.3	154.4	150.6	147.5	146.7
77.5°	124.5	122.9	119.1	118.3	116.0
80°	94.5	92.2	90.7	89.1	88.4
82.5°	65.3	64.5	64.5	63.8	63.0
85°	41.5	41.5	40.0	40.0	39.2
87.5°	20.0	19.2	18.4	18.4	18.4
90°	2.3	10.6	16.7	21.2	22.7
92.5°	19.7	29.5	33.3	35.6	36.3
95°	45.4	52.2	57.5	59.8	59.8
97.5°	72.7	78.7	84.8	87.8	87.8
100°	106.0	109.0	115.8	117.3	117.3
102.5°	140.8	141.6	147.6	149.9	150.6
105°	176.4	177.1	180.2	182.4	184.7
107.5°	213.5	214.2	215.0	218.0	217.3
110°	251.3	252.8	252.1	250.6	252.8

TEST NUMBER: P1001644

CATALOG NUMBER: SA4XXDIP-B575D810UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	290.7	290.7	289.2	289.2	289.2
115°	330.1	330.1	328.5	327.8	327.0
117.5°	367.2	367.2	366.4	364.1	361.9
120°	404.3	407.3	405.0	401.2	402.7
122.5°	442.9	443.6	442.9	440.6	436.8
125°	480.7	480.7	480.0	478.4	476.9
127.5°	514.8	517.0	515.5	514.0	513.3
130°	551.1	553.4	553.4	551.9	548.8
132.5°	588.2	589.7	589.0	587.5	586.7
135°	620.0	624.5	624.5	623.0	620.8
137.5°	655.6	657.9	659.4	657.1	657.9
140°	691.2	692.7	692.7	691.9	691.2
142.5°	723.7	725.2	724.5	724.5	724.5
145°	753.2	756.3	757.0	756.3	754.0
147.5°	783.5	787.3	786.6	785.8	785.0
150°	810.8	813.8	813.8	813.8	813.0
152.5°	836.5	838.0	838.8	841.1	838.8
155°	863.0	863.0	862.3	865.3	862.3
157.5°	885.7	884.2	884.2	886.5	884.2
160°	905.4	904.6	903.9	906.2	902.4
162.5°	923.6	921.3	920.5	925.1	921.3
165°	939.5	937.2	935.7	940.2	937.2
167.5°	952.3	949.3	949.3	953.9	949.3
170°	962.9	959.2	959.9	964.5	959.2
172.5°	970.5	967.5	967.5	972.8	967.5
175°	977.3	973.5	972.8	978.1	972.8
177.5°	980.3	976.6	976.6	981.9	975.8
180°	978.8	978.8	978.8	978.8	978.8

(END OF REPORT)