

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001674

Luminaire Tested: SA4XXDIP-B575D810UB35-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001674
REPORT IS A COMBINATION OF REPORTS P996296 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D810UB35-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5123.0 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001674

CATALOG NUMBER: SA4XXDIP-B575D810UB35-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001674

CATALOG NUMBER: SA4XXDIP-B575D810UB35-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	95	91	86	83	87	83	79	76	68	66	63	55	53	51	42	41	40
2	86	79	72	67	79	72	66	62	59	55	52	48	45	42	37	35	33
3	79	69	61	55	71	63	56	51	52	47	43	42	38	35	32	30	28
4	72	61	53	46	65	56	48	43	46	41	36	37	33	30	29	26	24
5	66	54	46	39	60	49	42	37	41	35	31	33	29	26	26	23	20
6	60	48	40	34	55	44	37	32	37	31	27	30	26	22	23	20	18
7	56	43	35	30	51	40	33	28	33	28	24	27	23	20	21	18	16
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	19	16	14
9	48	36	28	23	44	33	26	22	28	22	19	23	18	16	18	15	13
10	45	33	25	21	41	30	24	19	25	20	17	21	17	14	17	14	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5668	5668	5668
5°	5684	5521	5531
10°	5647	5412	5397
15°	5594	5290	5246
20°	5516	5157	5098
25°	5428	5012	4940
30°	5333	4868	4779
35°	5224	4720	4635
40°	5137	4578	4486
45°	5010	4445	4354
50°	4901	4294	4216
55°	4787	4148	4055
60°	4611	3967	3905
65°	4419	3772	3724
70°	4185	3547	3514
75°	3859	3300	3315
80°	3488	3046	3106
85°	3005	2793	2937

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5010 cd/sqm

TEST NUMBER: P1001674

CATALOG NUMBER: SA4XXDIP-B575D810UB35-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	1.3
10°-20°	188.7	3.7
20°-30°	285.3	5.6
30°-40°	345.2	6.7
40°-50°	364.9	7.1
50°-60°	343.5	6.7
60°-70°	285.0	5.6
70°-80°	200.0	3.9
80°-90°	114.9	2.2
90°-100°	131.7	2.6
100°-110°	243.3	4.7
110°-120°	362.2	7.1
120°-130°	452.5	8.8
130°-140°	495.2	9.7
140°-150°	480.4	9.4
150°-160°	402.7	7.9
160°-170°	267.9	5.2
170°-180°	93.8	1.8
0°-30°	539.9	10.5
0°-40°	885.1	17.3
0°-60°	1593.5	31.1
0°-90°	2193.4	42.8
90°-120°	737.2	14.4
90°-150°	2165.2	42.3
90°-180°	2930.0	57.2
0°-180°	5123.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	695	695	695	695	695	
5°	696	694	688	694	694	66
15°	667	668	666	673	672	188
25°	610	615	617	626	627	281
35°	534	543	551	562	564	334
45°	445	460	475	488	492	344
55°	349	365	388	404	409	311
65°	241	266	293	312	318	239
75°	134	163	195	217	224	142
85°	41	74	109	132	140	43
90°	15	54	94	121	129	12
95°	56	89	126	149	156	58
105°	186	202	234	256	264	197
115°	339	346	369	386	390	335
125°	490	489	508	521	524	437
135°	630	634	640	651	653	487
145°	764	766	767	771	772	478
155°	874	874	873	876	873	402
165°	952	949	948	952	949	268
175°	990	986	985	991	985	94
180°	991	991	991	991	991	

TEST NUMBER: P1001674

CATALOG NUMBER: SA4XXDIP-B575D810UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	695.1	695.1	695.1	695.1	695.1
2.5°	698.2	695.9	689.7	695.1	694.4
5°	695.9	693.6	688.1	694.4	693.6
7.5°	691.2	689.7	685.0	692.0	691.2
10°	685.0	684.2	680.3	687.4	686.6
12.5°	676.5	676.5	674.1	680.3	680.3
15°	667.1	667.9	665.6	672.6	671.8
17.5°	654.7	657.0	656.2	663.2	662.4
20°	641.4	643.8	644.5	652.3	652.3
22.5°	626.6	629.7	631.3	639.1	640.6
25°	610.3	615.0	617.3	625.9	626.6
27.5°	592.4	599.4	602.5	610.3	611.1
30°	574.5	580.7	586.2	594.7	596.3
32.5°	555.0	562.8	569.0	579.1	580.7
35°	534.0	543.3	551.1	562.0	564.4
37.5°	513.0	523.9	533.2	544.1	546.5
40°	492.7	502.9	513.8	525.4	528.6
42.5°	469.4	481.1	494.3	507.5	509.9
45°	445.3	460.1	474.8	488.1	492.0
47.5°	422.7	437.5	454.6	467.8	472.5
50°	397.8	414.9	432.0	447.6	452.3
52.5°	372.9	390.0	410.2	425.8	430.5
55°	348.7	365.1	388.4	404.0	408.7
57.5°	321.5	341.7	364.3	383.0	386.9
60°	295.0	315.3	341.0	358.9	365.1
62.5°	269.3	291.9	317.6	335.5	341.7
65°	241.3	266.2	292.7	312.1	318.4
67.5°	214.8	241.3	269.3	288.8	295.0
70°	187.6	214.1	243.6	264.7	270.1
72.5°	161.1	188.4	220.3	240.5	246.8
75°	133.9	162.7	195.4	217.2	224.2
77.5°	108.2	138.6	172.8	194.6	202.4
80°	84.8	116.0	150.2	173.6	179.8
82.5°	61.5	94.2	128.4	152.6	159.6
85°	41.3	74.0	109.0	132.3	140.1
87.5°	25.7	57.6	91.9	114.4	121.4
90°	14.8	54.3	94.0	121.1	128.9
92.5°	31.6	68.8	106.1	130.2	137.2
95°	56.1	88.7	126.0	149.3	156.3
97.5°	82.9	111.6	149.7	173.0	180.0
100°	115.9	139.2	176.5	199.1	204.5
102.5°	151.2	169.1	204.8	227.3	234.3
105°	185.7	202.0	233.9	255.6	264.2
107.5°	223.2	237.2	265.3	287.7	292.5
110°	260.8	273.2	299.7	316.1	324.6

TEST NUMBER: P1001674

CATALOG NUMBER: SA4XXDIP-B575D810UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	299.8	309.2	333.4	350.5	356.7
115°	339.0	346.0	369.4	385.7	390.4
117.5°	376.6	381.2	403.8	417.8	421.8
120°	413.4	418.7	439.0	450.8	458.5
122.5°	452.5	453.2	473.5	486.8	488.3
125°	490.0	489.2	507.9	521.2	524.4
127.5°	524.5	526.0	540.1	552.5	557.3
130°	560.5	562.1	574.5	587.0	588.6
132.5°	598.1	598.9	607.5	619.1	623.1
135°	629.6	634.2	639.6	650.6	652.9
137.5°	665.6	667.1	671.8	681.2	685.8
140°	701.7	702.4	703.2	712.5	715.7
142.5°	733.8	735.4	733.8	742.4	745.5
145°	763.7	766.0	766.8	770.7	771.5
147.5°	794.4	797.4	796.7	796.7	799.0
150°	822.0	824.3	824.3	824.3	823.5
152.5°	847.3	848.8	849.6	851.9	849.6
155°	874.1	874.1	873.4	876.4	873.4
157.5°	897.1	895.6	895.6	897.9	895.6
160°	917.1	916.3	915.5	917.8	914.0
162.5°	935.5	933.2	932.4	937.0	933.2
165°	951.6	949.3	947.7	952.3	949.3
167.5°	964.6	961.5	961.5	966.1	961.5
170°	975.3	971.5	972.3	976.9	971.5
172.5°	983.0	979.9	979.9	985.3	979.9
175°	989.9	986.1	985.3	990.7	985.3
177.5°	993.0	989.1	989.1	994.5	988.4
180°	991.4	991.4	991.4	991.4	991.4

(END OF REPORT)