

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001683

Luminaire Tested: SA4XXDIP-B575D810UB40-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001683
REPORT IS A COMBINATION OF REPORTS P996305 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D810UB40-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5072.0 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001683

CATALOG NUMBER: SA4XXDIP-B575D810UB40-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001683

CATALOG NUMBER: SA4XXDIP-B575D810UB40-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	95	91	86	83	87	83	79	76	68	66	63	55	53	51	42	41	40
2	86	79	72	67	79	72	66	62	59	55	52	48	45	42	37	35	33
3	79	69	61	55	71	63	56	51	52	47	43	42	38	35	32	30	28
4	72	61	53	46	65	56	48	43	46	41	36	37	33	30	29	26	24
5	66	54	46	39	60	49	42	37	41	35	31	33	29	26	26	23	20
6	60	48	40	34	55	44	37	32	37	31	27	30	26	22	23	20	18
7	56	43	35	30	51	40	33	28	33	28	24	27	23	20	21	18	16
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	19	16	14
9	48	36	28	23	44	33	26	22	28	22	19	23	18	16	18	15	13
10	45	33	25	21	41	30	24	19	25	20	17	21	17	14	17	14	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5611	5611	5611
5°	5627	5465	5475
10°	5590	5358	5342
15°	5538	5236	5192
20°	5460	5105	5047
25°	5373	4961	4890
30°	5279	4818	4730
35°	5172	4672	4587
40°	5086	4532	4440
45°	4959	4400	4310
50°	4850	4251	4173
55°	4738	4106	4014
60°	4565	3927	3865
65°	4375	3733	3686
70°	4143	3512	3479
75°	3818	3266	3281
80°	3455	3016	3075
85°	2969	2765	2907

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4959 cd/sqm

TEST NUMBER: P1001683

CATALOG NUMBER: SA4XXDIP-B575D810UB40-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.2	1.3
10°-20°	186.8	3.7
20°-30°	282.4	5.6
30°-40°	341.7	6.7
40°-50°	361.2	7.1
50°-60°	340.0	6.7
60°-70°	282.1	5.6
70°-80°	198.0	3.9
80°-90°	113.7	2.2
90°-100°	130.4	2.6
100°-110°	240.9	4.7
110°-120°	358.6	7.1
120°-130°	448.0	8.8
130°-140°	490.3	9.7
140°-150°	475.6	9.4
150°-160°	398.7	7.9
160°-170°	265.3	5.2
170°-180°	92.9	1.8
0°-30°	534.4	10.5
0°-40°	876.2	17.3
0°-60°	1577.4	31.1
0°-90°	2171.2	42.8
90°-120°	729.9	14.4
90°-150°	2144.0	42.3
90°-180°	2901.0	57.2
0°-180°	5072.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	688	688	688	688	688	
5°	689	687	681	687	687	65
15°	660	661	659	666	665	186
25°	604	609	611	620	620	278
35°	529	538	546	556	559	331
45°	441	455	470	483	487	341
55°	345	361	384	400	404	308
65°	239	264	290	309	315	237
75°	132	161	193	215	222	141
85°	41	73	108	131	139	43
90°	15	54	93	120	128	12
95°	56	88	125	148	155	57
105°	184	200	232	253	262	195
115°	336	343	366	382	387	331
125°	485	484	503	516	519	433
135°	623	628	633	644	646	482
145°	756	758	759	763	764	473
155°	866	866	865	868	865	398
165°	942	940	938	943	940	266
175°	980	976	976	981	976	93
180°	982	982	982	982	982	

TEST NUMBER: P1001683

CATALOG NUMBER: SA4XXDIP-B575D810UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	688.1	688.1	688.1	688.1	688.1
2.5°	691.2	688.9	682.7	688.1	687.3
5°	688.9	686.6	681.2	687.3	686.6
7.5°	684.2	682.7	678.1	685.0	684.2
10°	678.1	677.3	673.5	680.4	679.6
12.5°	669.6	669.6	667.3	673.5	673.5
15°	660.4	661.1	658.8	665.7	665.0
17.5°	648.0	650.3	649.6	656.5	655.7
20°	634.9	637.2	638.0	645.7	645.7
22.5°	620.3	623.4	624.9	632.6	634.2
25°	604.1	608.7	611.0	619.5	620.3
27.5°	586.4	593.3	596.4	604.1	604.9
30°	568.7	574.8	580.2	588.7	590.2
32.5°	549.4	557.1	563.3	573.3	574.8
35°	528.6	537.8	545.5	556.3	558.6
37.5°	507.8	518.6	527.8	538.6	540.9
40°	487.8	497.8	508.6	520.1	523.2
42.5°	464.6	476.2	489.3	502.4	504.7
45°	440.8	455.4	470.0	483.1	487.0
47.5°	418.4	433.0	450.0	463.1	467.7
50°	393.7	410.7	427.7	443.1	447.7
52.5°	369.1	386.0	406.1	421.5	426.1
55°	345.2	361.4	384.5	399.9	404.5
57.5°	318.2	338.3	360.6	379.1	383.0
60°	292.0	312.1	337.5	355.2	361.4
62.5°	266.6	289.0	314.4	332.1	338.3
65°	238.9	263.5	289.7	309.0	315.2
67.5°	212.7	238.9	266.6	285.9	292.0
70°	185.7	211.9	241.2	262.0	267.4
72.5°	159.5	186.5	218.1	238.1	244.3
75°	132.5	161.0	193.4	215.0	221.9
77.5°	107.1	137.2	171.1	192.6	200.3
80°	84.0	114.8	148.7	171.8	178.0
82.5°	60.9	93.2	127.1	151.0	158.0
85°	40.8	73.2	107.9	131.0	138.7
87.5°	25.4	57.0	90.9	113.3	120.2
90°	14.6	53.8	93.0	119.9	127.6
92.5°	31.3	68.1	105.1	128.9	135.8
95°	55.6	87.8	124.7	147.8	154.8
97.5°	82.1	110.6	148.2	171.3	178.3
100°	114.8	137.8	174.8	197.1	202.5
102.5°	149.7	167.4	202.8	225.0	232.0
105°	183.8	200.0	231.6	253.1	261.6
107.5°	221.0	234.9	262.6	285.0	289.6
110°	258.3	270.6	296.7	312.9	321.4

TEST NUMBER: P1001683

CATALOG NUMBER: SA4XXDIP-B575D810UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	297.0	306.2	330.1	347.0	353.2
115°	335.6	342.6	365.7	382.0	386.6
117.5°	372.8	377.4	399.9	413.7	417.6
120°	409.3	414.7	434.7	446.3	454.0
122.5°	448.1	448.8	468.9	482.0	483.6
125°	485.2	484.4	503.0	516.0	519.1
127.5°	519.4	520.9	534.8	547.1	551.8
130°	555.0	556.5	568.9	581.2	582.9
132.5°	592.2	593.0	601.5	613.1	616.9
135°	623.3	627.9	633.3	644.2	646.5
137.5°	659.0	660.6	665.2	674.4	679.1
140°	694.7	695.5	696.2	705.6	708.6
142.5°	726.6	728.2	726.6	735.1	738.2
145°	756.3	758.5	759.3	763.1	763.9
147.5°	786.6	789.6	788.9	788.9	791.2
150°	814.0	816.2	816.2	816.2	815.4
152.5°	839.0	840.5	841.3	843.5	841.3
155°	865.6	865.6	864.8	867.8	864.8
157.5°	888.3	886.8	886.8	889.1	886.8
160°	908.1	907.3	906.5	908.8	905.0
162.5°	926.3	924.0	923.3	927.8	924.0
165°	942.2	940.0	938.4	943.0	940.0
167.5°	955.1	952.1	952.1	956.7	952.1
170°	965.8	962.0	962.7	967.3	962.0
172.5°	973.4	970.3	970.3	975.6	970.3
175°	980.2	976.4	975.6	981.0	975.6
177.5°	983.2	979.4	979.4	984.8	978.7
180°	981.7	981.7	981.7	981.7	981.7

(END OF REPORT)