

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001687

Luminaire Tested: SA4XXDIP-B575D810UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001687
REPORT IS A COMBINATION OF REPORTS P996309 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D810UB40-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5289.6 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001687

CATALOG NUMBER: SA4XXDIP-B575D810UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001687

CATALOG NUMBER: SA4XXDIP-B575D810UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53
1	97	93	89	85	89	85	82	79	71	69	67	59	57	55	47	46	45
2	88	81	75	70	81	75	69	65	63	59	55	51	49	46	41	39	38
3	81	71	64	58	74	66	59	54	55	50	46	45	42	39	37	34	32
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24
6	62	50	42	36	57	47	39	34	39	34	30	33	29	25	27	24	21
7	58	45	37	32	53	42	35	30	36	30	26	30	26	22	24	21	19
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	46	34	27	22	43	32	26	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7841	7841	7841
5°	7848	7615	7625
10°	7781	7404	7353
15°	7669	7153	7045
20°	7527	6880	6726
25°	7367	6594	6384
30°	7173	6283	6008
35°	6973	5965	5644
40°	6763	5623	5258
45°	6545	5280	4896
50°	6302	4947	4495
55°	6038	4558	4098
60°	5770	4133	3683
65°	5461	3693	3217
70°	5104	3164	2717
75°	4573	2550	2176
80°	3899	1844	1530
85°	3027	1028	824

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6545 cd/sqm

TEST NUMBER: P1001687

CATALOG NUMBER: SA4XXDIP-B575D810UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	1.7
10°-20°	255.3	4.8
20°-30°	375.8	7.1
30°-40°	436.8	8.3
40°-50°	436.8	8.3
50°-60°	382.0	7.2
60°-70°	283.6	5.4
70°-80°	160.9	3.0
80°-90°	47.6	0.9
90°-100°	287.0	5.4
100°-110°	583.8	11.0
110°-120°	520.4	9.8
120°-130°	437.1	8.3
130°-140°	364.8	6.9
140°-150°	278.6	5.3
150°-160°	195.8	3.7
160°-170°	115.2	2.2
170°-180°	37.4	0.7
0°-30°	721.7	13.6
0°-40°	1158.6	21.9
0°-60°	1977.4	37.4
0°-90°	2469.5	46.7
90°-120°	1391.3	26.3
90°-150°	2471.7	46.7
90°-180°	2820.0	53.3
0°-180°	5289.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	962	962	962	962	962	
5°	961	958	949	958	956	91
15°	914	912	900	904	902	258
25°	828	823	812	813	810	381
35°	713	707	696	691	687	446
45°	582	576	564	556	553	448
55°	440	438	427	418	413	394
65°	298	294	287	279	275	295
75°	159	155	151	148	147	168
85°	42	42	40	40	39	45
90°	1	6	14	15	16	4
95°	25	79	619	306	185	27
105°	89	129	498	1072	1068	95
115°	156	196	444	853	1026	155
125°	218	259	442	726	818	194
135°	259	308	438	645	732	200
145°	298	342	436	544	598	187
155°	339	366	424	480	500	157
165°	370	381	406	430	436	104
175°	386	386	390	395	393	37
180°	386	386	386	386	386	

TEST NUMBER: P1001687

CATALOG NUMBER: SA4XXDIP-B575D810UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	961.5	961.5	961.5	961.5	961.5
2.5°	964.6	962.3	953.8	961.5	960.8
5°	960.8	957.7	949.2	957.7	956.2
7.5°	953.8	950.8	941.5	948.4	947.7
10°	943.8	940.7	930.7	936.9	935.4
12.5°	930.7	927.6	916.9	923.8	921.5
15°	914.5	911.5	899.9	904.5	902.2
17.5°	896.1	892.2	881.4	884.5	883.0
20°	875.3	871.4	859.8	862.2	860.6
22.5°	852.9	847.5	836.0	840.6	837.5
25°	828.3	822.9	812.1	812.8	809.8
27.5°	800.5	795.1	785.1	783.6	779.7
30°	772.8	766.6	756.6	753.5	749.7
32.5°	743.5	738.1	727.3	723.5	719.6
35°	712.7	707.3	696.5	691.1	687.3
37.5°	680.3	675.7	664.1	658.8	653.4
40°	648.7	642.6	631.0	623.3	619.5
42.5°	614.8	611.8	598.7	589.4	587.1
45°	581.7	576.3	564.0	555.5	553.2
47.5°	547.0	543.2	531.6	522.4	516.2
50°	511.6	508.5	497.7	486.9	482.3
52.5°	476.9	473.1	461.5	452.3	446.1
55°	439.9	437.6	426.8	417.6	413.0
57.5°	405.3	403.0	392.2	382.9	378.3
60°	369.1	365.2	355.2	348.3	344.4
62.5°	333.6	330.5	319.7	313.6	309.7
65°	298.2	294.3	286.6	278.9	275.1
67.5°	262.0	258.9	251.2	243.5	242.7
70°	228.8	223.4	217.3	211.1	208.8
72.5°	193.4	188.0	183.4	178.7	176.4
75°	158.7	154.9	151.0	147.9	147.2
77.5°	124.8	123.3	119.4	118.7	116.3
80°	94.8	92.5	90.9	89.4	88.6
82.5°	65.5	64.7	64.7	63.9	63.2
85°	41.6	41.6	40.1	40.1	39.3
87.5°	20.0	19.3	18.5	18.5	18.5
90°	0.8	6.1	13.7	15.2	15.9
92.5°	10.6	58.4	297.6	98.3	69.1
95°	25.1	79.0	618.7	306.4	185.2
97.5°	41.8	87.3	662.0	625.6	444.9
100°	57.7	98.6	610.4	865.5	696.2
102.5°	72.9	112.4	545.9	1015.8	914.8
105°	88.8	128.7	498.0	1072.4	1068.2
107.5°	106.3	145.4	466.9	1055.3	1141.1
110°	123.7	162.0	452.5	994.6	1142.6

TEST NUMBER: P1001687

CATALOG NUMBER: SA4XXDIP-B575D810UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	140.5	178.8	445.6	920.2	1097.8
115°	156.4	196.2	444.1	853.4	1025.7
117.5°	173.1	212.6	443.4	801.0	955.1
120°	189.8	228.5	443.4	765.7	897.4
122.5°	205.0	244.0	442.6	742.5	851.8
125°	217.9	258.9	441.9	726.2	818.4
127.5°	230.0	272.5	440.3	710.6	797.2
130°	239.9	285.8	439.6	692.0	778.9
132.5°	249.8	297.2	438.8	670.0	758.4
135°	258.9	308.2	438.1	644.6	731.9
137.5°	268.0	317.7	438.1	617.2	700.7
140°	277.9	326.5	437.3	590.7	666.6
142.5°	288.5	334.4	437.3	566.0	630.1
145°	298.4	341.6	435.8	543.6	597.5
147.5°	309.8	348.5	433.5	525.0	567.1
150°	320.4	354.9	431.2	507.9	542.1
152.5°	330.3	361.0	427.4	493.5	519.3
155°	339.4	366.3	423.6	479.8	500.3
157.5°	348.5	371.2	419.8	466.9	482.8
160°	356.8	375.4	415.3	454.0	466.9
162.5°	364.4	378.8	410.7	441.4	451.7
165°	369.7	381.1	406.2	430.1	436.5
167.5°	375.8	383.0	401.6	420.2	424.4
170°	379.6	384.5	397.1	410.4	413.0
172.5°	383.4	385.6	392.5	401.6	401.6
175°	385.7	386.4	389.5	394.8	393.3
177.5°	387.2	386.4	387.2	389.8	387.2
180°	386.4	386.4	386.4	386.4	386.4

(END OF REPORT)