

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001692

Luminaire Tested: SA4XXDIP-B575D810UB50-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001692
REPORT IS A COMBINATION OF REPORTS P996314 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D810UB50-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4905.0 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001692

CATALOG NUMBER: SA4XXDIP-B575D810UB50-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001692

CATALOG NUMBER: SA4XXDIP-B575D810UB50-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	95	91	86	83	87	83	79	76	68	66	63	55	53	51	42	41	40
2	86	79	72	67	79	72	66	62	59	55	52	48	45	42	37	35	33
3	79	69	61	55	71	63	56	51	52	47	43	42	38	35	32	30	28
4	72	61	53	46	65	56	48	43	46	41	36	37	33	30	29	26	24
5	66	54	46	39	60	49	42	37	41	35	31	33	29	26	26	23	20
6	60	48	40	34	55	44	37	32	37	31	27	30	26	22	23	20	18
7	56	43	35	30	51	40	33	28	33	28	24	27	23	20	21	18	16
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	19	16	14
9	48	36	28	23	44	33	26	22	28	22	19	23	18	16	18	15	13
10	45	33	25	21	41	30	24	19	25	20	17	21	17	14	17	14	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5427	5427	5427
5°	5442	5285	5295
10°	5406	5182	5167
15°	5356	5065	5022
20°	5281	4938	4881
25°	5197	4798	4729
30°	5105	4660	4575
35°	5001	4518	4437
40°	4918	4383	4294
45°	4796	4255	4168
50°	4691	4111	4036
55°	4583	3972	3883
60°	4416	3798	3738
65°	4230	3611	3565
70°	4007	3397	3364
75°	3694	3160	3173
80°	3340	2916	2975
85°	2874	2673	2811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4796 cd/sqm

TEST NUMBER: P1001692

CATALOG NUMBER: SA4XXDIP-B575D810UB50-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	1.3
10°-20°	180.7	3.7
20°-30°	273.2	5.6
30°-40°	330.5	6.7
40°-50°	349.4	7.1
50°-60°	328.8	6.7
60°-70°	272.9	5.6
70°-80°	191.5	3.9
80°-90°	110.0	2.2
90°-100°	126.2	2.6
100°-110°	232.9	4.7
110°-120°	346.8	7.1
120°-130°	433.2	8.8
130°-140°	474.1	9.7
140°-150°	459.9	9.4
150°-160°	385.5	7.9
160°-170°	256.5	5.2
170°-180°	89.8	1.8
0°-30°	516.9	10.5
0°-40°	847.4	17.3
0°-60°	1525.6	31.1
0°-90°	2099.9	42.8
90°-120°	705.9	14.4
90°-150°	2073.2	42.3
90°-180°	2805.0	57.2
0°-180°	4905.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	666	666	666	666	666	
5°	666	664	659	665	664	63
15°	639	639	637	644	643	180
25°	584	589	591	599	600	269
35°	511	520	528	538	540	320
45°	426	440	455	467	471	329
55°	334	350	372	387	391	298
65°	231	255	280	299	305	229
75°	128	156	187	208	215	136
85°	40	71	104	127	134	41
90°	14	52	90	116	123	11
95°	54	85	121	143	150	55
105°	178	193	224	245	253	189
115°	325	331	354	369	374	320
125°	469	468	486	499	502	418
135°	603	607	612	623	625	467
145°	731	734	734	738	739	458
155°	837	837	836	839	836	385
165°	911	909	908	912	909	257
175°	948	944	943	949	943	90
180°	949	949	949	949	949	

TEST NUMBER: P1001692

CATALOG NUMBER: SA4XXDIP-B575D810UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	665.5	665.5	665.5	665.5	665.5
2.5°	668.5	666.3	660.3	665.5	664.8
5°	666.3	664.0	658.8	664.8	664.0
7.5°	661.8	660.3	655.8	662.5	661.8
10°	655.8	655.1	651.4	658.1	657.3
12.5°	647.6	647.6	645.4	651.4	651.4
15°	638.7	639.4	637.2	643.9	643.2
17.5°	626.8	629.0	628.2	635.0	634.2
20°	614.1	616.3	617.1	624.5	624.5
22.5°	599.9	602.9	604.4	611.9	613.3
25°	584.3	588.7	591.0	599.2	599.9
27.5°	567.1	573.8	576.8	584.3	585.0
30°	550.0	556.0	561.2	569.4	570.9
32.5°	531.4	538.8	544.8	554.5	556.0
35°	511.2	520.2	527.6	538.1	540.3
37.5°	491.1	501.6	510.5	520.9	523.2
40°	471.7	481.4	491.9	503.0	506.0
42.5°	449.4	460.6	473.2	485.9	488.1
45°	426.3	440.4	454.6	467.3	471.0
47.5°	404.7	418.8	435.2	447.9	452.4
50°	380.8	397.2	413.6	428.5	433.0
52.5°	357.0	373.4	392.7	407.7	412.1
55°	333.9	349.5	371.9	386.8	391.3
57.5°	307.8	327.2	348.8	366.7	370.4
60°	282.5	301.8	326.4	343.6	349.5
62.5°	257.9	279.5	304.1	321.2	327.2
65°	231.0	254.9	280.2	298.8	304.8
67.5°	205.7	231.0	257.9	276.5	282.5
70°	179.6	204.9	233.3	253.4	258.6
72.5°	154.3	180.4	210.9	230.3	236.2
75°	128.2	155.8	187.1	207.9	214.6
77.5°	103.6	132.7	165.4	186.3	193.8
80°	81.2	111.0	143.8	166.2	172.2
82.5°	58.9	90.2	123.0	146.1	152.8
85°	39.5	70.8	104.3	126.7	134.1
87.5°	24.6	55.1	87.9	109.6	116.3
90°	14.1	52.0	90.0	116.0	123.4
92.5°	30.3	65.9	101.6	124.7	131.3
95°	53.8	85.0	120.6	143.0	149.7
97.5°	79.4	107.0	143.3	165.7	172.4
100°	111.0	133.3	168.9	190.6	195.8
102.5°	144.8	161.9	196.1	217.7	224.4
105°	177.8	193.4	223.9	244.7	252.9
107.5°	213.7	227.2	254.0	275.5	280.0
110°	249.8	261.6	287.0	302.6	310.8

TEST NUMBER: P1001692

CATALOG NUMBER: SA4XXDIP-B575D810UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	287.1	296.1	319.3	335.6	341.6
115°	324.6	331.3	353.6	369.3	373.8
117.5°	360.6	365.0	386.6	400.1	403.8
120°	395.8	401.0	420.4	431.6	439.0
122.5°	433.2	433.9	453.3	466.1	467.6
125°	469.2	468.4	486.4	499.0	502.0
127.5°	502.2	503.7	517.1	529.1	533.6
130°	536.7	538.2	550.1	562.0	563.6
132.5°	572.7	573.4	581.6	592.8	596.6
135°	602.8	607.2	612.4	622.8	625.1
137.5°	637.3	638.7	643.2	652.2	656.6
140°	671.8	672.5	673.3	682.2	685.2
142.5°	702.6	704.1	702.6	710.8	713.8
145°	731.2	733.5	734.2	738.0	738.8
147.5°	760.6	763.6	762.8	762.8	765.1
150°	787.0	789.3	789.3	789.3	788.5
152.5°	811.3	812.7	813.5	815.7	813.5
155°	837.0	837.0	836.2	839.2	836.2
157.5°	859.0	857.5	857.5	859.7	857.5
160°	878.1	877.4	876.6	878.8	875.2
162.5°	895.7	893.5	892.8	897.2	893.5
165°	911.1	908.9	907.5	911.9	908.9
167.5°	923.6	920.7	920.7	925.1	920.7
170°	933.9	930.2	930.9	935.4	930.2
172.5°	941.2	938.3	938.3	943.4	938.3
175°	947.8	944.2	943.4	948.6	943.4
177.5°	950.8	947.1	947.1	952.2	946.4
180°	949.3	949.3	949.3	949.3	949.3

(END OF REPORT)