

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000732

Luminaire Tested: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000732
REPORT IS A COMBINATION OF REPORTS P995345 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6201.0 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000732

CATALOG NUMBER: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1000732

CATALOG NUMBER: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	99	94	90	86	93	88	84	81	77	74	71	67	65	63	57	56	54
2	90	82	75	69	84	76	70	65	67	62	58	58	54	51	50	47	45
3	82	71	63	57	76	67	60	54	59	53	48	51	46	43	44	40	37
4	75	63	54	48	69	59	51	45	52	46	41	45	40	36	39	35	32
5	68	56	47	41	64	53	45	39	46	40	35	40	35	31	35	31	28
6	63	50	41	35	59	47	39	34	42	35	30	36	31	27	31	27	24
7	58	45	37	31	54	43	35	29	38	31	27	33	28	24	29	25	21
8	54	41	33	27	50	39	31	26	34	28	24	30	25	21	26	22	19
9	50	37	30	24	47	35	28	23	31	25	21	28	23	19	24	20	17
10	47	34	27	22	44	33	26	21	29	23	19	26	21	17	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9952	9952	9952
5°	9979	9692	9710
10°	9915	9502	9475
15°	9822	9287	9209
20°	9684	9055	8951
25°	9530	8800	8673
30°	9362	8546	8390
35°	9172	8286	8137
40°	9020	8037	7876
45°	8795	7804	7644
50°	8604	7539	7400
55°	8405	7283	7120
60°	8097	6965	6856
65°	7759	6622	6538
70°	7349	6230	6169
75°	6775	5792	5820
80°	6128	5350	5453
85°	5268	4902	5156

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8795 cd/sqm

TEST NUMBER: P1000732

CATALOG NUMBER: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.6	1.9
10°-20°	331.3	5.3
20°-30°	501.0	8.1
30°-40°	606.1	9.8
40°-50°	640.7	10.3
50°-60°	603.0	9.7
60°-70°	500.4	8.1
70°-80°	351.1	5.7
80°-90°	199.5	3.2
90°-100°	165.8	2.7
100°-110°	230.7	3.7
110°-120°	302.2	4.9
120°-130°	354.3	5.7
130°-140°	375.2	6.1
140°-150°	357.6	5.8
150°-160°	298.4	4.8
160°-170°	198.5	3.2
170°-180°	69.5	1.1
0°-30°	947.9	15.3
0°-40°	1554.0	25.1
0°-60°	2797.7	45.1
0°-90°	3848.8	62.1
90°-120°	698.7	11.3
90°-150°	1785.8	28.8
90°-180°	2352.0	37.9
0°-180°	6201.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1220	1220	1220	1220	1220	
5°	1222	1218	1208	1219	1218	116
15°	1171	1173	1168	1181	1179	330
25°	1072	1080	1084	1099	1100	494
35°	938	954	968	987	991	587
45°	782	808	834	857	864	604
55°	612	641	682	709	718	546
65°	424	467	514	548	559	420
75°	235	286	343	381	394	250
85°	72	130	191	232	246	75
90°	24	84	148	191	203	17
95°	52	102	162	201	213	51
105°	145	173	225	261	274	154
115°	256	268	311	340	349	253
125°	366	365	398	423	430	327
135°	468	472	481	502	508	363
145°	567	568	568	576	580	355
155°	648	648	647	649	647	298
165°	705	703	702	706	703	199
175°	734	731	730	734	730	70
180°	735	735	735	735	735	

TEST NUMBER: P1000732

CATALOG NUMBER: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1220.4	1220.4	1220.4	1220.4	1220.4
2.5°	1225.9	1221.8	1210.9	1220.4	1219.1
5°	1221.8	1217.7	1208.1	1219.1	1217.7
7.5°	1213.6	1210.9	1202.7	1215.0	1213.6
10°	1202.7	1201.3	1194.5	1206.8	1205.4
12.5°	1187.6	1187.6	1183.5	1194.5	1194.5
15°	1171.2	1172.6	1168.5	1180.8	1179.4
17.5°	1149.4	1153.5	1152.1	1164.4	1163.0
20°	1126.1	1130.2	1131.6	1145.3	1145.3
22.5°	1100.2	1105.6	1108.4	1122.0	1124.8
25°	1071.5	1079.7	1083.8	1098.8	1100.2
27.5°	1040.0	1052.3	1057.8	1071.5	1072.8
30°	1008.6	1019.5	1029.1	1044.1	1046.9
32.5°	974.4	988.1	999.0	1016.8	1019.5
35°	937.5	953.9	967.6	986.7	990.8
37.5°	900.6	919.8	936.2	955.3	959.4
40°	865.1	882.9	902.0	922.5	928.0
42.5°	824.1	844.6	867.8	891.1	895.2
45°	781.7	807.7	833.7	856.9	863.7
47.5°	742.1	768.1	798.1	821.4	829.6
50°	698.4	728.4	758.5	785.8	794.0
52.5°	654.6	684.7	720.2	747.6	755.8
55°	612.3	641.0	682.0	709.3	717.5
57.5°	564.4	600.0	639.6	672.4	679.2
60°	518.0	553.5	598.6	630.0	641.0
62.5°	472.9	512.5	557.6	589.0	600.0
65°	423.7	467.4	513.9	548.0	559.0
67.5°	377.2	423.7	472.9	507.0	518.0
70°	329.4	375.8	427.8	464.7	474.2
72.5°	282.9	330.7	386.8	422.3	433.2
75°	235.1	285.6	343.0	381.3	393.6
77.5°	190.0	243.3	303.4	341.7	355.3
80°	149.0	203.6	263.8	304.8	315.7
82.5°	108.0	165.4	225.5	267.9	280.2
85°	72.4	129.8	191.3	232.3	246.0
87.5°	45.1	101.1	161.3	200.9	213.2
90°	23.6	84.5	147.8	190.8	202.9
92.5°	35.3	90.5	152.1	192.1	203.6
95°	51.9	102.1	162.1	200.7	213.0
97.5°	70.9	115.1	175.7	213.5	225.8
100°	94.5	132.4	190.8	228.9	238.4
102.5°	120.7	151.4	207.8	245.1	256.6
105°	144.7	172.6	225.4	261.3	273.9
107.5°	172.5	196.3	244.8	281.1	290.2
110°	199.5	219.9	267.1	297.4	310.1



TEST NUMBER: P1000732

CATALOG NUMBER: SA4XXDIP-B1020D590UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	227.8	244.2	288.1	318.1	329.1
115°	255.9	268.2	310.8	340.3	349.4
117.5°	283.8	292.0	332.4	359.4	368.6
120°	310.2	316.6	354.6	379.0	391.1
122.5°	339.2	339.8	376.1	401.8	408.4
125°	366.3	364.9	398.5	423.3	430.4
127.5°	391.9	392.2	418.3	441.8	450.8
130°	417.7	418.0	439.9	463.4	469.3
132.5°	445.6	445.3	461.1	483.3	490.9
135°	468.0	471.5	481.1	501.8	508.3
137.5°	494.8	495.2	501.7	520.5	528.0
140°	521.5	521.3	522.6	539.8	546.1
142.5°	544.6	545.7	543.8	558.8	564.3
145°	566.7	567.6	568.2	575.8	579.6
147.5°	589.5	590.9	590.3	591.2	596.0
150°	609.9	610.8	610.8	610.8	610.2
152.5°	627.8	629.0	629.6	631.3	629.6
155°	647.7	647.7	647.2	649.4	647.2
157.5°	664.8	663.6	663.6	665.3	663.6
160°	679.6	679.0	678.4	680.1	677.3
162.5°	693.2	691.5	690.9	694.3	691.5
165°	705.1	703.4	702.3	705.7	703.4
167.5°	714.8	712.5	712.5	715.9	712.5
170°	722.7	719.9	720.5	723.9	719.9
172.5°	728.4	726.1	726.1	730.1	726.1
175°	733.5	730.7	730.1	734.1	730.1
177.5°	735.8	733.0	733.0	736.9	732.4
180°	734.7	734.7	734.7	734.7	734.7

(END OF REPORT)