

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001701

Luminaire Tested: SA4XXDIP-B795D1035UB27-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001701
REPORT IS A COMBINATION OF REPORTS P996323 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1035UB27-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6745.0 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001701

CATALOG NUMBER: SA4XXDIP-B795D1035UB27-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001701

CATALOG NUMBER: SA4XXDIP-B795D1035UB27-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	91	87	83	87	83	80	76	69	66	64	56	54	52	44	42	41
2	87	79	72	67	79	72	67	62	60	56	52	48	45	43	38	36	34
3	79	69	61	55	72	63	57	51	52	47	43	42	39	36	33	31	28
4	72	61	53	46	65	56	49	43	46	41	37	38	34	30	29	27	24
5	66	54	46	40	60	50	42	37	41	36	31	34	29	26	26	23	21
6	61	48	40	34	55	44	37	32	37	31	27	30	26	23	24	21	18
7	56	43	35	30	51	40	33	28	34	28	24	27	23	20	22	19	16
8	52	39	32	26	47	36	29	24	30	25	21	25	21	18	20	17	14
9	48	36	28	23	44	33	26	22	28	23	19	23	19	16	18	15	13
10	45	33	26	21	41	30	24	19	26	20	17	21	17	14	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7721	7721	7721
5°	7742	7519	7533
10°	7692	7371	7350
15°	7619	7205	7144
20°	7513	7025	6944
25°	7393	6827	6729
30°	7263	6630	6508
35°	7116	6428	6313
40°	6997	6236	6110
45°	6824	6054	5931
50°	6674	5848	5741
55°	6520	5650	5523
60°	6281	5403	5319
65°	6020	5136	5071
70°	5700	4833	4786
75°	5256	4494	4514
80°	4754	4149	4230
85°	4090	3803	3999

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6824 cd/sqm

TEST NUMBER: P1001701

CATALOG NUMBER: SA4XXDIP-B795D1035UB27-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.7	1.3
10°-20°	257.0	3.8
20°-30°	388.6	5.8
30°-40°	470.2	7.0
40°-50°	497.1	7.4
50°-60°	467.8	6.9
60°-70°	388.2	5.8
70°-80°	272.4	4.0
80°-90°	156.3	2.3
90°-100°	174.0	2.6
100°-110°	315.0	4.7
110°-120°	465.5	6.9
120°-130°	579.6	8.6
130°-140°	633.3	9.4
140°-150°	613.8	9.1
150°-160°	514.4	7.6
160°-170°	342.3	5.1
170°-180°	119.8	1.8
0°-30°	735.4	10.9
0°-40°	1205.6	17.9
0°-60°	2170.4	32.2
0°-90°	2987.3	44.3
90°-120°	954.5	14.2
90°-150°	2781.2	41.2
90°-180°	3758.0	55.7
0°-180°	6745.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	948	945	937	946	945	90
15°	909	910	906	916	915	256
25°	831	838	841	852	854	383
35°	727	740	751	766	769	455
45°	606	627	647	665	670	469
55°	475	497	529	550	557	423
65°	329	363	399	425	434	326
75°	182	222	266	296	305	194
85°	56	101	148	180	191	59
90°	20	73	127	163	174	16
95°	73	116	167	198	208	75
105°	238	260	303	333	344	253
115°	434	443	475	497	504	428
125°	626	625	651	669	673	558
135°	804	810	818	833	836	623
145°	976	979	980	985	986	611
155°	1117	1117	1116	1120	1116	514
165°	1216	1213	1211	1217	1213	343
175°	1265	1260	1259	1266	1259	120
180°	1267	1267	1267	1267	1267	

TEST NUMBER: P1001701

CATALOG NUMBER: SA4XXDIP-B795D1035UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	946.8	946.8	946.8	946.8	946.8
2.5°	951.0	947.9	939.4	946.8	945.7
5°	947.9	944.7	937.2	945.7	944.7
7.5°	941.5	939.4	933.0	942.6	941.5
10°	933.0	931.9	926.6	936.2	935.1
12.5°	921.3	921.3	918.2	926.6	926.6
15°	908.6	909.7	906.5	916.0	915.0
17.5°	891.7	894.8	893.8	903.3	902.3
20°	873.6	876.8	877.9	888.5	888.5
22.5°	853.5	857.7	859.9	870.5	872.6
25°	831.2	837.6	840.8	852.4	853.5
27.5°	806.8	816.4	820.6	831.2	832.3
30°	782.5	790.9	798.4	810.0	812.1
32.5°	755.9	766.6	775.0	788.8	790.9
35°	727.3	740.0	750.6	765.5	768.7
37.5°	698.7	713.5	726.3	741.1	744.3
40°	671.1	684.9	699.8	715.7	719.9
42.5°	639.3	655.2	673.3	691.3	694.5
45°	606.5	626.6	646.7	664.8	670.1
47.5°	575.7	595.9	619.2	637.2	643.6
50°	541.8	565.1	588.4	609.6	616.0
52.5°	507.9	531.2	558.7	579.9	586.3
55°	475.0	497.3	529.1	550.3	556.6
57.5°	437.9	465.4	496.2	521.6	526.9
60°	401.8	429.4	464.4	488.8	497.3
62.5°	366.8	397.6	432.6	457.0	465.4
65°	328.7	362.6	398.6	425.2	433.6
67.5°	292.6	328.7	366.8	393.3	401.8
70°	255.5	291.6	331.9	360.5	367.9
72.5°	219.5	256.6	300.0	327.6	336.1
75°	182.4	221.6	266.1	295.8	305.3
77.5°	147.4	188.7	235.4	265.1	275.7
80°	115.6	158.0	204.6	236.4	244.9
82.5°	83.8	128.3	174.9	207.8	217.3
85°	56.2	100.7	148.4	180.2	190.8
87.5°	35.0	78.5	125.1	155.9	165.4
90°	19.9	73.1	126.6	163.1	173.6
92.5°	41.4	91.2	141.7	174.3	183.8
95°	72.6	116.4	166.6	198.3	207.8
97.5°	106.7	145.4	196.6	228.1	237.6
100°	148.8	180.3	230.5	261.0	268.4
102.5°	193.9	218.2	266.3	296.8	306.2
105°	237.7	259.9	303.1	332.6	344.0
107.5°	285.7	304.8	342.9	373.3	379.7
110°	333.7	350.5	386.6	409.0	420.5

TEST NUMBER: P1001701

CATALOG NUMBER: SA4XXDIP-B795D1035UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	383.6	396.3	429.3	452.7	461.1
115°	433.5	443.0	474.9	497.4	503.8
117.5°	481.5	487.8	518.6	538.0	543.5
120°	528.4	535.5	563.3	579.6	590.0
122.5°	578.3	579.3	606.9	625.2	627.8
125°	626.2	625.2	650.7	668.9	673.3
127.5°	670.3	672.2	691.5	708.6	715.0
130°	716.3	718.2	735.2	752.3	754.7
132.5°	764.3	765.2	776.9	793.0	798.4
135°	804.4	810.2	817.6	832.7	836.1
137.5°	850.4	852.3	858.5	871.5	877.7
140°	896.4	897.4	898.4	911.2	915.5
142.5°	937.6	939.5	937.4	949.1	953.3
145°	975.8	978.6	979.6	985.0	986.2
147.5°	1015.0	1018.7	1017.8	1017.9	1021.1
150°	1050.2	1053.0	1053.0	1053.0	1052.1
152.5°	1082.4	1084.4	1085.4	1088.3	1085.4
155°	1116.7	1116.7	1115.7	1119.6	1115.7
157.5°	1146.1	1144.1	1144.1	1147.1	1144.1
160°	1171.6	1170.6	1169.6	1172.5	1167.6
162.5°	1195.1	1192.1	1191.2	1197.0	1192.1
165°	1215.6	1212.7	1210.7	1216.6	1212.7
167.5°	1232.3	1228.4	1228.4	1234.3	1228.4
170°	1246.0	1241.1	1242.1	1248.0	1241.1
172.5°	1255.8	1251.9	1251.9	1258.7	1251.9
175°	1264.6	1259.7	1258.7	1265.6	1258.7
177.5°	1268.5	1263.6	1263.6	1270.5	1262.7
180°	1266.6	1266.6	1266.6	1266.6	1266.6

(END OF REPORT)