

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001704

Luminaire Tested: SA4XXDIP-B795D1035UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001704
REPORT IS A COMBINATION OF REPORTS P996326 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1035UB27-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6913.0 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001704

CATALOG NUMBER: SA4XXDIP-B795D1035UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001704

CATALOG NUMBER: SA4XXDIP-B795D1035UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33
4	74	63	55	49	68	59	52	46	50	45	40	42	38	34	34	31	29
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25
6	63	51	42	37	58	47	40	35	40	35	30	34	29	26	28	25	22
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	22	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10789	10789	10789
5°	10798	10479	10492
10°	10706	10188	10117
15°	10553	9842	9694
20°	10357	9468	9255
25°	10136	9072	8784
30°	9870	8645	8267
35°	9595	8208	7766
40°	9307	7737	7234
45°	9005	7265	6737
50°	8673	6807	6186
55°	8310	6272	5639
60°	7938	5686	5069
65°	7514	5082	4427
70°	7025	4354	3738
75°	6294	3509	2994
80°	5363	2537	2106
85°	4162	1412	1134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9005 cd/sqm

TEST NUMBER: P1001704

CATALOG NUMBER: SA4XXDIP-B795D1035UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.7	1.8
10°-20°	351.3	5.1
20°-30°	517.1	7.5
30°-40°	601.1	8.7
40°-50°	601.0	8.7
50°-60°	525.7	7.6
60°-70°	390.3	5.6
70°-80°	221.4	3.2
80°-90°	66.1	1.0
90°-100°	82.6	1.2
100°-110°	247.3	3.6
110°-120°	420.1	6.1
120°-130°	554.0	8.0
130°-140°	622.3	9.0
140°-150°	611.6	8.8
150°-160°	514.4	7.4
160°-170°	342.3	5.0
170°-180°	119.8	1.7
0°-30°	993.1	14.4
0°-40°	1594.2	23.1
0°-60°	2720.9	39.4
0°-90°	3398.7	49.2
90°-120°	749.9	10.8
90°-150°	2537.8	36.7
90°-180°	3514.0	50.8
0°-180°	6913.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1323	1323	1323	1323	1323	
5°	1322	1318	1306	1318	1316	125
15°	1258	1254	1238	1245	1242	355
25°	1140	1132	1117	1118	1114	524
35°	981	973	958	951	946	613
45°	800	793	776	764	761	617
55°	605	602	587	575	568	542
65°	410	405	394	384	378	406
75°	218	213	208	204	202	232
85°	57	57	55	55	54	62
90°	3	14	22	27	29	8
95°	59	68	74	77	77	64
105°	228	229	233	236	239	242
115°	427	427	425	424	423	421
125°	622	622	621	619	617	554
135°	802	808	808	806	803	621
145°	975	979	980	979	976	610
155°	1117	1117	1116	1120	1116	514
165°	1216	1213	1211	1217	1213	343
175°	1265	1260	1259	1266	1259	120
180°	1267	1267	1267	1267	1267	

TEST NUMBER: P1001704

CATALOG NUMBER: SA4XXDIP-B795D1035UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1323.1	1323.1	1323.1	1323.1	1323.1
2.5°	1327.3	1324.2	1312.5	1323.1	1322.0
5°	1322.0	1317.8	1306.1	1317.8	1315.7
7.5°	1312.5	1308.3	1295.5	1305.1	1304.0
10°	1298.7	1294.5	1280.7	1289.2	1287.1
12.5°	1280.7	1276.5	1261.6	1271.2	1268.0
15°	1258.4	1254.2	1238.3	1244.6	1241.5
17.5°	1233.0	1227.7	1212.8	1217.1	1215.0
20°	1204.4	1199.1	1183.2	1186.3	1184.2
22.5°	1173.6	1166.2	1150.3	1156.7	1152.4
25°	1139.7	1132.3	1117.4	1118.5	1114.2
27.5°	1101.5	1094.1	1080.3	1078.2	1072.9
30°	1063.4	1054.9	1041.1	1036.9	1031.6
32.5°	1023.1	1015.7	1000.8	995.5	990.2
35°	980.7	973.2	958.4	951.0	945.7
37.5°	936.1	929.8	913.9	906.5	899.0
40°	892.7	884.2	868.3	857.7	852.4
42.5°	846.0	841.8	823.8	811.0	807.9
45°	800.4	793.0	776.1	764.4	761.2
47.5°	752.7	747.4	731.5	718.8	710.3
50°	704.0	699.7	684.9	670.0	663.7
52.5°	656.3	650.9	635.0	622.3	613.8
55°	605.4	602.2	587.3	574.6	568.3
57.5°	557.7	554.5	539.6	526.9	520.5
60°	507.8	502.5	488.7	479.2	473.9
62.5°	459.1	454.8	440.0	431.5	426.2
65°	410.3	405.0	394.4	383.8	378.5
67.5°	360.5	356.2	345.6	335.0	334.0
70°	314.9	307.5	299.0	290.5	287.3
72.5°	266.1	258.7	252.3	246.0	242.8
75°	218.4	213.1	207.8	203.6	202.5
77.5°	171.7	169.6	164.3	163.3	160.1
80°	130.4	127.2	125.1	123.0	121.9
82.5°	90.1	89.1	89.1	88.0	86.9
85°	57.2	57.2	55.1	55.1	54.1
87.5°	27.6	26.5	25.4	25.4	25.4
90°	2.9	13.7	21.6	27.4	29.4
92.5°	25.5	38.2	43.1	46.0	47.0
95°	58.8	67.6	74.4	77.4	77.4
97.5°	94.0	101.9	109.7	113.6	113.6
100°	137.1	141.1	149.9	151.8	151.8
102.5°	182.2	183.2	191.0	194.0	194.9
105°	228.2	229.2	233.1	236.1	239.0
107.5°	276.2	277.2	278.2	282.1	281.1
110°	325.2	327.2	326.2	324.2	327.2

TEST NUMBER: P1001704

CATALOG NUMBER: SA4XXDIP-B795D1035UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.2	376.2	374.2	374.2	374.2
115°	427.1	427.1	425.1	424.2	423.2
117.5°	475.1	475.1	474.1	471.2	468.2
120°	523.1	527.0	524.1	519.2	521.1
122.5°	573.0	574.0	573.0	570.1	565.2
125°	622.0	622.0	621.0	619.1	617.1
127.5°	666.1	669.0	667.1	665.1	664.1
130°	713.1	716.1	716.1	714.1	710.2
132.5°	761.1	763.1	762.1	760.1	759.2
135°	802.3	808.1	808.1	806.2	803.2
137.5°	848.3	851.2	853.2	850.3	851.2
140°	894.3	896.3	896.3	895.3	894.3
142.5°	936.5	938.4	937.4	937.4	937.4
145°	974.7	978.6	979.6	978.6	975.6
147.5°	1013.9	1018.7	1017.8	1016.8	1015.8
150°	1049.1	1053.0	1053.0	1053.0	1052.1
152.5°	1082.4	1084.4	1085.4	1088.3	1085.4
155°	1116.7	1116.7	1115.7	1119.6	1115.7
157.5°	1146.1	1144.1	1144.1	1147.1	1144.1
160°	1171.6	1170.6	1169.6	1172.5	1167.6
162.5°	1195.1	1192.1	1191.2	1197.0	1192.1
165°	1215.6	1212.7	1210.7	1216.6	1212.7
167.5°	1232.3	1228.4	1228.4	1234.3	1228.4
170°	1246.0	1241.1	1242.1	1248.0	1241.1
172.5°	1255.8	1251.9	1251.9	1258.7	1251.9
175°	1264.6	1259.7	1258.7	1265.6	1258.7
177.5°	1268.5	1263.6	1263.6	1270.5	1262.7
180°	1266.6	1266.6	1266.6	1266.6	1266.6

(END OF REPORT)