

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000742

Luminaire Tested: SA4XXDIP-B1020D590UB50-4F0-XX-W2A-D4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000742
REPORT IS A COMBINATION OF REPORTS P995355 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D590UB50-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6066.0 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000742

CATALOG NUMBER: SA4XXDIP-B1020D590UB50-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1000742

CATALOG NUMBER: SA4XXDIP-B1020D590UB50-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	99	94	90	86	92	88	84	81	77	74	71	66	64	62	57	55	54
2	90	82	75	69	83	76	70	65	67	62	58	58	54	51	49	47	44
3	82	71	63	57	76	67	60	54	58	53	48	51	46	43	43	40	37
4	74	63	54	48	69	59	51	45	52	45	41	45	40	36	38	35	32
5	68	56	47	41	63	52	45	39	46	40	35	40	35	31	34	30	27
6	63	50	41	35	58	47	39	34	41	35	30	36	31	27	31	27	24
7	58	45	37	31	54	42	35	29	37	31	27	33	28	24	28	24	21
8	54	41	33	27	50	39	31	26	34	28	24	30	25	21	26	22	19
9	50	37	30	24	47	35	28	23	31	25	21	28	23	19	24	20	17
10	47	34	27	22	44	32	25	21	29	23	19	25	21	17	22	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9622	9622	9622
5°	9649	9371	9388
10°	9586	9187	9160
15°	9496	8980	8904
20°	9363	8755	8654
25°	9213	8507	8386
30°	9052	8262	8112
35°	8868	8012	7867
40°	8720	7771	7614
45°	8503	7545	7391
50°	8318	7289	7155
55°	8126	7042	6883
60°	7829	6734	6628
65°	7501	6402	6320
70°	7103	6023	5965
75°	6550	5602	5627
80°	5923	5172	5272
85°	5094	4741	4985

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8503 cd/sqm

TEST NUMBER: P1000742

CATALOG NUMBER: SA4XXDIP-B1020D590UB50-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.8	1.8
10°-20°	320.3	5.3
20°-30°	484.4	8.0
30°-40°	586.0	9.7
40°-50°	619.5	10.2
50°-60°	583.0	9.6
60°-70°	483.8	8.0
70°-80°	339.5	5.6
80°-90°	192.5	3.2
90°-100°	321.8	5.3
100°-110°	507.1	8.4
110°-120°	433.4	7.1
120°-130°	348.4	5.7
130°-140°	277.9	4.6
140°-150°	204.4	3.4
150°-160°	141.8	2.3
160°-170°	83.4	1.4
170°-180°	27.1	0.4
0°-30°	916.5	15.1
0°-40°	1502.5	24.8
0°-60°	2705.0	44.6
0°-90°	3720.7	61.3
90°-120°	1262.3	20.8
90°-150°	2093.0	34.5
90°-180°	2345.0	38.7
0°-180°	6066.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1180	1180	1180	1180	1180	
5°	1181	1177	1168	1179	1177	112
15°	1132	1134	1130	1142	1140	319
25°	1036	1044	1048	1062	1064	477
35°	906	922	936	954	958	568
45°	756	781	806	828	835	584
55°	592	620	659	686	694	528
65°	410	452	497	530	540	406
75°	227	276	332	369	381	241
85°	70	126	185	225	238	73
90°	22	78	141	180	191	16
95°	35	118	563	372	297	34
105°	76	131	448	897	904	82
115°	121	162	384	709	843	121
125°	163	191	357	588	663	146
135°	190	226	329	500	571	147
145°	217	247	316	402	446	137
155°	246	265	307	347	362	113
165°	268	276	294	311	316	76
175°	279	280	282	286	285	27
180°	280	280	280	280	280	

TEST NUMBER: P1000742

CATALOG NUMBER: SA4XXDIP-B1020D590UB50-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1180.0	1180.0	1180.0	1180.0	1180.0
2.5°	1185.3	1181.3	1170.7	1180.0	1178.6
5°	1181.3	1177.3	1168.1	1178.6	1177.3
7.5°	1173.4	1170.7	1162.8	1174.7	1173.4
10°	1162.8	1161.5	1154.9	1166.8	1165.4
12.5°	1148.3	1148.3	1144.3	1154.9	1154.9
15°	1132.4	1133.7	1129.8	1141.7	1140.3
17.5°	1111.3	1115.2	1113.9	1125.8	1124.5
20°	1088.8	1092.8	1094.1	1107.3	1107.3
22.5°	1063.7	1069.0	1071.6	1084.8	1087.5
25°	1035.9	1043.9	1047.8	1062.4	1063.7
27.5°	1005.6	1017.4	1022.7	1035.9	1037.3
30°	975.2	985.7	995.0	1009.5	1012.2
32.5°	942.1	955.3	965.9	983.1	985.7
35°	906.4	922.3	935.5	954.0	958.0
37.5°	870.8	889.3	905.1	923.6	927.6
40°	836.4	853.6	872.1	891.9	897.2
42.5°	796.8	816.6	839.1	861.5	865.5
45°	755.8	780.9	806.0	828.5	835.1
47.5°	717.5	742.6	771.7	794.1	802.1
50°	675.2	704.3	733.4	759.8	767.7
52.5°	632.9	662.0	696.4	722.8	730.7
55°	592.0	619.7	659.4	685.8	693.7
57.5°	545.7	580.1	618.4	650.1	656.7
60°	500.8	535.1	578.8	609.1	619.7
62.5°	457.2	495.5	539.1	569.5	580.1
65°	409.6	451.9	496.8	529.9	540.4
67.5°	364.7	409.6	457.2	490.2	500.8
70°	318.4	363.4	413.6	449.3	458.5
72.5°	273.5	319.8	373.9	408.3	418.9
75°	227.3	276.2	331.7	368.7	380.6
77.5°	183.7	235.2	293.3	330.3	343.6
80°	144.0	196.9	255.0	294.7	305.2
82.5°	104.4	159.9	218.0	259.0	270.9
85°	70.0	125.5	185.0	224.6	237.8
87.5°	43.6	97.8	155.9	194.2	206.1
90°	21.6	78.4	140.7	180.1	191.2
92.5°	27.5	108.4	338.4	231.1	220.5
95°	35.3	118.0	563.0	372.4	296.6
97.5°	46.1	117.4	587.8	595.7	476.7
100°	56.3	120.4	542.4	762.8	649.4
102.5°	67.3	125.0	489.0	863.7	801.1
105°	76.2	131.4	447.8	896.6	904.3
107.5°	88.9	139.6	418.7	877.7	949.1
110°	100.2	146.4	402.9	825.8	943.6

TEST NUMBER: P1000742

CATALOG NUMBER: SA4XXDIP-B1020D590UB50-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	110.9	154.5	391.4	764.0	903.3
115°	121.1	161.9	383.7	709.1	843.1
117.5°	133.2	169.8	376.5	663.2	785.3
120°	144.0	176.1	369.9	629.7	735.7
122.5°	155.0	183.4	362.8	606.3	694.8
125°	163.1	191.4	356.9	587.9	662.6
127.5°	171.9	201.4	349.2	568.7	640.6
130°	177.7	209.6	342.1	548.6	619.5
132.5°	184.9	217.8	336.2	526.2	598.1
135°	190.1	225.8	329.1	499.8	570.9
137.5°	196.7	231.4	323.8	473.4	540.4
140°	203.8	237.7	319.2	447.4	509.1
142.5°	210.2	243.4	316.6	424.3	476.1
145°	217.3	247.4	315.5	401.5	445.8
147.5°	225.6	252.3	313.9	381.4	417.2
150°	233.3	257.0	312.2	367.8	392.5
152.5°	239.1	261.4	309.5	357.4	376.0
155°	245.7	265.2	306.7	347.4	362.3
157.5°	252.3	268.8	304.0	338.0	349.6
160°	258.4	271.8	300.7	328.7	338.1
162.5°	263.9	274.3	297.4	319.6	327.1
165°	267.7	276.0	294.1	311.4	316.1
167.5°	272.1	277.4	290.8	304.2	307.3
170°	274.9	278.5	287.5	297.1	299.0
172.5°	277.6	279.2	284.2	290.8	290.8
175°	279.3	279.8	282.0	285.9	284.8
177.5°	280.4	279.8	280.4	282.3	280.4
180°	279.8	279.8	279.8	279.8	279.8

(END OF REPORT)