

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001728

Luminaire Tested: SA4XXDIP-B795D1035UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001728
REPORT IS A COMBINATION OF REPORTS P996350 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1035UB30-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6973.0 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001728

CATALOG NUMBER: SA4XXDIP-B795D1035UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001728

CATALOG NUMBER: SA4XXDIP-B795D1035UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49		
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41		
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39	35		
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33	29		
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29	25		
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22		
6	63	51	42	37	58	47	40	35	40	35	30	34	29	26	28	25	22	19		
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17		
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15		
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	22	18	16	14		
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10881	10881	10881
5°	10890	10568	10581
10°	10798	10275	10203
15°	10643	9926	9777
20°	10445	9549	9334
25°	10223	9150	8859
30°	9954	8719	8338
35°	9676	8278	7833
40°	9387	7803	7296
45°	9083	7327	6794
50°	8747	6865	6238
55°	8380	6326	5687
60°	8007	5735	5111
65°	7578	5126	4464
70°	7086	4390	3770
75°	6349	3540	3019
80°	5408	2559	2125
85°	4199	1425	1142

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9083 cd/sqm

TEST NUMBER: P1001728

CATALOG NUMBER: SA4XXDIP-B795D1035UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.8	1.8
10°-20°	354.3	5.1
20°-30°	521.5	7.5
30°-40°	606.2	8.7
40°-50°	606.2	8.7
50°-60°	530.2	7.6
60°-70°	393.6	5.6
70°-80°	223.3	3.2
80°-90°	66.7	1.0
90°-100°	83.3	1.2
100°-110°	249.5	3.6
110°-120°	423.8	6.1
120°-130°	558.9	8.0
130°-140°	627.7	9.0
140°-150°	617.0	8.8
150°-160°	518.9	7.4
160°-170°	345.3	5.0
170°-180°	120.9	1.7
0°-30°	1001.6	14.4
0°-40°	1607.8	23.1
0°-60°	2744.1	39.4
0°-90°	3427.7	49.2
90°-120°	756.6	10.8
90°-150°	2560.2	36.7
90°-180°	3545.0	50.8
0°-180°	6973.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1334	1334	1334	1334	1334	
5°	1333	1329	1317	1329	1327	127
15°	1269	1265	1249	1255	1252	358
25°	1149	1142	1127	1128	1124	529
35°	989	982	967	959	954	618
45°	807	800	783	771	768	622
55°	610	607	592	580	573	547
65°	414	408	398	387	382	410
75°	220	215	210	205	204	234
85°	58	58	56	56	54	62
90°	3	14	22	28	30	8
95°	59	68	75	78	78	64
105°	230	231	235	238	241	244
115°	431	431	429	428	427	425
125°	628	628	626	624	623	559
135°	809	815	815	813	810	626
145°	983	987	988	987	984	615
155°	1126	1126	1126	1130	1126	518
165°	1226	1223	1221	1227	1223	346
175°	1276	1271	1270	1277	1270	121
180°	1278	1278	1278	1278	1278	

TEST NUMBER: P1001728

CATALOG NUMBER: SA4XXDIP-B795D1035UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1334.4	1334.4	1334.4	1334.4	1334.4
2.5°	1338.7	1335.5	1323.7	1334.4	1333.3
5°	1333.3	1329.1	1317.3	1329.1	1326.9
7.5°	1323.7	1319.4	1306.6	1316.2	1315.2
10°	1309.8	1305.5	1291.6	1300.2	1298.0
12.5°	1291.6	1287.4	1272.4	1282.0	1278.8
15°	1269.2	1264.9	1248.9	1255.3	1252.1
17.5°	1243.5	1238.2	1223.2	1227.5	1225.3
20°	1214.6	1209.3	1193.3	1196.5	1194.3
22.5°	1183.6	1176.2	1160.1	1166.5	1162.3
25°	1149.4	1141.9	1127.0	1128.0	1123.8
27.5°	1110.9	1103.4	1089.5	1087.4	1082.1
30°	1072.4	1063.9	1050.0	1045.7	1040.4
32.5°	1031.8	1024.3	1009.4	1004.0	998.7
35°	989.0	981.6	966.6	959.1	953.8
37.5°	944.1	937.7	921.7	914.2	906.7
40°	900.3	891.7	875.7	865.0	859.7
42.5°	853.2	849.0	830.8	818.0	814.8
45°	807.3	799.8	782.7	770.9	767.7
47.5°	759.2	753.8	737.8	724.9	716.4
50°	710.0	705.7	690.7	675.8	669.3
52.5°	661.9	656.5	640.5	627.6	619.1
55°	610.5	607.3	592.4	579.5	573.1
57.5°	562.4	559.2	544.2	531.4	525.0
60°	512.2	506.8	492.9	483.3	477.9
62.5°	463.0	458.7	443.7	435.2	429.8
65°	413.8	408.4	397.8	387.1	381.7
67.5°	363.5	359.3	348.6	337.9	336.8
70°	317.6	310.1	301.5	293.0	289.8
72.5°	268.4	260.9	254.5	248.1	244.9
75°	220.3	214.9	209.6	205.3	204.2
77.5°	173.2	171.1	165.7	164.7	161.5
80°	131.5	128.3	126.2	124.0	123.0
82.5°	90.9	89.8	89.8	88.7	87.7
85°	57.7	57.7	55.6	55.6	54.5
87.5°	27.8	26.7	25.7	25.7	25.7
90°	3.0	13.8	21.7	27.7	29.6
92.5°	25.7	38.5	43.5	46.4	47.4
95°	59.3	68.2	75.1	78.1	78.1
97.5°	94.9	102.8	110.7	114.6	114.6
100°	138.3	142.3	151.2	153.2	153.2
102.5°	183.8	184.8	192.7	195.7	196.7
105°	230.3	231.2	235.2	238.2	241.1
107.5°	278.7	279.7	280.6	284.6	283.6
110°	328.1	330.1	329.1	327.1	330.1

TEST NUMBER: P1001728

CATALOG NUMBER: SA4XXDIP-B795D1035UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	379.5	379.5	377.5	377.5	377.5
115°	430.9	430.9	428.9	427.9	426.9
117.5°	479.3	479.3	478.3	475.3	472.4
120°	527.7	531.7	528.7	523.7	525.7
122.5°	578.1	579.1	578.1	575.1	570.2
125°	627.5	627.5	626.5	624.5	622.6
127.5°	672.0	674.9	673.0	671.0	670.0
130°	719.4	722.4	722.4	720.4	716.4
132.5°	767.8	769.8	768.8	766.8	765.9
135°	809.3	815.3	815.3	813.3	810.3
137.5°	855.8	858.7	860.7	857.8	858.7
140°	902.2	904.2	904.2	903.2	902.2
142.5°	944.7	946.7	945.7	945.7	945.7
145°	983.3	987.2	988.2	987.2	984.2
147.5°	1022.8	1027.7	1026.7	1025.8	1024.8
150°	1058.4	1062.3	1062.3	1062.3	1061.3
152.5°	1092.0	1093.9	1094.9	1097.9	1094.9
155°	1126.5	1126.5	1125.6	1129.5	1125.6
157.5°	1156.2	1154.2	1154.2	1157.2	1154.2
160°	1181.9	1180.9	1179.9	1182.9	1177.9
162.5°	1205.6	1202.6	1201.7	1207.6	1202.6
165°	1226.4	1223.4	1221.4	1227.3	1223.4
167.5°	1243.2	1239.2	1239.2	1245.1	1239.2
170°	1257.0	1252.1	1253.0	1259.0	1252.1
172.5°	1266.9	1262.9	1262.9	1269.8	1262.9
175°	1275.8	1270.8	1269.8	1276.8	1269.8
177.5°	1279.7	1274.8	1274.8	1281.7	1273.8
180°	1277.7	1277.7	1277.7	1277.7	1277.7

(END OF REPORT)