

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000774

Luminaire Tested: SA4XXDIP-B1020D810UB30-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000774
REPORT IS A COMBINATION OF REPORTS P995387 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D810UB30-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6925.0 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000774

CATALOG NUMBER: SA4XXDIP-B1020D810UB30-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1000774

CATALOG NUMBER: SA4XXDIP-B1020D810UB30-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	98	93	89	85	91	87	83	79	74	71	69	63	61	59	53	51	50
2	89	81	74	68	82	75	69	64	64	60	56	55	51	48	46	43	41
3	81	71	63	56	74	66	59	53	56	51	47	48	44	40	40	37	34
4	74	62	54	47	68	58	50	45	50	44	39	42	38	34	36	32	29
5	67	55	47	40	62	52	44	38	45	38	34	38	33	29	32	28	25
6	62	49	41	35	57	46	39	33	40	34	29	34	29	26	29	25	22
7	57	45	36	30	53	42	34	29	36	30	26	31	26	23	26	22	20
8	53	40	32	27	49	38	31	25	33	27	23	28	24	20	24	20	17
9	50	37	29	24	46	35	28	23	30	24	20	26	21	18	22	18	16
10	46	34	26	21	43	32	25	20	28	22	18	24	19	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10007	10007	10007
5°	10035	9746	9764
10°	9969	9555	9527
15°	9876	9339	9260
20°	9738	9106	9001
25°	9582	8848	8722
30°	9414	8593	8436
35°	9223	8333	8182
40°	9070	8082	7919
45°	8844	7847	7686
50°	8650	7580	7441
55°	8452	7323	7159
60°	8141	7003	6893
65°	7801	6658	6574
70°	7389	6263	6205
75°	6813	5825	5852
80°	6161	5378	5483
85°	5298	4930	5186

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8844 cd/sqm

TEST NUMBER: P1000774

CATALOG NUMBER: SA4XXDIP-B1020D810UB30-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.3	1.7
10°-20°	333.2	4.8
20°-30°	503.7	7.3
30°-40°	609.4	8.8
40°-50°	644.3	9.3
50°-60°	606.3	8.8
60°-70°	503.1	7.3
70°-80°	353.1	5.1
80°-90°	201.2	2.9
90°-100°	182.9	2.6
100°-110°	280.5	4.1
110°-120°	386.3	5.6
120°-130°	464.9	6.7
130°-140°	499.3	7.2
140°-150°	479.5	6.9
150°-160°	400.9	5.8
160°-170°	266.7	3.9
170°-180°	93.4	1.3
0°-30°	953.2	13.8
0°-40°	1562.6	22.6
0°-60°	2813.2	40.6
0°-90°	3870.6	55.9
90°-120°	849.6	12.3
90°-150°	2293.3	33.1
90°-180°	3054.0	44.1
0°-180°	6925.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1227	1227	1227	1227	1227	
5°	1229	1224	1215	1226	1224	117
15°	1178	1179	1175	1187	1186	332
25°	1077	1086	1090	1105	1106	496
35°	943	959	973	992	996	590
45°	786	812	838	862	868	608
55°	616	644	686	713	722	549
65°	426	470	517	551	562	422
75°	236	287	345	383	396	251
85°	73	131	192	234	247	76
90°	24	88	153	197	210	18
95°	64	116	178	217	229	64
105°	190	218	272	309	322	203
115°	341	354	396	425	434	337
125°	490	489	522	547	554	437
135°	628	632	642	663	669	486
145°	761	763	763	771	774	476
155°	870	870	870	873	870	401
165°	947	945	944	948	945	267
175°	986	982	981	986	981	94
180°	987	987	987	987	987	

TEST NUMBER: P1000774

CATALOG NUMBER: SA4XXDIP-B1020D810UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1227.2	1227.2	1227.2	1227.2	1227.2
2.5°	1232.7	1228.6	1217.6	1227.2	1225.8
5°	1228.6	1224.4	1214.8	1225.8	1224.4
7.5°	1220.3	1217.6	1209.3	1221.7	1220.3
10°	1209.3	1208.0	1201.1	1213.4	1212.1
12.5°	1194.2	1194.2	1190.1	1201.1	1201.1
15°	1177.7	1179.1	1175.0	1187.3	1186.0
17.5°	1155.7	1159.9	1158.5	1170.8	1169.5
20°	1132.4	1136.5	1137.9	1151.6	1151.6
22.5°	1106.3	1111.8	1114.5	1128.2	1131.0
25°	1077.4	1085.6	1089.8	1104.9	1106.3
27.5°	1045.8	1058.2	1063.7	1077.4	1078.8
30°	1014.2	1025.2	1034.8	1049.9	1052.7
32.5°	979.8	993.6	1004.6	1022.4	1025.2
35°	942.7	959.2	973.0	992.2	996.3
37.5°	905.6	924.9	941.4	960.6	964.7
40°	869.9	887.8	907.0	927.6	933.1
42.5°	828.7	849.3	872.6	896.0	900.1
45°	786.1	812.2	838.3	861.6	868.5
47.5°	746.2	772.3	802.6	825.9	834.2
50°	702.2	732.5	762.7	790.2	798.4
52.5°	658.3	688.5	724.2	751.7	760.0
55°	615.7	644.5	685.7	713.2	721.5
57.5°	567.6	603.3	643.1	676.1	683.0
60°	520.8	556.6	601.9	633.5	644.5
62.5°	475.5	515.3	560.7	592.3	603.3
65°	426.0	470.0	516.7	551.1	562.1
67.5°	379.3	426.0	475.5	509.8	520.8
70°	331.2	377.9	430.1	467.2	476.9
72.5°	284.5	332.6	388.9	424.6	435.6
75°	236.4	287.2	344.9	383.4	395.8
77.5°	191.0	244.6	305.1	343.6	357.3
80°	149.8	204.8	265.2	306.5	317.4
82.5°	108.6	166.3	226.7	269.4	281.7
85°	72.8	130.6	192.4	233.6	247.4
87.5°	45.3	101.7	162.2	202.0	214.4
90°	24.3	87.7	152.8	197.3	209.8
92.5°	40.4	98.5	161.4	202.2	213.9
95°	63.7	115.9	177.6	217.0	229.3
97.5°	89.8	135.7	198.2	237.0	249.4
100°	122.0	160.7	221.2	259.8	269.5
102.5°	157.1	188.1	246.5	284.5	296.2
105°	190.3	218.5	272.4	309.1	322.3
107.5°	227.7	251.8	300.6	338.1	346.9
110°	264.5	285.2	332.5	362.6	375.9

TEST NUMBER: P1000774

CATALOG NUMBER: SA4XXDIP-B1020D810UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	302.8	319.3	363.1	393.3	404.3
115°	341.1	353.5	395.9	425.4	434.2
117.5°	378.5	386.8	427.2	453.8	462.5
120°	414.6	421.7	459.2	482.9	495.4
122.5°	453.5	454.3	490.6	515.8	521.6
125°	490.3	488.9	522.5	547.1	553.8
127.5°	524.6	525.5	551.5	574.7	583.6
130°	559.9	560.8	582.8	606.0	611.2
132.5°	597.3	597.4	613.2	635.0	642.5
135°	628.0	632.5	642.2	662.7	668.6
137.5°	663.8	664.8	671.8	690.2	697.8
140°	699.7	699.9	701.2	718.4	724.5
142.5°	731.2	732.8	730.6	745.7	751.2
145°	761.0	762.7	763.4	770.9	774.1
147.5°	791.6	794.0	793.2	793.8	798.6
150°	819.0	820.7	820.7	820.7	819.9
152.5°	843.6	845.1	845.9	848.2	845.9
155°	870.3	870.3	869.5	872.6	869.5
157.5°	893.2	891.7	891.7	894.0	891.7
160°	913.1	912.3	911.5	913.8	910.0
162.5°	931.4	929.1	928.3	932.9	929.1
165°	947.4	945.1	943.6	948.2	945.1
167.5°	960.4	957.3	957.3	961.9	957.3
170°	971.1	967.3	968.0	972.6	967.3
172.5°	978.7	975.7	975.7	981.0	975.7
175°	985.6	981.8	981.0	986.4	981.0
177.5°	988.6	984.8	984.8	990.2	984.1
180°	987.1	987.1	987.1	987.1	987.1

(END OF REPORT)