

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001747

Luminaire Tested: SA4XXDIP-B795D1035UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001747
REPORT IS A COMBINATION OF REPORTS P996369 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1035UB40-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7058.3 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001747

CATALOG NUMBER: SA4XXDIP-B795D1035UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001747

CATALOG NUMBER: SA4XXDIP-B795D1035UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25
6	63	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19
8	54	41	34	28	49	38	32	27	33	27	24	28	24	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10821	10821	10821
5°	10830	10510	10523
10°	10738	10218	10146
15°	10584	9871	9722
20°	10387	9495	9283
25°	10166	9099	8810
30°	9899	8671	8291
35°	9623	8232	7789
40°	9335	7759	7255
45°	9032	7286	6756
50°	8697	6827	6204
55°	8334	6291	5655
60°	7961	5703	5084
65°	7536	5096	4439
70°	7045	4367	3750
75°	6311	3519	3003
80°	5380	2545	2113
85°	4177	1417	1136

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9032 cd/sqm

TEST NUMBER: P1001747

CATALOG NUMBER: SA4XXDIP-B795D1035UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	1.8
10°-20°	352.4	5.0
20°-30°	518.6	7.3
30°-40°	602.8	8.5
40°-50°	602.8	8.5
50°-60°	527.2	7.5
60°-70°	391.4	5.5
70°-80°	222.1	3.1
80°-90°	65.5	0.9
90°-100°	371.5	5.3
100°-110°	755.7	10.7
110°-120°	673.6	9.5
120°-130°	565.8	8.0
130°-140°	472.2	6.7
140°-150°	360.6	5.1
150°-160°	253.5	3.6
160°-170°	149.1	2.1
170°-180°	48.5	0.7
0°-30°	996.1	14.1
0°-40°	1598.9	22.7
0°-60°	2728.9	38.7
0°-90°	3407.9	48.3
90°-120°	1800.8	25.5
90°-150°	3199.4	45.3
90°-180°	3650.0	51.7
0°-180°	7058.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1327	1327	1327	1327	1327	
5°	1326	1322	1310	1322	1320	126
15°	1262	1258	1242	1248	1245	356
25°	1143	1136	1121	1122	1118	526
35°	984	976	961	954	948	615
45°	803	795	778	767	763	619
55°	607	604	589	576	570	544
65°	412	406	396	385	380	407
75°	219	214	208	204	203	232
85°	57	57	55	55	54	62
90°	1	8	18	20	21	6
95°	32	102	801	396	240	36
105°	115	167	645	1388	1383	122
115°	202	254	575	1105	1328	201
125°	282	335	572	940	1059	251
135°	335	399	567	834	947	259
145°	386	442	564	704	773	242
155°	439	474	548	621	648	203
165°	479	493	526	557	565	135
175°	499	500	504	511	509	47
180°	500	500	500	500	500	

TEST NUMBER: P1001747

CATALOG NUMBER: SA4XXDIP-B795D1035UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1327.0	1327.0	1327.0	1327.0	1327.0
2.5°	1331.3	1328.1	1316.4	1327.0	1325.9
5°	1325.9	1321.7	1310.0	1321.7	1319.6
7.5°	1316.4	1312.1	1299.4	1308.9	1307.9
10°	1302.5	1298.3	1284.5	1293.0	1290.8
12.5°	1284.5	1280.2	1265.3	1274.9	1271.7
15°	1262.1	1257.9	1241.9	1248.3	1245.1
17.5°	1236.6	1231.3	1216.4	1220.7	1218.5
20°	1207.9	1202.6	1186.6	1189.8	1187.7
22.5°	1177.1	1169.6	1153.7	1160.1	1155.8
25°	1143.0	1135.6	1120.7	1121.8	1117.5
27.5°	1104.8	1097.3	1083.5	1081.4	1076.1
30°	1066.5	1058.0	1044.2	1039.9	1034.6
32.5°	1026.1	1018.6	1003.8	998.4	993.1
35°	983.6	976.1	961.2	953.8	948.5
37.5°	938.9	932.5	916.6	909.1	901.7
40°	895.3	886.8	870.8	860.2	854.9
42.5°	848.5	844.3	826.2	813.4	810.2
45°	802.8	795.3	778.3	766.6	763.4
47.5°	754.9	749.6	733.7	720.9	712.4
50°	706.0	701.8	686.9	672.0	665.6
52.5°	658.2	652.9	636.9	624.2	615.7
55°	607.1	604.0	589.1	576.3	569.9
57.5°	559.3	556.1	541.2	528.5	522.1
60°	509.3	504.0	490.2	480.6	475.3
62.5°	460.4	456.2	441.3	432.8	427.4
65°	411.5	406.2	395.5	384.9	379.6
67.5°	361.5	357.3	346.6	336.0	334.9
70°	315.8	308.4	299.9	291.3	288.2
72.5°	266.9	259.4	253.1	246.7	243.5
75°	219.0	213.7	208.4	204.2	203.1
77.5°	172.3	170.1	164.8	163.7	160.6
80°	130.8	127.6	125.5	123.3	122.3
82.5°	90.4	89.3	89.3	88.3	87.2
85°	57.4	57.4	55.3	55.3	54.2
87.5°	27.6	26.6	25.5	25.5	25.5
90°	1.0	7.9	17.7	19.7	20.6
92.5°	13.8	75.6	385.2	127.2	89.4
95°	32.4	102.2	800.9	396.5	239.8
97.5°	54.0	113.0	856.9	809.8	575.9
100°	74.7	127.8	790.1	1120.2	901.1
102.5°	94.3	145.4	706.6	1314.8	1184.2
105°	115.0	166.6	644.6	1388.1	1382.7
107.5°	137.6	188.2	604.4	1366.0	1477.0
110°	160.2	209.8	585.7	1287.4	1479.0

TEST NUMBER: P1001747

CATALOG NUMBER: SA4XXDIP-B795D1035UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	181.8	231.4	576.8	1191.0	1421.0
115°	202.4	254.0	574.9	1104.6	1327.6
117.5°	224.1	275.2	573.9	1036.8	1236.2
120°	245.7	295.8	573.9	991.0	1161.5
122.5°	265.3	316.0	572.9	961.1	1102.6
125°	282.0	335.1	571.9	940.0	1059.3
127.5°	297.8	352.8	570.0	919.8	1031.8
130°	310.5	370.0	569.0	895.8	1008.2
132.5°	323.3	384.8	568.0	867.2	981.7
135°	335.1	399.0	567.0	834.3	947.3
137.5°	346.9	411.2	567.0	798.9	907.0
140°	359.7	422.6	566.0	764.6	862.8
142.5°	373.4	432.9	566.0	732.6	815.6
145°	386.2	442.2	564.1	703.6	773.4
147.5°	400.9	451.0	561.1	679.5	734.1
150°	414.7	459.4	558.2	657.4	701.6
152.5°	427.5	467.2	553.3	638.8	672.2
155°	439.3	474.2	548.3	621.1	647.6
157.5°	451.1	480.5	543.4	604.3	625.0
160°	461.9	485.9	537.5	587.7	604.4
162.5°	471.7	490.4	531.6	571.4	584.7
165°	478.6	493.4	525.7	556.7	565.1
167.5°	486.4	495.8	519.8	543.9	549.3
170°	491.3	497.8	514.0	531.2	534.6
172.5°	496.3	499.2	508.1	519.8	519.8
175°	499.2	500.2	504.1	511.0	509.0
177.5°	501.2	500.2	501.2	504.6	501.2
180°	500.2	500.2	500.2	500.2	500.2

(END OF REPORT)