

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001755

Luminaire Tested: SA4XXDIP-B795D1035UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001755
REPORT IS A COMBINATION OF REPORTS P996377 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1035UB50-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6704.0 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001755

CATALOG NUMBER: SA4XXDIP-B795D1035UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001755

CATALOG NUMBER: SA4XXDIP-B795D1035UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49		
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41		
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39	35		
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33	29		
4	74	63	55	49	68	59	52	46	50	45	40	42	38	34	34	31	29	25		
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22		
6	63	51	42	37	58	47	40	35	40	35	30	34	29	26	28	25	22	19		
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17		
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15		
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	22	18	16	14		
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10462	10462	10462
5°	10470	10161	10174
10°	10382	9879	9810
15°	10233	9543	9399
20°	10043	9181	8975
25°	9829	8797	8518
30°	9571	8383	8016
35°	9303	7958	7531
40°	9025	7503	7014
45°	8733	7044	6532
50°	8409	6600	5998
55°	8058	6082	5467
60°	7697	5514	4915
65°	7285	4927	4292
70°	6811	4222	3625
75°	6104	3403	2904
80°	5199	2460	2042
85°	4039	1371	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8733 cd/sqm

TEST NUMBER: P1001755

CATALOG NUMBER: SA4XXDIP-B795D1035UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	1.8
10°-20°	340.7	5.1
20°-30°	501.4	7.5
30°-40°	582.8	8.7
40°-50°	582.8	8.7
50°-60°	509.7	7.6
60°-70°	378.4	5.6
70°-80°	214.7	3.2
80°-90°	64.1	1.0
90°-100°	80.1	1.2
100°-110°	239.8	3.6
110°-120°	407.4	6.1
120°-130°	537.3	8.0
130°-140°	603.5	9.0
140°-150°	593.2	8.8
150°-160°	498.9	7.4
160°-170°	332.0	5.0
170°-180°	116.2	1.7
0°-30°	963.0	14.4
0°-40°	1545.9	23.1
0°-60°	2638.4	39.4
0°-90°	3295.6	49.2
90°-120°	727.4	10.8
90°-150°	2461.3	36.7
90°-180°	3408.0	50.8
0°-180°	6704.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1283	1283	1283	1283	1283	
5°	1282	1278	1266	1278	1276	122
15°	1220	1216	1201	1207	1204	344
25°	1105	1098	1084	1085	1080	509
35°	951	944	929	922	917	595
45°	776	769	752	741	738	598
55°	587	584	570	557	551	526
65°	398	393	382	372	367	394
75°	212	207	202	197	196	225
85°	56	56	54	54	52	60
90°	3	13	21	27	28	8
95°	57	66	72	75	75	62
105°	221	222	226	229	232	235
115°	414	414	412	411	410	409
125°	603	603	602	600	598	538
135°	778	784	784	782	779	602
145°	945	949	950	949	946	592
155°	1083	1083	1082	1086	1082	498
165°	1179	1176	1174	1180	1176	332
175°	1226	1222	1221	1228	1221	116
180°	1228	1228	1228	1228	1228	

TEST NUMBER: P1001755

CATALOG NUMBER: SA4XXDIP-B795D1035UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1283.0	1283.0	1283.0	1283.0	1283.0
2.5°	1287.1	1284.0	1272.7	1283.0	1281.9
5°	1281.9	1277.8	1266.5	1277.8	1275.8
7.5°	1272.7	1268.6	1256.2	1265.5	1264.5
10°	1259.3	1255.2	1241.9	1250.1	1248.0
12.5°	1241.9	1237.7	1223.3	1232.6	1229.5
15°	1220.3	1216.2	1200.7	1206.9	1203.8
17.5°	1195.6	1190.5	1176.1	1180.2	1178.1
20°	1167.8	1162.7	1147.3	1150.4	1148.3
22.5°	1138.0	1130.8	1115.4	1121.6	1117.5
25°	1105.1	1097.9	1083.5	1084.6	1080.5
27.5°	1068.1	1060.9	1047.6	1045.5	1040.4
30°	1031.1	1022.9	1009.5	1005.4	1000.3
32.5°	992.0	984.8	970.5	965.3	960.2
35°	950.9	943.7	929.3	922.1	917.0
37.5°	907.7	901.6	886.2	879.0	871.8
40°	865.6	857.4	842.0	831.7	826.5
42.5°	820.4	816.3	798.8	786.4	783.4
45°	776.2	769.0	752.5	741.2	738.1
47.5°	729.9	724.8	709.3	697.0	688.8
50°	682.6	678.5	664.1	649.7	643.5
52.5°	636.3	631.2	615.8	603.4	595.2
55°	587.0	583.9	569.5	557.2	551.0
57.5°	540.7	537.7	523.3	510.9	504.8
60°	492.4	487.3	473.9	464.7	459.5
62.5°	445.1	441.0	426.6	418.4	413.3
65°	397.8	392.7	382.4	372.1	367.0
67.5°	349.5	345.4	335.1	324.9	323.8
70°	305.3	298.1	289.9	281.7	278.6
72.5°	258.0	250.8	244.7	238.5	235.4
75°	211.8	206.6	201.5	197.4	196.4
77.5°	166.5	164.5	159.3	158.3	155.2
80°	126.4	123.4	121.3	119.3	118.2
82.5°	87.4	86.4	86.4	85.3	84.3
85°	55.5	55.5	53.5	53.5	52.4
87.5°	26.7	25.7	24.7	24.7	24.7
90°	2.9	13.3	20.9	26.6	28.5
92.5°	24.7	37.1	41.8	44.7	45.6
95°	57.0	65.6	72.2	75.1	75.1
97.5°	91.2	98.8	106.4	110.2	110.2
100°	133.0	136.8	145.4	147.3	147.3
102.5°	176.7	177.7	185.3	188.1	189.1
105°	221.4	222.3	226.1	229.0	231.8
107.5°	267.9	268.9	269.8	273.6	272.7
110°	315.4	317.3	316.4	314.5	317.3

TEST NUMBER: P1001755

CATALOG NUMBER: SA4XXDIP-B795D1035UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	364.8	364.8	362.9	362.9	362.9
115°	414.2	414.2	412.3	411.4	410.4
117.5°	460.8	460.8	459.8	457.0	454.1
120°	507.3	511.1	508.3	503.5	505.4
122.5°	555.8	556.7	555.8	552.9	548.2
125°	603.3	603.3	602.3	600.4	598.5
127.5°	646.0	648.9	647.0	645.1	644.1
130°	691.6	694.5	694.5	692.6	688.8
132.5°	738.2	740.1	739.1	737.2	736.3
135°	778.1	783.8	783.8	781.9	779.0
137.5°	822.7	825.6	827.5	824.6	825.6
140°	867.4	869.3	869.3	868.3	867.4
142.5°	908.2	910.1	909.2	909.2	909.2
145°	945.3	949.1	950.0	949.1	946.2
147.5°	983.3	988.0	987.1	986.1	985.2
150°	1017.5	1021.3	1021.3	1021.3	1020.3
152.5°	1049.8	1051.7	1052.6	1055.5	1052.6
155°	1083.0	1083.0	1082.1	1085.9	1082.1
157.5°	1111.6	1109.7	1109.7	1112.5	1109.7
160°	1136.3	1135.3	1134.4	1137.2	1132.5
162.5°	1159.1	1156.2	1155.3	1161.0	1156.2
165°	1179.0	1176.2	1174.3	1180.0	1176.2
167.5°	1195.2	1191.4	1191.4	1197.1	1191.4
170°	1208.5	1203.7	1204.7	1210.4	1203.7
172.5°	1218.0	1214.2	1214.2	1220.8	1214.2
175°	1226.5	1221.8	1220.8	1227.5	1220.8
177.5°	1230.3	1225.6	1225.6	1232.2	1224.6
180°	1228.4	1228.4	1228.4	1228.4	1228.4

(END OF REPORT)