

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001756

Luminaire Tested: SA4XXDIP-B795D1035UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001756
REPORT IS A COMBINATION OF REPORTS P996378 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1035UB50-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6825.0 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001756

CATALOG NUMBER: SA4XXDIP-B795D1035UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001756

CATALOG NUMBER: SA4XXDIP-B795D1035UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48		
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46	41		
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34		
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29		
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28	25		
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	21		
6	63	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19		
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19	17		
8	54	41	34	28	49	38	32	27	33	27	24	28	24	20	23	20	17	15		
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	13		
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10462	10462	10462
5°	10470	10161	10174
10°	10382	9879	9810
15°	10233	9543	9399
20°	10043	9181	8975
25°	9829	8797	8518
30°	9571	8383	8016
35°	9303	7958	7531
40°	9025	7503	7014
45°	8733	7044	6532
50°	8409	6600	5998
55°	8058	6082	5467
60°	7697	5514	4915
65°	7285	4927	4292
70°	6811	4222	3625
75°	6104	3403	2904
80°	5199	2460	2042
85°	4039	1371	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8733 cd/sqm

TEST NUMBER: P1001756

CATALOG NUMBER: SA4XXDIP-B795D1035UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	1.8
10°-20°	340.7	5.0
20°-30°	501.4	7.3
30°-40°	582.8	8.5
40°-50°	582.8	8.5
50°-60°	509.7	7.5
60°-70°	378.4	5.5
70°-80°	214.7	3.1
80°-90°	63.4	0.9
90°-100°	359.3	5.3
100°-110°	730.8	10.7
110°-120°	651.4	9.5
120°-130°	547.2	8.0
130°-140°	456.6	6.7
140°-150°	348.7	5.1
150°-160°	245.1	3.6
160°-170°	144.2	2.1
170°-180°	46.9	0.7
0°-30°	963.0	14.1
0°-40°	1545.9	22.6
0°-60°	2638.4	38.7
0°-90°	3294.9	48.3
90°-120°	1741.5	25.5
90°-150°	3094.0	45.3
90°-180°	3530.0	51.7
0°-180°	6825.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1283	1283	1283	1283	1283	
5°	1282	1278	1266	1278	1276	122
15°	1220	1216	1201	1207	1204	344
25°	1105	1098	1084	1085	1080	509
35°	951	944	929	922	917	595
45°	776	769	752	741	738	598
55°	587	584	570	557	551	526
65°	398	393	382	372	367	394
75°	212	207	202	197	196	225
85°	56	56	54	54	52	60
90°	1	8	17	19	20	6
95°	31	99	774	384	232	34
105°	111	161	623	1342	1337	118
115°	196	246	556	1068	1284	194
125°	273	324	553	909	1024	243
135°	324	386	548	807	916	250
145°	374	428	546	680	748	234
155°	425	459	530	601	626	196
165°	463	477	508	538	546	131
175°	483	484	488	494	492	46
180°	484	484	484	484	484	

TEST NUMBER: P1001756

CATALOG NUMBER: SA4XXDIP-B795D1035UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1283.0	1283.0	1283.0	1283.0	1283.0
2.5°	1287.1	1284.0	1272.7	1283.0	1281.9
5°	1281.9	1277.8	1266.5	1277.8	1275.8
7.5°	1272.7	1268.6	1256.2	1265.5	1264.5
10°	1259.3	1255.2	1241.9	1250.1	1248.0
12.5°	1241.9	1237.7	1223.3	1232.6	1229.5
15°	1220.3	1216.2	1200.7	1206.9	1203.8
17.5°	1195.6	1190.5	1176.1	1180.2	1178.1
20°	1167.8	1162.7	1147.3	1150.4	1148.3
22.5°	1138.0	1130.8	1115.4	1121.6	1117.5
25°	1105.1	1097.9	1083.5	1084.6	1080.5
27.5°	1068.1	1060.9	1047.6	1045.5	1040.4
30°	1031.1	1022.9	1009.5	1005.4	1000.3
32.5°	992.0	984.8	970.5	965.3	960.2
35°	950.9	943.7	929.3	922.1	917.0
37.5°	907.7	901.6	886.2	879.0	871.8
40°	865.6	857.4	842.0	831.7	826.5
42.5°	820.4	816.3	798.8	786.4	783.4
45°	776.2	769.0	752.5	741.2	738.1
47.5°	729.9	724.8	709.3	697.0	688.8
50°	682.6	678.5	664.1	649.7	643.5
52.5°	636.3	631.2	615.8	603.4	595.2
55°	587.0	583.9	569.5	557.2	551.0
57.5°	540.7	537.7	523.3	510.9	504.8
60°	492.4	487.3	473.9	464.7	459.5
62.5°	445.1	441.0	426.6	418.4	413.3
65°	397.8	392.7	382.4	372.1	367.0
67.5°	349.5	345.4	335.1	324.9	323.8
70°	305.3	298.1	289.9	281.7	278.6
72.5°	258.0	250.8	244.7	238.5	235.4
75°	211.8	206.6	201.5	197.4	196.4
77.5°	166.5	164.5	159.3	158.3	155.2
80°	126.4	123.4	121.3	119.3	118.2
82.5°	87.4	86.4	86.4	85.3	84.3
85°	55.5	55.5	53.5	53.5	52.4
87.5°	26.7	25.7	24.7	24.7	24.7
90°	1.0	7.6	17.1	19.0	20.0
92.5°	13.3	73.2	372.5	123.0	86.5
95°	31.4	98.8	774.5	383.5	231.9
97.5°	52.3	109.3	828.7	783.1	556.9
100°	72.2	123.6	764.1	1083.4	871.5
102.5°	91.2	140.6	683.3	1271.6	1145.2
105°	111.2	161.1	623.4	1342.4	1337.1
107.5°	133.0	182.0	584.5	1321.0	1428.4
110°	154.9	202.9	566.4	1245.0	1430.3

TEST NUMBER: P1001756

CATALOG NUMBER: SA4XXDIP-B795D1035UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.8	223.8	557.9	1151.8	1374.2
115°	195.8	245.6	556.0	1068.2	1283.9
117.5°	216.7	266.1	555.0	1002.6	1195.5
120°	237.6	286.0	555.0	958.4	1123.3
122.5°	256.6	305.5	554.1	929.4	1066.3
125°	272.7	324.1	553.1	909.0	1024.5
127.5°	288.0	341.2	551.2	889.5	997.9
130°	300.3	357.8	550.2	866.2	975.1
132.5°	312.7	372.0	549.3	838.7	949.4
135°	324.1	385.8	548.3	806.8	916.1
137.5°	335.5	397.7	548.3	772.6	877.2
140°	347.8	408.6	547.4	739.3	834.4
142.5°	361.1	418.6	547.4	708.5	788.8
145°	373.5	427.6	545.5	680.4	747.9
147.5°	387.7	436.2	542.6	657.2	709.9
150°	401.0	444.3	539.8	635.8	678.5
152.5°	413.4	451.9	535.0	617.8	650.0
155°	424.8	458.6	530.3	600.6	626.3
157.5°	436.2	464.7	525.5	584.4	604.4
160°	446.7	470.0	519.8	568.3	584.5
162.5°	456.2	474.2	514.1	552.6	565.5
165°	462.8	477.0	508.4	538.4	546.4
167.5°	470.4	479.4	502.7	526.0	531.2
170°	475.2	481.4	497.0	513.7	517.0
172.5°	479.9	482.8	491.3	502.8	502.7
175°	482.8	483.7	487.5	494.2	492.3
177.5°	484.7	483.7	484.7	488.0	484.7
180°	483.7	483.7	483.7	483.7	483.7

(END OF REPORT)