

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001765

Luminaire Tested: SA4XXDIP-B795D1205UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001765
REPORT IS A COMBINATION OF REPORTS P996387 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1205UB27-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7674.5 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001765

CATALOG NUMBER: SA4XXDIP-B795D1205UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001765

CATALOG NUMBER: SA4XXDIP-B795D1205UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	92	88	85	88	85	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	38	36
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	73	63	55	49	67	58	51	45	48	43	39	39	36	33	31	29	26
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	26	23	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	27	22	19	21	18	16
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10789	10789	10789
5°	10798	10479	10492
10°	10706	10188	10117
15°	10553	9842	9694
20°	10357	9468	9255
25°	10136	9072	8784
30°	9870	8645	8267
35°	9595	8208	7766
40°	9307	7737	7234
45°	9005	7265	6737
50°	8673	6807	6186
55°	8310	6272	5639
60°	7938	5686	5069
65°	7514	5082	4427
70°	7025	4354	3738
75°	6294	3509	2994
80°	5363	2537	2106
85°	4162	1412	1134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9005 cd/sqm

TEST NUMBER: P1001765

CATALOG NUMBER: SA4XXDIP-B795D1205UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.7	1.6
10°-20°	351.3	4.6
20°-30°	517.1	6.7
30°-40°	601.1	7.8
40°-50°	601.0	7.8
50°-60°	525.7	6.8
60°-70°	390.3	5.1
70°-80°	221.4	2.9
80°-90°	65.7	0.9
90°-100°	435.3	5.7
100°-110°	885.3	11.5
110°-120°	789.1	10.3
120°-130°	662.8	8.6
130°-140°	553.1	7.2
140°-150°	422.4	5.5
150°-160°	296.9	3.9
160°-170°	174.6	2.3
170°-180°	56.8	0.7
0°-30°	993.1	12.9
0°-40°	1594.2	20.8
0°-60°	2720.9	35.5
0°-90°	3398.3	44.3
90°-120°	2109.6	27.5
90°-150°	3748.0	48.8
90°-180°	4276.0	55.7
0°-180°	7674.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1323	1323	1323	1323	1323	
5°	1322	1318	1306	1318	1316	125
15°	1258	1254	1238	1245	1242	355
25°	1140	1132	1117	1118	1114	524
35°	981	973	958	951	946	613
45°	800	793	776	764	761	617
55°	605	602	587	575	568	542
65°	410	405	394	384	378	406
75°	218	213	208	204	202	232
85°	57	57	55	55	54	62
90°	1	9	21	23	24	6
95°	38	120	938	464	281	42
105°	135	195	755	1626	1620	143
115°	237	298	674	1294	1555	235
125°	330	392	670	1101	1241	294
135°	393	467	664	977	1110	303
145°	452	518	661	824	906	284
155°	515	555	642	728	759	237
165°	561	578	616	652	662	158
175°	585	586	591	599	596	56
180°	586	586	586	586	586	

TEST NUMBER: P1001765

CATALOG NUMBER: SA4XXDIP-B795D1205UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1323.1	1323.1	1323.1	1323.1	1323.1
2.5°	1327.3	1324.2	1312.5	1323.1	1322.0
5°	1322.0	1317.8	1306.1	1317.8	1315.7
7.5°	1312.5	1308.3	1295.5	1305.1	1304.0
10°	1298.7	1294.5	1280.7	1289.2	1287.1
12.5°	1280.7	1276.5	1261.6	1271.2	1268.0
15°	1258.4	1254.2	1238.3	1244.6	1241.5
17.5°	1233.0	1227.7	1212.8	1217.1	1215.0
20°	1204.4	1199.1	1183.2	1186.3	1184.2
22.5°	1173.6	1166.2	1150.3	1156.7	1152.4
25°	1139.7	1132.3	1117.4	1118.5	1114.2
27.5°	1101.5	1094.1	1080.3	1078.2	1072.9
30°	1063.4	1054.9	1041.1	1036.9	1031.6
32.5°	1023.1	1015.7	1000.8	995.5	990.2
35°	980.7	973.2	958.4	951.0	945.7
37.5°	936.1	929.8	913.9	906.5	899.0
40°	892.7	884.2	868.3	857.7	852.4
42.5°	846.0	841.8	823.8	811.0	807.9
45°	800.4	793.0	776.1	764.4	761.2
47.5°	752.7	747.4	731.5	718.8	710.3
50°	704.0	699.7	684.9	670.0	663.7
52.5°	656.3	650.9	635.0	622.3	613.8
55°	605.4	602.2	587.3	574.6	568.3
57.5°	557.7	554.5	539.6	526.9	520.5
60°	507.8	502.5	488.7	479.2	473.9
62.5°	459.1	454.8	440.0	431.5	426.2
65°	410.3	405.0	394.4	383.8	378.5
67.5°	360.5	356.2	345.6	335.0	334.0
70°	314.9	307.5	299.0	290.5	287.3
72.5°	266.1	258.7	252.3	246.0	242.8
75°	218.4	213.1	207.8	203.6	202.5
77.5°	171.7	169.6	164.3	163.3	160.1
80°	130.4	127.2	125.1	123.0	121.9
82.5°	90.1	89.1	89.1	88.0	86.9
85°	57.2	57.2	55.1	55.1	54.1
87.5°	27.6	26.5	25.4	25.4	25.4
90°	1.2	9.2	20.7	23.0	24.2
92.5°	16.1	88.6	451.3	149.1	104.8
95°	38.0	119.7	938.2	464.5	280.9
97.5°	63.3	132.4	1003.8	948.6	674.6
100°	87.5	149.6	925.6	1312.4	1055.6
102.5°	110.5	170.4	827.7	1540.3	1387.2
105°	134.7	195.1	755.2	1626.1	1619.7
107.5°	161.2	220.4	708.0	1600.2	1730.3
110°	187.6	245.8	686.1	1508.1	1732.6

TEST NUMBER: P1001765

CATALOG NUMBER: SA4XXDIP-B795D1205UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.0	271.1	675.8	1395.2	1664.6
115°	237.1	297.6	673.5	1294.0	1555.3
117.5°	262.5	322.4	672.3	1214.6	1448.2
120°	287.8	346.5	672.3	1161.0	1360.7
122.5°	310.8	370.2	671.1	1125.8	1291.6
125°	330.4	392.5	670.0	1101.2	1241.0
127.5°	348.8	413.3	667.7	1077.6	1208.8
130°	363.8	433.4	666.5	1049.3	1181.1
132.5°	378.7	450.7	665.4	1015.9	1150.0
135°	392.6	467.4	664.2	977.4	1109.8
137.5°	406.4	481.8	664.2	935.9	1062.6
140°	421.3	495.0	663.1	895.6	1010.8
142.5°	437.5	507.1	663.1	858.2	955.5
145°	452.4	518.0	660.8	824.2	906.0
147.5°	469.7	528.4	657.3	796.0	859.9
150°	485.8	538.2	653.9	770.2	822.0
152.5°	500.8	547.4	648.1	748.2	787.4
155°	514.6	555.4	642.4	727.6	758.6
157.5°	528.4	562.9	636.6	708.0	732.2
160°	541.1	569.2	629.7	688.4	708.0
162.5°	552.6	574.4	622.8	669.4	685.0
165°	560.6	577.9	615.9	652.2	661.9
167.5°	569.8	580.8	609.0	637.2	643.5
170°	575.6	583.1	602.1	622.2	626.3
172.5°	581.4	584.8	595.2	609.0	609.0
175°	584.8	586.0	590.6	598.6	596.3
177.5°	587.1	586.0	587.1	591.2	587.1
180°	586.0	586.0	586.0	586.0	586.0

(END OF REPORT)