

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000814

Luminaire Tested: SA4XXDIP-B1195D1035UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000814
REPORT IS A COMBINATION OF REPORTS P995427 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1035UB27-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8723.3 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000814

CATALOG NUMBER: SA4XXDIP-B1195D1035UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000814

CATALOG NUMBER: SA4XXDIP-B1195D1035UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	95	91	88	93	89	85	82	77	75	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	50	47	45
3	83	73	66	60	77	68	62	56	60	54	50	51	48	44	44	41	39
4	76	65	57	51	70	61	53	48	53	47	43	46	42	38	39	36	33
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	28	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18
10	48	36	28	24	45	34	27	23	30	24	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16146	16146	16146
5°	16159	15681	15700
10°	16022	15246	15139
15°	15792	14729	14506
20°	15499	14169	13850
25°	15168	13577	13145
30°	14770	12938	12371
35°	14357	12282	11622
40°	13928	11578	10826
45°	13476	10871	10081
50°	12977	10186	9257
55°	12435	9386	8438
60°	11879	8510	7585
65°	11244	7605	6624
70°	10512	6515	5593
75°	9418	5252	4480
80°	8024	3797	3151
85°	6236	2114	1696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13476 cd/sqm

TEST NUMBER: P1000814

CATALOG NUMBER: SA4XXDIP-B1195D1035UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	2.1
10°-20°	525.8	6.0
20°-30°	773.8	8.9
30°-40°	899.5	10.3
40°-50°	899.4	10.3
50°-60°	786.6	9.0
60°-70°	584.0	6.7
70°-80°	331.4	3.8
80°-90°	96.8	1.1
90°-100°	370.4	4.2
100°-110°	753.4	8.6
110°-120°	671.5	7.7
120°-130°	564.1	6.5
130°-140°	470.7	5.4
140°-150°	359.5	4.1
150°-160°	252.7	2.9
160°-170°	148.6	1.7
170°-180°	48.3	0.6
0°-30°	1486.2	17.0
0°-40°	2385.7	27.3
0°-60°	4071.7	46.7
0°-90°	5083.9	58.3
90°-120°	1795.4	20.6
90°-150°	3189.7	36.6
90°-180°	3639.0	41.7
0°-180°	8723.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1980	1980	1980	1980	1980	
5°	1978	1972	1955	1972	1969	188
15°	1883	1877	1853	1863	1858	531
25°	1706	1694	1672	1674	1667	785
35°	1468	1456	1434	1423	1415	918
45°	1198	1187	1161	1144	1139	923
55°	906	901	879	860	850	811
65°	614	606	590	574	566	608
75°	327	319	311	305	303	347
85°	86	86	82	82	81	92
90°	1	8	18	20	21	8
95°	32	102	798	395	239	35
105°	115	166	643	1384	1378	122
115°	202	253	573	1101	1324	200
125°	281	334	570	937	1056	251
135°	334	398	565	832	944	258
145°	385	441	562	702	771	242
155°	438	473	547	619	646	202
165°	477	492	524	555	563	135
175°	498	499	503	510	508	47
180°	499	499	499	499	499	

TEST NUMBER: P1000814

CATALOG NUMBER: SA4XXDIP-B1195D1035UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1980.0	1980.0	1980.0	1980.0	1980.0
2.5°	1986.3	1981.6	1964.1	1980.0	1978.4
5°	1978.4	1972.0	1954.6	1972.0	1968.9
7.5°	1964.1	1957.8	1938.7	1953.0	1951.4
10°	1943.5	1937.1	1916.5	1929.2	1926.0
12.5°	1916.5	1910.2	1888.0	1902.2	1897.5
15°	1883.2	1876.9	1853.1	1862.6	1857.8
17.5°	1845.1	1837.2	1815.0	1821.3	1818.2
20°	1802.3	1794.4	1770.6	1775.3	1772.1
22.5°	1756.3	1745.2	1721.4	1730.9	1724.5
25°	1705.5	1694.4	1672.2	1673.8	1667.4
27.5°	1648.4	1637.3	1616.7	1613.5	1605.6
30°	1591.3	1578.6	1558.0	1551.6	1543.7
32.5°	1531.0	1519.9	1497.7	1489.7	1481.8
35°	1467.5	1456.4	1434.2	1423.1	1415.2
37.5°	1400.9	1391.4	1367.6	1356.5	1345.4
40°	1335.9	1323.2	1299.4	1283.5	1275.6
42.5°	1266.0	1259.7	1232.7	1213.7	1208.9
45°	1197.8	1186.7	1161.3	1143.9	1139.1
47.5°	1126.4	1118.5	1094.7	1075.7	1063.0
50°	1053.4	1047.1	1024.9	1002.7	993.2
52.5°	982.1	974.1	950.3	931.3	918.6
55°	905.9	901.1	878.9	859.9	850.4
57.5°	834.5	829.8	807.5	788.5	779.0
60°	759.9	752.0	731.4	717.1	709.2
62.5°	687.0	680.6	658.4	645.7	637.8
65°	614.0	606.1	590.2	574.3	566.4
67.5°	539.4	533.1	517.2	501.3	499.8
70°	471.2	460.1	447.4	434.7	429.9
72.5°	398.2	387.1	377.6	368.1	363.3
75°	326.8	318.9	311.0	304.6	303.0
77.5°	257.0	253.8	245.9	244.3	239.6
80°	195.1	190.4	187.2	184.0	182.4
82.5°	134.9	133.3	133.3	131.7	130.1
85°	85.7	85.7	82.5	82.5	80.9
87.5°	41.2	39.7	38.1	38.1	38.1
90°	1.0	7.8	17.6	19.6	20.6
92.5°	13.7	75.4	384.1	126.8	89.2
95°	32.3	101.9	798.5	395.3	239.1
97.5°	53.9	112.6	854.3	807.3	574.1
100°	74.5	127.4	787.7	1116.8	898.4
102.5°	94.1	145.0	704.4	1310.9	1180.6
105°	114.6	166.1	642.7	1383.9	1378.5
107.5°	137.2	187.6	602.5	1361.8	1472.5
110°	159.7	209.2	583.9	1283.4	1474.5

TEST NUMBER: P1000814

CATALOG NUMBER: SA4XXDIP-B1195D1035UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	181.3	230.8	575.1	1187.4	1416.7
115°	201.8	253.2	573.1	1101.2	1323.6
117.5°	223.4	274.3	572.2	1033.6	1232.5
120°	244.9	294.9	572.2	988.0	1158.0
122.5°	264.5	315.0	571.2	958.2	1099.3
125°	281.2	334.1	570.2	937.2	1056.2
127.5°	296.9	351.7	568.2	917.0	1028.7
130°	309.6	368.9	567.3	893.0	1005.2
132.5°	322.3	383.6	566.3	864.6	978.8
135°	334.1	397.8	565.3	831.8	944.5
137.5°	345.8	410.0	565.3	796.6	904.3
140°	358.6	421.2	564.3	762.2	860.2
142.5°	372.3	431.6	564.3	730.4	813.2
145°	385.0	440.9	562.4	701.5	771.0
147.5°	399.7	449.7	559.4	677.5	731.9
150°	413.4	458.0	556.5	655.4	699.5
152.5°	426.2	465.8	551.6	636.8	670.1
155°	437.9	472.8	546.7	619.2	645.6
157.5°	449.7	479.1	541.8	602.5	623.1
160°	460.5	484.5	535.9	585.9	602.5
162.5°	470.3	488.9	530.0	569.7	582.9
165°	477.1	491.8	524.2	555.0	563.3
167.5°	485.0	494.2	518.3	542.3	547.7
170°	489.9	496.2	512.4	529.6	533.0
172.5°	494.8	497.7	506.5	518.3	518.3
175°	497.7	498.7	502.6	509.5	507.5
177.5°	499.7	498.7	499.7	503.1	499.7
180°	498.7	498.7	498.7	498.7	498.7

(END OF REPORT)