

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000837

Luminaire Tested: SA4XXDIP-B1195D1035UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000837
REPORT IS A COMBINATION OF REPORTS P995450 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1035UB30-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8674.0 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000837

CATALOG NUMBER: SA4XXDIP-B1195D1035UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1000837

CATALOG NUMBER: SA4XXDIP-B1195D1035UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	95	91	88	93	89	86	83	78	75	73	67	65	63	57	56	54
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16285	16285	16285
5°	16299	15817	15836
10°	16161	15378	15270
15°	15929	14856	14632
20°	15633	14291	13971
25°	15300	13695	13259
30°	14899	13050	12478
35°	14482	12389	11722
40°	14048	11678	10919
45°	13593	10965	10169
50°	13090	10275	9337
55°	12542	9467	8511
60°	11982	8583	7650
65°	11341	7671	6681
70°	10604	6572	5643
75°	9501	5298	4518
80°	8094	3829	3178
85°	6287	2132	1710

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13593 cd/sqm

TEST NUMBER: P1000837

CATALOG NUMBER: SA4XXDIP-B1195D1035UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.2	2.2
10°-20°	530.3	6.1
20°-30°	780.5	9.0
30°-40°	907.3	10.5
40°-50°	907.2	10.5
50°-60°	793.4	9.1
60°-70°	589.1	6.8
70°-80°	334.2	3.9
80°-90°	98.4	1.1
90°-100°	83.3	1.0
100°-110°	249.5	2.9
110°-120°	423.8	4.9
120°-130°	558.9	6.4
130°-140°	627.7	7.2
140°-150°	617.0	7.1
150°-160°	518.9	6.0
160°-170°	345.3	4.0
170°-180°	120.9	1.4
0°-30°	1499.1	17.3
0°-40°	2406.3	27.7
0°-60°	4107.0	47.3
0°-90°	5128.7	59.1
90°-120°	756.6	8.7
90°-150°	2560.2	29.5
90°-180°	3545.0	40.9
0°-180°	8674.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1997	1997	1997	1997	1997	
5°	1996	1989	1972	1989	1986	189
15°	1900	1893	1869	1879	1874	535
25°	1720	1709	1687	1688	1682	792
35°	1480	1469	1447	1435	1427	926
45°	1208	1197	1171	1154	1149	931
55°	914	909	886	867	858	818
65°	619	611	595	579	571	613
75°	330	322	314	307	306	350
85°	86	86	83	83	82	93
90°	3	14	22	28	30	10
95°	59	68	75	78	78	64
105°	230	231	235	238	241	244
115°	431	431	429	428	427	425
125°	628	628	626	624	623	559
135°	809	815	815	813	810	626
145°	983	987	988	987	984	615
155°	1126	1126	1126	1130	1126	518
165°	1226	1223	1221	1227	1223	346
175°	1276	1271	1270	1277	1270	121
180°	1278	1278	1278	1278	1278	

TEST NUMBER: P1000837

CATALOG NUMBER: SA4XXDIP-B1195D1035UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1997.1	1997.1	1997.1	1997.1	1997.1
2.5°	2003.5	1998.7	1981.1	1997.1	1995.5
5°	1995.5	1989.1	1971.5	1989.1	1985.9
7.5°	1981.1	1974.7	1955.5	1969.9	1968.3
10°	1960.3	1953.9	1933.1	1945.9	1942.7
12.5°	1933.1	1926.7	1904.3	1918.7	1913.9
15°	1899.5	1893.1	1869.1	1878.7	1873.9
17.5°	1861.1	1853.1	1830.7	1837.1	1833.9
20°	1817.9	1809.9	1785.9	1790.7	1787.5
22.5°	1771.5	1760.3	1736.3	1745.9	1739.5
25°	1720.3	1709.1	1686.7	1688.3	1681.9
27.5°	1662.7	1651.5	1630.7	1627.5	1619.5
30°	1605.1	1592.3	1571.5	1565.1	1557.1
32.5°	1544.2	1533.0	1510.6	1502.6	1494.6
35°	1480.2	1469.0	1446.6	1435.4	1427.4
37.5°	1413.0	1403.4	1379.4	1368.2	1357.0
40°	1347.4	1334.6	1310.6	1294.6	1286.6
42.5°	1277.0	1270.6	1243.4	1224.2	1219.4
45°	1208.2	1197.0	1171.4	1153.8	1149.0
47.5°	1136.2	1128.2	1104.2	1085.0	1072.2
50°	1062.6	1056.2	1033.8	1011.4	1001.8
52.5°	990.6	982.6	958.6	939.4	926.5
55°	913.7	908.9	886.5	867.3	857.7
57.5°	841.7	836.9	814.5	795.3	785.7
60°	766.5	758.5	737.7	723.3	715.3
62.5°	692.9	686.5	664.1	651.3	643.3
65°	619.3	611.3	595.3	579.3	571.3
67.5°	544.1	537.7	521.7	505.7	504.1
70°	475.3	464.1	451.3	438.5	433.7
72.5°	401.7	390.5	380.9	371.3	366.5
75°	329.7	321.7	313.7	307.2	305.6
77.5°	259.2	256.0	248.0	246.4	241.6
80°	196.8	192.0	188.8	185.6	184.0
82.5°	136.0	134.4	134.4	132.8	131.2
85°	86.4	86.4	83.2	83.2	81.6
87.5°	41.6	40.0	38.4	38.4	38.4
90°	3.0	13.8	21.7	27.7	29.6
92.5°	25.7	38.5	43.5	46.4	47.4
95°	59.3	68.2	75.1	78.1	78.1
97.5°	94.9	102.8	110.7	114.6	114.6
100°	138.3	142.3	151.2	153.2	153.2
102.5°	183.8	184.8	192.7	195.7	196.7
105°	230.3	231.2	235.2	238.2	241.1
107.5°	278.7	279.7	280.6	284.6	283.6
110°	328.1	330.1	329.1	327.1	330.1

TEST NUMBER: P1000837

CATALOG NUMBER: SA4XXDIP-B1195D1035UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	379.5	379.5	377.5	377.5	377.5
115°	430.9	430.9	428.9	427.9	426.9
117.5°	479.3	479.3	478.3	475.3	472.4
120°	527.7	531.7	528.7	523.7	525.7
122.5°	578.1	579.1	578.1	575.1	570.2
125°	627.5	627.5	626.5	624.5	622.6
127.5°	672.0	674.9	673.0	671.0	670.0
130°	719.4	722.4	722.4	720.4	716.4
132.5°	767.8	769.8	768.8	766.8	765.9
135°	809.3	815.3	815.3	813.3	810.3
137.5°	855.8	858.7	860.7	857.8	858.7
140°	902.2	904.2	904.2	903.2	902.2
142.5°	944.7	946.7	945.7	945.7	945.7
145°	983.3	987.2	988.2	987.2	984.2
147.5°	1022.8	1027.7	1026.7	1025.8	1024.8
150°	1058.4	1062.3	1062.3	1062.3	1061.3
152.5°	1092.0	1093.9	1094.9	1097.9	1094.9
155°	1126.5	1126.5	1125.6	1129.5	1125.6
157.5°	1156.2	1154.2	1154.2	1157.2	1154.2
160°	1181.9	1180.9	1179.9	1182.9	1177.9
162.5°	1205.6	1202.6	1201.7	1207.6	1202.6
165°	1226.4	1223.4	1221.4	1227.3	1223.4
167.5°	1243.2	1239.2	1239.2	1245.1	1239.2
170°	1257.0	1252.1	1253.0	1259.0	1252.1
172.5°	1266.9	1262.9	1262.9	1269.8	1262.9
175°	1275.8	1270.8	1269.8	1276.8	1269.8
177.5°	1279.7	1274.8	1274.8	1281.7	1273.8
180°	1277.7	1277.7	1277.7	1277.7	1277.7

(END OF REPORT)