

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001807

Luminaire Tested: SA4XXDIP-B795D1205UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001807
REPORT IS A COMBINATION OF REPORTS P996429 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1205UB40-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7697.6 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001807

CATALOG NUMBER: SA4XXDIP-B795D1205UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001807

CATALOG NUMBER: SA4XXDIP-B795D1205UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	92	88	85	88	85	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	38	36
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	73	63	55	49	67	58	51	45	48	43	39	39	36	33	31	29	26
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	26	23	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	27	22	19	21	18	16
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10821	10821	10821
5°	10830	10510	10523
10°	10738	10218	10146
15°	10584	9871	9722
20°	10387	9495	9283
25°	10166	9099	8810
30°	9899	8671	8291
35°	9623	8232	7789
40°	9335	7759	7255
45°	9032	7286	6756
50°	8697	6827	6204
55°	8334	6291	5655
60°	7961	5703	5084
65°	7536	5096	4439
70°	7045	4367	3750
75°	6311	3519	3003
80°	5380	2545	2113
85°	4177	1417	1136

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9032 cd/sqm

TEST NUMBER: P1001807

CATALOG NUMBER: SA4XXDIP-B795D1205UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	1.6
10°-20°	352.4	4.6
20°-30°	518.6	6.7
30°-40°	602.8	7.8
40°-50°	602.8	7.8
50°-60°	527.2	6.8
60°-70°	391.4	5.1
70°-80°	222.1	2.9
80°-90°	65.9	0.9
90°-100°	436.6	5.7
100°-110°	888.0	11.5
110°-120°	791.5	10.3
120°-130°	664.8	8.6
130°-140°	554.8	7.2
140°-150°	423.7	5.5
150°-160°	297.8	3.9
160°-170°	175.2	2.3
170°-180°	57.0	0.7
0°-30°	996.1	12.9
0°-40°	1598.9	20.8
0°-60°	2728.9	35.5
0°-90°	3408.3	44.3
90°-120°	2116.0	27.5
90°-150°	3759.4	48.8
90°-180°	4289.0	55.7
0°-180°	7697.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1327	1327	1327	1327	1327	
5°	1326	1322	1310	1322	1320	126
15°	1262	1258	1242	1248	1245	356
25°	1143	1136	1121	1122	1118	526
35°	984	976	961	954	948	615
45°	803	795	778	767	763	619
55°	607	604	589	576	570	544
65°	412	406	396	385	380	407
75°	219	214	208	204	203	232
85°	57	57	55	55	54	62
90°	1	9	21	23	24	6
95°	38	120	941	466	282	42
105°	135	196	758	1631	1625	144
115°	238	298	676	1298	1560	236
125°	331	394	672	1104	1245	295
135°	394	469	666	980	1113	304
145°	454	520	663	827	909	285
155°	516	557	644	730	761	238
165°	562	580	618	654	664	159
175°	587	588	592	600	598	56
180°	588	588	588	588	588	

TEST NUMBER: P1001807

CATALOG NUMBER: SA4XXDIP-B795D1205UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1327.0	1327.0	1327.0	1327.0	1327.0
2.5°	1331.3	1328.1	1316.4	1327.0	1325.9
5°	1325.9	1321.7	1310.0	1321.7	1319.6
7.5°	1316.4	1312.1	1299.4	1308.9	1307.9
10°	1302.5	1298.3	1284.5	1293.0	1290.8
12.5°	1284.5	1280.2	1265.3	1274.9	1271.7
15°	1262.1	1257.9	1241.9	1248.3	1245.1
17.5°	1236.6	1231.3	1216.4	1220.7	1218.5
20°	1207.9	1202.6	1186.6	1189.8	1187.7
22.5°	1177.1	1169.6	1153.7	1160.1	1155.8
25°	1143.0	1135.6	1120.7	1121.8	1117.5
27.5°	1104.8	1097.3	1083.5	1081.4	1076.1
30°	1066.5	1058.0	1044.2	1039.9	1034.6
32.5°	1026.1	1018.6	1003.8	998.4	993.1
35°	983.6	976.1	961.2	953.8	948.5
37.5°	938.9	932.5	916.6	909.1	901.7
40°	895.3	886.8	870.8	860.2	854.9
42.5°	848.5	844.3	826.2	813.4	810.2
45°	802.8	795.3	778.3	766.6	763.4
47.5°	754.9	749.6	733.7	720.9	712.4
50°	706.0	701.8	686.9	672.0	665.6
52.5°	658.2	652.9	636.9	624.2	615.7
55°	607.1	604.0	589.1	576.3	569.9
57.5°	559.3	556.1	541.2	528.5	522.1
60°	509.3	504.0	490.2	480.6	475.3
62.5°	460.4	456.2	441.3	432.8	427.4
65°	411.5	406.2	395.5	384.9	379.6
67.5°	361.5	357.3	346.6	336.0	334.9
70°	315.8	308.4	299.9	291.3	288.2
72.5°	266.9	259.4	253.1	246.7	243.5
75°	219.0	213.7	208.4	204.2	203.1
77.5°	172.3	170.1	164.8	163.7	160.6
80°	130.8	127.6	125.5	123.3	122.3
82.5°	90.4	89.3	89.3	88.3	87.2
85°	57.4	57.4	55.3	55.3	54.2
87.5°	27.6	26.6	25.5	25.5	25.5
90°	1.2	9.2	20.8	23.1	24.2
92.5°	16.2	88.9	452.6	149.6	105.1
95°	38.1	120.0	941.1	465.9	281.7
97.5°	63.5	132.8	1006.9	951.4	676.7
100°	87.8	150.1	928.4	1316.4	1058.9
102.5°	110.9	170.9	830.2	1545.0	1391.4
105°	135.1	195.8	757.5	1631.0	1624.7
107.5°	161.7	221.2	710.1	1605.0	1735.5
110°	188.2	246.5	688.2	1512.7	1737.8

TEST NUMBER: P1001807

CATALOG NUMBER: SA4XXDIP-B795D1205UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.6	271.9	677.8	1399.5	1669.7
115°	237.9	298.5	675.5	1297.9	1560.0
117.5°	263.3	323.4	674.3	1218.2	1452.6
120°	288.7	347.5	674.3	1164.5	1364.9
122.5°	311.8	371.2	673.2	1129.3	1295.6
125°	331.4	393.8	672.0	1104.4	1244.8
127.5°	349.9	414.6	669.7	1080.8	1212.4
130°	364.9	434.8	668.6	1052.5	1184.7
132.5°	379.9	452.1	667.4	1019.0	1153.5
135°	393.8	468.8	666.3	980.4	1113.1
137.5°	407.6	483.2	666.3	938.8	1065.8
140°	422.6	496.6	665.1	898.4	1013.8
142.5°	438.8	508.6	665.1	860.8	958.4
145°	453.8	519.6	662.8	826.8	908.8
147.5°	471.1	530.0	659.3	798.5	862.6
150°	487.3	539.8	655.9	772.5	824.5
152.5°	502.3	549.0	650.1	750.6	789.8
155°	516.2	557.2	644.3	729.8	760.9
157.5°	530.0	564.7	638.6	710.2	734.4
160°	542.7	571.0	631.6	690.5	710.1
162.5°	554.3	576.2	624.7	671.4	687.0
165°	562.3	579.7	617.8	654.2	664.0
167.5°	571.6	582.6	610.8	639.2	645.5
170°	577.4	584.8	603.9	624.1	628.2
172.5°	583.1	586.6	597.0	610.8	610.8
175°	586.6	587.7	592.4	600.4	598.1
177.5°	588.9	587.7	588.9	593.0	588.9
180°	587.7	587.7	587.7	587.7	587.7

(END OF REPORT)