

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001815

Luminaire Tested: SA4XXDIP-B795D1205UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001815
REPORT IS A COMBINATION OF REPORTS P996437 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1205UB50-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7301.0 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001815

CATALOG NUMBER: SA4XXDIP-B795D1205UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001815

CATALOG NUMBER: SA4XXDIP-B795D1205UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	45	44
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27
5	67	56	48	42	61	51	44	39	43	38	34	36	32	29	29	26	23
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16
9	49	37	30	25	45	35	28	23	29	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10462	10462	10462
5°	10470	10161	10174
10°	10382	9879	9810
15°	10233	9543	9399
20°	10043	9181	8975
25°	9829	8797	8518
30°	9571	8383	8016
35°	9303	7958	7531
40°	9025	7503	7014
45°	8733	7044	6532
50°	8409	6600	5998
55°	8058	6082	5467
60°	7697	5514	4915
65°	7285	4927	4292
70°	6811	4222	3625
75°	6104	3403	2904
80°	5199	2460	2042
85°	4039	1371	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8733 cd/sqm

TEST NUMBER: P1001815

CATALOG NUMBER: SA4XXDIP-B795D1205UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	1.7
10°-20°	340.7	4.7
20°-30°	501.4	6.9
30°-40°	582.8	8.0
40°-50°	582.8	8.0
50°-60°	509.7	7.0
60°-70°	378.4	5.2
70°-80°	214.7	2.9
80°-90°	64.6	0.9
90°-100°	94.1	1.3
100°-110°	281.8	3.9
110°-120°	478.7	6.6
120°-130°	631.4	8.6
130°-140°	709.1	9.7
140°-150°	697.0	9.5
150°-160°	586.2	8.0
160°-170°	390.0	5.3
170°-180°	136.6	1.9
0°-30°	963.0	13.2
0°-40°	1545.9	21.2
0°-60°	2638.4	36.1
0°-90°	3296.1	45.1
90°-120°	854.6	11.7
90°-150°	2892.1	39.6
90°-180°	4005.0	54.9
0°-180°	7301.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1283	1283	1283	1283	1283	
5°	1282	1278	1266	1278	1276	122
15°	1220	1216	1201	1207	1204	344
25°	1105	1098	1084	1085	1080	509
35°	951	944	929	922	917	595
45°	776	769	752	741	738	598
55°	587	584	570	557	551	526
65°	398	393	382	372	367	394
75°	212	207	202	197	196	225
85°	56	56	54	54	52	60
90°	3	16	25	31	34	9
95°	67	77	85	88	88	73
105°	260	261	266	269	272	276
115°	487	487	484	483	482	480
125°	709	709	708	706	703	632
135°	914	921	921	919	915	707
145°	1111	1115	1116	1115	1112	695
155°	1273	1273	1272	1276	1272	586
165°	1385	1382	1380	1386	1382	391
175°	1441	1436	1434	1442	1434	137
180°	1443	1443	1443	1443	1443	

TEST NUMBER: P1001815

CATALOG NUMBER: SA4XXDIP-B795D1205UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1283.0	1283.0	1283.0	1283.0	1283.0
2.5°	1287.1	1284.0	1272.7	1283.0	1281.9
5°	1281.9	1277.8	1266.5	1277.8	1275.8
7.5°	1272.7	1268.6	1256.2	1265.5	1264.5
10°	1259.3	1255.2	1241.9	1250.1	1248.0
12.5°	1241.9	1237.7	1223.3	1232.6	1229.5
15°	1220.3	1216.2	1200.7	1206.9	1203.8
17.5°	1195.6	1190.5	1176.1	1180.2	1178.1
20°	1167.8	1162.7	1147.3	1150.4	1148.3
22.5°	1138.0	1130.8	1115.4	1121.6	1117.5
25°	1105.1	1097.9	1083.5	1084.6	1080.5
27.5°	1068.1	1060.9	1047.6	1045.5	1040.4
30°	1031.1	1022.9	1009.5	1005.4	1000.3
32.5°	992.0	984.8	970.5	965.3	960.2
35°	950.9	943.7	929.3	922.1	917.0
37.5°	907.7	901.6	886.2	879.0	871.8
40°	865.6	857.4	842.0	831.7	826.5
42.5°	820.4	816.3	798.8	786.4	783.4
45°	776.2	769.0	752.5	741.2	738.1
47.5°	729.9	724.8	709.3	697.0	688.8
50°	682.6	678.5	664.1	649.7	643.5
52.5°	636.3	631.2	615.8	603.4	595.2
55°	587.0	583.9	569.5	557.2	551.0
57.5°	540.7	537.7	523.3	510.9	504.8
60°	492.4	487.3	473.9	464.7	459.5
62.5°	445.1	441.0	426.6	418.4	413.3
65°	397.8	392.7	382.4	372.1	367.0
67.5°	349.5	345.4	335.1	324.9	323.8
70°	305.3	298.1	289.9	281.7	278.6
72.5°	258.0	250.8	244.7	238.5	235.4
75°	211.8	206.6	201.5	197.4	196.4
77.5°	166.5	164.5	159.3	158.3	155.2
80°	126.4	123.4	121.3	119.3	118.2
82.5°	87.4	86.4	86.4	85.3	84.3
85°	55.5	55.5	53.5	53.5	52.4
87.5°	26.7	25.7	24.7	24.7	24.7
90°	3.3	15.6	24.6	31.3	33.5
92.5°	29.0	43.5	49.1	52.5	53.6
95°	67.0	77.0	84.8	88.2	88.2
97.5°	107.2	116.1	125.0	129.5	129.5
100°	156.3	160.8	170.8	173.0	173.0
102.5°	207.6	208.8	217.7	221.0	222.1
105°	260.1	261.2	265.7	269.0	272.4
107.5°	314.8	315.9	317.0	321.5	320.4
110°	370.6	372.9	371.7	369.5	372.9

TEST NUMBER: P1001815

CATALOG NUMBER: SA4XXDIP-B795D1205UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	428.7	428.7	426.4	426.4	426.4
115°	486.7	486.7	484.5	483.4	482.3
117.5°	541.4	541.4	540.3	537.0	533.6
120°	596.1	600.6	597.2	591.7	593.9
122.5°	653.0	654.2	653.0	649.7	644.1
125°	708.9	708.9	707.7	705.5	703.3
127.5°	759.1	762.4	760.2	758.0	756.9
130°	812.7	816.0	816.0	813.8	809.3
132.5°	867.4	869.6	868.5	866.3	865.1
135°	914.3	921.0	921.0	918.7	915.4
137.5°	966.7	970.1	972.3	969.0	970.1
140°	1019.2	1021.4	1021.4	1020.3	1019.2
142.5°	1067.2	1069.4	1068.3	1068.3	1068.3
145°	1110.7	1115.2	1116.3	1115.2	1111.9
147.5°	1155.4	1161.0	1159.9	1158.7	1157.6
150°	1195.6	1200.0	1200.0	1200.0	1198.9
152.5°	1233.5	1235.8	1236.9	1240.2	1236.9
155°	1272.6	1272.6	1271.5	1276.0	1271.5
157.5°	1306.1	1303.9	1303.9	1307.2	1303.9
160°	1335.1	1334.0	1332.9	1336.2	1330.7
162.5°	1361.9	1358.6	1357.4	1364.1	1358.6
165°	1385.4	1382.0	1379.8	1386.5	1382.0
167.5°	1404.3	1399.9	1399.9	1406.6	1399.9
170°	1420.0	1414.4	1415.5	1422.2	1414.4
172.5°	1431.1	1426.7	1426.7	1434.5	1426.7
175°	1441.2	1435.6	1434.5	1442.3	1434.5
177.5°	1445.6	1440.1	1440.1	1447.9	1438.9
180°	1443.4	1443.4	1443.4	1443.4	1443.4

(END OF REPORT)