

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001816

Luminaire Tested: SA4XXDIP-B795D1205UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001816
REPORT IS A COMBINATION OF REPORTS P996438 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D1205UB50-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7443.3 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001816

CATALOG NUMBER: SA4XXDIP-B795D1205UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001816

CATALOG NUMBER: SA4XXDIP-B795D1205UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	92	88	85	88	85	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	38	36
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	73	63	55	49	67	58	51	45	48	43	39	39	36	33	31	29	26
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	26	23	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	27	22	19	21	18	16
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10462	10462	10462
5°	10470	10161	10174
10°	10382	9879	9810
15°	10233	9543	9399
20°	10043	9181	8975
25°	9829	8797	8518
30°	9571	8383	8016
35°	9303	7958	7531
40°	9025	7503	7014
45°	8733	7044	6532
50°	8409	6600	5998
55°	8058	6082	5467
60°	7697	5514	4915
65°	7285	4927	4292
70°	6811	4222	3625
75°	6104	3403	2904
80°	5199	2460	2042
85°	4039	1371	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8733 cd/sqm

TEST NUMBER: P1001816

CATALOG NUMBER: SA4XXDIP-B795D1205UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	1.6
10°-20°	340.7	4.6
20°-30°	501.4	6.7
30°-40°	582.8	7.8
40°-50°	582.8	7.8
50°-60°	509.7	6.8
60°-70°	378.4	5.1
70°-80°	214.7	2.9
80°-90°	63.7	0.9
90°-100°	422.2	5.7
100°-110°	858.7	11.5
110°-120°	765.4	10.3
120°-130°	642.9	8.6
130°-140°	536.5	7.2
140°-150°	409.8	5.5
150°-160°	288.0	3.9
160°-170°	169.4	2.3
170°-180°	55.1	0.7
0°-30°	963.0	12.9
0°-40°	1545.9	20.8
0°-60°	2638.4	35.4
0°-90°	3295.2	44.3
90°-120°	2046.3	27.5
90°-150°	3635.6	48.8
90°-180°	4148.0	55.7
0°-180°	7443.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1283	1283	1283	1283	1283	
5°	1282	1278	1266	1278	1276	122
15°	1220	1216	1201	1207	1204	344
25°	1105	1098	1084	1085	1080	509
35°	951	944	929	922	917	595
45°	776	769	752	741	738	598
55°	587	584	570	557	551	526
65°	398	393	382	372	367	394
75°	212	207	202	197	196	225
85°	56	56	54	54	52	60
90°	1	9	20	22	24	6
95°	37	116	910	451	272	40
105°	131	189	732	1577	1571	139
115°	230	289	653	1255	1509	228
125°	320	381	650	1068	1204	286
135°	381	453	644	948	1076	294
145°	439	502	641	800	879	275
155°	499	539	623	706	736	230
165°	544	561	597	633	642	154
175°	567	568	573	581	578	54
180°	568	568	568	568	568	

TEST NUMBER: P1001816

CATALOG NUMBER: SA4XXDIP-B795D1205UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1283.0	1283.0	1283.0	1283.0	1283.0
2.5°	1287.1	1284.0	1272.7	1283.0	1281.9
5°	1281.9	1277.8	1266.5	1277.8	1275.8
7.5°	1272.7	1268.6	1256.2	1265.5	1264.5
10°	1259.3	1255.2	1241.9	1250.1	1248.0
12.5°	1241.9	1237.7	1223.3	1232.6	1229.5
15°	1220.3	1216.2	1200.7	1206.9	1203.8
17.5°	1195.6	1190.5	1176.1	1180.2	1178.1
20°	1167.8	1162.7	1147.3	1150.4	1148.3
22.5°	1138.0	1130.8	1115.4	1121.6	1117.5
25°	1105.1	1097.9	1083.5	1084.6	1080.5
27.5°	1068.1	1060.9	1047.6	1045.5	1040.4
30°	1031.1	1022.9	1009.5	1005.4	1000.3
32.5°	992.0	984.8	970.5	965.3	960.2
35°	950.9	943.7	929.3	922.1	917.0
37.5°	907.7	901.6	886.2	879.0	871.8
40°	865.6	857.4	842.0	831.7	826.5
42.5°	820.4	816.3	798.8	786.4	783.4
45°	776.2	769.0	752.5	741.2	738.1
47.5°	729.9	724.8	709.3	697.0	688.8
50°	682.6	678.5	664.1	649.7	643.5
52.5°	636.3	631.2	615.8	603.4	595.2
55°	587.0	583.9	569.5	557.2	551.0
57.5°	540.7	537.7	523.3	510.9	504.8
60°	492.4	487.3	473.9	464.7	459.5
62.5°	445.1	441.0	426.6	418.4	413.3
65°	397.8	392.7	382.4	372.1	367.0
67.5°	349.5	345.4	335.1	324.9	323.8
70°	305.3	298.1	289.9	281.7	278.6
72.5°	258.0	250.8	244.7	238.5	235.4
75°	211.8	206.6	201.5	197.4	196.4
77.5°	166.5	164.5	159.3	158.3	155.2
80°	126.4	123.4	121.3	119.3	118.2
82.5°	87.4	86.4	86.4	85.3	84.3
85°	55.5	55.5	53.5	53.5	52.4
87.5°	26.7	25.7	24.7	24.7	24.7
90°	1.1	8.9	20.1	22.3	23.5
92.5°	15.6	86.0	437.7	144.6	101.6
95°	36.9	116.2	910.1	450.6	272.5
97.5°	61.4	128.4	973.8	920.2	654.4
100°	84.9	145.2	897.8	1273.0	1024.0
102.5°	107.2	165.2	802.9	1494.2	1345.6
105°	130.7	189.3	732.5	1577.3	1571.2
107.5°	156.3	213.8	686.8	1552.2	1678.4
110°	182.0	238.4	665.5	1462.8	1680.6

TEST NUMBER: P1001816

CATALOG NUMBER: SA4XXDIP-B795D1205UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	206.6	263.0	655.5	1353.4	1614.7
115°	230.0	288.6	653.3	1255.2	1508.6
117.5°	254.6	312.6	652.1	1178.1	1404.8
120°	279.2	336.2	652.1	1126.2	1319.9
122.5°	301.5	359.0	651.0	1092.1	1252.9
125°	320.5	380.8	649.9	1068.1	1203.8
127.5°	338.4	400.9	647.7	1045.2	1172.5
130°	352.9	420.4	646.6	1017.9	1145.7
132.5°	367.4	437.2	645.4	985.5	1115.6
135°	380.8	453.4	644.3	948.1	1076.5
137.5°	394.2	467.4	644.3	907.9	1030.7
140°	408.7	480.2	643.2	868.8	980.5
142.5°	424.3	491.9	643.2	832.4	926.9
145°	438.9	502.5	641.0	799.6	878.8
147.5°	455.6	512.6	637.6	772.2	834.2
150°	471.2	522.0	634.3	747.0	797.3
152.5°	485.8	531.0	628.7	725.8	763.8
155°	499.2	538.8	623.1	705.7	735.9
157.5°	512.6	546.1	617.5	686.8	710.2
160°	524.8	552.2	610.8	667.8	686.8
162.5°	536.0	557.2	604.1	649.3	664.4
165°	543.8	560.6	597.4	632.6	642.1
167.5°	552.8	563.4	590.7	618.1	624.2
170°	558.3	565.6	584.0	603.6	607.5
172.5°	563.9	567.3	577.3	590.7	590.7
175°	567.3	568.4	572.9	580.7	578.4
177.5°	569.5	568.4	569.5	573.4	569.5
180°	568.4	568.4	568.4	568.4	568.4

(END OF REPORT)