

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001845

Luminaire Tested: SA4XXDIP-B795D365UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001845
REPORT IS A COMBINATION OF REPORTS P996470 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB30-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4701.1 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001845

CATALOG NUMBER: SA4XXDIP-B795D365UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001845

CATALOG NUMBER: SA4XXDIP-B795D365UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	93	90	87	84	82	79	76	74	72	68	67	65
2	94	86	80	74	89	82	76	71	74	69	65	67	63	60	60	57	55
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35
6	66	54	45	39	63	51	44	38	47	41	36	43	37	33	39	34	31
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10881	10881	10881
5°	10890	10568	10581
10°	10798	10275	10203
15°	10643	9926	9777
20°	10445	9549	9334
25°	10223	9150	8859
30°	9954	8719	8338
35°	9676	8278	7833
40°	9387	7803	7296
45°	9083	7327	6794
50°	8747	6865	6238
55°	8380	6326	5687
60°	8007	5735	5111
65°	7578	5126	4464
70°	7086	4390	3770
75°	6349	3540	3019
80°	5408	2559	2125
85°	4199	1425	1142

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9083 cd/sqm

TEST NUMBER: P1001845

CATALOG NUMBER: SA4XXDIP-B795D365UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.8	2.7
10°-20°	354.3	7.5
20°-30°	521.5	11.1
30°-40°	606.2	12.9
40°-50°	606.2	12.9
50°-60°	530.2	11.3
60°-70°	393.6	8.4
70°-80°	223.3	4.8
80°-90°	64.9	1.4
90°-100°	30.0	0.6
100°-110°	89.7	1.9
110°-120°	152.4	3.2
120°-130°	201.0	4.3
130°-140°	225.8	4.8
140°-150°	221.9	4.7
150°-160°	186.6	4.0
160°-170°	124.2	2.6
170°-180°	43.5	0.9
0°-30°	1001.6	21.3
0°-40°	1607.8	34.2
0°-60°	2744.1	58.4
0°-90°	3426.0	72.9
90°-120°	272.1	5.8
90°-150°	920.8	19.6
90°-180°	1275.0	27.1
0°-180°	4701.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1334	1334	1334	1334	1334	
5°	1333	1329	1317	1329	1327	127
15°	1269	1265	1249	1255	1252	358
25°	1149	1142	1127	1128	1124	529
35°	989	982	967	959	954	618
45°	807	800	783	771	768	622
55°	610	607	592	580	573	547
65°	414	408	398	387	382	410
75°	220	215	210	205	204	234
85°	58	58	56	56	54	62
90°	1	5	8	10	11	5
95°	21	24	27	28	28	23
105°	83	83	85	86	87	88
115°	155	155	154	154	154	153
125°	226	226	225	225	224	201
135°	291	293	293	292	291	225
145°	354	355	355	355	354	221
155°	405	405	405	406	405	186
165°	441	440	439	441	440	124
175°	459	457	457	459	457	44
180°	460	460	460	460	460	

TEST NUMBER: P1001845

CATALOG NUMBER: SA4XXDIP-B795D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1334.4	1334.4	1334.4	1334.4	1334.4
2.5°	1338.7	1335.5	1323.7	1334.4	1333.3
5°	1333.3	1329.1	1317.3	1329.1	1326.9
7.5°	1323.7	1319.4	1306.6	1316.2	1315.2
10°	1309.8	1305.5	1291.6	1300.2	1298.0
12.5°	1291.6	1287.4	1272.4	1282.0	1278.8
15°	1269.2	1264.9	1248.9	1255.3	1252.1
17.5°	1243.5	1238.2	1223.2	1227.5	1225.3
20°	1214.6	1209.3	1193.3	1196.5	1194.3
22.5°	1183.6	1176.2	1160.1	1166.5	1162.3
25°	1149.4	1141.9	1127.0	1128.0	1123.8
27.5°	1110.9	1103.4	1089.5	1087.4	1082.1
30°	1072.4	1063.9	1050.0	1045.7	1040.4
32.5°	1031.8	1024.3	1009.4	1004.0	998.7
35°	989.0	981.6	966.6	959.1	953.8
37.5°	944.1	937.7	921.7	914.2	906.7
40°	900.3	891.7	875.7	865.0	859.7
42.5°	853.2	849.0	830.8	818.0	814.8
45°	807.3	799.8	782.7	770.9	767.7
47.5°	759.2	753.8	737.8	724.9	716.4
50°	710.0	705.7	690.7	675.8	669.3
52.5°	661.9	656.5	640.5	627.6	619.1
55°	610.5	607.3	592.4	579.5	573.1
57.5°	562.4	559.2	544.2	531.4	525.0
60°	512.2	506.8	492.9	483.3	477.9
62.5°	463.0	458.7	443.7	435.2	429.8
65°	413.8	408.4	397.8	387.1	381.7
67.5°	363.5	359.3	348.6	337.9	336.8
70°	317.6	310.1	301.5	293.0	289.8
72.5°	268.4	260.9	254.5	248.1	244.9
75°	220.3	214.9	209.6	205.3	204.2
77.5°	173.2	171.1	165.7	164.7	161.5
80°	131.5	128.3	126.2	124.0	123.0
82.5°	90.9	89.8	89.8	88.7	87.7
85°	57.7	57.7	55.6	55.6	54.5
87.5°	27.8	26.7	25.7	25.7	25.7
90°	1.1	5.0	7.8	10.0	10.7
92.5°	9.2	13.9	15.6	16.7	17.1
95°	21.3	24.5	27.0	28.1	28.1
97.5°	34.1	37.0	39.8	41.2	41.2
100°	49.8	51.2	54.4	55.1	55.1
102.5°	66.1	66.5	69.3	70.4	70.7
105°	82.8	83.2	84.6	85.7	86.7
107.5°	100.2	100.6	100.9	102.4	102.0
110°	118.0	118.7	118.3	117.6	118.7

TEST NUMBER: P1001845

CATALOG NUMBER: SA4XXDIP-B795D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	136.5	136.5	135.8	135.8	135.8
115°	155.0	155.0	154.2	153.9	153.5
117.5°	172.4	172.4	172.0	170.9	169.9
120°	189.8	191.2	190.1	188.4	189.1
122.5°	207.9	208.3	207.9	206.8	205.1
125°	225.7	225.7	225.3	224.6	223.9
127.5°	241.7	242.7	242.0	241.3	241.0
130°	258.7	259.8	259.8	259.1	257.7
132.5°	276.1	276.9	276.5	275.8	275.4
135°	291.1	293.2	293.2	292.5	291.4
137.5°	307.8	308.8	309.5	308.5	308.8
140°	324.5	325.2	325.2	324.8	324.5
142.5°	339.8	340.5	340.1	340.1	340.1
145°	353.6	355.0	355.4	355.0	354.0
147.5°	367.8	369.6	369.3	368.9	368.5
150°	380.6	382.1	382.1	382.1	381.7
152.5°	392.7	393.4	393.8	394.8	393.8
155°	405.2	405.2	404.8	406.2	404.8
157.5°	415.8	415.1	415.1	416.2	415.1
160°	425.1	424.7	424.3	425.4	423.6
162.5°	433.6	432.5	432.2	434.3	432.5
165°	441.0	440.0	439.3	441.4	440.0
167.5°	447.1	445.7	445.7	447.8	445.7
170°	452.1	450.3	450.6	452.8	450.3
172.5°	455.6	454.2	454.2	456.7	454.2
175°	458.8	457.0	456.7	459.2	456.7
177.5°	460.2	458.5	458.5	460.9	458.1
180°	459.5	459.5	459.5	459.5	459.5

(END OF REPORT)