

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000852

Luminaire Tested: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000852
REPORT IS A COMBINATION OF REPORTS P995465 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8373.0 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000852

CATALOG NUMBER: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1000852

CATALOG NUMBER: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	97	93	88	84	90	86	82	79	73	70	68	62	59	58	51	49	48
2	88	80	74	68	81	74	69	64	63	59	55	53	50	47	44	42	40
3	80	70	62	56	74	65	58	53	56	50	46	47	43	39	39	36	33
4	73	62	54	47	67	57	50	44	49	43	39	41	37	33	34	31	28
5	67	55	46	40	62	51	44	38	44	38	33	37	32	29	31	27	24
6	62	49	41	35	57	46	38	33	39	33	29	33	29	25	28	24	21
7	57	44	36	30	53	41	34	29	36	30	25	30	26	22	25	22	19
8	53	40	32	27	49	38	30	25	32	27	22	28	23	20	23	20	17
9	49	37	29	24	46	34	27	22	30	24	20	25	21	18	21	18	15
10	46	34	26	21	43	31	25	20	27	22	18	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11588	11588	11588
5°	11620	11286	11307
10°	11545	11064	11033
15°	11437	10814	10723
20°	11277	10544	10422
25°	11096	10246	10099
30°	10901	9951	9769
35°	10681	9649	9474
40°	10502	9359	9170
45°	10241	9087	8901
50°	10018	8778	8617
55°	9786	8480	8290
60°	9428	8109	7982
65°	9034	7709	7612
70°	8556	7253	7184
75°	7887	6745	6776
80°	7136	6228	6350
85°	6134	5709	6003

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10241 cd/sqm

TEST NUMBER: P1000852

CATALOG NUMBER: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.6	1.6
10°-20°	385.8	4.6
20°-30°	583.3	7.0
30°-40°	705.7	8.4
40°-50°	746.0	8.9
50°-60°	702.1	8.4
60°-70°	582.6	7.0
70°-80°	408.9	4.9
80°-90°	233.2	2.8
90°-100°	220.0	2.6
100°-110°	349.7	4.2
110°-120°	489.6	5.8
120°-130°	594.2	7.1
130°-140°	640.8	7.7
140°-150°	616.8	7.4
150°-160°	516.0	6.2
160°-170°	343.3	4.1
170°-180°	120.2	1.4
0°-30°	1103.7	13.2
0°-40°	1809.5	21.6
0°-60°	3257.6	38.9
0°-90°	4482.3	53.5
90°-120°	1059.3	12.7
90°-150°	2911.1	34.8
90°-180°	3891.0	46.5
0°-180°	8373.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1421	1421	1421	1421	1421	
5°	1423	1418	1407	1420	1418	135
15°	1364	1365	1361	1375	1373	384
25°	1248	1257	1262	1279	1281	575
35°	1092	1111	1127	1149	1154	684
45°	910	940	971	998	1006	704
55°	713	746	794	826	836	635
65°	493	544	598	638	651	489
75°	274	333	399	444	458	291
85°	84	151	223	270	286	88
90°	28	103	179	231	246	22
95°	80	141	213	259	273	80
105°	243	276	339	382	397	259
115°	438	452	501	535	545	433
125°	630	629	668	696	703	562
135°	808	814	825	848	855	626
145°	979	982	983	991	995	613
155°	1120	1120	1119	1123	1119	516
165°	1219	1216	1214	1220	1216	344
175°	1269	1264	1263	1270	1263	120
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1000852

CATALOG NUMBER: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1421.1	1421.1	1421.1	1421.1	1421.1
2.5°	1427.4	1422.7	1409.9	1421.1	1419.5
5°	1422.7	1417.9	1406.7	1419.5	1417.9
7.5°	1413.1	1409.9	1400.4	1414.7	1413.1
10°	1400.4	1398.8	1390.8	1405.2	1403.6
12.5°	1382.9	1382.9	1378.1	1390.8	1390.8
15°	1363.8	1365.4	1360.6	1374.9	1373.3
17.5°	1338.3	1343.1	1341.5	1355.8	1354.2
20°	1311.3	1316.0	1317.6	1333.5	1333.5
22.5°	1281.0	1287.4	1290.6	1306.5	1309.7
25°	1247.6	1257.2	1261.9	1279.4	1281.0
27.5°	1211.0	1225.3	1231.7	1247.6	1249.2
30°	1174.4	1187.1	1198.3	1215.8	1219.0
32.5°	1134.6	1150.5	1163.3	1184.0	1187.1
35°	1091.7	1110.8	1126.7	1148.9	1153.7
37.5°	1048.7	1071.0	1090.1	1112.3	1117.1
40°	1007.3	1028.0	1050.3	1074.2	1080.5
42.5°	959.6	983.4	1010.5	1037.6	1042.3
45°	910.2	940.5	970.7	997.8	1005.7
47.5°	864.1	894.3	929.3	956.4	965.9
50°	813.2	848.2	883.2	915.0	924.6
52.5°	762.3	797.3	838.6	870.5	880.0
55°	712.9	746.3	794.1	825.9	835.5
57.5°	657.2	698.6	744.7	782.9	790.9
60°	603.1	644.5	697.0	733.6	746.3
62.5°	550.6	596.8	649.3	685.9	698.6
65°	493.3	544.2	598.3	638.1	650.9
67.5°	439.2	493.3	550.6	590.4	603.1
70°	383.5	437.6	498.1	541.1	552.2
72.5°	329.4	385.1	450.3	491.7	504.5
75°	273.7	332.6	399.4	444.0	458.3
77.5°	221.2	283.3	353.3	397.8	413.7
80°	173.5	237.1	307.1	354.9	367.6
82.5°	125.7	192.6	262.6	311.9	326.2
85°	84.3	151.2	222.8	270.5	286.4
87.5°	52.5	117.8	187.8	233.9	248.2
90°	28.4	102.9	179.1	231.2	245.9
92.5°	49.4	117.9	191.2	238.8	252.5
95°	79.7	141.0	213.1	259.0	273.3
97.5°	113.4	167.4	240.6	285.9	300.2
100°	155.1	200.4	271.2	316.2	327.3
102.5°	200.3	236.3	304.6	349.0	362.6
105°	243.3	276.0	338.9	381.6	397.3
107.5°	291.4	319.5	376.2	419.9	430.0
110°	338.9	363.2	417.9	452.6	468.2

TEST NUMBER: P1000852

CATALOG NUMBER: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	388.4	407.5	458.1	493.2	505.9
115°	437.9	452.3	501.3	535.3	545.4
117.5°	486.1	495.7	542.4	572.9	582.7
120°	532.7	541.4	584.6	611.5	626.2
122.5°	582.8	583.8	625.7	654.6	660.9
125°	630.4	628.8	667.6	695.8	703.4
127.5°	674.6	675.9	705.8	732.4	742.6
130°	720.2	721.5	746.9	773.6	779.2
132.5°	768.3	768.7	786.8	811.8	820.4
135°	808.0	813.9	825.0	848.5	855.1
137.5°	854.2	855.5	863.9	884.7	893.7
140°	900.3	900.7	902.3	922.0	928.9
142.5°	941.0	943.0	940.4	957.9	964.3
145°	979.3	981.6	982.6	991.1	994.6
147.5°	1018.6	1021.9	1021.0	1021.6	1027.0
150°	1054.0	1056.3	1056.3	1056.3	1055.3
152.5°	1085.8	1087.8	1088.8	1091.7	1088.8
155°	1120.2	1120.2	1119.2	1123.1	1119.2
157.5°	1149.7	1147.7	1147.7	1150.7	1147.7
160°	1175.2	1174.2	1173.3	1176.2	1171.3
162.5°	1198.8	1195.9	1194.9	1200.8	1195.9
165°	1219.4	1216.5	1214.5	1220.4	1216.5
167.5°	1236.1	1232.2	1232.2	1238.1	1232.2
170°	1249.9	1245.0	1246.0	1251.9	1245.0
172.5°	1259.7	1255.8	1255.8	1262.7	1255.8
175°	1268.6	1263.7	1262.7	1269.6	1262.7
177.5°	1272.5	1267.6	1267.6	1274.5	1266.6
180°	1270.5	1270.5	1270.5	1270.5	1270.5

(END OF REPORT)