

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001851

Luminaire Tested: SA4XXDIP-B795D365UB35-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001851
REPORT IS A COMBINATION OF REPORTS P996476 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB35-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4552.0 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001851

CATALOG NUMBER: SA4XXDIP-B795D365UB35-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001851

CATALOG NUMBER: SA4XXDIP-B795D365UB35-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71
1	100	95	91	87	94	90	86	82	79	76	73	70	67	65	61	59	58
2	91	82	75	70	85	78	71	66	69	64	60	60	57	53	53	50	47
3	82	72	64	57	77	68	61	55	60	54	50	53	48	45	46	43	40
4	75	63	55	48	70	60	52	46	53	47	42	47	42	38	41	37	34
5	69	56	48	41	64	53	45	39	47	41	36	42	37	33	37	33	29
6	63	51	42	36	59	48	40	34	43	36	31	38	32	28	33	29	26
7	59	46	37	31	55	43	35	30	39	32	27	34	29	25	30	26	23
8	54	41	33	28	51	39	32	26	35	29	24	31	26	22	28	23	20
9	51	38	30	25	48	36	29	24	32	26	22	29	24	20	26	21	18
10	47	35	27	22	45	33	26	21	30	24	20	27	22	18	24	20	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7821	7821	7821
5°	7843	7617	7631
10°	7791	7467	7446
15°	7718	7299	7237
20°	7611	7116	7034
25°	7489	6915	6816
30°	7357	6715	6593
35°	7208	6512	6395
40°	7089	6317	6190
45°	6911	6133	6008
50°	6761	5924	5816
55°	6605	5723	5595
60°	6364	5473	5387
65°	6097	5203	5138
70°	5774	4896	4849
75°	5323	4553	4573
80°	4816	4204	4286
85°	4141	3854	4052

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6911 cd/sqm

TEST NUMBER: P1001851

CATALOG NUMBER: SA4XXDIP-B795D365UB35-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	2.0
10°-20°	260.4	5.7
20°-30°	393.7	8.6
30°-40°	476.3	10.5
40°-50°	503.5	11.1
50°-60°	473.9	10.4
60°-70°	393.2	8.6
70°-80°	276.0	6.1
80°-90°	156.6	3.4
90°-100°	122.7	2.7
100°-110°	158.7	3.5
110°-120°	199.1	4.4
120°-130°	227.9	5.0
130°-140°	238.0	5.2
140°-150°	225.2	4.9
150°-160°	187.5	4.1
160°-170°	124.8	2.7
170°-180°	43.7	1.0
0°-30°	744.9	16.4
0°-40°	1221.2	26.8
0°-60°	2198.6	48.3
0°-90°	3024.4	66.4
90°-120°	480.6	10.6
90°-150°	1171.6	25.7
90°-180°	1528.0	33.6
0°-180°	4552.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	959	959	959	959	959	
5°	960	957	949	958	957	91
15°	920	922	918	928	927	259
25°	842	848	852	864	865	388
35°	737	750	760	776	779	461
45°	614	635	655	673	679	475
55°	481	504	536	557	564	429
65°	333	367	404	431	439	330
75°	185	224	270	300	309	196
85°	57	102	150	183	193	59
90°	18	65	114	148	157	13
95°	35	74	120	151	160	34
105°	93	115	156	184	193	99
115°	162	172	206	229	236	160
125°	231	230	256	276	282	206
135°	294	297	304	321	326	228
145°	356	357	357	363	366	223
155°	407	407	407	408	407	187
165°	443	442	441	444	442	125
175°	461	459	459	461	459	44
180°	462	462	462	462	462	

TEST NUMBER: P1001851

CATALOG NUMBER: SA4XXDIP-B795D365UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	959.1	959.1	959.1	959.1	959.1
2.5°	963.4	960.2	951.6	959.1	958.0
5°	960.2	957.0	949.4	958.0	957.0
7.5°	953.7	951.6	945.1	954.8	953.7
10°	945.1	944.1	938.7	948.4	947.3
12.5°	933.3	933.3	930.1	938.7	938.7
15°	920.4	921.5	918.3	928.0	926.9
17.5°	903.3	906.5	905.4	915.1	914.0
20°	885.0	888.2	889.3	900.0	900.0
22.5°	864.6	868.9	871.0	881.8	883.9
25°	842.0	848.5	851.7	863.5	864.6
27.5°	817.3	827.0	831.3	842.0	843.1
30°	792.6	801.2	808.7	820.6	822.7
32.5°	765.8	776.5	785.1	799.1	801.2
35°	736.8	749.7	760.4	775.5	778.7
37.5°	707.8	722.8	735.7	750.7	754.0
40°	679.9	693.8	708.9	725.0	729.3
42.5°	647.6	663.8	682.0	700.3	703.5
45°	614.3	634.8	655.2	673.4	678.8
47.5°	583.2	603.6	627.2	645.5	651.9
50°	548.8	572.5	596.1	617.6	624.0
52.5°	514.5	538.1	566.0	587.5	593.9
55°	481.2	503.7	535.9	557.4	563.9
57.5°	443.6	471.5	502.6	528.4	533.8
60°	407.1	435.0	470.4	495.1	503.7
62.5°	371.6	402.8	438.2	462.9	471.5
65°	332.9	367.3	403.8	430.7	439.3
67.5°	296.4	332.9	371.6	398.5	407.1
70°	258.8	295.4	336.2	365.2	372.7
72.5°	222.3	259.9	304.0	331.9	340.5
75°	184.7	224.5	269.6	299.7	309.3
77.5°	149.3	191.2	238.4	268.5	279.2
80°	117.1	160.0	207.3	239.5	248.1
82.5°	84.8	130.0	177.2	210.5	220.2
85°	56.9	102.0	150.4	182.6	193.3
87.5°	35.4	79.5	126.7	157.9	167.5
90°	18.3	65.1	114.2	147.5	156.8
92.5°	25.4	67.6	115.6	146.8	155.7
95°	35.4	74.0	120.5	150.6	160.3
97.5°	47.2	81.1	128.1	157.4	167.1
100°	61.8	91.1	136.2	165.9	173.4
102.5°	78.2	102.2	145.9	174.9	183.9
105°	92.9	114.7	155.9	183.8	193.4
107.5°	110.4	128.9	166.9	195.2	202.4
110°	127.1	142.9	180.1	204.1	213.8



TEST NUMBER: P1001851

CATALOG NUMBER: SA4XXDIP-B795D365UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	144.6	157.5	192.2	215.9	224.5
115°	162.1	171.8	205.5	228.7	235.9
117.5°	179.6	186.1	217.9	239.4	247.0
120°	196.1	200.7	230.7	250.4	259.8
122.5°	214.3	214.6	243.3	263.6	269.4
125°	231.0	229.9	256.5	276.2	281.9
127.5°	247.1	247.1	267.9	286.4	293.7
130°	263.1	263.1	280.3	299.0	304.0
132.5°	280.6	280.3	292.8	310.4	316.4
135°	294.5	296.7	304.3	320.8	326.1
137.5°	311.3	311.4	316.4	331.4	337.2
140°	328.1	327.8	328.8	342.5	347.5
142.5°	342.5	343.2	341.7	353.5	357.8
145°	356.4	356.7	357.1	363.1	366.3
147.5°	370.7	371.3	371.0	371.7	375.7
150°	383.5	383.8	383.8	383.8	383.5
152.5°	394.6	395.3	395.6	396.7	395.6
155°	407.1	407.1	406.7	408.1	406.7
157.5°	417.8	417.1	417.1	418.1	417.1
160°	427.1	426.7	426.3	427.4	425.6
162.5°	435.6	434.6	434.2	436.3	434.6
165°	443.1	442.0	441.3	443.5	442.0
167.5°	449.2	447.8	447.8	449.9	447.8
170°	454.2	452.4	452.8	454.9	452.4
172.5°	457.8	456.3	456.3	458.8	456.3
175°	461.0	459.2	458.8	461.3	458.8
177.5°	462.4	460.6	460.6	463.1	460.3
180°	461.7	461.7	461.7	461.7	461.7

(END OF REPORT)