

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000853

Luminaire Tested: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-D4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000853
REPORT IS A COMBINATION OF REPORTS P995466 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8497.3 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000853

CATALOG NUMBER: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1000853

CATALOG NUMBER: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	97	93	88	84	90	86	82	79	73	70	68	61	59	57	50	49	47
2	88	80	74	68	81	74	68	64	63	59	55	53	50	47	43	41	39
3	80	70	62	56	74	65	58	53	55	50	46	46	42	39	38	35	33
4	73	62	53	47	67	57	50	44	49	43	39	41	37	33	34	31	28
5	67	55	46	40	62	51	43	38	44	38	33	37	32	29	30	27	24
6	62	49	41	35	57	46	38	33	39	33	29	33	28	25	27	24	21
7	57	44	36	30	52	41	34	29	35	30	25	30	25	22	25	21	19
8	53	40	32	27	49	37	30	25	32	26	22	27	23	19	23	19	17
9	49	37	29	24	45	34	27	22	30	24	20	25	21	17	21	18	15
10	46	34	26	21	42	31	25	20	27	22	18	23	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11588	11588	11588
5°	11620	11286	11307
10°	11545	11064	11033
15°	11437	10814	10723
20°	11277	10544	10422
25°	11096	10246	10099
30°	10901	9951	9769
35°	10681	9649	9474
40°	10502	9359	9170
45°	10241	9087	8901
50°	10018	8778	8617
55°	9786	8480	8290
60°	9428	8109	7982
65°	9034	7709	7612
70°	8556	7253	7184
75°	7887	6745	6776
80°	7136	6228	6350
85°	6134	5709	6003

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10241 cd/sqm

TEST NUMBER: P1000853

CATALOG NUMBER: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.6	1.6
10°-20°	385.8	4.5
20°-30°	583.3	6.9
30°-40°	705.7	8.3
40°-50°	746.0	8.8
50°-60°	702.1	8.3
60°-70°	582.6	6.9
70°-80°	408.9	4.8
80°-90°	232.4	2.7
90°-100°	508.8	6.0
100°-110°	857.3	10.1
110°-120°	741.8	8.7
120°-130°	604.2	7.1
130°-140°	488.8	5.8
140°-150°	363.9	4.3
150°-160°	253.5	3.0
160°-170°	149.1	1.8
170°-180°	48.5	0.6
0°-30°	1103.7	13.0
0°-40°	1809.5	21.3
0°-60°	3257.6	38.3
0°-90°	4481.6	52.7
90°-120°	2107.8	24.8
90°-150°	3564.7	42.0
90°-180°	4016.0	47.3
0°-180°	8497.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1421	1421	1421	1421	1421	
5°	1423	1418	1407	1420	1418	135
15°	1364	1365	1361	1375	1373	384
25°	1248	1257	1262	1279	1281	575
35°	1092	1111	1127	1149	1154	684
45°	910	940	971	998	1006	704
55°	713	746	794	826	836	635
65°	493	544	598	638	651	489
75°	274	333	399	444	458	291
85°	84	151	223	270	286	88
90°	26	97	175	223	237	20
95°	53	175	939	578	436	52
105°	129	213	750	1533	1540	139
115°	212	278	650	1214	1448	211
125°	288	340	616	1015	1144	257
135°	338	402	581	874	997	262
145°	388	442	564	713	789	244
155°	439	474	548	621	648	203
165°	479	493	526	557	565	135
175°	499	500	504	511	509	47
180°	500	500	500	500	500	

TEST NUMBER: P1000853

CATALOG NUMBER: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1421.1	1421.1	1421.1	1421.1	1421.1
2.5°	1427.4	1422.7	1409.9	1421.1	1419.5
5°	1422.7	1417.9	1406.7	1419.5	1417.9
7.5°	1413.1	1409.9	1400.4	1414.7	1413.1
10°	1400.4	1398.8	1390.8	1405.2	1403.6
12.5°	1382.9	1382.9	1378.1	1390.8	1390.8
15°	1363.8	1365.4	1360.6	1374.9	1373.3
17.5°	1338.3	1343.1	1341.5	1355.8	1354.2
20°	1311.3	1316.0	1317.6	1333.5	1333.5
22.5°	1281.0	1287.4	1290.6	1306.5	1309.7
25°	1247.6	1257.2	1261.9	1279.4	1281.0
27.5°	1211.0	1225.3	1231.7	1247.6	1249.2
30°	1174.4	1187.1	1198.3	1215.8	1219.0
32.5°	1134.6	1150.5	1163.3	1184.0	1187.1
35°	1091.7	1110.8	1126.7	1148.9	1153.7
37.5°	1048.7	1071.0	1090.1	1112.3	1117.1
40°	1007.3	1028.0	1050.3	1074.2	1080.5
42.5°	959.6	983.4	1010.5	1037.6	1042.3
45°	910.2	940.5	970.7	997.8	1005.7
47.5°	864.1	894.3	929.3	956.4	965.9
50°	813.2	848.2	883.2	915.0	924.6
52.5°	762.3	797.3	838.6	870.5	880.0
55°	712.9	746.3	794.1	825.9	835.5
57.5°	657.2	698.6	744.7	782.9	790.9
60°	603.1	644.5	697.0	733.6	746.3
62.5°	550.6	596.8	649.3	685.9	698.6
65°	493.3	544.2	598.3	638.1	650.9
67.5°	439.2	493.3	550.6	590.4	603.1
70°	383.5	437.6	498.1	541.1	552.2
72.5°	329.4	385.1	450.3	491.7	504.5
75°	273.7	332.6	399.4	444.0	458.3
77.5°	221.2	283.3	353.3	397.8	413.7
80°	173.5	237.1	307.1	354.9	367.6
82.5°	125.7	192.6	262.6	311.9	326.2
85°	84.3	151.2	222.8	270.5	286.4
87.5°	52.5	117.8	187.8	233.9	248.2
90°	26.5	97.0	175.2	223.4	237.0
92.5°	37.7	155.2	533.2	319.8	294.7
95°	53.1	175.4	939.3	577.9	435.5
97.5°	73.1	178.2	987.4	981.6	762.1
100°	92.2	186.6	911.0	1284.2	1076.1
102.5°	111.8	198.0	819.6	1469.2	1351.3
105°	129.3	212.6	749.6	1532.9	1540.2
107.5°	151.9	229.6	701.5	1502.9	1625.0
110°	172.9	244.8	676.4	1414.6	1619.0

TEST NUMBER: P1000853

CATALOG NUMBER: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	192.9	261.6	659.5	1308.8	1551.5
115°	211.9	278.0	649.7	1214.4	1448.5
117.5°	233.6	294.2	640.7	1137.0	1349.2
120°	253.7	308.4	632.8	1081.8	1264.9
122.5°	273.3	324.0	623.8	1043.8	1196.5
125°	288.4	339.9	616.5	1014.8	1143.6
127.5°	304.2	357.6	606.6	985.0	1108.2
130°	315.3	373.2	597.6	953.0	1075.0
132.5°	328.1	388.0	590.3	916.6	1040.6
135°	338.3	402.2	581.3	874.1	996.6
137.5°	350.1	412.8	575.0	830.7	946.8
140°	362.9	424.2	569.2	788.4	894.6
142.5°	375.0	434.5	566.0	750.1	839.5
145°	387.8	442.2	564.1	713.2	789.3
147.5°	402.5	451.0	561.1	681.1	742.1
150°	416.3	459.4	558.2	657.4	701.6
152.5°	427.5	467.2	553.3	638.8	672.2
155°	439.3	474.2	548.3	621.1	647.6
157.5°	451.1	480.5	543.4	604.3	625.0
160°	461.9	485.9	537.5	587.7	604.4
162.5°	471.7	490.4	531.6	571.4	584.7
165°	478.6	493.4	525.7	556.7	565.1
167.5°	486.4	495.8	519.8	543.9	549.3
170°	491.3	497.8	514.0	531.2	534.6
172.5°	496.3	499.2	508.1	519.8	519.8
175°	499.2	500.2	504.1	511.0	509.0
177.5°	501.2	500.2	501.2	504.6	501.2
180°	500.2	500.2	500.2	500.2	500.2

(END OF REPORT)