

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000856

Luminaire Tested: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000856
REPORT IS A COMBINATION OF REPORTS P995469 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8749.3 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000856

CATALOG NUMBER: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000856

CATALOG NUMBER: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	95	91	88	93	89	85	82	77	75	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	50	47	45
3	83	73	66	60	77	68	62	56	60	54	50	51	48	44	44	41	39
4	76	65	57	51	70	61	53	48	53	47	43	46	42	38	39	36	33
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	28	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18
10	48	36	28	24	45	34	27	23	30	24	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16193	16193	16193
5°	16206	15728	15747
10°	16069	15291	15184
15°	15839	14772	14549
20°	15545	14210	13892
25°	15213	13617	13184
30°	14814	12976	12407
35°	14400	12318	11656
40°	13969	11612	10857
45°	13517	10904	10111
50°	13016	10216	9284
55°	12472	9414	8463
60°	11915	8534	7608
65°	11277	7627	6644
70°	10544	6534	5610
75°	9446	5267	4493
80°	8049	3809	3161
85°	6251	2119	1702

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13517 cd/sqm

TEST NUMBER: P1000856

CATALOG NUMBER: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	2.1
10°-20°	527.3	6.0
20°-30°	776.1	8.9
30°-40°	902.1	10.3
40°-50°	902.1	10.3
50°-60°	789.0	9.0
60°-70°	585.7	6.7
70°-80°	332.3	3.8
80°-90°	97.1	1.1
90°-100°	371.5	4.2
100°-110°	755.7	8.6
110°-120°	673.6	7.7
120°-130°	565.8	6.5
130°-140°	472.2	5.4
140°-150°	360.6	4.1
150°-160°	253.5	2.9
160°-170°	149.1	1.7
170°-180°	48.5	0.6
0°-30°	1490.6	17.0
0°-40°	2392.7	27.3
0°-60°	4083.7	46.7
0°-90°	5098.9	58.3
90°-120°	1800.8	20.6
90°-150°	3199.4	36.6
90°-180°	3650.0	41.7
0°-180°	8749.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1986	1986	1986	1986	1986	
5°	1984	1978	1960	1978	1975	188
15°	1889	1882	1858	1868	1863	532
25°	1710	1699	1677	1679	1672	787
35°	1472	1461	1438	1427	1419	920
45°	1201	1190	1165	1147	1142	926
55°	909	904	882	862	853	814
65°	616	608	592	576	568	609
75°	328	320	312	306	304	348
85°	86	86	83	83	81	92
90°	1	8	18	20	21	8
95°	32	102	801	396	240	36
105°	115	167	645	1388	1383	122
115°	202	254	575	1105	1328	201
125°	282	335	572	940	1059	251
135°	335	399	567	834	947	259
145°	386	442	564	704	773	242
155°	439	474	548	621	648	203
165°	479	493	526	557	565	135
175°	499	500	504	511	509	47
180°	500	500	500	500	500	

TEST NUMBER: P1000856

CATALOG NUMBER: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1985.8	1985.8	1985.8	1985.8	1985.8
2.5°	1992.2	1987.4	1969.9	1985.8	1984.2
5°	1984.2	1977.9	1960.4	1977.9	1974.7
7.5°	1969.9	1963.5	1944.5	1958.8	1957.2
10°	1949.2	1942.9	1922.2	1934.9	1931.7
12.5°	1922.2	1915.8	1893.5	1907.9	1903.1
15°	1888.8	1882.4	1858.5	1868.1	1863.3
17.5°	1850.6	1842.6	1820.3	1826.7	1823.5
20°	1807.6	1799.7	1775.8	1780.6	1777.4
22.5°	1761.5	1750.3	1726.5	1736.0	1729.6
25°	1710.5	1699.4	1677.1	1678.7	1672.4
27.5°	1653.3	1642.1	1621.4	1618.3	1610.3
30°	1596.0	1583.2	1562.6	1556.2	1548.2
32.5°	1535.5	1524.4	1502.1	1494.1	1486.2
35°	1471.9	1460.7	1438.4	1427.3	1419.4
37.5°	1405.0	1395.5	1371.6	1360.5	1349.3
40°	1339.8	1327.1	1303.2	1287.3	1279.3
42.5°	1269.8	1263.4	1236.4	1217.3	1212.5
45°	1201.4	1190.2	1164.8	1147.3	1142.5
47.5°	1129.8	1121.8	1097.9	1078.8	1066.1
50°	1056.6	1050.2	1027.9	1005.6	996.1
52.5°	985.0	977.0	953.1	934.0	921.3
55°	908.6	903.8	881.5	862.4	852.9
57.5°	837.0	832.2	809.9	790.8	781.3
60°	762.2	754.2	733.5	719.2	711.3
62.5°	689.0	682.6	660.3	647.6	639.7
65°	615.8	607.8	591.9	576.0	568.1
67.5°	541.0	534.6	518.7	502.8	501.2
70°	472.6	461.4	448.7	436.0	431.2
72.5°	399.4	388.3	378.7	369.2	364.4
75°	327.8	319.8	311.9	305.5	303.9
77.5°	257.8	254.6	246.6	245.0	240.3
80°	195.7	190.9	187.8	184.6	183.0
82.5°	135.3	133.7	133.7	132.1	130.5
85°	85.9	85.9	82.7	82.7	81.2
87.5°	41.4	39.8	38.2	38.2	38.2
90°	1.0	7.9	17.7	19.7	20.6
92.5°	13.8	75.6	385.2	127.2	89.4
95°	32.4	102.2	800.9	396.5	239.8
97.5°	54.0	113.0	856.9	809.8	575.9
100°	74.7	127.8	790.1	1120.2	901.1
102.5°	94.3	145.4	706.6	1314.8	1184.2
105°	115.0	166.6	644.6	1388.1	1382.7
107.5°	137.6	188.2	604.4	1366.0	1477.0
110°	160.2	209.8	585.7	1287.4	1479.0

TEST NUMBER: P1000856

CATALOG NUMBER: SA4XXDIP-B1195D1035UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	181.8	231.4	576.8	1191.0	1421.0
115°	202.4	254.0	574.9	1104.6	1327.6
117.5°	224.1	275.2	573.9	1036.8	1236.2
120°	245.7	295.8	573.9	991.0	1161.5
122.5°	265.3	316.0	572.9	961.1	1102.6
125°	282.0	335.1	571.9	940.0	1059.3
127.5°	297.8	352.8	570.0	919.8	1031.8
130°	310.5	370.0	569.0	895.8	1008.2
132.5°	323.3	384.8	568.0	867.2	981.7
135°	335.1	399.0	567.0	834.3	947.3
137.5°	346.9	411.2	567.0	798.9	907.0
140°	359.7	422.6	566.0	764.6	862.8
142.5°	373.4	432.9	566.0	732.6	815.6
145°	386.2	442.2	564.1	703.6	773.4
147.5°	400.9	451.0	561.1	679.5	734.1
150°	414.7	459.4	558.2	657.4	701.6
152.5°	427.5	467.2	553.3	638.8	672.2
155°	439.3	474.2	548.3	621.1	647.6
157.5°	451.1	480.5	543.4	604.3	625.0
160°	461.9	485.9	537.5	587.7	604.4
162.5°	471.7	490.4	531.6	571.4	584.7
165°	478.6	493.4	525.7	556.7	565.1
167.5°	486.4	495.8	519.8	543.9	549.3
170°	491.3	497.8	514.0	531.2	534.6
172.5°	496.3	499.2	508.1	519.8	519.8
175°	499.2	500.2	504.1	511.0	509.0
177.5°	501.2	500.2	501.2	504.6	501.2
180°	500.2	500.2	500.2	500.2	500.2

(END OF REPORT)