

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001863

Luminaire Tested: SA4XXDIP-B795D365UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001863
REPORT IS A COMBINATION OF REPORTS P996488 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB40-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4675.0 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001863

CATALOG NUMBER: SA4XXDIP-B795D365UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001863

CATALOG NUMBER: SA4XXDIP-B795D365UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	93	90	87	84	82	79	76	74	72	68	67	65
2	94	86	80	74	89	82	76	71	74	69	65	67	63	60	60	57	55
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35
6	66	54	45	39	63	51	44	38	47	41	36	43	37	33	39	34	31
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10821	10821	10821
5°	10830	10510	10523
10°	10738	10218	10146
15°	10584	9871	9722
20°	10387	9495	9283
25°	10166	9099	8810
30°	9899	8671	8291
35°	9623	8232	7789
40°	9335	7759	7255
45°	9032	7286	6756
50°	8697	6827	6204
55°	8334	6291	5655
60°	7961	5703	5084
65°	7536	5096	4439
70°	7045	4367	3750
75°	6311	3519	3003
80°	5380	2545	2113
85°	4177	1417	1136

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9032 cd/sqm

TEST NUMBER: P1001863

CATALOG NUMBER: SA4XXDIP-B795D365UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	2.7
10°-20°	352.4	7.5
20°-30°	518.6	11.1
30°-40°	602.8	12.9
40°-50°	602.8	12.9
50°-60°	527.2	11.3
60°-70°	391.4	8.4
70°-80°	222.1	4.8
80°-90°	64.6	1.4
90°-100°	29.8	0.6
100°-110°	89.2	1.9
110°-120°	151.6	3.2
120°-130°	199.9	4.3
130°-140°	224.5	4.8
140°-150°	220.7	4.7
150°-160°	185.6	4.0
160°-170°	123.5	2.6
170°-180°	43.2	0.9
0°-30°	996.1	21.3
0°-40°	1598.9	34.2
0°-60°	2728.9	58.4
0°-90°	3407.0	72.9
90°-120°	270.6	5.8
90°-150°	915.7	19.6
90°-180°	1268.0	27.1
0°-180°	4675.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1327	1327	1327	1327	1327	
5°	1326	1322	1310	1322	1320	126
15°	1262	1258	1242	1248	1245	356
25°	1143	1136	1121	1122	1118	526
35°	984	976	961	954	948	615
45°	803	795	778	767	763	619
55°	607	604	589	576	570	544
65°	412	406	396	385	380	407
75°	219	214	208	204	203	232
85°	57	57	55	55	54	62
90°	1	5	8	10	11	5
95°	21	24	27	28	28	23
105°	82	83	84	85	86	87
115°	154	154	153	153	153	152
125°	224	224	224	223	223	200
135°	290	292	292	291	290	224
145°	352	353	353	353	352	220
155°	403	403	403	404	403	185
165°	439	438	437	439	438	124
175°	456	454	454	457	454	43
180°	457	457	457	457	457	

TEST NUMBER: P1001863

CATALOG NUMBER: SA4XXDIP-B795D365UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1327.0	1327.0	1327.0	1327.0	1327.0
2.5°	1331.3	1328.1	1316.4	1327.0	1325.9
5°	1325.9	1321.7	1310.0	1321.7	1319.6
7.5°	1316.4	1312.1	1299.4	1308.9	1307.9
10°	1302.5	1298.3	1284.5	1293.0	1290.8
12.5°	1284.5	1280.2	1265.3	1274.9	1271.7
15°	1262.1	1257.9	1241.9	1248.3	1245.1
17.5°	1236.6	1231.3	1216.4	1220.7	1218.5
20°	1207.9	1202.6	1186.6	1189.8	1187.7
22.5°	1177.1	1169.6	1153.7	1160.1	1155.8
25°	1143.0	1135.6	1120.7	1121.8	1117.5
27.5°	1104.8	1097.3	1083.5	1081.4	1076.1
30°	1066.5	1058.0	1044.2	1039.9	1034.6
32.5°	1026.1	1018.6	1003.8	998.4	993.1
35°	983.6	976.1	961.2	953.8	948.5
37.5°	938.9	932.5	916.6	909.1	901.7
40°	895.3	886.8	870.8	860.2	854.9
42.5°	848.5	844.3	826.2	813.4	810.2
45°	802.8	795.3	778.3	766.6	763.4
47.5°	754.9	749.6	733.7	720.9	712.4
50°	706.0	701.8	686.9	672.0	665.6
52.5°	658.2	652.9	636.9	624.2	615.7
55°	607.1	604.0	589.1	576.3	569.9
57.5°	559.3	556.1	541.2	528.5	522.1
60°	509.3	504.0	490.2	480.6	475.3
62.5°	460.4	456.2	441.3	432.8	427.4
65°	411.5	406.2	395.5	384.9	379.6
67.5°	361.5	357.3	346.6	336.0	334.9
70°	315.8	308.4	299.9	291.3	288.2
72.5°	266.9	259.4	253.1	246.7	243.5
75°	219.0	213.7	208.4	204.2	203.1
77.5°	172.3	170.1	164.8	163.7	160.6
80°	130.8	127.6	125.5	123.3	122.3
82.5°	90.4	89.3	89.3	88.3	87.2
85°	57.4	57.4	55.3	55.3	54.2
87.5°	27.6	26.6	25.5	25.5	25.5
90°	1.1	4.9	7.8	9.9	10.6
92.5°	9.2	13.8	15.6	16.6	17.0
95°	21.2	24.4	26.9	27.9	27.9
97.5°	33.9	36.8	39.6	41.0	41.0
100°	49.5	50.9	54.1	54.8	54.8
102.5°	65.7	66.1	68.9	70.0	70.3
105°	82.4	82.7	84.1	85.2	86.2
107.5°	99.7	100.0	100.4	101.8	101.4
110°	117.3	118.1	117.7	117.0	118.1



TEST NUMBER: P1001863

CATALOG NUMBER: SA4XXDIP-B795D365UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.7	135.7	135.0	135.0	135.0
115°	154.1	154.1	153.4	153.0	152.7
117.5°	171.4	171.4	171.1	170.0	168.9
120°	188.7	190.2	189.1	187.3	188.0
122.5°	206.8	207.1	206.8	205.7	203.9
125°	224.4	224.4	224.1	223.4	222.7
127.5°	240.3	241.4	240.7	240.0	239.6
130°	257.3	258.4	258.4	257.7	256.2
132.5°	274.6	275.3	275.0	274.3	273.9
135°	289.5	291.6	291.6	290.9	289.8
137.5°	306.1	307.1	307.9	306.8	307.1
140°	322.7	323.4	323.4	323.0	322.7
142.5°	337.9	338.6	338.2	338.2	338.2
145°	351.7	353.1	353.4	353.1	352.0
147.5°	365.8	367.6	367.2	366.9	366.5
150°	378.5	380.0	380.0	380.0	379.6
152.5°	390.6	391.3	391.6	392.7	391.6
155°	402.9	402.9	402.6	404.0	402.6
157.5°	413.5	412.8	412.8	413.9	412.8
160°	422.7	422.4	422.0	423.1	421.3
162.5°	431.2	430.1	429.8	431.9	430.1
165°	438.6	437.6	436.9	439.0	437.6
167.5°	444.6	443.2	443.2	445.3	443.2
170°	449.6	447.8	448.2	450.3	447.8
172.5°	453.1	451.7	451.7	454.2	451.7
175°	456.3	454.5	454.2	456.7	454.2
177.5°	457.7	455.9	455.9	458.4	455.6
180°	457.0	457.0	457.0	457.0	457.0

(END OF REPORT)