

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000861

Luminaire Tested: SA4XXDIP-B1195D1035UB50-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000861
REPORT IS A COMBINATION OF REPORTS P995474 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1035UB50-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8096.0 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000861

CATALOG NUMBER: SA4XXDIP-B1195D1035UB50-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1000861

CATALOG NUMBER: SA4XXDIP-B1195D1035UB50-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	97	93	88	84	90	86	82	79	73	70	68	62	59	58	51	49	48
2	88	80	74	68	81	74	69	64	63	59	55	53	50	47	44	42	40
3	80	70	62	56	74	65	58	53	56	50	46	47	43	39	39	36	33
4	73	62	54	47	67	57	50	44	49	43	39	41	37	33	34	31	28
5	67	55	46	40	62	51	44	38	44	38	33	37	32	29	31	27	24
6	62	49	41	35	57	46	38	33	39	33	29	33	29	25	28	24	21
7	57	44	36	30	53	41	34	29	36	30	25	30	26	22	25	22	19
8	53	40	32	27	49	38	30	25	32	27	22	28	23	20	23	20	17
9	49	37	29	24	46	34	27	22	30	24	20	25	21	18	21	18	15
10	46	34	26	21	43	31	25	20	27	22	18	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11205	11205	11205
5°	11236	10913	10933
10°	11163	10699	10668
15°	11059	10457	10369
20°	10904	10196	10078
25°	10729	9908	9765
30°	10541	9622	9446
35°	10327	9330	9162
40°	10156	9050	8867
45°	9903	8787	8607
50°	9686	8488	8332
55°	9463	8201	8017
60°	9117	7842	7719
65°	8735	7456	7361
70°	8272	7013	6947
75°	7628	6522	6553
80°	6897	6023	6141
85°	5938	5520	5806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9903 cd/sqm

TEST NUMBER: P1000861

CATALOG NUMBER: SA4XXDIP-B1195D1035UB50-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.2	1.6
10°-20°	373.1	4.6
20°-30°	564.1	7.0
30°-40°	682.4	8.4
40°-50°	721.4	8.9
50°-60°	678.9	8.4
60°-70°	563.4	7.0
70°-80°	395.4	4.9
80°-90°	225.5	2.8
90°-100°	212.8	2.6
100°-110°	338.1	4.2
110°-120°	473.4	5.8
120°-130°	574.5	7.1
130°-140°	619.6	7.7
140°-150°	596.3	7.4
150°-160°	498.9	6.2
160°-170°	332.0	4.1
170°-180°	116.2	1.4
0°-30°	1067.3	13.2
0°-40°	1749.7	21.6
0°-60°	3150.1	38.9
0°-90°	4334.3	53.5
90°-120°	1024.3	12.7
90°-150°	2814.6	34.8
90°-180°	3762.0	46.5
0°-180°	8096.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1374	1374	1374	1374	1374	
5°	1376	1371	1360	1373	1371	131
15°	1319	1320	1316	1330	1328	372
25°	1206	1216	1220	1237	1239	556
35°	1056	1074	1090	1111	1116	661
45°	880	909	939	965	972	680
55°	689	722	768	799	808	614
65°	477	526	579	617	629	473
75°	265	322	386	429	443	281
85°	82	146	215	262	277	85
90°	28	100	173	224	238	21
95°	77	136	206	250	264	78
105°	235	267	328	369	384	250
115°	423	437	485	518	527	418
125°	610	608	645	673	680	544
135°	781	787	798	820	827	605
145°	947	949	950	958	962	593
155°	1083	1083	1082	1086	1082	499
165°	1179	1176	1174	1180	1176	332
175°	1226	1222	1221	1228	1221	116
180°	1228	1228	1228	1228	1228	

TEST NUMBER: P1000861

CATALOG NUMBER: SA4XXDIP-B1195D1035UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1374.1	1374.1	1374.1	1374.1	1374.1
2.5°	1380.3	1375.7	1363.4	1374.1	1372.6
5°	1375.7	1371.1	1360.3	1372.6	1371.1
7.5°	1366.4	1363.4	1354.1	1368.0	1366.4
10°	1354.1	1352.6	1344.9	1358.8	1357.2
12.5°	1337.2	1337.2	1332.6	1344.9	1344.9
15°	1318.7	1320.3	1315.7	1329.5	1328.0
17.5°	1294.1	1298.7	1297.2	1311.0	1309.5
20°	1268.0	1272.6	1274.1	1289.5	1289.5
22.5°	1238.7	1244.9	1248.0	1263.3	1266.4
25°	1206.4	1215.6	1220.3	1237.2	1238.7
27.5°	1171.0	1184.9	1191.0	1206.4	1207.9
30°	1135.6	1147.9	1158.7	1175.6	1178.7
32.5°	1097.2	1112.5	1124.9	1144.9	1147.9
35°	1055.6	1074.1	1089.5	1111.0	1115.6
37.5°	1014.1	1035.6	1054.1	1075.6	1080.2
40°	974.1	994.1	1015.6	1038.7	1044.8
42.5°	927.9	951.0	977.1	1003.3	1007.9
45°	880.2	909.4	938.7	964.8	972.5
47.5°	835.6	864.8	898.7	924.8	934.0
50°	786.3	820.2	854.0	884.8	894.0
52.5°	737.1	770.9	810.9	841.7	850.9
55°	689.4	721.7	767.9	798.6	807.9
57.5°	635.5	675.5	720.2	757.1	764.8
60°	583.2	623.2	674.0	709.4	721.7
62.5°	532.4	577.0	627.8	663.2	675.5
65°	477.0	526.3	578.6	617.1	629.4
67.5°	424.7	477.0	532.4	570.9	583.2
70°	370.8	423.2	481.6	523.2	534.0
72.5°	318.5	372.4	435.5	475.5	487.8
75°	264.7	321.6	386.2	429.3	443.2
77.5°	213.9	273.9	341.6	384.7	400.1
80°	167.7	229.3	297.0	343.1	355.5
82.5°	121.6	186.2	253.9	301.6	315.5
85°	81.6	146.2	215.4	261.6	277.0
87.5°	50.8	113.9	181.6	226.2	240.1
90°	27.5	99.5	173.2	223.6	237.8
92.5°	47.8	114.0	184.9	230.9	244.1
95°	77.0	136.4	206.1	250.5	264.4
97.5°	109.7	161.9	232.6	276.4	290.2
100°	149.9	193.7	262.3	305.8	316.6
102.5°	193.6	228.5	294.6	337.4	350.7
105°	235.2	266.9	327.7	369.0	384.1
107.5°	281.7	308.9	363.7	405.9	415.8
110°	327.7	351.2	404.1	437.6	452.7

TEST NUMBER: P1000861

CATALOG NUMBER: SA4XXDIP-B1195D1035UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.6	394.0	442.9	476.8	489.1
115°	423.4	437.3	484.6	517.6	527.3
117.5°	470.0	479.3	524.4	553.9	563.4
120°	515.0	523.4	565.2	591.2	605.4
122.5°	563.5	564.4	605.0	632.9	639.0
125°	609.5	607.9	645.4	672.7	680.1
127.5°	652.2	653.5	682.4	708.2	718.0
130°	696.2	697.6	722.2	748.0	753.4
132.5°	742.8	743.2	760.6	784.9	793.2
135°	781.2	786.9	797.6	820.4	826.7
137.5°	825.8	827.1	835.2	855.4	864.1
140°	870.5	870.8	872.4	891.4	898.2
142.5°	909.7	911.6	909.2	926.1	932.3
145°	946.8	949.1	950.0	958.3	961.6
147.5°	984.8	988.0	987.1	987.6	992.9
150°	1019.0	1021.3	1021.3	1021.3	1020.3
152.5°	1049.8	1051.7	1052.6	1055.5	1052.6
155°	1083.0	1083.0	1082.1	1085.9	1082.1
157.5°	1111.6	1109.7	1109.7	1112.5	1109.7
160°	1136.3	1135.3	1134.4	1137.2	1132.5
162.5°	1159.1	1156.2	1155.3	1161.0	1156.2
165°	1179.0	1176.2	1174.3	1180.0	1176.2
167.5°	1195.2	1191.4	1191.4	1197.1	1191.4
170°	1208.5	1203.7	1204.7	1210.4	1203.7
172.5°	1218.0	1214.2	1214.2	1220.8	1214.2
175°	1226.5	1221.8	1220.8	1227.5	1220.8
177.5°	1230.3	1225.6	1225.6	1232.2	1224.6
180°	1228.4	1228.4	1228.4	1228.4	1228.4

(END OF REPORT)