

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001868

Luminaire Tested: SA4XXDIP-B795D365UB50-4F0-XX-W2A-D

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001868
REPORT IS A COMBINATION OF REPORTS P996493 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB50-4F0-XX-W2A-D
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4545.0 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001868

CATALOG NUMBER: SA4XXDIP-B795D365UB50-4F0-XX-W2A-D

Luminous Intensity Polar Plot



TEST NUMBER: P1001868

CATALOG NUMBER: SA4XXDIP-B795D365UB50-4F0-XX-W2A-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	100	95	90	86	93	89	85	81	78	75	72	68	66	64	59	57	55
2	90	82	75	69	84	77	71	66	68	63	59	59	55	52	51	48	46
3	82	72	64	57	76	67	60	54	59	53	49	52	47	43	45	41	38
4	75	63	55	48	70	59	52	46	52	46	41	46	41	37	40	36	33
5	69	56	47	41	64	53	45	39	47	40	35	41	36	32	36	31	28
6	63	50	42	35	59	47	40	34	42	36	31	37	32	28	32	28	25
7	58	45	37	31	54	43	35	30	38	32	27	34	28	24	29	25	22
8	54	41	33	27	51	39	31	26	35	28	24	31	25	22	27	23	19
9	50	38	30	24	47	36	28	23	32	26	21	28	23	19	25	21	18
10	47	34	27	22	44	33	26	21	29	23	19	26	21	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7486	7486	7486
5°	7507	7291	7304
10°	7458	7147	7127
15°	7388	6986	6927
20°	7285	6812	6733
25°	7168	6619	6524
30°	7042	6428	6311
35°	6899	6234	6121
40°	6785	6046	5924
45°	6616	5870	5750
50°	6471	5671	5567
55°	6323	5478	5355
60°	6090	5239	5157
65°	5836	4980	4918
70°	5528	4686	4641
75°	5095	4357	4378
80°	4611	4024	4103
85°	3966	3687	3878

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6616 cd/sqm

TEST NUMBER: P1001868

CATALOG NUMBER: SA4XXDIP-B795D365UB50-4F0-XX-W2A-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.9
10°-20°	249.2	5.5
20°-30°	376.8	8.3
30°-40°	455.9	10.0
40°-50°	482.0	10.6
50°-60°	453.6	10.0
60°-70°	376.4	8.3
70°-80°	264.1	5.8
80°-90°	149.9	3.3
90°-100°	103.8	2.3
100°-110°	165.5	3.6
110°-120°	234.8	5.2
120°-130°	267.0	5.9
130°-140°	269.8	5.9
140°-150°	244.4	5.4
150°-160°	195.4	4.3
160°-170°	126.0	2.8
170°-180°	43.4	1.0
0°-30°	713.1	15.7
0°-40°	1169.0	25.7
0°-60°	2104.5	46.3
0°-90°	2894.9	63.7
90°-120°	504.2	11.1
90°-150°	1285.3	28.3
90°-180°	1650.0	36.3
0°-180°	4545.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	918	918	918	918	918	
5°	919	916	909	917	916	87
15°	881	882	879	888	887	248
25°	806	812	815	827	828	371
35°	705	718	728	742	745	442
45°	588	608	627	645	650	454
55°	461	482	513	534	540	410
65°	319	352	386	412	420	316
75°	177	215	258	287	296	188
85°	54	98	144	175	185	57
90°	17	62	109	141	150	12
95°	32	54	97	127	136	34
105°	112	135	174	203	199	118
115°	198	208	241	264	272	196
125°	274	274	300	320	327	245
135°	337	337	345	362	369	260
145°	387	387	387	394	399	242
155°	424	424	423	424	423	195
165°	447	445	445	448	445	126
175°	457	455	455	458	454	44
180°	457	457	457	457	457	

TEST NUMBER: P1001868

CATALOG NUMBER: SA4XXDIP-B795D365UB50-4F0-XX-W2A-D

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	918.0	918.0	918.0	918.0	918.0
2.5°	922.2	919.1	910.9	918.0	917.0
5°	919.1	916.0	908.8	917.0	916.0
7.5°	912.9	910.9	904.7	913.9	912.9
10°	904.7	903.7	898.5	907.8	906.7
12.5°	893.4	893.4	890.3	898.5	898.5
15°	881.0	882.1	879.0	888.2	887.2
17.5°	864.6	867.7	866.6	875.9	874.9
20°	847.1	850.2	851.2	861.5	861.5
22.5°	827.6	831.7	833.7	844.0	846.1
25°	806.0	812.2	815.2	826.6	827.6
27.5°	782.3	791.6	795.7	806.0	807.0
30°	758.7	766.9	774.1	785.4	787.5
32.5°	733.0	743.3	751.5	764.9	766.9
35°	705.2	717.6	727.9	742.3	745.3
37.5°	677.5	691.9	704.2	718.6	721.7
40°	650.8	664.1	678.5	693.9	698.0
42.5°	619.9	635.3	652.8	670.3	673.4
45°	588.0	607.6	627.1	644.6	649.7
47.5°	558.2	577.8	600.4	617.9	624.0
50°	525.3	547.9	570.6	591.1	597.3
52.5°	492.4	515.1	541.8	562.3	568.5
55°	460.6	482.2	513.0	533.6	539.7
57.5°	424.6	451.3	481.1	505.8	510.9
60°	389.6	416.4	450.3	473.9	482.2
62.5°	355.7	385.5	419.4	443.1	451.3
65°	318.7	351.6	386.5	412.2	420.5
67.5°	283.7	318.7	355.7	381.4	389.6
70°	247.8	282.7	321.8	349.5	356.7
72.5°	212.8	248.8	290.9	317.7	325.9
75°	176.8	214.9	258.0	286.8	296.1
77.5°	142.9	183.0	228.2	257.0	267.3
80°	112.1	153.2	198.4	229.3	237.5
82.5°	81.2	124.4	169.6	201.5	210.7
85°	54.5	97.7	143.9	174.8	185.0
87.5°	33.9	76.1	121.3	151.1	160.4
90°	17.4	62.4	109.3	141.2	150.1
92.5°	20.5	55.8	102.8	133.6	141.8
95°	32.2	54.5	96.9	126.8	136.3
97.5°	48.2	85.5	91.8	120.2	129.9
100°	67.4	100.2	93.1	115.1	122.7
102.5°	89.9	116.6	159.8	109.6	117.8
105°	112.2	134.7	174.5	203.3	199.2
107.5°	134.4	152.8	191.2	218.6	227.2
110°	155.9	171.3	209.3	233.6	242.9



TEST NUMBER: P1001868

CATALOG NUMBER: SA4XXDIP-B795D365UB50-4F0-XX-W2A-D

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.7	191.1	225.8	248.0	257.6
115°	198.3	208.5	241.1	264.4	271.6
117.5°	218.5	225.9	257.8	279.1	287.3
120°	237.9	242.3	271.8	293.1	300.6
122.5°	257.0	257.7	286.2	307.1	313.6
125°	274.1	274.5	299.5	320.0	326.6
127.5°	291.5	290.9	313.1	331.3	338.1
130°	307.3	306.6	324.1	342.9	349.1
132.5°	322.7	322.4	336.0	353.9	359.6
135°	337.1	336.7	345.3	362.4	369.3
137.5°	350.7	349.6	355.4	371.6	376.4
140°	364.1	363.6	365.4	379.8	385.3
142.5°	374.9	376.3	375.6	387.6	391.7
145°	387.2	387.3	387.3	393.8	398.6
147.5°	396.8	397.8	397.5	398.8	403.3
150°	407.4	407.8	407.4	407.4	407.8
152.5°	415.3	416.3	415.6	416.3	416.0
155°	423.5	423.8	422.8	424.2	423.1
157.5°	430.7	430.7	429.3	431.0	429.3
160°	436.8	435.8	435.4	437.5	435.4
162.5°	442.3	440.9	440.6	442.6	440.2
165°	446.7	445.0	445.0	447.8	444.7
167.5°	450.5	448.8	448.4	451.5	448.1
170°	453.6	451.5	451.9	454.6	451.2
172.5°	455.6	453.6	453.9	456.6	452.9
175°	457.0	454.9	455.3	458.3	454.2
177.5°	458.0	455.6	456.3	459.0	454.9
180°	457.0	457.0	457.0	457.0	457.0

(END OF REPORT)