

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000864

Luminaire Tested: SA4XXDIP-B1195D1035UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000864
REPORT IS A COMBINATION OF REPORTS P995477 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1035UB50-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8340.0 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000864

CATALOG NUMBER: SA4XXDIP-B1195D1035UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1000864

CATALOG NUMBER: SA4XXDIP-B1195D1035UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	95	91	88	93	89	86	83	78	75	73	67	65	63	57	56	54
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15660	15660	15660
5°	15672	15209	15228
10°	15540	14787	14684
15°	15317	14285	14069
20°	15032	13742	13434
25°	14712	13168	12749
30°	14326	12548	11998
35°	13926	11912	11272
40°	13508	11229	10500
45°	13071	10544	9778
50°	12586	9879	8978
55°	12060	9104	8184
60°	11522	8254	7356
65°	10906	7376	6424
70°	10196	6318	5425
75°	9135	5093	4345
80°	7786	3683	3057
85°	6047	2050	1645

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13071 cd/sqm

TEST NUMBER: P1000864

CATALOG NUMBER: SA4XXDIP-B1195D1035UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.2
10°-20°	509.9	6.1
20°-30°	750.5	9.0
30°-40°	872.4	10.5
40°-50°	872.3	10.5
50°-60°	763.0	9.1
60°-70°	566.4	6.8
70°-80°	321.4	3.9
80°-90°	94.7	1.1
90°-100°	80.1	1.0
100°-110°	239.8	2.9
110°-120°	407.4	4.9
120°-130°	537.3	6.4
130°-140°	603.5	7.2
140°-150°	593.2	7.1
150°-160°	498.9	6.0
160°-170°	332.0	4.0
170°-180°	116.2	1.4
0°-30°	1441.4	17.3
0°-40°	2313.8	27.7
0°-60°	3949.1	47.4
0°-90°	4931.6	59.1
90°-120°	727.4	8.7
90°-150°	2461.3	29.5
90°-180°	3408.0	40.9
0°-180°	8340.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1920	1920	1920	1920	1920	
5°	1919	1913	1896	1913	1910	182
15°	1826	1820	1797	1806	1802	515
25°	1654	1643	1622	1623	1617	761
35°	1423	1413	1391	1380	1373	890
45°	1162	1151	1126	1109	1105	896
55°	879	874	852	834	825	787
65°	596	588	572	557	549	589
75°	317	309	302	295	294	336
85°	83	83	80	80	78	89
90°	3	13	21	27	28	10
95°	57	66	72	75	75	62
105°	221	222	226	229	232	235
115°	414	414	412	411	410	409
125°	603	603	602	600	598	538
135°	778	784	784	782	779	602
145°	945	949	950	949	946	592
155°	1083	1083	1082	1086	1082	498
165°	1179	1176	1174	1180	1176	332
175°	1226	1222	1221	1228	1221	116
180°	1228	1228	1228	1228	1228	

TEST NUMBER: P1000864

CATALOG NUMBER: SA4XXDIP-B1195D1035UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1920.4	1920.4	1920.4	1920.4	1920.4
2.5°	1926.5	1921.9	1905.0	1920.4	1918.8
5°	1918.8	1912.7	1895.7	1912.7	1909.6
7.5°	1905.0	1898.8	1880.4	1894.2	1892.7
10°	1885.0	1878.8	1858.8	1871.1	1868.1
12.5°	1858.8	1852.7	1831.1	1845.0	1840.4
15°	1826.5	1820.3	1797.3	1806.5	1801.9
17.5°	1789.6	1781.9	1760.3	1766.5	1763.4
20°	1748.0	1740.3	1717.3	1721.9	1718.8
22.5°	1703.4	1692.6	1669.6	1678.8	1672.6
25°	1654.2	1643.4	1621.8	1623.4	1617.2
27.5°	1598.8	1588.0	1568.0	1564.9	1557.2
30°	1543.4	1531.1	1511.1	1504.9	1497.2
32.5°	1484.9	1474.1	1452.6	1444.9	1437.2
35°	1423.4	1412.6	1391.0	1380.3	1372.6
37.5°	1358.7	1349.5	1326.4	1315.6	1304.9
40°	1295.6	1283.3	1260.2	1244.9	1237.2
42.5°	1227.9	1221.8	1195.6	1177.1	1172.5
45°	1161.8	1151.0	1126.4	1109.4	1104.8
47.5°	1092.5	1084.8	1061.7	1043.3	1031.0
50°	1021.7	1015.6	994.0	972.5	963.3
52.5°	952.5	944.8	921.7	903.3	890.9
55°	878.6	874.0	852.5	834.0	824.8
57.5°	809.4	804.8	783.2	764.8	755.5
60°	737.1	729.4	709.4	695.5	687.8
62.5°	666.3	660.1	638.6	626.3	618.6
65°	595.5	587.8	572.4	557.0	549.3
67.5°	523.2	517.0	501.6	486.2	484.7
70°	457.0	446.2	433.9	421.6	417.0
72.5°	386.2	375.5	366.2	357.0	352.4
75°	317.0	309.3	301.6	295.4	293.9
77.5°	249.3	246.2	238.5	237.0	232.4
80°	189.3	184.7	181.6	178.5	177.0
82.5°	130.8	129.3	129.3	127.7	126.2
85°	83.1	83.1	80.0	80.0	78.5
87.5°	40.0	38.5	36.9	36.9	36.9
90°	2.9	13.3	20.9	26.6	28.5
92.5°	24.7	37.1	41.8	44.7	45.6
95°	57.0	65.6	72.2	75.1	75.1
97.5°	91.2	98.8	106.4	110.2	110.2
100°	133.0	136.8	145.4	147.3	147.3
102.5°	176.7	177.7	185.3	188.1	189.1
105°	221.4	222.3	226.1	229.0	231.8
107.5°	267.9	268.9	269.8	273.6	272.7
110°	315.4	317.3	316.4	314.5	317.3

TEST NUMBER: P1000864

CATALOG NUMBER: SA4XXDIP-B1195D1035UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	364.8	364.8	362.9	362.9	362.9
115°	414.2	414.2	412.3	411.4	410.4
117.5°	460.8	460.8	459.8	457.0	454.1
120°	507.3	511.1	508.3	503.5	505.4
122.5°	555.8	556.7	555.8	552.9	548.2
125°	603.3	603.3	602.3	600.4	598.5
127.5°	646.0	648.9	647.0	645.1	644.1
130°	691.6	694.5	694.5	692.6	688.8
132.5°	738.2	740.1	739.1	737.2	736.3
135°	778.1	783.8	783.8	781.9	779.0
137.5°	822.7	825.6	827.5	824.6	825.6
140°	867.4	869.3	869.3	868.3	867.4
142.5°	908.2	910.1	909.2	909.2	909.2
145°	945.3	949.1	950.0	949.1	946.2
147.5°	983.3	988.0	987.1	986.1	985.2
150°	1017.5	1021.3	1021.3	1021.3	1020.3
152.5°	1049.8	1051.7	1052.6	1055.5	1052.6
155°	1083.0	1083.0	1082.1	1085.9	1082.1
157.5°	1111.6	1109.7	1109.7	1112.5	1109.7
160°	1136.3	1135.3	1134.4	1137.2	1132.5
162.5°	1159.1	1156.2	1155.3	1161.0	1156.2
165°	1179.0	1176.2	1174.3	1180.0	1176.2
167.5°	1195.2	1191.4	1191.4	1197.1	1191.4
170°	1208.5	1203.7	1204.7	1210.4	1203.7
172.5°	1218.0	1214.2	1214.2	1220.8	1214.2
175°	1226.5	1221.8	1220.8	1227.5	1220.8
177.5°	1230.3	1225.6	1225.6	1232.2	1224.6
180°	1228.4	1228.4	1228.4	1228.4	1228.4

(END OF REPORT)