

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001871

Luminaire Tested: SA4XXDIP-B795D365UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001871
REPORT IS A COMBINATION OF REPORTS P996496 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB50-4F0-XX-W2A-F
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4708.0 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001871

CATALOG NUMBER: SA4XXDIP-B795D365UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1001871

CATALOG NUMBER: SA4XXDIP-B795D365UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	102	98	94	90	96	93	89	86	83	80	78	74	72	70	66	64	63
2	93	85	79	74	88	81	75	70	73	68	64	65	62	58	58	55	53
3	85	75	67	61	80	71	64	59	64	59	54	57	53	50	51	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39
5	72	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27
8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	32	27	24
9	53	40	33	27	50	39	31	27	35	29	25	32	27	23	29	25	22
10	50	37	30	25	47	36	29	24	33	27	22	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10462	10462	10462
5°	10470	10161	10174
10°	10382	9879	9810
15°	10233	9543	9399
20°	10043	9181	8975
25°	9829	8797	8518
30°	9571	8383	8016
35°	9303	7958	7531
40°	9025	7503	7014
45°	8733	7044	6532
50°	8409	6600	5998
55°	8058	6082	5467
60°	7697	5514	4915
65°	7285	4927	4292
70°	6811	4222	3625
75°	6104	3403	2904
80°	5199	2460	2042
85°	4039	1371	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8733 cd/sqm

TEST NUMBER: P1001871

CATALOG NUMBER: SA4XXDIP-B795D365UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	2.6
10°-20°	340.7	7.2
20°-30°	501.4	10.6
30°-40°	582.8	12.4
40°-50°	582.8	12.4
50°-60°	509.7	10.8
60°-70°	378.4	8.0
70°-80°	214.7	4.6
80°-90°	62.5	1.3
90°-100°	15.2	0.3
100°-110°	99.9	2.1
110°-120°	190.8	4.1
120°-130°	242.2	5.1
130°-140°	259.1	5.5
140°-150°	242.2	5.1
150°-160°	195.4	4.1
160°-170°	126.0	2.7
170°-180°	43.4	0.9
0°-30°	963.0	20.5
0°-40°	1545.9	32.8
0°-60°	2638.4	56.0
0°-90°	3294.0	70.0
90°-120°	305.8	6.5
90°-150°	1049.3	22.3
90°-180°	1414.0	30.0
0°-180°	4708.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1283	1283	1283	1283	1283	
5°	1282	1278	1266	1278	1276	122
15°	1220	1216	1201	1207	1204	344
25°	1105	1098	1084	1085	1080	509
35°	951	944	929	922	917	595
45°	776	769	752	741	738	598
55°	587	584	570	557	551	526
65°	398	393	382	372	367	394
75°	212	207	202	197	196	225
85°	56	56	54	54	52	60
90°	1	5	8	10	10	5
95°	19	7	8	10	10	23
105°	103	105	107	110	97	108
115°	192	193	193	194	194	189
125°	270	271	271	272	272	241
135°	335	335	336	337	337	258
145°	386	387	387	388	388	241
155°	424	424	423	424	423	195
165°	447	445	445	448	445	126
175°	457	455	455	458	454	44
180°	457	457	457	457	457	

TEST NUMBER: P1001871

CATALOG NUMBER: SA4XXDIP-B795D365UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1283.0	1283.0	1283.0	1283.0	1283.0
2.5°	1287.1	1284.0	1272.7	1283.0	1281.9
5°	1281.9	1277.8	1266.5	1277.8	1275.8
7.5°	1272.7	1268.6	1256.2	1265.5	1264.5
10°	1259.3	1255.2	1241.9	1250.1	1248.0
12.5°	1241.9	1237.7	1223.3	1232.6	1229.5
15°	1220.3	1216.2	1200.7	1206.9	1203.8
17.5°	1195.6	1190.5	1176.1	1180.2	1178.1
20°	1167.8	1162.7	1147.3	1150.4	1148.3
22.5°	1138.0	1130.8	1115.4	1121.6	1117.5
25°	1105.1	1097.9	1083.5	1084.6	1080.5
27.5°	1068.1	1060.9	1047.6	1045.5	1040.4
30°	1031.1	1022.9	1009.5	1005.4	1000.3
32.5°	992.0	984.8	970.5	965.3	960.2
35°	950.9	943.7	929.3	922.1	917.0
37.5°	907.7	901.6	886.2	879.0	871.8
40°	865.6	857.4	842.0	831.7	826.5
42.5°	820.4	816.3	798.8	786.4	783.4
45°	776.2	769.0	752.5	741.2	738.1
47.5°	729.9	724.8	709.3	697.0	688.8
50°	682.6	678.5	664.1	649.7	643.5
52.5°	636.3	631.2	615.8	603.4	595.2
55°	587.0	583.9	569.5	557.2	551.0
57.5°	540.7	537.7	523.3	510.9	504.8
60°	492.4	487.3	473.9	464.7	459.5
62.5°	445.1	441.0	426.6	418.4	413.3
65°	397.8	392.7	382.4	372.1	367.0
67.5°	349.5	345.4	335.1	324.9	323.8
70°	305.3	298.1	289.9	281.7	278.6
72.5°	258.0	250.8	244.7	238.5	235.4
75°	211.8	206.6	201.5	197.4	196.4
77.5°	166.5	164.5	159.3	158.3	155.2
80°	126.4	123.4	121.3	119.3	118.2
82.5°	87.4	86.4	86.4	85.3	84.3
85°	55.5	55.5	53.5	53.5	52.4
87.5°	26.7	25.7	24.7	24.7	24.7
90°	1.0	4.8	7.5	9.6	10.3
92.5°	5.1	4.4	7.2	9.2	9.2
95°	18.8	7.2	7.5	9.6	9.9
97.5°	35.9	43.4	7.5	9.2	9.6
100°	56.1	62.2	15.0	9.2	9.6
102.5°	78.6	82.7	86.8	9.9	9.9
105°	102.9	104.9	106.6	109.7	97.4
107.5°	125.1	126.1	128.5	130.2	131.6
110°	147.7	148.7	150.7	151.4	152.4

TEST NUMBER: P1001871

CATALOG NUMBER: SA4XXDIP-B795D365UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	169.5	171.6	172.3	171.9	173.3
115°	192.1	193.1	192.8	193.5	193.5
117.5°	212.3	213.6	214.6	214.3	214.3
120°	232.8	234.1	233.8	234.5	233.8
122.5°	251.9	252.6	253.3	253.6	252.9
125°	270.0	271.4	270.7	271.7	272.1
127.5°	287.4	287.8	289.5	289.2	288.8
130°	304.2	304.5	305.6	305.9	305.9
132.5°	319.6	320.3	321.6	322.0	321.6
135°	335.0	334.6	336.0	336.7	337.4
137.5°	348.6	348.6	350.3	351.0	350.7
140°	362.0	362.6	363.3	364.4	364.7
142.5°	373.9	375.3	375.6	376.3	376.3
145°	386.2	387.3	387.3	387.6	388.3
147.5°	395.8	397.8	397.5	397.8	398.2
150°	406.4	407.8	407.4	407.4	407.8
152.5°	415.3	416.3	415.6	416.3	416.0
155°	423.5	423.8	422.8	424.2	423.1
157.5°	430.7	430.7	429.3	431.0	429.3
160°	436.8	435.8	435.4	437.5	435.4
162.5°	442.3	440.9	440.6	442.6	440.2
165°	446.7	445.0	445.0	447.8	444.7
167.5°	450.5	448.8	448.4	451.5	448.1
170°	453.6	451.5	451.9	454.6	451.2
172.5°	455.6	453.6	453.9	456.6	452.9
175°	457.0	454.9	455.3	458.3	454.2
177.5°	458.0	455.6	456.3	459.0	454.9
180°	457.0	457.0	457.0	457.0	457.0

(END OF REPORT)