

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001872

Luminaire Tested: SA4XXDIP-B795D365UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001872
REPORT IS A COMBINATION OF REPORTS P996497 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D365UB50-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4520.0 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001872

CATALOG NUMBER: SA4XXDIP-B795D365UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001872

CATALOG NUMBER: SA4XXDIP-B795D365UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	93	90	87	84	82	79	76	74	72	68	67	65
2	94	86	80	74	89	82	76	71	74	69	65	67	63	60	60	57	55
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35
6	66	54	45	39	63	51	44	38	47	41	36	43	37	33	39	34	31
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10462	10462	10462
5°	10470	10161	10174
10°	10382	9879	9810
15°	10233	9543	9399
20°	10043	9181	8975
25°	9829	8797	8518
30°	9571	8383	8016
35°	9303	7958	7531
40°	9025	7503	7014
45°	8733	7044	6532
50°	8409	6600	5998
55°	8058	6082	5467
60°	7697	5514	4915
65°	7285	4927	4292
70°	6811	4222	3625
75°	6104	3403	2904
80°	5199	2460	2042
85°	4039	1371	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8733 cd/sqm

TEST NUMBER: P1001872

CATALOG NUMBER: SA4XXDIP-B795D365UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	2.7
10°-20°	340.7	7.5
20°-30°	501.4	11.1
30°-40°	582.8	12.9
40°-50°	582.8	12.9
50°-60°	509.7	11.3
60°-70°	378.4	8.4
70°-80°	214.7	4.8
80°-90°	62.5	1.4
90°-100°	28.8	0.6
100°-110°	86.3	1.9
110°-120°	146.5	3.2
120°-130°	193.3	4.3
130°-140°	217.1	4.8
140°-150°	213.4	4.7
150°-160°	179.5	4.0
160°-170°	119.4	2.6
170°-180°	41.8	0.9
0°-30°	963.0	21.3
0°-40°	1545.9	34.2
0°-60°	2638.4	58.4
0°-90°	3294.0	72.9
90°-120°	261.6	5.8
90°-150°	885.4	19.6
90°-180°	1226.0	27.1
0°-180°	4520.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1283	1283	1283	1283	1283	
5°	1282	1278	1266	1278	1276	122
15°	1220	1216	1201	1207	1204	344
25°	1105	1098	1084	1085	1080	509
35°	951	944	929	922	917	595
45°	776	769	752	741	738	598
55°	587	584	570	557	551	526
65°	398	393	382	372	367	394
75°	212	207	202	197	196	225
85°	56	56	54	54	52	60
90°	1	5	8	10	10	5
95°	20	24	26	27	27	22
105°	80	80	81	82	83	84
115°	149	149	148	148	148	147
125°	217	217	217	216	215	193
135°	280	282	282	281	280	217
145°	340	341	342	341	340	213
155°	390	390	389	391	389	179
165°	424	423	422	424	423	120
175°	441	440	439	442	439	42
180°	442	442	442	442	442	

TEST NUMBER: P1001872

CATALOG NUMBER: SA4XXDIP-B795D365UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1283.0	1283.0	1283.0	1283.0	1283.0
2.5°	1287.1	1284.0	1272.7	1283.0	1281.9
5°	1281.9	1277.8	1266.5	1277.8	1275.8
7.5°	1272.7	1268.6	1256.2	1265.5	1264.5
10°	1259.3	1255.2	1241.9	1250.1	1248.0
12.5°	1241.9	1237.7	1223.3	1232.6	1229.5
15°	1220.3	1216.2	1200.7	1206.9	1203.8
17.5°	1195.6	1190.5	1176.1	1180.2	1178.1
20°	1167.8	1162.7	1147.3	1150.4	1148.3
22.5°	1138.0	1130.8	1115.4	1121.6	1117.5
25°	1105.1	1097.9	1083.5	1084.6	1080.5
27.5°	1068.1	1060.9	1047.6	1045.5	1040.4
30°	1031.1	1022.9	1009.5	1005.4	1000.3
32.5°	992.0	984.8	970.5	965.3	960.2
35°	950.9	943.7	929.3	922.1	917.0
37.5°	907.7	901.6	886.2	879.0	871.8
40°	865.6	857.4	842.0	831.7	826.5
42.5°	820.4	816.3	798.8	786.4	783.4
45°	776.2	769.0	752.5	741.2	738.1
47.5°	729.9	724.8	709.3	697.0	688.8
50°	682.6	678.5	664.1	649.7	643.5
52.5°	636.3	631.2	615.8	603.4	595.2
55°	587.0	583.9	569.5	557.2	551.0
57.5°	540.7	537.7	523.3	510.9	504.8
60°	492.4	487.3	473.9	464.7	459.5
62.5°	445.1	441.0	426.6	418.4	413.3
65°	397.8	392.7	382.4	372.1	367.0
67.5°	349.5	345.4	335.1	324.9	323.8
70°	305.3	298.1	289.9	281.7	278.6
72.5°	258.0	250.8	244.7	238.5	235.4
75°	211.8	206.6	201.5	197.4	196.4
77.5°	166.5	164.5	159.3	158.3	155.2
80°	126.4	123.4	121.3	119.3	118.2
82.5°	87.4	86.4	86.4	85.3	84.3
85°	55.5	55.5	53.5	53.5	52.4
87.5°	26.7	25.7	24.7	24.7	24.7
90°	1.0	4.8	7.5	9.6	10.3
92.5°	8.9	13.3	15.0	16.1	16.4
95°	20.5	23.6	26.0	27.0	27.0
97.5°	32.8	35.5	38.3	39.6	39.6
100°	47.8	49.2	52.3	53.0	53.0
102.5°	63.6	63.9	66.6	67.7	68.0
105°	79.6	80.0	81.3	82.4	83.4
107.5°	96.4	96.7	97.1	98.4	98.1
110°	113.5	114.1	113.8	113.1	114.1



TEST NUMBER: P1001872

CATALOG NUMBER: SA4XXDIP-B795D365UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	131.2	131.2	130.5	130.5	130.5
115°	149.0	149.0	148.3	148.0	147.6
117.5°	165.7	165.7	165.4	164.4	163.4
120°	182.5	183.9	182.8	181.1	181.8
122.5°	199.9	200.3	199.9	198.9	197.2
125°	217.0	217.0	216.7	216.0	215.3
127.5°	232.4	233.4	232.7	232.0	231.7
130°	248.8	249.8	249.8	249.1	247.8
132.5°	265.5	266.2	265.9	265.2	264.9
135°	279.9	281.9	281.9	281.3	280.2
137.5°	296.0	297.0	297.7	296.6	297.0
140°	312.0	312.7	312.7	312.4	312.0
142.5°	326.7	327.4	327.1	327.1	327.1
145°	340.0	341.4	341.7	341.4	340.4
147.5°	353.7	355.4	355.1	354.7	354.4
150°	366.0	367.4	367.4	367.4	367.0
152.5°	377.6	378.3	378.7	379.7	378.7
155°	389.6	389.6	389.3	390.6	389.3
157.5°	399.8	399.2	399.2	400.2	399.2
160°	408.7	408.4	408.0	409.1	407.4
162.5°	416.9	415.9	415.6	417.6	415.9
165°	424.1	423.1	422.4	424.5	423.1
167.5°	429.9	428.6	428.6	430.6	428.6
170°	434.7	433.0	433.3	435.4	433.0
172.5°	438.1	436.8	436.8	439.1	436.8
175°	441.2	439.5	439.1	441.5	439.1
177.5°	442.6	440.9	440.9	443.2	440.5
180°	441.9	441.9	441.9	441.9	441.9

(END OF REPORT)