

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000874

Luminaire Tested: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000874
REPORT IS A COMBINATION OF REPORTS P995487 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9360.6 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000874

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000874

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	67	61	56	58	53	49	49	46	43	41	39	36
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	41	46	40	36	40	35	32	33	30	27
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	55	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16146	16146	16146
5°	16159	15681	15700
10°	16022	15246	15139
15°	15792	14729	14506
20°	15499	14169	13850
25°	15168	13577	13145
30°	14770	12938	12371
35°	14357	12282	11622
40°	13928	11578	10826
45°	13476	10871	10081
50°	12977	10186	9257
55°	12435	9386	8438
60°	11879	8510	7585
65°	11244	7605	6624
70°	10512	6515	5593
75°	9418	5252	4480
80°	8024	3797	3151
85°	6236	2114	1696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13476 cd/sqm

TEST NUMBER: P1000874

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	2.0
10°-20°	525.8	5.6
20°-30°	773.8	8.3
30°-40°	899.5	9.6
40°-50°	899.4	9.6
50°-60°	786.6	8.4
60°-70°	584.0	6.2
70°-80°	331.4	3.5
80°-90°	97.2	1.0
90°-100°	435.3	4.6
100°-110°	885.3	9.5
110°-120°	789.1	8.4
120°-130°	662.8	7.1
130°-140°	553.1	5.9
140°-150°	422.4	4.5
150°-160°	296.9	3.2
160°-170°	174.6	1.9
170°-180°	56.8	0.6
0°-30°	1486.2	15.9
0°-40°	2385.7	25.5
0°-60°	4071.7	43.5
0°-90°	5084.3	54.3
90°-120°	2109.6	22.5
90°-150°	3748.0	40.0
90°-180°	4276.0	45.7
0°-180°	9360.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1980	1980	1980	1980	1980	
5°	1978	1972	1955	1972	1969	188
15°	1883	1877	1853	1863	1858	531
25°	1706	1694	1672	1674	1667	785
35°	1468	1456	1434	1423	1415	918
45°	1198	1187	1161	1144	1139	923
55°	906	901	879	860	850	811
65°	614	606	590	574	566	608
75°	327	319	311	305	303	347
85°	86	86	82	82	81	92
90°	1	9	21	23	24	8
95°	38	120	938	464	281	42
105°	135	195	755	1626	1620	143
115°	237	298	674	1294	1555	235
125°	330	392	670	1101	1241	294
135°	393	467	664	977	1110	303
145°	452	518	661	824	906	284
155°	515	555	642	728	759	237
165°	561	578	616	652	662	158
175°	585	586	591	599	596	56
180°	586	586	586	586	586	

TEST NUMBER: P1000874

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1980.0	1980.0	1980.0	1980.0	1980.0
2.5°	1986.3	1981.6	1964.1	1980.0	1978.4
5°	1978.4	1972.0	1954.6	1972.0	1968.9
7.5°	1964.1	1957.8	1938.7	1953.0	1951.4
10°	1943.5	1937.1	1916.5	1929.2	1926.0
12.5°	1916.5	1910.2	1888.0	1902.2	1897.5
15°	1883.2	1876.9	1853.1	1862.6	1857.8
17.5°	1845.1	1837.2	1815.0	1821.3	1818.2
20°	1802.3	1794.4	1770.6	1775.3	1772.1
22.5°	1756.3	1745.2	1721.4	1730.9	1724.5
25°	1705.5	1694.4	1672.2	1673.8	1667.4
27.5°	1648.4	1637.3	1616.7	1613.5	1605.6
30°	1591.3	1578.6	1558.0	1551.6	1543.7
32.5°	1531.0	1519.9	1497.7	1489.7	1481.8
35°	1467.5	1456.4	1434.2	1423.1	1415.2
37.5°	1400.9	1391.4	1367.6	1356.5	1345.4
40°	1335.9	1323.2	1299.4	1283.5	1275.6
42.5°	1266.0	1259.7	1232.7	1213.7	1208.9
45°	1197.8	1186.7	1161.3	1143.9	1139.1
47.5°	1126.4	1118.5	1094.7	1075.7	1063.0
50°	1053.4	1047.1	1024.9	1002.7	993.2
52.5°	982.1	974.1	950.3	931.3	918.6
55°	905.9	901.1	878.9	859.9	850.4
57.5°	834.5	829.8	807.5	788.5	779.0
60°	759.9	752.0	731.4	717.1	709.2
62.5°	687.0	680.6	658.4	645.7	637.8
65°	614.0	606.1	590.2	574.3	566.4
67.5°	539.4	533.1	517.2	501.3	499.8
70°	471.2	460.1	447.4	434.7	429.9
72.5°	398.2	387.1	377.6	368.1	363.3
75°	326.8	318.9	311.0	304.6	303.0
77.5°	257.0	253.8	245.9	244.3	239.6
80°	195.1	190.4	187.2	184.0	182.4
82.5°	134.9	133.3	133.3	131.7	130.1
85°	85.7	85.7	82.5	82.5	80.9
87.5°	41.2	39.7	38.1	38.1	38.1
90°	1.2	9.2	20.7	23.0	24.2
92.5°	16.1	88.6	451.3	149.1	104.8
95°	38.0	119.7	938.2	464.5	280.9
97.5°	63.3	132.4	1003.8	948.6	674.6
100°	87.5	149.6	925.6	1312.4	1055.6
102.5°	110.5	170.4	827.7	1540.3	1387.2
105°	134.7	195.1	755.2	1626.1	1619.7
107.5°	161.2	220.4	708.0	1600.2	1730.3
110°	187.6	245.8	686.1	1508.1	1732.6



TEST NUMBER: P1000874

CATALOG NUMBER: SA4XXDIP-B1195D1205UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.0	271.1	675.8	1395.2	1664.6
115°	237.1	297.6	673.5	1294.0	1555.3
117.5°	262.5	322.4	672.3	1214.6	1448.2
120°	287.8	346.5	672.3	1161.0	1360.7
122.5°	310.8	370.2	671.1	1125.8	1291.6
125°	330.4	392.5	670.0	1101.2	1241.0
127.5°	348.8	413.3	667.7	1077.6	1208.8
130°	363.8	433.4	666.5	1049.3	1181.1
132.5°	378.7	450.7	665.4	1015.9	1150.0
135°	392.6	467.4	664.2	977.4	1109.8
137.5°	406.4	481.8	664.2	935.9	1062.6
140°	421.3	495.0	663.1	895.6	1010.8
142.5°	437.5	507.1	663.1	858.2	955.5
145°	452.4	518.0	660.8	824.2	906.0
147.5°	469.7	528.4	657.3	796.0	859.9
150°	485.8	538.2	653.9	770.2	822.0
152.5°	500.8	547.4	648.1	748.2	787.4
155°	514.6	555.4	642.4	727.6	758.6
157.5°	528.4	562.9	636.6	708.0	732.2
160°	541.1	569.2	629.7	688.4	708.0
162.5°	552.6	574.4	622.8	669.4	685.0
165°	560.6	577.9	615.9	652.2	661.9
167.5°	569.8	580.8	609.0	637.2	643.5
170°	575.6	583.1	602.1	622.2	626.3
172.5°	581.4	584.8	595.2	609.0	609.0
175°	584.8	586.0	590.6	598.6	596.3
177.5°	587.1	586.0	587.1	591.2	587.1
180°	586.0	586.0	586.0	586.0	586.0

(END OF REPORT)