

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001882

Luminaire Tested: SA4XXDIP-B795D590UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001882
REPORT IS A COMBINATION OF REPORTS P996507 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D590UB27-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5502.2 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001882

CATALOG NUMBER: SA4XXDIP-B795D590UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001882

CATALOG NUMBER: SA4XXDIP-B795D590UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	56
2	91	84	78	72	85	79	73	68	69	65	61	60	57	54	52	50	48
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	38	35
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21
9	52	39	32	27	49	37	30	25	33	28	23	30	25	21	26	22	19
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10789	10789	10789
5°	10798	10479	10492
10°	10706	10188	10117
15°	10553	9842	9694
20°	10357	9468	9255
25°	10136	9072	8784
30°	9870	8645	8267
35°	9595	8208	7766
40°	9307	7737	7234
45°	9005	7265	6737
50°	8673	6807	6186
55°	8310	6272	5639
60°	7938	5686	5069
65°	7514	5082	4427
70°	7025	4354	3738
75°	6294	3509	2994
80°	5363	2537	2106
85°	4162	1412	1134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9005 cd/sqm

TEST NUMBER: P1001882

CATALOG NUMBER: SA4XXDIP-B795D590UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.7	2.3
10°-20°	351.3	6.4
20°-30°	517.1	9.4
30°-40°	601.1	10.9
40°-50°	601.0	10.9
50°-60°	525.7	9.6
60°-70°	390.3	7.1
70°-80°	221.4	4.0
80°-90°	64.5	1.2
90°-100°	214.3	3.9
100°-110°	435.8	7.9
110°-120°	388.4	7.1
120°-130°	326.3	5.9
130°-140°	272.3	4.9
140°-150°	207.9	3.8
150°-160°	146.2	2.7
160°-170°	86.0	1.6
170°-180°	28.0	0.5
0°-30°	993.1	18.0
0°-40°	1594.2	29.0
0°-60°	2720.9	49.5
0°-90°	3397.1	61.7
90°-120°	1038.5	18.9
90°-150°	1845.0	33.5
90°-180°	2105.0	38.3
0°-180°	5502.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1323	1323	1323	1323	1323	
5°	1322	1318	1306	1318	1316	125
15°	1258	1254	1238	1245	1242	355
25°	1140	1132	1117	1118	1114	524
35°	981	973	958	951	946	613
45°	800	793	776	764	761	617
55°	605	602	587	575	568	542
65°	410	405	394	384	378	406
75°	218	213	208	204	202	232
85°	57	57	55	55	54	62
90°	1	4	10	11	12	5
95°	19	59	462	229	138	21
105°	66	96	372	800	797	71
115°	117	146	332	637	766	116
125°	163	193	330	542	611	145
135°	193	230	327	481	546	149
145°	223	255	325	406	446	140
155°	253	273	316	358	374	117
165°	276	284	303	321	326	78
175°	288	288	291	295	294	27
180°	288	288	288	288	288	

TEST NUMBER: P1001882

CATALOG NUMBER: SA4XXDIP-B795D590UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1323.1	1323.1	1323.1	1323.1	1323.1
2.5°	1327.3	1324.2	1312.5	1323.1	1322.0
5°	1322.0	1317.8	1306.1	1317.8	1315.7
7.5°	1312.5	1308.3	1295.5	1305.1	1304.0
10°	1298.7	1294.5	1280.7	1289.2	1287.1
12.5°	1280.7	1276.5	1261.6	1271.2	1268.0
15°	1258.4	1254.2	1238.3	1244.6	1241.5
17.5°	1233.0	1227.7	1212.8	1217.1	1215.0
20°	1204.4	1199.1	1183.2	1186.3	1184.2
22.5°	1173.6	1166.2	1150.3	1156.7	1152.4
25°	1139.7	1132.3	1117.4	1118.5	1114.2
27.5°	1101.5	1094.1	1080.3	1078.2	1072.9
30°	1063.4	1054.9	1041.1	1036.9	1031.6
32.5°	1023.1	1015.7	1000.8	995.5	990.2
35°	980.7	973.2	958.4	951.0	945.7
37.5°	936.1	929.8	913.9	906.5	899.0
40°	892.7	884.2	868.3	857.7	852.4
42.5°	846.0	841.8	823.8	811.0	807.9
45°	800.4	793.0	776.1	764.4	761.2
47.5°	752.7	747.4	731.5	718.8	710.3
50°	704.0	699.7	684.9	670.0	663.7
52.5°	656.3	650.9	635.0	622.3	613.8
55°	605.4	602.2	587.3	574.6	568.3
57.5°	557.7	554.5	539.6	526.9	520.5
60°	507.8	502.5	488.7	479.2	473.9
62.5°	459.1	454.8	440.0	431.5	426.2
65°	410.3	405.0	394.4	383.8	378.5
67.5°	360.5	356.2	345.6	335.0	334.0
70°	314.9	307.5	299.0	290.5	287.3
72.5°	266.1	258.7	252.3	246.0	242.8
75°	218.4	213.1	207.8	203.6	202.5
77.5°	171.7	169.6	164.3	163.3	160.1
80°	130.4	127.2	125.1	123.0	121.9
82.5°	90.1	89.1	89.1	88.0	86.9
85°	57.2	57.2	55.1	55.1	54.1
87.5°	27.6	26.5	25.4	25.4	25.4
90°	0.6	4.5	10.2	11.3	11.9
92.5°	7.9	43.6	222.1	73.4	51.6
95°	18.7	58.9	461.9	228.6	138.3
97.5°	31.2	65.2	494.2	467.0	332.1
100°	43.1	73.6	455.6	646.0	519.7
102.5°	54.4	83.9	407.5	758.2	682.9
105°	66.3	96.0	371.8	800.4	797.4
107.5°	79.3	108.5	348.5	787.7	851.8
110°	92.4	121.0	337.8	742.4	852.9

TEST NUMBER: P1001882

CATALOG NUMBER: SA4XXDIP-B795D590UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	104.8	133.4	332.7	686.8	819.5
115°	116.7	146.4	331.5	637.0	765.6
117.5°	129.2	158.6	331.0	597.9	712.9
120°	141.7	170.6	331.0	571.5	669.8
122.5°	153.0	182.2	330.4	554.2	635.8
125°	162.6	193.2	329.8	542.0	610.9
127.5°	171.7	203.4	328.7	530.4	595.0
130°	179.1	213.4	328.1	516.6	581.4
132.5°	186.4	221.8	327.6	500.1	566.1
135°	193.2	230.0	327.0	481.2	546.3
137.5°	200.0	237.2	327.0	460.8	523.1
140°	207.4	243.7	326.4	440.9	497.6
142.5°	215.3	249.6	326.4	422.5	470.4
145°	222.7	255.0	325.3	405.8	446.0
147.5°	231.2	260.1	323.6	391.9	423.3
150°	239.1	264.9	321.9	379.1	404.6
152.5°	246.5	269.5	319.1	368.4	387.6
155°	253.3	273.4	316.2	358.2	373.5
157.5°	260.1	277.1	313.4	348.5	360.4
160°	266.4	280.2	310.0	338.9	348.5
162.5°	272.0	282.8	306.6	329.6	337.2
165°	276.0	284.5	303.2	321.0	325.9
167.5°	280.5	285.9	299.8	313.6	316.8
170°	283.4	287.0	296.4	306.4	308.3
172.5°	286.2	287.9	293.0	299.8	299.8
175°	287.9	288.5	290.7	294.7	293.6
177.5°	289.0	288.5	289.0	291.0	289.0
180°	288.5	288.5	288.5	288.5	288.5

(END OF REPORT)