

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000894

Luminaire Tested: SA4XXDIP-B1195D1205UB30-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000894
REPORT IS A COMBINATION OF REPORTS P995507 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1205UB30-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9041.0 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000894

CATALOG NUMBER: SA4XXDIP-B1195D1205UB30-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1000894

CATALOG NUMBER: SA4XXDIP-B1195D1205UB30-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	97	92	88	84	89	85	81	78	71	69	66	59	57	55	48	47	45
2	88	80	73	68	80	74	68	63	62	58	54	51	48	45	42	39	37
3	80	70	62	56	73	64	58	52	54	49	45	45	41	38	36	34	31
4	73	61	53	47	67	57	50	44	48	42	38	40	36	32	32	29	27
5	67	55	46	40	61	51	43	37	43	37	33	36	31	28	29	26	23
6	61	49	40	34	56	45	38	32	38	33	28	32	28	24	26	23	20
7	57	44	36	30	52	41	33	28	35	29	25	29	25	21	24	20	18
8	52	40	32	26	48	37	30	25	32	26	22	27	22	19	22	18	16
9	49	36	29	24	45	34	27	22	29	23	20	24	20	17	20	17	14
10	46	33	26	21	42	31	24	20	27	21	18	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11653	11653	11653
5°	11685	11349	11370
10°	11609	11126	11094
15°	11501	10875	10783
20°	11339	10603	10481
25°	11158	10303	10156
30°	10962	10006	9823
35°	10739	9702	9528
40°	10561	9411	9221
45°	10298	9137	8950
50°	10073	8827	8665
55°	9841	8527	8336
60°	9481	8155	8027
65°	9085	7753	7654
70°	8605	7294	7225
75°	7931	6784	6815
80°	7173	6263	6384
85°	6171	5740	6037

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10298 cd/sqm

TEST NUMBER: P1000894

CATALOG NUMBER: SA4XXDIP-B1195D1205UB30-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.4	1.5
10°-20°	387.9	4.3
20°-30°	586.6	6.5
30°-40°	709.6	7.8
40°-50°	750.2	8.3
50°-60°	706.0	7.8
60°-70°	585.9	6.5
70°-80°	411.1	4.5
80°-90°	235.0	2.6
90°-100°	235.8	2.6
100°-110°	395.3	4.4
110°-120°	566.5	6.3
120°-130°	695.3	7.7
130°-140°	754.3	8.3
140°-150°	728.3	8.1
150°-160°	609.8	6.7
160°-170°	405.7	4.5
170°-180°	142.1	1.6
0°-30°	1109.9	12.3
0°-40°	1819.6	20.1
0°-60°	3275.8	36.2
0°-90°	4507.8	49.9
90°-120°	1197.7	13.2
90°-150°	3375.6	37.3
90°-180°	4533.0	50.1
0°-180°	9041.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1429	1429	1429	1429	1429	
5°	1431	1426	1415	1427	1426	136
15°	1371	1373	1368	1383	1381	386
25°	1255	1264	1269	1287	1288	578
35°	1098	1117	1133	1155	1160	687
45°	915	946	976	1003	1011	707
55°	717	750	798	830	840	639
65°	496	547	602	642	654	492
75°	275	334	402	446	461	292
85°	85	152	224	272	288	88
90°	29	106	184	237	252	23
95°	90	154	227	274	288	92
105°	285	318	382	425	442	303
115°	516	530	579	613	623	509
125°	744	742	781	809	816	663
135°	954	961	972	996	1002	739
145°	1157	1160	1161	1170	1172	724
155°	1324	1324	1323	1327	1323	609
165°	1441	1438	1435	1442	1438	406
175°	1499	1493	1492	1500	1492	142
180°	1501	1501	1501	1501	1501	

TEST NUMBER: P1000894

CATALOG NUMBER: SA4XXDIP-B1195D1205UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1429.0	1429.0	1429.0	1429.0	1429.0
2.5°	1435.4	1430.6	1417.8	1429.0	1427.4
5°	1430.6	1425.8	1414.6	1427.4	1425.8
7.5°	1421.0	1417.8	1408.2	1422.6	1421.0
10°	1408.2	1406.6	1398.6	1413.0	1411.4
12.5°	1390.6	1390.6	1385.8	1398.6	1398.6
15°	1371.4	1373.0	1368.2	1382.6	1381.0
17.5°	1345.8	1350.6	1349.0	1363.4	1361.8
20°	1318.6	1323.4	1325.0	1341.0	1341.0
22.5°	1288.2	1294.6	1297.8	1313.8	1317.0
25°	1254.6	1264.2	1269.0	1286.6	1288.2
27.5°	1217.8	1232.2	1238.6	1254.6	1256.2
30°	1181.0	1193.8	1205.0	1222.6	1225.8
32.5°	1140.9	1157.0	1169.8	1190.6	1193.8
35°	1097.7	1116.9	1132.9	1155.4	1160.2
37.5°	1054.5	1076.9	1096.1	1118.5	1123.3
40°	1012.9	1033.7	1056.1	1080.1	1086.5
42.5°	964.9	988.9	1016.1	1043.3	1048.1
45°	915.3	945.7	976.1	1003.3	1011.3
47.5°	868.9	899.3	934.5	961.7	971.3
50°	817.7	852.9	888.1	920.1	929.7
52.5°	766.5	801.7	843.3	875.3	884.9
55°	716.9	750.5	798.5	830.5	840.1
57.5°	660.9	702.5	748.9	787.3	795.3
60°	606.5	648.1	700.9	737.7	750.5
62.5°	553.7	600.1	652.9	689.7	702.5
65°	496.1	547.3	601.7	641.7	654.5
67.5°	441.7	496.1	553.7	593.7	606.5
70°	385.7	440.1	500.9	544.1	555.3
72.5°	331.2	387.3	452.9	494.5	507.3
75°	275.2	334.4	401.7	446.5	460.9
77.5°	222.4	284.8	355.2	400.1	416.1
80°	174.4	238.4	308.8	356.8	369.6
82.5°	126.4	193.6	264.0	313.6	328.0
85°	84.8	152.0	224.0	272.0	288.0
87.5°	52.8	118.4	188.8	235.2	249.6
90°	29.1	105.9	183.9	237.3	252.4
92.5°	54.2	125.3	199.9	248.2	262.1
95°	90.5	153.7	227.4	274.1	288.5
97.5°	130.7	186.4	261.3	307.5	321.9
100°	180.2	226.4	299.3	344.8	356.0
102.5°	233.6	269.9	340.0	385.1	399.1
105°	285.0	318.1	382.0	425.4	441.7
107.5°	341.8	370.2	427.4	472.0	482.1
110°	398.3	423.0	477.9	512.3	528.6

TEST NUMBER: P1000894

CATALOG NUMBER: SA4XXDIP-B1195D1205UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	457.1	476.3	526.8	562.0	574.8
115°	515.9	530.3	579.1	613.2	623.2
117.5°	572.8	582.4	629.2	659.3	668.6
120°	628.1	637.5	680.4	706.6	721.7
122.5°	687.3	688.4	730.5	759.0	764.4
125°	743.7	742.1	781.0	809.1	816.3
127.5°	796.0	797.9	827.6	854.0	864.1
130°	850.1	852.0	877.6	904.1	909.0
132.5°	907.0	907.7	925.8	950.7	959.1
135°	954.2	961.2	972.4	995.6	1001.8
137.5°	1008.8	1010.7	1019.4	1039.9	1049.1
140°	1063.3	1064.1	1065.7	1085.3	1092.1
142.5°	1111.7	1114.0	1111.2	1128.8	1135.2
145°	1157.0	1160.0	1161.2	1169.6	1172.5
147.5°	1203.4	1207.6	1206.4	1206.9	1212.1
150°	1245.2	1248.3	1248.3	1248.3	1247.1
152.5°	1283.1	1285.4	1286.6	1290.1	1286.6
155°	1323.7	1323.7	1322.6	1327.2	1322.6
157.5°	1358.6	1356.2	1356.2	1359.7	1356.2
160°	1388.8	1387.6	1386.4	1389.9	1384.1
162.5°	1416.6	1413.1	1412.0	1418.9	1413.1
165°	1441.0	1437.5	1435.2	1442.2	1437.5
167.5°	1460.7	1456.1	1456.1	1463.1	1456.1
170°	1477.0	1471.2	1472.4	1479.3	1471.2
172.5°	1488.6	1484.0	1484.0	1492.1	1484.0
175°	1499.1	1493.3	1492.1	1500.2	1492.1
177.5°	1503.7	1497.9	1497.9	1506.0	1496.7
180°	1501.4	1501.4	1501.4	1501.4	1501.4

(END OF REPORT)