

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001906

Luminaire Tested: SA4XXDIP-B795D590UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001906
REPORT IS A COMBINATION OF REPORTS P996531 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D590UB30-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5549.3 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001906

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001906

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	56
2	91	84	78	72	85	79	73	68	69	65	61	60	57	54	52	50	48
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	38	35
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21
9	52	39	32	27	49	37	30	25	33	28	23	30	25	21	26	22	19
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10881	10881	10881
5°	10890	10568	10581
10°	10798	10275	10203
15°	10643	9926	9777
20°	10445	9549	9334
25°	10223	9150	8859
30°	9954	8719	8338
35°	9676	8278	7833
40°	9387	7803	7296
45°	9083	7327	6794
50°	8747	6865	6238
55°	8380	6326	5687
60°	8007	5735	5111
65°	7578	5126	4464
70°	7086	4390	3770
75°	6349	3540	3019
80°	5408	2559	2125
85°	4199	1425	1142

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9083 cd/sqm

TEST NUMBER: P1001906

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.8	2.3
10°-20°	354.3	6.4
20°-30°	521.5	9.4
30°-40°	606.2	10.9
40°-50°	606.2	10.9
50°-60°	530.2	9.6
60°-70°	393.6	7.1
70°-80°	223.3	4.0
80°-90°	65.1	1.2
90°-100°	216.1	3.9
100°-110°	439.5	7.9
110°-120°	391.8	7.1
120°-130°	329.1	5.9
130°-140°	274.6	4.9
140°-150°	209.7	3.8
150°-160°	147.4	2.7
160°-170°	86.7	1.6
170°-180°	28.2	0.5
0°-30°	1001.6	18.0
0°-40°	1607.8	29.0
0°-60°	2744.1	49.5
0°-90°	3426.1	61.7
90°-120°	1047.4	18.9
90°-150°	1860.8	33.5
90°-180°	2123.0	38.3
0°-180°	5549.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1334	1334	1334	1334	1334	
5°	1333	1329	1317	1329	1327	127
15°	1269	1265	1249	1255	1252	358
25°	1149	1142	1127	1128	1124	529
35°	989	982	967	959	954	618
45°	807	800	783	771	768	622
55°	610	607	592	580	573	547
65°	414	408	398	387	382	410
75°	220	215	210	205	204	234
85°	58	58	56	56	54	62
90°	1	5	10	11	12	5
95°	19	59	466	231	140	21
105°	67	97	375	807	804	71
115°	118	148	334	642	772	117
125°	164	195	333	547	616	146
135°	195	232	330	485	551	151
145°	225	257	328	409	450	141
155°	256	276	319	361	377	118
165°	278	287	306	324	329	79
175°	290	291	293	297	296	28
180°	291	291	291	291	291	

TEST NUMBER: P1001906

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1334.4	1334.4	1334.4	1334.4	1334.4
2.5°	1338.7	1335.5	1323.7	1334.4	1333.3
5°	1333.3	1329.1	1317.3	1329.1	1326.9
7.5°	1323.7	1319.4	1306.6	1316.2	1315.2
10°	1309.8	1305.5	1291.6	1300.2	1298.0
12.5°	1291.6	1287.4	1272.4	1282.0	1278.8
15°	1269.2	1264.9	1248.9	1255.3	1252.1
17.5°	1243.5	1238.2	1223.2	1227.5	1225.3
20°	1214.6	1209.3	1193.3	1196.5	1194.3
22.5°	1183.6	1176.2	1160.1	1166.5	1162.3
25°	1149.4	1141.9	1127.0	1128.0	1123.8
27.5°	1110.9	1103.4	1089.5	1087.4	1082.1
30°	1072.4	1063.9	1050.0	1045.7	1040.4
32.5°	1031.8	1024.3	1009.4	1004.0	998.7
35°	989.0	981.6	966.6	959.1	953.8
37.5°	944.1	937.7	921.7	914.2	906.7
40°	900.3	891.7	875.7	865.0	859.7
42.5°	853.2	849.0	830.8	818.0	814.8
45°	807.3	799.8	782.7	770.9	767.7
47.5°	759.2	753.8	737.8	724.9	716.4
50°	710.0	705.7	690.7	675.8	669.3
52.5°	661.9	656.5	640.5	627.6	619.1
55°	610.5	607.3	592.4	579.5	573.1
57.5°	562.4	559.2	544.2	531.4	525.0
60°	512.2	506.8	492.9	483.3	477.9
62.5°	463.0	458.7	443.7	435.2	429.8
65°	413.8	408.4	397.8	387.1	381.7
67.5°	363.5	359.3	348.6	337.9	336.8
70°	317.6	310.1	301.5	293.0	289.8
72.5°	268.4	260.9	254.5	248.1	244.9
75°	220.3	214.9	209.6	205.3	204.2
77.5°	173.2	171.1	165.7	164.7	161.5
80°	131.5	128.3	126.2	124.0	123.0
82.5°	90.9	89.8	89.8	88.7	87.7
85°	57.7	57.7	55.6	55.6	54.5
87.5°	27.8	26.7	25.7	25.7	25.7
90°	0.6	4.6	10.3	11.4	12.0
92.5°	8.0	44.0	224.0	74.1	52.0
95°	18.9	59.4	465.8	230.6	139.5
97.5°	31.4	65.7	498.4	471.0	334.9
100°	43.4	74.3	459.5	651.6	524.1
102.5°	54.9	84.6	410.9	764.8	688.7
105°	66.9	96.9	374.9	807.3	804.2
107.5°	80.0	109.4	351.5	794.5	859.0
110°	93.2	122.0	340.6	748.8	860.2



TEST NUMBER: P1001906

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	105.7	134.6	335.5	692.8	826.5
115°	117.7	147.8	334.4	642.4	772.2
117.5°	130.3	160.0	333.8	603.0	719.0
120°	142.9	172.0	333.8	576.4	675.6
122.5°	154.3	183.8	333.2	559.0	641.3
125°	164.0	194.9	332.6	546.7	616.1
127.5°	173.2	205.2	331.5	535.0	600.1
130°	180.6	215.2	330.9	521.0	586.4
132.5°	188.0	223.8	330.4	504.4	571.0
135°	194.9	232.0	329.8	485.2	551.0
137.5°	201.8	239.2	329.8	464.6	527.5
140°	209.2	245.8	329.2	444.7	501.8
142.5°	217.2	251.8	329.2	426.1	474.4
145°	224.6	257.2	328.1	409.2	449.8
147.5°	233.2	262.4	326.4	395.2	427.0
150°	241.2	267.2	324.6	382.4	408.1
152.5°	248.6	271.8	321.8	371.5	390.9
155°	255.5	275.8	318.9	361.2	376.7
157.5°	262.3	279.5	316.1	351.5	363.5
160°	268.6	282.6	312.6	341.8	351.5
162.5°	274.3	285.2	309.2	332.4	340.1
165°	278.3	286.9	305.8	323.8	328.6
167.5°	282.9	288.4	302.4	316.4	319.5
170°	285.8	289.5	298.9	309.0	310.9
172.5°	288.6	290.4	295.5	302.4	302.4
175°	290.4	290.9	293.2	297.2	296.1
177.5°	291.5	290.9	291.5	293.5	291.5
180°	290.9	290.9	290.9	290.9	290.9

(END OF REPORT)