

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000913

Luminaire Tested: SA4XXDIP-B1195D1205UB40-4F0-XX-W2A-D4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000913
REPORT IS A COMBINATION OF REPORTS P995526 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1205UB40-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9136.5 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000913

CATALOG NUMBER: SA4XXDIP-B1195D1205UB40-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1000913

CATALOG NUMBER: SA4XXDIP-B1195D1205UB40-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	97	92	88	84	89	85	81	78	71	68	66	59	57	55	47	46	45
2	88	80	73	68	80	73	68	63	62	57	54	51	48	45	41	39	37
3	80	70	62	56	73	64	57	52	54	49	45	45	41	38	36	33	31
4	73	61	53	47	66	57	49	44	48	42	38	40	35	32	32	29	26
5	67	54	46	40	61	50	43	37	43	37	32	35	31	27	29	25	23
6	61	49	40	34	56	45	38	32	38	32	28	32	27	24	26	23	20
7	57	44	36	30	52	41	33	28	35	29	25	29	24	21	24	20	18
8	52	40	32	26	48	37	30	25	32	26	22	26	22	19	22	18	16
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	17	14
10	46	33	26	21	42	31	24	20	27	21	17	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11588	11588	11588
5°	11620	11286	11307
10°	11545	11064	11033
15°	11437	10814	10723
20°	11277	10544	10422
25°	11096	10246	10099
30°	10901	9951	9769
35°	10681	9649	9474
40°	10502	9359	9170
45°	10241	9087	8901
50°	10018	8778	8617
55°	9786	8480	8290
60°	9428	8109	7982
65°	9034	7709	7612
70°	8556	7253	7184
75°	7887	6745	6776
80°	7136	6228	6350
85°	6134	5709	6003

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10241 cd/sqm

TEST NUMBER: P1000913

CATALOG NUMBER: SA4XXDIP-B1195D1205UB40-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.6	1.5
10°-20°	385.8	4.2
20°-30°	583.3	6.4
30°-40°	705.7	7.7
40°-50°	746.0	8.2
50°-60°	702.1	7.7
60°-70°	582.6	6.4
70°-80°	408.9	4.5
80°-90°	232.8	2.5
90°-100°	573.8	6.3
100°-110°	989.6	10.8
110°-120°	859.7	9.4
120°-130°	703.2	7.7
130°-140°	571.4	6.3
140°-150°	427.0	4.7
150°-160°	297.8	3.3
160°-170°	175.2	1.9
170°-180°	57.0	0.6
0°-30°	1103.7	12.1
0°-40°	1809.5	19.8
0°-60°	3257.6	35.7
0°-90°	4481.9	49.1
90°-120°	2423.1	26.5
90°-150°	4124.7	45.1
90°-180°	4655.0	50.9
0°-180°	9136.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1421	1421	1421	1421	1421	
5°	1423	1418	1407	1420	1418	135
15°	1364	1365	1361	1375	1373	384
25°	1248	1257	1262	1279	1281	575
35°	1092	1111	1127	1149	1154	684
45°	910	940	971	998	1006	704
55°	713	746	794	826	836	635
65°	493	544	598	638	651	489
75°	274	333	399	444	458	291
85°	84	151	223	270	286	88
90°	27	98	178	227	241	20
95°	59	193	1080	647	477	58
105°	149	242	862	1776	1782	160
115°	247	322	750	1408	1681	246
125°	338	399	717	1179	1329	302
135°	397	472	681	1020	1162	307
145°	455	520	663	836	925	286
155°	516	557	644	730	761	238
165°	562	580	618	654	664	159
175°	587	588	592	600	598	56
180°	588	588	588	588	588	

TEST NUMBER: P1000913

CATALOG NUMBER: SA4XXDIP-B1195D1205UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1421.1	1421.1	1421.1	1421.1	1421.1
2.5°	1427.4	1422.7	1409.9	1421.1	1419.5
5°	1422.7	1417.9	1406.7	1419.5	1417.9
7.5°	1413.1	1409.9	1400.4	1414.7	1413.1
10°	1400.4	1398.8	1390.8	1405.2	1403.6
12.5°	1382.9	1382.9	1378.1	1390.8	1390.8
15°	1363.8	1365.4	1360.6	1374.9	1373.3
17.5°	1338.3	1343.1	1341.5	1355.8	1354.2
20°	1311.3	1316.0	1317.6	1333.5	1333.5
22.5°	1281.0	1287.4	1290.6	1306.5	1309.7
25°	1247.6	1257.2	1261.9	1279.4	1281.0
27.5°	1211.0	1225.3	1231.7	1247.6	1249.2
30°	1174.4	1187.1	1198.3	1215.8	1219.0
32.5°	1134.6	1150.5	1163.3	1184.0	1187.1
35°	1091.7	1110.8	1126.7	1148.9	1153.7
37.5°	1048.7	1071.0	1090.1	1112.3	1117.1
40°	1007.3	1028.0	1050.3	1074.2	1080.5
42.5°	959.6	983.4	1010.5	1037.6	1042.3
45°	910.2	940.5	970.7	997.8	1005.7
47.5°	864.1	894.3	929.3	956.4	965.9
50°	813.2	848.2	883.2	915.0	924.6
52.5°	762.3	797.3	838.6	870.5	880.0
55°	712.9	746.3	794.1	825.9	835.5
57.5°	657.2	698.6	744.7	782.9	790.9
60°	603.1	644.5	697.0	733.6	746.3
62.5°	550.6	596.8	649.3	685.9	698.6
65°	493.3	544.2	598.3	638.1	650.9
67.5°	439.2	493.3	550.6	590.4	603.1
70°	383.5	437.6	498.1	541.1	552.2
72.5°	329.4	385.1	450.3	491.7	504.5
75°	273.7	332.6	399.4	444.0	458.3
77.5°	221.2	283.3	353.3	397.8	413.7
80°	173.5	237.1	307.1	354.9	367.6
82.5°	125.7	192.6	262.6	311.9	326.2
85°	84.3	151.2	222.8	270.5	286.4
87.5°	52.5	117.8	187.8	233.9	248.2
90°	26.7	98.3	178.3	226.8	240.6
92.5°	40.1	168.5	600.6	342.2	310.4
95°	58.8	193.2	1079.5	647.3	477.4
97.5°	82.6	198.0	1137.4	1123.4	862.9
100°	105.3	209.0	1049.3	1480.2	1233.9
102.5°	128.4	223.4	943.2	1699.4	1558.5
105°	149.4	241.8	862.5	1775.8	1782.2
107.5°	176.0	262.6	807.2	1741.9	1883.5
110°	200.9	281.5	778.9	1640.0	1877.8

TEST NUMBER: P1000913

CATALOG NUMBER: SA4XXDIP-B1195D1205UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	224.7	302.1	760.5	1517.3	1800.2
115°	247.4	322.4	750.3	1407.7	1680.9
117.5°	272.8	342.5	741.1	1318.5	1565.6
120°	296.7	360.2	733.2	1255.2	1468.3
122.5°	319.8	379.2	724.1	1212.0	1389.5
125°	337.8	398.6	716.6	1179.2	1329.1
127.5°	356.3	419.4	706.3	1146.0	1288.8
130°	369.7	438.0	697.2	1109.8	1251.5
132.5°	384.7	455.3	689.7	1068.3	1212.4
135°	397.0	472.0	680.6	1020.2	1162.4
137.5°	410.8	484.8	674.3	970.6	1105.6
140°	425.8	498.2	668.3	922.2	1045.6
142.5°	440.4	510.2	665.1	878.3	982.3
145°	455.4	519.6	662.8	836.2	924.7
147.5°	472.7	530.0	659.3	800.1	870.6
150°	488.9	539.8	655.9	772.5	824.5
152.5°	502.3	549.0	650.1	750.6	789.8
155°	516.2	557.2	644.3	729.8	760.9
157.5°	530.0	564.7	638.6	710.2	734.4
160°	542.7	571.0	631.6	690.5	710.1
162.5°	554.3	576.2	624.7	671.4	687.0
165°	562.3	579.7	617.8	654.2	664.0
167.5°	571.6	582.6	610.8	639.2	645.5
170°	577.4	584.8	603.9	624.1	628.2
172.5°	583.1	586.6	597.0	610.8	610.8
175°	586.6	587.7	592.4	600.4	598.1
177.5°	588.9	587.7	588.9	593.0	588.9
180°	587.7	587.7	587.7	587.7	587.7

(END OF REPORT)