

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001911

Luminaire Tested: SA4XXDIP-B795D590UB35-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001911
REPORT IS A COMBINATION OF REPORTS P996536 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D590UB35-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5331.0 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001911

CATALOG NUMBER: SA4XXDIP-B795D590UB35-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001911

CATALOG NUMBER: SA4XXDIP-B795D590UB35-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	98	93	89	85	91	87	83	80	75	72	69	64	61	59	53	52	50
2	89	81	74	68	82	75	69	64	65	60	56	55	52	49	46	44	41
3	81	71	63	56	75	66	59	53	57	51	47	48	44	41	41	37	35
4	74	62	54	47	68	58	51	45	50	44	40	43	38	35	36	33	30
5	68	55	47	40	62	52	44	38	45	39	34	38	33	30	32	29	26
6	62	50	41	35	58	46	39	33	40	34	29	35	30	26	29	25	22
7	57	45	36	31	53	42	34	29	36	30	26	31	26	23	27	23	20
8	53	41	32	27	49	38	31	26	33	27	23	29	24	20	24	21	18
9	50	37	29	24	46	35	28	23	30	25	20	26	22	18	22	19	16
10	46	34	26	21	43	32	25	20	28	22	18	24	20	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7821	7821	7821
5°	7843	7617	7631
10°	7791	7467	7446
15°	7718	7299	7237
20°	7611	7116	7034
25°	7489	6915	6816
30°	7357	6715	6593
35°	7208	6512	6395
40°	7089	6317	6190
45°	6911	6133	6008
50°	6761	5924	5816
55°	6605	5723	5595
60°	6364	5473	5387
65°	6097	5203	5138
70°	5774	4896	4849
75°	5323	4553	4573
80°	4816	4204	4286
85°	4141	3854	4052

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6911 cd/sqm

TEST NUMBER: P1001911

CATALOG NUMBER: SA4XXDIP-B795D590UB35-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	1.7
10°-20°	260.4	4.9
20°-30°	393.7	7.4
30°-40°	476.3	8.9
40°-50°	503.5	9.4
50°-60°	473.9	8.9
60°-70°	393.2	7.4
70°-80°	276.0	5.2
80°-90°	157.2	2.9
90°-100°	141.0	2.6
100°-110°	213.5	4.0
110°-120°	292.2	5.5
120°-130°	350.6	6.6
130°-140°	375.9	7.1
140°-150°	360.6	6.8
150°-160°	301.4	5.7
160°-170°	200.6	3.8
170°-180°	70.2	1.3
0°-30°	744.9	14.0
0°-40°	1221.2	22.9
0°-60°	2198.6	41.2
0°-90°	3025.0	56.7
90°-120°	646.7	12.1
90°-150°	1733.7	32.5
90°-180°	2306.0	43.3
0°-180°	5331.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	959	959	959	959	959	
5°	960	957	949	958	957	91
15°	920	922	918	928	927	259
25°	842	848	852	864	865	388
35°	737	750	760	776	779	461
45°	614	635	655	673	679	475
55°	481	504	536	557	564	429
65°	333	367	404	431	439	330
75°	185	224	270	300	309	196
85°	57	102	150	183	193	59
90°	19	68	119	154	163	14
95°	48	89	137	168	177	48
105°	144	165	208	236	246	153
115°	257	266	300	323	330	254
125°	369	368	394	413	418	329
135°	472	476	483	499	504	366
145°	572	574	574	580	582	358
155°	654	654	654	656	654	301
165°	712	711	710	713	711	201
175°	741	738	738	742	738	70
180°	742	742	742	742	742	

TEST NUMBER: P1001911

CATALOG NUMBER: SA4XXDIP-B795D590UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	959.1	959.1	959.1	959.1	959.1
2.5°	963.4	960.2	951.6	959.1	958.0
5°	960.2	957.0	949.4	958.0	957.0
7.5°	953.7	951.6	945.1	954.8	953.7
10°	945.1	944.1	938.7	948.4	947.3
12.5°	933.3	933.3	930.1	938.7	938.7
15°	920.4	921.5	918.3	928.0	926.9
17.5°	903.3	906.5	905.4	915.1	914.0
20°	885.0	888.2	889.3	900.0	900.0
22.5°	864.6	868.9	871.0	881.8	883.9
25°	842.0	848.5	851.7	863.5	864.6
27.5°	817.3	827.0	831.3	842.0	843.1
30°	792.6	801.2	808.7	820.6	822.7
32.5°	765.8	776.5	785.1	799.1	801.2
35°	736.8	749.7	760.4	775.5	778.7
37.5°	707.8	722.8	735.7	750.7	754.0
40°	679.9	693.8	708.9	725.0	729.3
42.5°	647.6	663.8	682.0	700.3	703.5
45°	614.3	634.8	655.2	673.4	678.8
47.5°	583.2	603.6	627.2	645.5	651.9
50°	548.8	572.5	596.1	617.6	624.0
52.5°	514.5	538.1	566.0	587.5	593.9
55°	481.2	503.7	535.9	557.4	563.9
57.5°	443.6	471.5	502.6	528.4	533.8
60°	407.1	435.0	470.4	495.1	503.7
62.5°	371.6	402.8	438.2	462.9	471.5
65°	332.9	367.3	403.8	430.7	439.3
67.5°	296.4	332.9	371.6	398.5	407.1
70°	258.8	295.4	336.2	365.2	372.7
72.5°	222.3	259.9	304.0	331.9	340.5
75°	184.7	224.5	269.6	299.7	309.3
77.5°	149.3	191.2	238.4	268.5	279.2
80°	117.1	160.0	207.3	239.5	248.1
82.5°	84.8	130.0	177.2	210.5	220.2
85°	56.9	102.0	150.4	182.6	193.3
87.5°	35.4	79.5	126.7	157.9	167.5
90°	18.9	68.1	118.9	153.6	163.3
92.5°	31.0	76.1	125.2	157.0	166.2
95°	48.4	89.0	137.0	167.7	177.4
97.5°	68.0	103.7	152.4	182.6	192.3
100°	92.2	122.4	169.4	199.6	207.1
102.5°	118.6	142.7	188.2	217.9	227.0
105°	143.5	165.4	207.5	236.0	246.4
107.5°	171.6	190.4	228.5	257.7	264.6
110°	199.2	215.3	252.4	275.9	286.2



TEST NUMBER: P1001911

CATALOG NUMBER: SA4XXDIP-B795D590UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	227.9	240.8	275.1	298.8	307.4
115°	256.7	266.4	299.6	322.7	329.6
117.5°	284.8	291.3	322.9	343.8	350.7
120°	311.9	317.4	346.8	365.4	375.2
122.5°	341.2	341.8	370.2	389.9	394.6
125°	368.8	367.7	394.0	413.3	418.5
127.5°	394.6	395.3	415.6	433.8	440.8
130°	421.1	421.7	438.9	457.2	461.3
132.5°	449.2	449.3	461.6	478.8	484.6
135°	472.2	475.7	483.3	499.3	504.0
137.5°	499.2	499.9	505.4	519.8	525.7
140°	526.2	526.3	527.3	540.8	545.6
142.5°	549.9	551.0	549.4	561.2	565.5
145°	572.3	573.5	574.0	579.9	582.4
147.5°	595.2	597.0	596.4	596.9	600.7
150°	615.9	617.1	617.1	617.1	616.5
152.5°	634.3	635.5	636.0	637.8	636.0
155°	654.4	654.4	653.8	656.1	653.8
157.5°	671.6	670.5	670.5	672.2	670.5
160°	686.5	686.0	685.4	687.1	684.3
162.5°	700.3	698.6	698.0	701.5	698.6
165°	712.4	710.7	709.5	713.0	710.7
167.5°	722.1	719.8	719.8	723.3	719.8
170°	730.2	727.3	727.9	731.3	727.3
172.5°	735.9	733.6	733.6	737.6	733.6
175°	741.1	738.2	737.6	741.7	737.6
177.5°	743.4	740.5	740.5	744.5	739.9
180°	742.2	742.2	742.2	742.2	742.2

(END OF REPORT)