

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000916

Luminaire Tested: SA4XXDIP-B1195D1205UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000916
REPORT IS A COMBINATION OF REPORTS P995529 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1205UB40-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9388.6 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000916

CATALOG NUMBER: SA4XXDIP-B1195D1205UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000916

CATALOG NUMBER: SA4XXDIP-B1195D1205UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	67	61	56	58	53	49	49	46	43	41	39	36
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	41	46	40	36	40	35	32	33	30	27
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	55	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16193	16193	16193
5°	16206	15728	15747
10°	16069	15291	15184
15°	15839	14772	14549
20°	15545	14210	13892
25°	15213	13617	13184
30°	14814	12976	12407
35°	14400	12318	11656
40°	13969	11612	10857
45°	13517	10904	10111
50°	13016	10216	9284
55°	12472	9414	8463
60°	11915	8534	7608
65°	11277	7627	6644
70°	10544	6534	5610
75°	9446	5267	4493
80°	8049	3809	3161
85°	6251	2119	1702

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13517 cd/sqm

TEST NUMBER: P1000916

CATALOG NUMBER: SA4XXDIP-B1195D1205UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	2.0
10°-20°	527.3	5.6
20°-30°	776.1	8.3
30°-40°	902.1	9.6
40°-50°	902.1	9.6
50°-60°	789.0	8.4
60°-70°	585.7	6.2
70°-80°	332.3	3.5
80°-90°	97.4	1.0
90°-100°	436.6	4.7
100°-110°	888.0	9.5
110°-120°	791.5	8.4
120°-130°	664.8	7.1
130°-140°	554.8	5.9
140°-150°	423.7	4.5
150°-160°	297.8	3.2
160°-170°	175.2	1.9
170°-180°	57.0	0.6
0°-30°	1490.6	15.9
0°-40°	2392.7	25.5
0°-60°	4083.7	43.5
0°-90°	5099.2	54.3
90°-120°	2116.0	22.5
90°-150°	3759.4	40.0
90°-180°	4289.0	45.7
0°-180°	9388.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1986	1986	1986	1986	1986	
5°	1984	1978	1960	1978	1975	188
15°	1889	1882	1858	1868	1863	532
25°	1710	1699	1677	1679	1672	787
35°	1472	1461	1438	1427	1419	920
45°	1201	1190	1165	1147	1142	926
55°	909	904	882	862	853	814
65°	616	608	592	576	568	609
75°	328	320	312	306	304	348
85°	86	86	83	83	81	92
90°	1	9	21	23	24	8
95°	38	120	941	466	282	42
105°	135	196	758	1631	1625	144
115°	238	298	676	1298	1560	236
125°	331	394	672	1104	1245	295
135°	394	469	666	980	1113	304
145°	454	520	663	827	909	285
155°	516	557	644	730	761	238
165°	562	580	618	654	664	159
175°	587	588	592	600	598	56
180°	588	588	588	588	588	

TEST NUMBER: P1000916

CATALOG NUMBER: SA4XXDIP-B1195D1205UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1985.8	1985.8	1985.8	1985.8	1985.8
2.5°	1992.2	1987.4	1969.9	1985.8	1984.2
5°	1984.2	1977.9	1960.4	1977.9	1974.7
7.5°	1969.9	1963.5	1944.5	1958.8	1957.2
10°	1949.2	1942.9	1922.2	1934.9	1931.7
12.5°	1922.2	1915.8	1893.5	1907.9	1903.1
15°	1888.8	1882.4	1858.5	1868.1	1863.3
17.5°	1850.6	1842.6	1820.3	1826.7	1823.5
20°	1807.6	1799.7	1775.8	1780.6	1777.4
22.5°	1761.5	1750.3	1726.5	1736.0	1729.6
25°	1710.5	1699.4	1677.1	1678.7	1672.4
27.5°	1653.3	1642.1	1621.4	1618.3	1610.3
30°	1596.0	1583.2	1562.6	1556.2	1548.2
32.5°	1535.5	1524.4	1502.1	1494.1	1486.2
35°	1471.9	1460.7	1438.4	1427.3	1419.4
37.5°	1405.0	1395.5	1371.6	1360.5	1349.3
40°	1339.8	1327.1	1303.2	1287.3	1279.3
42.5°	1269.8	1263.4	1236.4	1217.3	1212.5
45°	1201.4	1190.2	1164.8	1147.3	1142.5
47.5°	1129.8	1121.8	1097.9	1078.8	1066.1
50°	1056.6	1050.2	1027.9	1005.6	996.1
52.5°	985.0	977.0	953.1	934.0	921.3
55°	908.6	903.8	881.5	862.4	852.9
57.5°	837.0	832.2	809.9	790.8	781.3
60°	762.2	754.2	733.5	719.2	711.3
62.5°	689.0	682.6	660.3	647.6	639.7
65°	615.8	607.8	591.9	576.0	568.1
67.5°	541.0	534.6	518.7	502.8	501.2
70°	472.6	461.4	448.7	436.0	431.2
72.5°	399.4	388.3	378.7	369.2	364.4
75°	327.8	319.8	311.9	305.5	303.9
77.5°	257.8	254.6	246.6	245.0	240.3
80°	195.7	190.9	187.8	184.6	183.0
82.5°	135.3	133.7	133.7	132.1	130.5
85°	85.9	85.9	82.7	82.7	81.2
87.5°	41.4	39.8	38.2	38.2	38.2
90°	1.2	9.2	20.8	23.1	24.2
92.5°	16.2	88.9	452.6	149.6	105.1
95°	38.1	120.0	941.1	465.9	281.7
97.5°	63.5	132.8	1006.9	951.4	676.7
100°	87.8	150.1	928.4	1316.4	1058.9
102.5°	110.9	170.9	830.2	1545.0	1391.4
105°	135.1	195.8	757.5	1631.0	1624.7
107.5°	161.7	221.2	710.1	1605.0	1735.5
110°	188.2	246.5	688.2	1512.7	1737.8

TEST NUMBER: P1000916

CATALOG NUMBER: SA4XXDIP-B1195D1205UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.6	271.9	677.8	1399.5	1669.7
115°	237.9	298.5	675.5	1297.9	1560.0
117.5°	263.3	323.4	674.3	1218.2	1452.6
120°	288.7	347.5	674.3	1164.5	1364.9
122.5°	311.8	371.2	673.2	1129.3	1295.6
125°	331.4	393.8	672.0	1104.4	1244.8
127.5°	349.9	414.6	669.7	1080.8	1212.4
130°	364.9	434.8	668.6	1052.5	1184.7
132.5°	379.9	452.1	667.4	1019.0	1153.5
135°	393.8	468.8	666.3	980.4	1113.1
137.5°	407.6	483.2	666.3	938.8	1065.8
140°	422.6	496.6	665.1	898.4	1013.8
142.5°	438.8	508.6	665.1	860.8	958.4
145°	453.8	519.6	662.8	826.8	908.8
147.5°	471.1	530.0	659.3	798.5	862.6
150°	487.3	539.8	655.9	772.5	824.5
152.5°	502.3	549.0	650.1	750.6	789.8
155°	516.2	557.2	644.3	729.8	760.9
157.5°	530.0	564.7	638.6	710.2	734.4
160°	542.7	571.0	631.6	690.5	710.1
162.5°	554.3	576.2	624.7	671.4	687.0
165°	562.3	579.7	617.8	654.2	664.0
167.5°	571.6	582.6	610.8	639.2	645.5
170°	577.4	584.8	603.9	624.1	628.2
172.5°	583.1	586.6	597.0	610.8	610.8
175°	586.6	587.7	592.4	600.4	598.1
177.5°	588.9	587.7	588.9	593.0	588.9
180°	587.7	587.7	587.7	587.7	587.7

(END OF REPORT)