

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000918

Luminaire Tested: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000918
REPORT IS A COMBINATION OF REPORTS P995531 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9133.0 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	99	95	91	88	92	89	85	82	76	74	72	65	64	62	55	54	53
2	91	83	77	72	84	78	72	68	67	63	60	58	55	52	49	47	45
3	83	74	66	60	77	69	62	57	60	55	51	51	48	44	43	41	38
4	76	65	57	51	70	61	54	49	53	48	43	46	42	38	39	36	33
5	70	58	50	44	65	55	47	42	48	42	38	41	37	33	35	32	29
6	64	52	44	39	60	49	42	37	43	37	33	37	33	29	32	29	26
7	60	47	39	34	55	45	37	32	39	33	29	34	29	26	29	26	23
8	55	43	35	30	52	41	34	29	36	30	26	31	27	23	27	23	21
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15145	15145	15145	15145
5°	15107	17375	15194	13055
10°	14994	20271	15108	11454
15°	14814	23369	14917	10249
20°	14622	25340	14728	9188
25°	14342	25050	14479	8407
30°	14069	20705	14240	8003
35°	13684	15429	13835	7759
40°	13236	11623	13364	7640
45°	12552	9328	12707	7477
50°	11734	7859	11904	7400
55°	10773	6841	10942	7314
60°	9837	6024	10126	7192
65°	8961	5183	9045	6892
70°	7931	4265	8101	6346
75°	6916	3276	6873	5392
80°	5441	2152	5380	4094
85°	3580	968	3362	2387

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 19584 cd/sqm

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.7	2.0
10°-20°	557.9	6.1
20°-30°	886.3	9.7
30°-40°	984.9	10.8
40°-50°	895.6	9.8
50°-60°	731.9	8.0
60°-70°	522.4	5.7
70°-80°	287.5	3.1
80°-90°	80.8	0.9
90°-100°	94.1	1.0
100°-110°	281.8	3.1
110°-120°	478.7	5.2
120°-130°	631.4	6.9
130°-140°	709.1	7.8
140°-150°	697.0	7.6
150°-160°	586.2	6.4
160°-170°	390.0	4.3
170°-180°	136.6	1.5
0°-30°	1625.0	17.8
0°-40°	2609.9	28.6
0°-60°	4237.4	46.4
0°-90°	5128.1	56.1
90°-120°	854.6	9.4
90°-150°	2892.1	31.7
90°-180°	4005.0	43.9
0°-180°	9133.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1857	1857	1857	1857	1857	
5°	1850	2179	1860	1637	1850	176
15°	1766	2993	1779	1313	1766	498
25°	1613	3178	1628	1066	1613	743
35°	1399	1879	1414	945	1399	874
45°	1116	1054	1129	845	1116	860
55°	785	689	797	737	785	706
65°	489	443	494	589	489	483
75°	240	222	238	365	240	252
85°	49	46	46	114	49	57
90°	3	34	3	34	3	8
95°	67	88	67	88	67	73
105°	260	272	260	272	260	276
115°	487	482	487	482	487	480
125°	709	703	709	703	709	632
135°	914	915	914	915	914	707
145°	1111	1112	1111	1112	1111	695
155°	1273	1272	1273	1272	1273	586
165°	1385	1382	1385	1382	1385	391
175°	1441	1434	1441	1434	1441	137
180°	1443	1443	1443	1443	1443	

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3
2.5°	1857.3	1875.7	1883.4	1889.6	1909.6	1915.7	1917.3	1926.5	1934.2	1935.7	1935.7
5°	1849.6	1878.8	1901.9	1923.4	1955.7	1969.6	1986.5	2005.0	2029.6	2045.0	2052.7
7.5°	1837.3	1880.4	1915.7	1952.7	1997.3	2025.0	2040.4	2089.6	2123.5	2151.2	2185.0
10°	1818.8	1874.2	1925.0	1978.8	2041.9	2075.8	2109.6	2169.6	2217.3	2271.2	2314.3
12.5°	1791.1	1863.4	1925.0	2000.4	2078.8	2118.9	2158.9	2263.5	2318.9	2366.6	2443.5
15°	1766.5	1838.8	1926.5	2003.5	2100.4	2160.4	2218.9	2286.6	2374.3	2477.4	2551.2
17.5°	1738.8	1829.6	1911.1	2018.8	2126.5	2183.5	2231.2	2335.8	2458.9	2560.5	2628.2
20°	1700.3	1792.6	1900.4	2014.2	2141.9	2186.6	2249.6	2389.7	2500.5	2600.5	2711.3
22.5°	1655.7	1763.4	1877.3	1986.5	2118.9	2212.7	2282.0	2405.1	2538.9	2654.3	2779.0
25°	1612.6	1729.6	1829.6	1978.8	2118.9	2181.9	2260.4	2406.6	2552.8	2692.8	2820.5
27.5°	1566.4	1675.7	1811.1	1929.6	2088.1	2157.3	2242.0	2402.0	2557.4	2697.4	2834.4
30°	1515.7	1632.6	1744.9	1885.0	2038.8	2128.1	2206.6	2380.4	2538.9	2685.1	2812.8
32.5°	1458.7	1569.5	1689.5	1821.9	1983.4	2074.2	2172.7	2351.2	2520.5	2646.6	2745.1
35°	1398.7	1511.1	1615.7	1751.1	1917.3	2008.1	2103.5	2300.4	2468.2	2571.2	2628.2
37.5°	1332.6	1438.7	1541.8	1675.7	1841.9	1938.8	2035.8	2226.6	2385.1	2471.2	2455.8
40°	1269.5	1364.9	1460.3	1586.4	1760.3	1863.4	1948.1	2140.4	2278.9	2315.8	2265.0
42.5°	1197.1	1278.7	1371.0	1500.3	1669.5	1766.5	1872.7	2048.1	2151.2	2135.8	2049.6
45°	1115.6	1187.9	1280.2	1401.8	1574.1	1674.2	1763.4	1929.6	2005.0	1966.5	1809.6
47.5°	1037.1	1107.9	1183.3	1304.9	1472.6	1557.2	1648.0	1797.3	1840.3	1758.8	1601.8
50°	952.5	1011.0	1089.4	1204.8	1361.8	1451.0	1526.4	1646.5	1661.8	1561.8	1398.7
52.5°	870.9	920.2	995.6	1109.4	1255.6	1326.4	1400.3	1506.4	1494.1	1391.0	1234.1
55°	784.8	830.9	900.2	1004.8	1134.1	1201.8	1264.9	1358.7	1332.6	1226.4	1089.4
57.5°	712.4	744.8	812.5	909.4	1015.6	1089.4	1143.3	1217.1	1177.1	1071.0	943.3
60°	629.3	669.4	726.3	804.8	909.4	958.6	1006.3	1055.6	1027.9	926.3	812.5
62.5°	553.9	584.7	634.0	709.4	790.9	835.5	886.3	917.1	889.4	795.5	700.1
65°	489.3	513.9	552.4	614.0	692.4	729.4	758.6	787.8	764.8	677.0	607.8
67.5°	418.5	440.1	472.4	521.6	587.8	614.0	641.7	661.7	635.5	577.0	509.3
70°	355.5	370.8	401.6	438.5	484.7	509.3	532.4	552.4	529.3	480.1	429.3
72.5°	290.8	303.1	330.8	357.0	398.5	415.5	432.4	447.8	440.1	393.9	352.4
75°	240.0	244.7	263.1	284.7	310.8	329.3	341.6	350.8	344.7	307.7	281.6
77.5°	181.6	187.7	201.6	218.5	241.6	252.4	260.0	269.3	261.6	232.4	213.9
80°	132.3	133.9	141.6	157.0	172.3	173.9	181.6	193.9	189.3	169.3	155.4
82.5°	84.6	89.2	92.3	101.6	112.3	115.4	120.0	123.1	121.6	109.3	104.6
85°	49.2	49.2	52.3	58.5	61.5	66.2	67.7	69.2	72.3	64.6	60.0
87.5°	21.5	23.1	23.1	24.6	27.7	27.7	29.2	30.8	32.3	30.8	26.2
90°	3.3	6.0	8.8	11.5	14.2	15.6	16.6	18.6	20.6	22.6	24.6
92.5°	29.0	32.2	35.4	38.7	41.9	43.5	44.1	45.4	46.6	47.9	49.1
95°	67.0	69.2	71.4	73.7	75.9	77.0	77.9	79.6	81.3	83.1	84.8
97.5°	107.2	109.2	111.2	113.1	115.1	116.1	117.1	119.1	121.0	123.0	125.0
100°	156.3	157.3	158.3	159.3	160.3	160.8	161.9	164.1	166.4	168.6	170.8
102.5°	207.6	207.9	208.1	208.4	208.7	208.8	209.8	211.8	213.7	215.7	217.7
105°	260.1	260.3	260.6	260.8	261.1	261.2	261.7	262.7	263.7	264.7	265.7
107.5°	314.8	315.0	315.3	315.5	315.8	315.9	316.0	316.3	316.5	316.8	317.0
110°	370.6	371.1	371.6	372.1	372.6	372.9	372.8	372.5	372.2	372.0	371.7

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	428.7	428.7	428.7	428.7	428.7	428.7	428.4	427.9	427.4	426.9	426.4
115°	486.7	486.7	486.7	486.7	486.7	486.7	486.5	486.0	485.5	485.0	484.5
117.5°	541.4	541.4	541.4	541.4	541.4	541.4	541.3	541.0	540.8	540.5	540.3
120°	596.1	597.1	598.1	599.1	600.1	600.6	600.2	599.5	598.7	598.0	597.2
122.5°	653.0	653.3	653.5	653.8	654.1	654.2	654.1	653.8	653.5	653.3	653.0
125°	708.9	708.9	708.9	708.9	708.9	708.9	708.8	708.5	708.2	708.0	707.7
127.5°	759.1	759.8	760.6	761.3	762.0	762.4	762.2	761.7	761.2	760.7	760.2
130°	812.7	813.4	814.2	814.9	815.6	816.0	816.0	816.0	816.0	816.0	816.0
132.5°	867.4	867.9	868.4	868.9	869.4	869.6	869.5	869.2	869.0	868.7	868.5
135°	914.3	915.8	917.3	918.8	920.3	921.0	921.0	921.0	921.0	921.0	921.0
137.5°	966.7	967.5	968.2	969.0	969.7	970.1	970.3	970.8	971.3	971.8	972.3
140°	1019.2	1019.7	1020.2	1020.7	1021.2	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4
142.5°	1067.2	1067.7	1068.2	1068.7	1069.2	1069.4	1069.3	1069.0	1068.8	1068.5	1068.3
145°	1110.7	1111.7	1112.7	1113.7	1114.7	1115.2	1115.3	1115.6	1115.8	1116.1	1116.3
147.5°	1155.4	1156.6	1157.9	1159.1	1160.4	1161.0	1160.9	1160.6	1160.4	1160.1	1159.9
150°	1195.6	1196.6	1197.6	1198.5	1199.5	1200.0	1200.0	1200.0	1200.0	1200.0	1200.0
152.5°	1233.5	1234.0	1234.5	1235.0	1235.5	1235.8	1235.9	1236.2	1236.4	1236.7	1236.9
155°	1272.6	1272.6	1272.6	1272.6	1272.6	1272.6	1272.5	1272.2	1272.0	1271.7	1271.5
157.5°	1306.1	1305.6	1305.1	1304.6	1304.1	1303.9	1303.9	1303.9	1303.9	1303.9	1303.9
160°	1335.1	1334.9	1334.6	1334.4	1334.1	1334.0	1333.9	1333.6	1333.4	1333.1	1332.9
162.5°	1361.9	1361.2	1360.4	1359.7	1359.0	1358.6	1358.5	1358.2	1357.9	1357.7	1357.4
165°	1385.4	1384.6	1383.9	1383.1	1382.4	1382.0	1381.8	1381.3	1380.8	1380.3	1379.8
167.5°	1404.3	1403.3	1402.3	1401.4	1400.4	1399.9	1399.9	1399.9	1399.9	1399.9	1399.9
170°	1420.0	1418.8	1417.5	1416.3	1415.0	1414.4	1414.5	1414.8	1415.0	1415.3	1415.5
172.5°	1431.1	1430.1	1429.1	1428.2	1427.2	1426.7	1426.7	1426.7	1426.7	1426.7	1426.7
175°	1441.2	1440.0	1438.7	1437.5	1436.2	1435.6	1435.5	1435.2	1435.0	1434.7	1434.5
177.5°	1445.6	1444.4	1443.2	1441.9	1440.7	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1
180°	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3
2.5°	1940.4	1968.1	1980.4	1983.4	2000.4	1989.6	1994.2	1992.7	2005.0	2006.5	2006.5
5°	2081.9	2114.2	2125.0	2140.4	2163.5	2169.6	2165.0	2174.3	2191.2	2178.9	2197.3
7.5°	2231.2	2266.6	2291.2	2325.0	2332.7	2352.7	2365.1	2375.8	2378.9	2380.4	2383.5
10°	2369.7	2414.3	2448.1	2505.1	2517.4	2528.2	2582.0	2560.5	2588.2	2578.9	2582.0
12.5°	2482.0	2569.7	2597.4	2692.8	2702.0	2739.0	2735.9	2769.7	2775.9	2788.2	2775.9
15°	2629.7	2731.3	2775.9	2829.8	2860.5	2903.6	2911.3	2957.5	2975.9	2992.9	2975.9
17.5°	2765.1	2819.0	2932.9	2975.9	2995.9	3019.0	3077.5	3094.4	3122.1	3111.3	3142.1
20°	2832.8	2909.8	3029.8	3103.7	3134.4	3156.0	3205.2	3231.4	3242.1	3242.1	3245.2
22.5°	2892.8	3003.6	3092.9	3177.5	3205.2	3220.6	3249.8	3269.8	3274.5	3277.5	3280.6
25°	2946.7	3046.7	3119.0	3166.7	3177.5	3177.5	3194.4	3182.1	3162.1	3177.5	3186.7
27.5°	2946.7	3017.5	3049.8	3066.7	3066.7	3025.2	3000.6	2949.8	2906.7	2894.4	2922.1
30°	2897.5	2929.8	2885.2	2843.6	2811.3	2783.6	2686.7	2609.7	2594.3	2583.6	2625.1
32.5°	2783.6	2742.0	2654.3	2534.3	2486.6	2423.5	2348.1	2289.7	2254.3	2242.0	2232.7
35°	2582.0	2474.3	2360.4	2198.9	2165.0	2085.0	1981.9	1938.8	1880.4	1878.8	1898.8
37.5°	2362.0	2195.8	2072.7	1918.8	1871.1	1786.5	1689.5	1644.9	1604.9	1574.1	1611.1
40°	2105.0	1960.4	1772.6	1646.5	1578.8	1534.1	1452.6	1403.3	1384.9	1369.5	1392.6
42.5°	1865.0	1706.5	1560.3	1431.0	1375.6	1324.9	1271.0	1223.3	1209.5	1207.9	1224.8
45°	1626.5	1471.0	1335.6	1224.8	1189.5	1158.7	1106.4	1092.5	1069.4	1054.0	1061.7
47.5°	1435.7	1275.6	1163.3	1078.7	1047.9	1021.7	987.9	964.8	944.8	938.6	947.9
50°	1247.9	1140.2	1024.8	954.0	930.9	906.3	880.2	858.6	849.4	843.2	849.4
52.5°	1097.1	981.7	903.2	846.3	823.2	804.8	786.3	777.1	764.8	767.8	774.0
55°	961.7	860.2	794.0	752.4	738.6	730.9	707.8	697.1	692.4	689.4	692.4
57.5°	834.0	760.1	710.9	675.5	657.0	652.4	634.0	634.0	629.3	624.7	626.3
60°	732.4	669.4	621.7	594.0	590.9	583.2	570.9	569.3	558.6	563.2	564.7
62.5°	629.3	578.6	546.3	529.3	518.6	515.5	507.8	506.2	501.6	503.2	500.1
65°	547.8	506.2	473.9	460.1	455.5	453.9	447.8	443.2	440.1	443.2	440.1
67.5°	466.2	438.5	413.9	400.1	393.9	392.4	387.8	384.7	386.2	381.6	384.7
70°	389.3	361.6	346.2	338.5	335.4	330.8	330.8	330.8	330.8	327.8	326.2
72.5°	327.8	300.1	289.3	284.7	281.6	280.1	275.4	277.0	275.4	273.9	280.1
75°	260.0	243.1	232.4	227.7	230.8	226.2	221.6	224.7	220.0	221.6	227.7
77.5°	197.0	189.3	183.1	180.0	177.0	173.9	173.9	170.8	170.8	170.8	170.8
80°	143.1	141.6	130.8	129.3	129.3	126.2	126.2	126.2	126.2	124.6	126.2
82.5°	95.4	93.9	90.8	89.2	86.2	87.7	87.7	84.6	84.6	83.1	84.6
85°	55.4	55.4	52.3	50.8	49.2	50.8	47.7	46.2	47.7	46.2	47.7
87.5°	26.2	23.1	24.6	23.1	20.0	21.5	18.5	20.0	18.5	16.9	20.0
90°	26.1	27.6	29.1	30.6	31.3	31.5	32.0	32.5	33.0	33.5	33.0
92.5°	49.9	50.6	51.4	52.1	52.5	52.6	52.9	53.1	53.4	53.6	53.4
95°	85.6	86.3	87.1	87.8	88.2	88.2	88.2	88.2	88.2	88.2	88.2
97.5°	126.0	127.0	128.0	129.0	129.5	129.5	129.5	129.5	129.5	129.5	129.5
100°	171.3	171.8	172.3	172.8	173.0	173.0	173.0	173.0	173.0	173.0	173.0
102.5°	218.4	219.2	219.9	220.6	221.0	221.1	221.4	221.6	221.9	222.1	221.9
105°	266.4	267.2	267.9	268.6	269.0	269.4	270.1	270.9	271.6	272.4	271.6
107.5°	318.0	319.0	320.0	321.0	321.5	321.4	321.1	320.9	320.6	320.4	320.6
110°	371.2	370.7	370.2	369.7	369.5	369.9	370.6	371.4	372.1	372.9	372.1

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	426.4	426.4	426.4	426.4	426.4	426.4	426.4	426.4	426.4	426.4	426.4
115°	484.3	484.0	483.8	483.5	483.4	483.3	483.0	482.8	482.5	482.3	482.5
117.5°	539.6	538.8	538.1	537.4	537.0	536.6	535.9	535.1	534.4	533.6	534.4
120°	596.0	594.8	593.5	592.3	591.7	591.9	592.4	592.9	593.4	593.9	593.4
122.5°	652.3	651.5	650.8	650.1	649.7	649.1	647.8	646.6	645.3	644.1	645.3
125°	707.2	706.7	706.2	705.7	705.5	705.3	704.8	704.3	703.8	703.3	703.8
127.5°	759.7	759.2	758.7	758.2	758.0	757.9	757.6	757.4	757.1	756.9	757.1
130°	815.5	815.0	814.5	814.0	813.8	813.3	812.3	811.3	810.3	809.3	810.3
132.5°	868.0	867.5	867.0	866.5	866.3	866.2	865.9	865.6	865.4	865.1	865.4
135°	920.5	920.0	919.5	919.0	918.7	918.3	917.6	916.9	916.1	915.4	916.1
137.5°	971.6	970.8	970.1	969.4	969.0	969.1	969.4	969.6	969.9	970.1	969.9
140°	1021.2	1020.9	1020.7	1020.4	1020.3	1020.2	1019.9	1019.7	1019.4	1019.2	1019.4
142.5°	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3
145°	1116.1	1115.8	1115.6	1115.3	1115.2	1114.8	1114.1	1113.4	1112.6	1111.9	1112.6
147.5°	1159.6	1159.4	1159.1	1158.8	1158.7	1158.6	1158.3	1158.1	1157.8	1157.6	1157.8
150°	1200.0	1200.0	1200.0	1200.0	1200.0	1199.9	1199.6	1199.4	1199.1	1198.9	1199.1
152.5°	1237.6	1238.4	1239.1	1239.8	1240.2	1239.8	1239.1	1238.4	1237.6	1236.9	1237.6
155°	1272.5	1273.5	1274.5	1275.5	1276.0	1275.5	1274.5	1273.5	1272.5	1271.5	1272.5
157.5°	1304.6	1305.4	1306.1	1306.8	1307.2	1306.8	1306.1	1305.4	1304.6	1303.9	1304.6
160°	1333.6	1334.4	1335.1	1335.8	1336.2	1335.6	1334.4	1333.1	1331.9	1330.7	1331.9
162.5°	1358.9	1360.4	1361.9	1363.4	1364.1	1363.5	1362.3	1361.0	1359.8	1358.6	1359.8
165°	1381.3	1382.8	1384.3	1385.8	1386.5	1386.0	1385.0	1384.0	1383.0	1382.0	1383.0
167.5°	1401.4	1402.9	1404.4	1405.9	1406.6	1405.9	1404.4	1402.9	1401.4	1399.9	1401.4
170°	1417.0	1418.5	1420.0	1421.5	1422.2	1421.3	1419.6	1417.9	1416.1	1414.4	1416.1
172.5°	1428.4	1430.2	1431.9	1433.6	1434.5	1433.6	1431.9	1430.2	1428.4	1426.7	1428.4
175°	1436.2	1438.0	1439.7	1441.4	1442.3	1441.4	1439.7	1438.0	1436.2	1434.5	1436.2
177.5°	1441.8	1443.6	1445.3	1447.0	1447.9	1446.9	1444.9	1442.9	1440.9	1438.9	1440.9
180°	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3
2.5°	2003.5	1998.8	1992.7	1992.7	1985.0	1985.0	1972.7	1951.1	1932.7	1926.5	1929.6
5°	2174.3	2175.8	2166.6	2158.9	2145.0	2134.2	2114.2	2075.8	2063.5	2038.8	2021.9
7.5°	2369.7	2363.5	2346.6	2334.3	2331.2	2306.6	2263.5	2217.3	2180.4	2155.8	2120.4
10°	2589.7	2565.1	2540.5	2532.8	2514.3	2472.8	2423.5	2372.7	2322.0	2268.1	2208.1
12.5°	2774.4	2726.7	2725.1	2706.7	2671.3	2648.2	2589.7	2517.4	2429.7	2369.7	2302.0
15°	2972.9	2928.2	2891.3	2857.5	2840.5	2772.8	2723.6	2632.8	2528.2	2463.5	2417.4
17.5°	3114.4	3094.4	3031.3	3015.9	2992.9	2914.4	2835.9	2746.7	2655.9	2565.1	2440.5
20°	3228.3	3216.0	3174.4	3152.9	3116.0	3054.4	2959.0	2855.9	2751.3	2622.0	2505.1
22.5°	3277.5	3262.1	3228.3	3209.8	3186.7	3134.4	3052.9	2935.9	2799.0	2683.6	2558.9
25°	3180.6	3208.3	3199.1	3191.4	3182.1	3151.4	3089.8	2986.7	2852.8	2722.0	2566.6
27.5°	2962.1	3009.8	3056.0	3062.1	3077.5	3089.8	3065.2	2991.3	2879.0	2740.5	2569.7
30°	2668.2	2689.7	2783.6	2811.3	2832.8	2911.3	2957.5	2939.0	2852.8	2728.2	2571.2
32.5°	2291.2	2348.1	2443.5	2509.7	2568.2	2655.9	2775.9	2823.6	2792.8	2691.3	2535.9
35°	1934.2	2001.9	2112.7	2197.3	2255.8	2380.4	2522.0	2625.1	2663.6	2612.8	2474.3
37.5°	1641.8	1723.4	1821.9	1854.2	1921.9	2075.8	2271.2	2414.3	2508.2	2512.8	2405.1
40°	1421.8	1463.3	1541.8	1591.1	1657.2	1786.5	1977.3	2166.6	2308.1	2355.8	2298.9
42.5°	1235.6	1267.9	1326.4	1386.4	1446.4	1544.9	1720.3	1897.3	2088.1	2183.5	2181.9
45°	1087.9	1121.7	1161.8	1211.0	1252.5	1358.7	1497.2	1678.8	1843.4	1991.1	2028.1
47.5°	958.6	987.9	1037.1	1058.7	1086.4	1186.4	1306.4	1475.7	1646.5	1815.7	1858.8
50°	863.2	887.9	921.7	935.6	966.3	1040.2	1138.7	1275.6	1464.9	1620.3	1700.3
52.5°	777.1	795.5	821.7	832.5	854.0	909.4	998.6	1106.4	1263.3	1423.3	1535.7
55°	703.2	715.5	734.0	746.3	761.7	810.9	877.1	974.0	1109.4	1247.9	1357.2
57.5°	634.0	643.2	661.7	667.8	680.1	718.6	764.8	846.3	971.0	1094.0	1200.2
60°	569.3	575.5	586.3	600.1	609.3	635.5	678.6	746.3	846.3	958.6	1044.8
62.5°	507.8	517.0	520.1	526.3	533.9	558.6	592.4	641.7	729.4	821.7	912.5
65°	444.7	452.4	458.5	460.1	467.8	486.2	517.0	560.1	617.0	697.1	781.7
67.5°	386.2	390.8	393.9	400.1	407.8	417.0	441.6	473.9	526.3	590.9	658.6
70°	332.4	332.4	337.0	338.5	347.8	358.5	369.3	400.1	446.2	498.6	544.7
72.5°	273.9	281.6	280.1	287.7	286.2	293.9	307.7	327.8	361.6	403.2	447.8
75°	223.1	227.7	227.7	227.7	230.8	237.0	244.7	263.1	289.3	323.1	349.3
77.5°	173.9	177.0	177.0	177.0	178.5	184.6	192.3	204.7	223.1	243.1	258.5
80°	124.6	127.7	127.7	130.8	130.8	132.3	140.0	146.2	155.4	170.8	186.2
82.5°	84.6	86.2	89.2	89.2	87.7	90.8	92.3	98.5	107.7	110.8	121.6
85°	46.2	47.7	49.2	49.2	50.8	53.9	52.3	58.5	58.5	64.6	67.7
87.5°	18.5	21.5	21.5	20.0	21.5	21.5	21.5	24.6	26.2	27.7	26.2
90°	32.5	32.0	31.5	31.3	30.6	29.1	27.6	26.1	24.6	22.6	20.6
92.5°	53.1	52.9	52.6	52.5	52.1	51.4	50.6	49.9	49.1	47.9	46.6
95°	88.2	88.2	88.2	88.2	87.8	87.1	86.3	85.6	84.8	83.1	81.3
97.5°	129.5	129.5	129.5	129.5	129.0	128.0	127.0	126.0	125.0	123.0	121.0
100°	173.0	173.0	173.0	173.0	172.8	172.3	171.8	171.3	170.8	168.6	166.4
102.5°	221.6	221.4	221.1	221.0	220.6	219.9	219.2	218.4	217.7	215.7	213.7
105°	270.9	270.1	269.4	269.0	268.6	267.9	267.2	266.4	265.7	264.7	263.7
107.5°	320.9	321.1	321.4	321.5	321.0	320.0	319.0	318.0	317.0	316.8	316.5
110°	371.4	370.6	369.9	369.5	369.7	370.2	370.7	371.2	371.7	372.0	372.2

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	426.4	426.4	426.4	426.4	426.4	426.4	426.4	426.4	426.4	426.9	427.4
115°	482.8	483.0	483.3	483.4	483.5	483.8	484.0	484.3	484.5	485.0	485.5
117.5°	535.1	535.9	536.6	537.0	537.4	538.1	538.8	539.6	540.3	540.5	540.8
120°	592.9	592.4	591.9	591.7	592.3	593.5	594.8	596.0	597.2	598.0	598.7
122.5°	646.6	647.8	649.1	649.7	650.1	650.8	651.5	652.3	653.0	653.3	653.5
125°	704.3	704.8	705.3	705.5	705.7	706.2	706.7	707.2	707.7	708.0	708.2
127.5°	757.4	757.6	757.9	758.0	758.2	758.7	759.2	759.7	760.2	760.7	761.2
130°	811.3	812.3	813.3	813.8	814.0	814.5	815.0	815.5	816.0	816.0	816.0
132.5°	865.6	865.9	866.2	866.3	866.5	867.0	867.5	868.0	868.5	868.7	869.0
135°	916.9	917.6	918.3	918.7	919.0	919.5	920.0	920.5	921.0	921.0	921.0
137.5°	969.6	969.4	969.1	969.0	969.4	970.1	970.8	971.6	972.3	971.8	971.3
140°	1019.7	1019.9	1020.2	1020.3	1020.4	1020.7	1020.9	1021.2	1021.4	1021.4	1021.4
142.5°	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3	1068.5	1068.8
145°	1113.4	1114.1	1114.8	1115.2	1115.3	1115.6	1115.8	1116.1	1116.3	1116.1	1115.8
147.5°	1158.1	1158.3	1158.6	1158.7	1158.8	1159.1	1159.4	1159.6	1159.9	1160.1	1160.4
150°	1199.4	1199.6	1199.9	1200.0	1200.0	1200.0	1200.0	1200.0	1200.0	1200.0	1200.0
152.5°	1238.4	1239.1	1239.8	1240.2	1239.8	1239.1	1238.4	1237.6	1236.9	1236.7	1236.4
155°	1273.5	1274.5	1275.5	1276.0	1275.5	1274.5	1273.5	1272.5	1271.5	1271.7	1272.0
157.5°	1305.4	1306.1	1306.8	1307.2	1306.8	1306.1	1305.4	1304.6	1303.9	1303.9	1303.9
160°	1333.1	1334.4	1335.6	1336.2	1335.8	1335.1	1334.4	1333.6	1332.9	1333.1	1333.4
162.5°	1361.0	1362.3	1363.5	1364.1	1363.4	1361.9	1360.4	1358.9	1357.4	1357.7	1357.9
165°	1384.0	1385.0	1386.0	1386.5	1385.8	1384.3	1382.8	1381.3	1379.8	1380.3	1380.8
167.5°	1402.9	1404.4	1405.9	1406.6	1405.9	1404.4	1402.9	1401.4	1399.9	1399.9	1399.9
170°	1417.9	1419.6	1421.3	1422.2	1421.5	1420.0	1418.5	1417.0	1415.5	1415.3	1415.0
172.5°	1430.2	1431.9	1433.6	1434.5	1433.6	1431.9	1430.2	1428.4	1426.7	1426.7	1426.7
175°	1438.0	1439.7	1441.4	1442.3	1441.4	1439.7	1438.0	1436.2	1434.5	1434.7	1435.0
177.5°	1442.9	1444.9	1446.9	1447.9	1447.0	1445.3	1443.6	1441.8	1440.1	1440.1	1440.1
180°	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3
2.5°	1915.7	1909.6	1905.0	1905.0	1891.1	1877.3	1869.6	1866.5	1863.4	1851.1	1834.2
5°	1994.2	1974.2	1960.4	1946.5	1923.4	1898.8	1874.2	1860.3	1840.3	1812.6	1792.6
7.5°	2081.9	2034.2	2018.8	2001.9	1955.7	1914.2	1880.4	1851.1	1818.8	1783.4	1748.0
10°	2155.8	2105.0	2071.2	2041.9	1981.9	1926.5	1875.7	1832.6	1791.1	1744.9	1701.9
12.5°	2226.6	2154.2	2118.9	2075.8	2012.7	1932.7	1866.5	1812.6	1751.1	1703.4	1651.1
15°	2325.0	2203.5	2145.0	2117.3	2032.7	1938.8	1858.8	1778.8	1728.0	1655.7	1609.5
17.5°	2340.4	2242.0	2203.5	2132.7	2031.1	1925.0	1832.6	1752.6	1675.7	1611.1	1551.1
20°	2394.3	2265.0	2203.5	2158.9	2025.0	1917.3	1815.7	1712.6	1638.8	1569.5	1501.8
22.5°	2428.1	2282.0	2217.3	2146.6	2018.8	1889.6	1769.6	1680.3	1589.5	1518.7	1464.9
25°	2418.9	2272.7	2200.4	2134.2	1978.8	1849.6	1741.9	1628.0	1543.4	1466.4	1395.6
27.5°	2414.3	2249.6	2172.7	2098.9	1952.7	1817.3	1681.9	1589.5	1495.7	1406.4	1354.1
30°	2402.0	2220.4	2131.2	2051.2	1898.8	1757.3	1641.8	1534.1	1440.3	1358.7	1289.5
32.5°	2360.4	2171.2	2085.0	1998.8	1840.3	1698.8	1581.8	1481.8	1388.0	1303.3	1237.2
35°	2305.0	2112.7	2018.8	1928.1	1769.6	1626.5	1518.7	1414.1	1326.4	1244.8	1181.8
37.5°	2249.6	2045.0	1957.3	1852.7	1706.5	1557.2	1446.4	1352.6	1271.0	1186.4	1117.1
40°	2169.6	1965.0	1868.0	1778.8	1608.0	1468.0	1366.4	1281.8	1201.8	1121.7	1063.3
42.5°	2060.4	1877.3	1777.3	1678.8	1518.7	1380.3	1281.8	1206.4	1131.0	1064.8	1000.2
45°	1949.6	1771.1	1681.9	1594.1	1420.3	1289.5	1198.7	1129.4	1066.4	994.0	941.7
47.5°	1815.7	1664.9	1575.7	1489.5	1324.9	1194.1	1111.0	1046.3	987.9	927.9	878.6
50°	1678.8	1548.0	1466.4	1377.2	1220.2	1101.7	1020.2	966.3	918.6	861.7	821.7
52.5°	1531.1	1417.2	1347.9	1261.8	1123.3	1014.0	930.9	877.1	837.1	795.5	760.1
55°	1374.1	1291.0	1217.1	1147.9	1017.1	918.6	844.8	797.1	769.4	730.9	700.1
57.5°	1232.5	1152.5	1107.9	1029.4	915.6	818.6	760.1	720.1	687.8	664.7	640.1
60°	1084.8	1020.2	971.0	914.0	814.0	732.4	670.9	647.8	614.0	597.0	586.3
62.5°	943.3	897.1	850.9	807.8	718.6	641.7	595.5	566.3	546.3	529.3	520.1
65°	809.4	766.3	734.0	695.5	621.7	560.1	517.0	493.9	473.9	469.3	458.5
67.5°	678.6	660.1	624.7	594.0	530.9	483.2	450.9	421.6	410.8	406.2	397.0
70°	567.8	546.3	518.6	492.4	444.7	403.2	373.9	363.1	347.8	346.2	335.4
72.5°	467.8	441.6	421.6	401.6	366.2	329.3	313.9	298.5	290.8	284.7	280.1
75°	370.8	352.4	338.5	321.6	290.8	266.2	244.7	238.5	233.9	232.4	229.3
77.5°	277.0	264.7	258.5	241.6	220.0	198.5	189.3	180.0	180.0	177.0	178.5
80°	197.0	189.3	181.6	172.3	153.9	144.6	136.9	130.8	127.7	126.2	127.7
82.5°	124.6	120.0	118.5	112.3	100.0	95.4	89.2	84.6	84.6	84.6	84.6
85°	69.2	69.2	69.2	60.0	55.4	50.8	47.7	46.2	46.2	46.2	47.7
87.5°	29.2	29.2	24.6	24.6	23.1	20.0	18.5	18.5	20.0	20.0	21.5
90°	18.6	16.6	15.6	14.2	11.5	8.8	6.0	3.3	6.0	8.8	11.5
92.5°	45.4	44.1	43.5	41.9	38.7	35.4	32.2	29.0	32.2	35.4	38.7
95°	79.6	77.9	77.0	75.9	73.7	71.4	69.2	67.0	69.2	71.4	73.7
97.5°	119.1	117.1	116.1	115.1	113.1	111.2	109.2	107.2	109.2	111.2	113.1
100°	164.1	161.9	160.8	160.3	159.3	158.3	157.3	156.3	157.3	158.3	159.3
102.5°	211.8	209.8	208.8	208.7	208.4	208.1	207.9	207.6	207.9	208.1	208.4
105°	262.7	261.7	261.2	261.1	260.8	260.6	260.3	260.1	260.3	260.6	260.8
107.5°	316.3	316.0	315.9	315.8	315.5	315.3	315.0	314.8	315.0	315.3	315.5
110°	372.5	372.8	372.9	372.6	372.1	371.6	371.1	370.6	371.1	371.6	372.1

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	427.9	428.4	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
115°	486.0	486.5	486.7	486.7	486.7	486.7	486.7	486.7	486.7	486.7	486.7
117.5°	541.0	541.3	541.4	541.4	541.4	541.4	541.4	541.4	541.4	541.4	541.4
120°	599.5	600.2	600.6	600.1	599.1	598.1	597.1	596.1	597.1	598.1	599.1
122.5°	653.8	654.1	654.2	654.1	653.8	653.5	653.3	653.0	653.3	653.5	653.8
125°	708.5	708.8	708.9	708.9	708.9	708.9	708.9	708.9	708.9	708.9	708.9
127.5°	761.7	762.2	762.4	762.0	761.3	760.6	759.8	759.1	759.8	760.6	761.3
130°	816.0	816.0	816.0	815.6	814.9	814.2	813.4	812.7	813.4	814.2	814.9
132.5°	869.2	869.5	869.6	869.4	868.9	868.4	867.9	867.4	867.9	868.4	868.9
135°	921.0	921.0	921.0	920.3	918.8	917.3	915.8	914.3	915.8	917.3	918.8
137.5°	970.8	970.3	970.1	969.7	969.0	968.2	967.5	966.7	967.5	968.2	969.0
140°	1021.4	1021.4	1021.4	1021.2	1020.7	1020.2	1019.7	1019.2	1019.7	1020.2	1020.7
142.5°	1069.0	1069.3	1069.4	1069.2	1068.7	1068.2	1067.7	1067.2	1067.7	1068.2	1068.7
145°	1115.6	1115.3	1115.2	1114.7	1113.7	1112.7	1111.7	1110.7	1111.7	1112.7	1113.7
147.5°	1160.6	1160.9	1161.0	1160.4	1159.1	1157.9	1156.6	1155.4	1156.6	1157.9	1159.1
150°	1200.0	1200.0	1200.0	1199.5	1198.5	1197.6	1196.6	1195.6	1196.6	1197.6	1198.5
152.5°	1236.2	1235.9	1235.8	1235.5	1235.0	1234.5	1234.0	1233.5	1234.0	1234.5	1235.0
155°	1272.2	1272.5	1272.6	1272.6	1272.6	1272.6	1272.6	1272.6	1272.6	1272.6	1272.6
157.5°	1303.9	1303.9	1303.9	1304.1	1304.6	1305.1	1305.6	1306.1	1305.6	1305.1	1304.6
160°	1333.6	1333.9	1334.0	1334.1	1334.4	1334.6	1334.9	1335.1	1334.9	1334.6	1334.4
162.5°	1358.2	1358.5	1358.6	1359.0	1359.7	1360.4	1361.2	1361.9	1361.2	1360.4	1359.7
165°	1381.3	1381.8	1382.0	1382.4	1383.1	1383.9	1384.6	1385.4	1384.6	1383.9	1383.1
167.5°	1399.9	1399.9	1399.9	1400.4	1401.4	1402.3	1403.3	1404.3	1403.3	1402.3	1401.4
170°	1414.8	1414.5	1414.4	1415.0	1416.3	1417.5	1418.8	1420.0	1418.8	1417.5	1416.3
172.5°	1426.7	1426.7	1426.7	1427.2	1428.2	1429.1	1430.1	1431.1	1430.1	1429.1	1428.2
175°	1435.2	1435.5	1435.6	1436.2	1437.5	1438.7	1440.0	1441.2	1440.0	1438.7	1437.5
177.5°	1440.1	1440.1	1440.1	1440.7	1441.9	1443.2	1444.4	1445.6	1444.4	1443.2	1441.9
180°	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3
2.5°	1829.6	1823.4	1826.5	1811.1	1797.3	1777.3	1760.3	1757.3	1754.2	1763.4	1757.3
5°	1777.3	1769.6	1761.9	1743.4	1715.7	1698.8	1674.2	1672.6	1663.4	1649.5	1652.6
7.5°	1720.3	1715.7	1704.9	1675.7	1651.1	1621.8	1601.8	1584.9	1577.2	1564.9	1560.3
10°	1674.2	1657.2	1648.0	1615.7	1586.4	1555.7	1529.5	1517.2	1503.4	1492.6	1484.9
12.5°	1611.1	1606.5	1580.3	1554.1	1529.5	1494.1	1474.1	1438.7	1420.3	1429.5	1426.4
15°	1569.5	1548.0	1541.8	1504.9	1463.3	1440.3	1403.3	1380.3	1372.6	1358.7	1341.8
17.5°	1514.1	1500.3	1478.7	1444.9	1397.2	1364.9	1338.7	1317.2	1307.9	1289.5	1275.6
20°	1461.8	1438.7	1421.8	1391.0	1344.9	1303.3	1271.0	1257.2	1234.1	1218.7	1211.0
22.5°	1414.1	1397.2	1372.6	1326.4	1286.4	1246.4	1207.9	1187.9	1166.4	1157.1	1144.8
25°	1355.6	1327.9	1311.0	1260.2	1217.1	1184.8	1149.4	1123.3	1111.0	1095.6	1092.5
27.5°	1298.7	1272.5	1252.5	1207.9	1155.6	1114.1	1092.5	1074.0	1052.5	1052.5	1044.8
30°	1241.8	1223.3	1192.5	1149.4	1100.2	1060.2	1035.6	1018.7	1011.0	1004.8	1003.3
32.5°	1184.8	1160.2	1141.8	1083.3	1046.3	1009.4	991.0	977.1	967.9	966.3	967.9
35°	1126.4	1098.7	1080.2	1027.9	991.0	957.1	949.4	937.1	932.5	930.9	938.6
37.5°	1064.8	1043.3	1020.2	977.1	935.6	915.6	900.2	895.6	894.0	903.2	906.3
40°	1007.9	989.4	967.9	921.7	890.9	869.4	861.7	857.1	863.2	872.5	877.1
42.5°	954.0	927.9	910.9	869.4	841.7	829.4	820.2	820.2	826.3	837.1	844.8
45°	897.1	877.1	860.2	823.2	798.6	784.8	783.2	784.8	792.5	800.1	809.4
47.5°	841.7	821.7	803.2	772.5	750.9	743.2	741.7	743.2	755.5	766.3	777.1
50°	790.9	769.4	752.4	723.2	706.3	697.1	698.6	706.3	715.5	730.9	744.8
52.5°	730.9	715.5	700.1	674.0	658.6	652.4	657.0	663.2	680.1	690.9	707.8
55°	672.4	658.6	646.3	626.3	614.0	609.3	612.4	621.7	635.5	654.0	674.0
57.5°	618.6	603.2	590.9	577.0	563.2	564.7	566.3	578.6	595.5	612.4	635.5
60°	558.6	549.3	538.6	521.6	515.5	515.5	520.1	533.9	549.3	577.0	597.0
62.5°	504.7	492.4	484.7	473.9	464.7	466.2	477.0	489.3	507.8	530.9	557.0
65°	449.3	435.5	429.3	420.1	417.0	418.5	426.2	444.7	464.7	484.7	509.3
67.5°	387.8	383.1	377.0	367.8	370.8	372.4	380.1	395.5	417.0	437.0	464.7
70°	335.4	326.2	324.7	317.0	317.0	321.6	337.0	347.8	367.8	389.3	418.5
72.5°	280.1	272.4	272.4	266.2	270.8	275.4	283.1	298.5	317.0	338.5	363.1
75°	223.1	220.0	223.1	220.0	220.0	227.7	237.0	249.3	269.3	292.4	312.4
77.5°	172.3	172.3	170.8	175.4	175.4	180.0	192.3	204.7	220.0	238.5	260.0
80°	126.2	126.2	126.2	130.8	135.4	135.4	143.1	158.5	172.3	184.6	204.7
82.5°	86.2	86.2	86.2	89.2	95.4	95.4	104.6	113.9	129.3	140.0	149.3
85°	52.3	52.3	50.8	53.9	55.4	60.0	67.7	73.9	81.6	90.8	100.0
87.5°	23.1	23.1	24.6	26.2	27.7	30.8	33.9	36.9	44.6	47.7	52.3
90°	14.2	15.6	16.6	18.6	20.6	22.6	24.6	26.1	27.6	29.1	30.6
92.5°	41.9	43.5	44.1	45.4	46.6	47.9	49.1	49.9	50.6	51.4	52.1
95°	75.9	77.0	77.9	79.6	81.3	83.1	84.8	85.6	86.3	87.1	87.8
97.5°	115.1	116.1	117.1	119.1	121.0	123.0	125.0	126.0	127.0	128.0	129.0
100°	160.3	160.8	161.9	164.1	166.4	168.6	170.8	171.3	171.8	172.3	172.8
102.5°	208.7	208.8	209.8	211.8	213.7	215.7	217.7	218.4	219.2	219.9	220.6
105°	261.1	261.2	261.7	262.7	263.7	264.7	265.7	266.4	267.2	267.9	268.6
107.5°	315.8	315.9	316.0	316.3	316.5	316.8	317.0	318.0	319.0	320.0	321.0
110°	372.6	372.9	372.8	372.5	372.2	372.0	371.7	371.2	370.7	370.2	369.7

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	428.7	428.7	428.4	427.9	427.4	426.9	426.4	426.4	426.4	426.4	426.4
115°	486.7	486.7	486.5	486.0	485.5	485.0	484.5	484.3	484.0	483.8	483.5
117.5°	541.4	541.4	541.3	541.0	540.8	540.5	540.3	539.6	538.8	538.1	537.4
120°	600.1	600.6	600.2	599.5	598.7	598.0	597.2	596.0	594.8	593.5	592.3
122.5°	654.1	654.2	654.1	653.8	653.5	653.3	653.0	652.3	651.5	650.8	650.1
125°	708.9	708.9	708.8	708.5	708.2	708.0	707.7	707.2	706.7	706.2	705.7
127.5°	762.0	762.4	762.2	761.7	761.2	760.7	760.2	759.7	759.2	758.7	758.2
130°	815.6	816.0	816.0	816.0	816.0	816.0	816.0	815.5	815.0	814.5	814.0
132.5°	869.4	869.6	869.5	869.2	869.0	868.7	868.5	868.0	867.5	867.0	866.5
135°	920.3	921.0	921.0	921.0	921.0	921.0	921.0	920.5	920.0	919.5	919.0
137.5°	969.7	970.1	970.3	970.8	971.3	971.8	972.3	971.6	970.8	970.1	969.4
140°	1021.2	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.2	1020.9	1020.7	1020.4
142.5°	1069.2	1069.4	1069.3	1069.0	1068.8	1068.5	1068.3	1068.3	1068.3	1068.3	1068.3
145°	1114.7	1115.2	1115.3	1115.6	1115.8	1116.1	1116.3	1116.1	1115.8	1115.6	1115.3
147.5°	1160.4	1161.0	1160.9	1160.6	1160.4	1160.1	1159.9	1159.6	1159.4	1159.1	1158.8
150°	1199.5	1200.0	1200.0	1200.0	1200.0	1200.0	1200.0	1200.0	1200.0	1200.0	1200.0
152.5°	1235.5	1235.8	1235.9	1236.2	1236.4	1236.7	1236.9	1237.6	1238.4	1239.1	1239.8
155°	1272.6	1272.6	1272.5	1272.2	1272.0	1271.7	1271.5	1272.5	1273.5	1274.5	1275.5
157.5°	1304.1	1303.9	1303.9	1303.9	1303.9	1303.9	1303.9	1304.6	1305.4	1306.1	1306.8
160°	1334.1	1334.0	1333.9	1333.6	1333.4	1333.1	1332.9	1333.6	1334.4	1335.1	1335.8
162.5°	1359.0	1358.6	1358.5	1358.2	1357.9	1357.7	1357.4	1358.9	1360.4	1361.9	1363.4
165°	1382.4	1382.0	1381.8	1381.3	1380.8	1380.3	1379.8	1381.3	1382.8	1384.3	1385.8
167.5°	1400.4	1399.9	1399.9	1399.9	1399.9	1399.9	1399.9	1401.4	1402.9	1404.4	1405.9
170°	1415.0	1414.4	1414.5	1414.8	1415.0	1415.3	1415.5	1417.0	1418.5	1420.0	1421.5
172.5°	1427.2	1426.7	1426.7	1426.7	1426.7	1426.7	1426.7	1428.4	1430.2	1431.9	1433.6
175°	1436.2	1435.6	1435.5	1435.2	1435.0	1434.7	1434.5	1436.2	1438.0	1439.7	1441.4
177.5°	1440.7	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1441.8	1443.6	1445.3	1447.0
180°	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3
2.5°	1752.6	1751.1	1743.4	1746.5	1737.2	1740.3	1744.9	1746.5	1752.6	1748.0	1746.5
5°	1644.9	1641.8	1637.2	1632.6	1631.1	1637.2	1626.5	1629.5	1632.6	1637.2	1643.4
7.5°	1557.2	1555.7	1551.1	1543.4	1540.3	1537.2	1538.7	1549.5	1548.0	1546.4	1557.2
10°	1477.2	1478.7	1469.5	1468.0	1458.7	1457.2	1458.7	1461.8	1466.4	1472.6	1474.1
12.5°	1394.1	1414.1	1397.2	1391.0	1377.2	1384.9	1388.0	1374.1	1381.8	1386.4	1409.5
15°	1341.8	1332.6	1321.8	1321.8	1315.6	1312.6	1304.9	1315.6	1321.8	1331.0	1327.9
17.5°	1269.5	1254.1	1247.9	1241.8	1243.3	1249.5	1232.5	1257.2	1257.2	1261.8	1254.1
20°	1206.4	1194.1	1186.4	1183.3	1178.7	1175.6	1174.1	1180.2	1189.5	1192.5	1200.2
22.5°	1140.2	1140.2	1127.9	1123.3	1120.2	1115.6	1123.3	1118.7	1124.8	1131.0	1143.3
25°	1084.8	1084.8	1080.2	1074.0	1069.4	1066.4	1071.0	1069.4	1074.0	1081.7	1084.8
27.5°	1040.2	1035.6	1034.0	1032.5	1031.0	1032.5	1031.0	1035.6	1040.2	1041.7	1038.7
30°	1001.7	997.1	998.6	998.6	1000.2	998.6	997.1	1001.7	1003.3	1000.2	1001.7
32.5°	966.3	966.3	969.4	971.0	971.0	972.5	974.0	971.0	972.5	967.9	969.4
35°	937.1	940.2	943.3	944.8	946.3	944.8	947.9	946.3	943.3	940.2	938.6
37.5°	907.9	910.9	917.1	918.6	923.2	924.8	921.7	921.7	920.2	914.0	910.9
40°	877.1	880.2	887.9	892.5	895.6	900.2	897.1	897.1	890.9	884.8	880.2
42.5°	847.9	854.0	861.7	866.3	872.5	872.5	872.5	869.4	861.7	855.5	850.9
45°	818.6	820.2	830.9	838.6	844.8	844.8	844.8	840.2	835.5	823.2	817.1
47.5°	786.3	790.9	803.2	810.9	817.1	818.6	818.6	814.0	804.8	794.0	786.3
50°	750.9	758.6	772.5	783.2	790.9	794.0	789.4	786.3	775.5	763.2	754.0
52.5°	717.1	726.3	743.2	752.4	763.2	764.8	763.2	758.6	746.3	729.4	721.7
55°	683.2	690.9	709.4	724.8	734.0	737.1	734.0	726.3	710.9	694.0	686.3
57.5°	646.3	657.0	677.0	692.4	703.2	704.7	701.7	694.0	681.7	660.1	649.4
60°	607.8	621.7	641.7	657.0	670.9	672.4	669.4	658.6	643.2	621.7	612.4
62.5°	569.3	580.1	603.2	620.1	630.9	638.6	632.4	621.7	606.3	584.7	570.9
65°	524.7	540.1	560.1	575.5	587.8	589.3	586.3	577.0	560.1	537.0	526.3
67.5°	481.6	492.4	512.4	532.4	537.0	541.6	537.0	527.8	513.9	493.9	478.6
70°	429.3	438.5	463.2	477.0	483.2	487.8	484.7	475.5	463.2	444.7	432.4
72.5°	377.0	384.7	407.8	418.5	430.8	429.3	427.8	421.6	404.7	392.4	384.7
75°	321.6	330.8	346.2	360.1	364.7	364.7	364.7	360.1	349.3	329.3	321.6
77.5°	270.8	275.4	287.7	295.4	300.1	301.6	300.1	292.4	286.2	272.4	267.7
80°	207.7	220.0	229.3	230.8	237.0	237.0	237.0	233.9	227.7	213.9	212.3
82.5°	157.0	160.0	169.3	173.9	177.0	175.4	175.4	169.3	167.7	160.0	157.0
85°	106.2	110.8	109.3	115.4	116.9	113.9	113.9	116.9	109.3	110.8	106.2
87.5°	58.5	58.5	61.5	60.0	66.2	66.2	63.1	64.6	61.5	60.0	58.5
90°	31.3	31.5	32.0	32.5	33.0	33.5	33.0	32.5	32.0	31.5	31.3
92.5°	52.5	52.6	52.9	53.1	53.4	53.6	53.4	53.1	52.9	52.6	52.5
95°	88.2	88.2	88.2	88.2	88.2	88.2	88.2	88.2	88.2	88.2	88.2
97.5°	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5
100°	173.0	173.0	173.0	173.0	173.0	173.0	173.0	173.0	173.0	173.0	173.0
102.5°	221.0	221.1	221.4	221.6	221.9	222.1	221.9	221.6	221.4	221.1	221.0
105°	269.0	269.4	270.1	270.9	271.6	272.4	271.6	270.9	270.1	269.4	269.0
107.5°	321.5	321.4	321.1	320.9	320.6	320.4	320.6	320.9	321.1	321.4	321.5
110°	369.5	369.9	370.6	371.4	372.1	372.9	372.1	371.4	370.6	369.9	369.5

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	426.4	426.4	426.4	426.4	426.4	426.4	426.4	426.4	426.4	426.4	426.4
115°	483.4	483.3	483.0	482.8	482.5	482.3	482.5	482.8	483.0	483.3	483.4
117.5°	537.0	536.6	535.9	535.1	534.4	533.6	534.4	535.1	535.9	536.6	537.0
120°	591.7	591.9	592.4	592.9	593.4	593.9	593.4	592.9	592.4	591.9	591.7
122.5°	649.7	649.1	647.8	646.6	645.3	644.1	645.3	646.6	647.8	649.1	649.7
125°	705.5	705.3	704.8	704.3	703.8	703.3	703.8	704.3	704.8	705.3	705.5
127.5°	758.0	757.9	757.6	757.4	757.1	756.9	757.1	757.4	757.6	757.9	758.0
130°	813.8	813.3	812.3	811.3	810.3	809.3	810.3	811.3	812.3	813.3	813.8
132.5°	866.3	866.2	865.9	865.6	865.4	865.1	865.4	865.6	865.9	866.2	866.3
135°	918.7	918.3	917.6	916.9	916.1	915.4	916.1	916.9	917.6	918.3	918.7
137.5°	969.0	969.1	969.4	969.6	969.9	970.1	969.9	969.6	969.4	969.1	969.0
140°	1020.3	1020.2	1019.9	1019.7	1019.4	1019.2	1019.4	1019.7	1019.9	1020.2	1020.3
142.5°	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3	1068.3
145°	1115.2	1114.8	1114.1	1113.4	1112.6	1111.9	1112.6	1113.4	1114.1	1114.8	1115.2
147.5°	1158.7	1158.6	1158.3	1158.1	1157.8	1157.6	1157.8	1158.1	1158.3	1158.6	1158.7
150°	1200.0	1199.9	1199.6	1199.4	1199.1	1198.9	1199.1	1199.4	1199.6	1199.9	1200.0
152.5°	1240.2	1239.8	1239.1	1238.4	1237.6	1236.9	1237.6	1238.4	1239.1	1239.8	1240.2
155°	1276.0	1275.5	1274.5	1273.5	1272.5	1271.5	1272.5	1273.5	1274.5	1275.5	1276.0
157.5°	1307.2	1306.8	1306.1	1305.4	1304.6	1303.9	1304.6	1305.4	1306.1	1306.8	1307.2
160°	1336.2	1335.6	1334.4	1333.1	1331.9	1330.7	1331.9	1333.1	1334.4	1335.6	1336.2
162.5°	1364.1	1363.5	1362.3	1361.0	1359.8	1358.6	1359.8	1361.0	1362.3	1363.5	1364.1
165°	1386.5	1386.0	1385.0	1384.0	1383.0	1382.0	1383.0	1384.0	1385.0	1386.0	1386.5
167.5°	1406.6	1405.9	1404.4	1402.9	1401.4	1399.9	1401.4	1402.9	1404.4	1405.9	1406.6
170°	1422.2	1421.3	1419.6	1417.9	1416.1	1414.4	1416.1	1417.9	1419.6	1421.3	1422.2
172.5°	1434.5	1433.6	1431.9	1430.2	1428.4	1426.7	1428.4	1430.2	1431.9	1433.6	1434.5
175°	1442.3	1441.4	1439.7	1438.0	1436.2	1434.5	1436.2	1438.0	1439.7	1441.4	1442.3
177.5°	1447.9	1446.9	1444.9	1442.9	1440.9	1438.9	1440.9	1442.9	1444.9	1446.9	1447.9
180°	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3	1857.3
2.5°	1746.5	1755.7	1746.5	1752.6	1755.7	1763.4	1766.5	1780.3	1784.9	1795.7	1795.7
5°	1641.8	1646.5	1648.0	1654.2	1660.3	1675.7	1686.5	1706.5	1729.6	1732.6	1746.5
7.5°	1557.2	1564.9	1577.2	1572.6	1583.4	1606.5	1620.3	1644.9	1668.0	1680.3	1697.2
10°	1481.8	1491.0	1495.7	1500.3	1520.3	1540.3	1561.8	1578.8	1609.5	1628.0	1641.8
12.5°	1420.3	1412.6	1421.8	1438.7	1461.8	1474.1	1503.4	1529.5	1552.6	1572.6	1584.9
15°	1340.2	1346.4	1355.6	1384.9	1391.0	1421.8	1432.6	1461.8	1504.9	1523.4	1538.7
17.5°	1263.3	1283.3	1301.8	1312.6	1331.0	1355.6	1386.4	1418.7	1446.4	1468.0	1486.4
20°	1201.8	1221.8	1232.5	1240.2	1258.7	1292.5	1321.8	1361.8	1397.2	1414.1	1438.7
22.5°	1152.5	1152.5	1167.9	1191.0	1201.8	1234.1	1258.7	1301.8	1340.2	1361.8	1384.9
25°	1091.0	1100.2	1112.5	1132.5	1147.9	1174.1	1209.5	1246.4	1287.9	1306.4	1335.6
27.5°	1040.2	1051.0	1067.9	1072.5	1087.9	1111.0	1147.9	1187.9	1231.0	1251.0	1275.6
30°	1001.7	1007.9	1014.0	1023.3	1037.1	1057.1	1087.9	1123.3	1175.6	1191.0	1221.8
32.5°	967.9	971.0	974.0	981.7	989.4	1009.4	1034.0	1072.5	1115.6	1138.7	1166.4
35°	937.1	934.0	935.6	940.2	947.9	955.6	981.7	1014.0	1054.0	1081.7	1103.3
37.5°	907.9	901.7	900.2	900.2	903.2	912.5	932.5	960.2	1003.3	1026.3	1047.9
40°	875.5	869.4	866.3	864.8	863.2	869.4	884.8	912.5	946.3	967.9	992.5
42.5°	844.8	838.6	830.9	829.4	826.3	829.4	840.2	866.3	895.6	917.1	937.1
45°	814.0	803.2	794.0	787.8	789.4	784.8	792.5	812.5	846.3	860.2	880.2
47.5°	780.1	767.8	755.5	749.4	743.2	746.3	749.4	766.3	795.5	809.4	829.4
50°	747.8	730.9	717.1	709.4	704.7	701.7	704.7	721.7	743.2	755.5	772.5
52.5°	710.9	694.0	680.1	667.8	661.7	657.0	658.6	674.0	694.0	706.3	723.2
55°	677.0	655.5	637.0	621.7	617.0	615.5	614.0	624.7	641.7	654.0	667.8
57.5°	638.6	617.0	597.0	578.6	569.3	567.8	567.8	570.9	592.4	601.7	609.3
60°	600.1	577.0	555.5	538.6	524.7	520.1	518.6	524.7	535.5	544.7	555.5
62.5°	557.0	533.9	507.8	492.4	478.6	466.2	470.9	472.4	487.8	492.4	501.6
65°	515.5	489.3	467.8	443.2	427.8	420.1	417.0	420.1	432.4	433.9	440.1
67.5°	467.8	443.2	417.0	400.1	386.2	372.4	369.3	369.3	375.5	380.1	387.8
70°	421.6	397.0	367.8	349.3	335.4	323.1	318.5	317.0	321.6	324.7	332.4
72.5°	367.8	343.1	321.6	301.6	284.7	275.4	270.8	267.7	272.4	275.4	277.0
75°	310.8	290.8	269.3	249.3	238.5	229.3	223.1	218.5	221.6	221.6	221.6
77.5°	257.0	237.0	220.0	206.2	192.3	181.6	177.0	172.3	173.9	173.9	177.0
80°	200.0	186.2	172.3	160.0	147.7	138.5	135.4	130.8	127.7	126.2	126.2
82.5°	147.7	136.9	124.6	113.9	107.7	98.5	95.4	89.2	89.2	87.7	87.7
85°	98.5	92.3	80.0	72.3	67.7	63.1	60.0	56.9	52.3	52.3	50.8
87.5°	52.3	49.2	46.2	36.9	36.9	32.3	30.8	29.2	24.6	26.2	26.2
90°	30.6	29.1	27.6	26.1	24.6	22.6	20.6	18.6	16.6	15.6	14.2
92.5°	52.1	51.4	50.6	49.9	49.1	47.9	46.6	45.4	44.1	43.5	41.9
95°	87.8	87.1	86.3	85.6	84.8	83.1	81.3	79.6	77.9	77.0	75.9
97.5°	129.0	128.0	127.0	126.0	125.0	123.0	121.0	119.1	117.1	116.1	115.1
100°	172.8	172.3	171.8	171.3	170.8	168.6	166.4	164.1	161.9	160.8	160.3
102.5°	220.6	219.9	219.2	218.4	217.7	215.7	213.7	211.8	209.8	208.8	208.7
105°	268.6	267.9	267.2	266.4	265.7	264.7	263.7	262.7	261.7	261.2	261.1
107.5°	321.0	320.0	319.0	318.0	317.0	316.8	316.5	316.3	316.0	315.9	315.8
110°	369.7	370.2	370.7	371.2	371.7	372.0	372.2	372.5	372.8	372.9	372.6

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	426.4	426.4	426.4	426.4	426.4	426.9	427.4	427.9	428.4	428.7	428.7
115°	483.5	483.8	484.0	484.3	484.5	485.0	485.5	486.0	486.5	486.7	486.7
117.5°	537.4	538.1	538.8	539.6	540.3	540.5	540.8	541.0	541.3	541.4	541.4
120°	592.3	593.5	594.8	596.0	597.2	598.0	598.7	599.5	600.2	600.6	600.1
122.5°	650.1	650.8	651.5	652.3	653.0	653.3	653.5	653.8	654.1	654.2	654.1
125°	705.7	706.2	706.7	707.2	707.7	708.0	708.2	708.5	708.8	708.9	708.9
127.5°	758.2	758.7	759.2	759.7	760.2	760.7	761.2	761.7	762.2	762.4	762.0
130°	814.0	814.5	815.0	815.5	816.0	816.0	816.0	816.0	816.0	816.0	815.6
132.5°	866.5	867.0	867.5	868.0	868.5	868.7	869.0	869.2	869.5	869.6	869.4
135°	919.0	919.5	920.0	920.5	921.0	921.0	921.0	921.0	921.0	921.0	920.3
137.5°	969.4	970.1	970.8	971.6	972.3	971.8	971.3	970.8	970.3	970.1	969.7
140°	1020.4	1020.7	1020.9	1021.2	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.2
142.5°	1068.3	1068.3	1068.3	1068.3	1068.3	1068.5	1068.8	1069.0	1069.3	1069.4	1069.2
145°	1115.3	1115.6	1115.8	1116.1	1116.3	1116.1	1115.8	1115.6	1115.3	1115.2	1114.7
147.5°	1158.8	1159.1	1159.4	1159.6	1159.9	1160.1	1160.4	1160.6	1160.9	1161.0	1160.4
150°	1200.0	1200.0	1200.0	1200.0	1200.0	1200.0	1200.0	1200.0	1200.0	1200.0	1199.5
152.5°	1239.8	1239.1	1238.4	1237.6	1236.9	1236.7	1236.4	1236.2	1235.9	1235.8	1235.5
155°	1275.5	1274.5	1273.5	1272.5	1271.5	1271.7	1272.0	1272.2	1272.5	1272.6	1272.6
157.5°	1306.8	1306.1	1305.4	1304.6	1303.9	1303.9	1303.9	1303.9	1303.9	1303.9	1304.1
160°	1335.8	1335.1	1334.4	1333.6	1332.9	1333.1	1333.4	1333.6	1333.9	1334.0	1334.1
162.5°	1363.4	1361.9	1360.4	1358.9	1357.4	1357.7	1357.9	1358.2	1358.5	1358.6	1359.0
165°	1385.8	1384.3	1382.8	1381.3	1379.8	1380.3	1380.8	1381.3	1381.8	1382.0	1382.4
167.5°	1405.9	1404.4	1402.9	1401.4	1399.9	1399.9	1399.9	1399.9	1399.9	1399.9	1400.4
170°	1421.5	1420.0	1418.5	1417.0	1415.5	1415.3	1415.0	1414.8	1414.5	1414.4	1415.0
172.5°	1433.6	1431.9	1430.2	1428.4	1426.7	1426.7	1426.7	1426.7	1426.7	1426.7	1427.2
175°	1441.4	1439.7	1438.0	1436.2	1434.5	1434.7	1435.0	1435.2	1435.5	1435.6	1436.2
177.5°	1447.0	1445.3	1443.6	1441.8	1440.1	1440.1	1440.1	1440.1	1440.1	1440.1	1440.7
180°	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4	1443.4

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1857.3	1857.3	1857.3	1857.3
2.5°	1806.5	1821.9	1835.7	1857.3
5°	1766.5	1788.0	1817.3	1849.6
7.5°	1720.3	1754.2	1792.6	1837.3
10°	1677.2	1715.7	1764.9	1818.8
12.5°	1632.6	1678.8	1732.6	1791.1
15°	1581.8	1628.0	1688.0	1766.5
17.5°	1535.7	1591.1	1655.7	1738.8
20°	1481.8	1534.1	1604.9	1700.3
22.5°	1434.1	1494.1	1572.6	1655.7
25°	1381.8	1434.1	1512.6	1612.6
27.5°	1329.5	1394.1	1469.5	1566.4
30°	1278.7	1332.6	1414.1	1515.7
32.5°	1223.3	1287.9	1363.3	1458.7
35°	1163.3	1224.8	1295.6	1398.7
37.5°	1109.4	1169.4	1241.8	1332.6
40°	1049.4	1112.5	1178.7	1269.5
42.5°	991.0	1047.9	1114.1	1197.1
45°	934.0	983.3	1043.3	1115.6
47.5°	875.5	917.1	972.5	1037.1
50°	812.5	857.1	898.6	952.5
52.5°	754.0	792.5	826.3	870.9
55°	697.1	723.2	750.9	784.8
57.5°	637.0	657.0	677.0	712.4
60°	577.0	595.5	606.3	629.3
62.5°	518.6	526.3	540.1	553.9
65°	453.9	464.7	472.4	489.3
67.5°	395.5	400.1	407.8	418.5
70°	333.9	344.7	347.8	355.5
72.5°	281.6	286.2	289.3	290.8
75°	223.1	227.7	230.8	240.0
77.5°	175.4	173.9	180.0	181.6
80°	129.3	124.6	126.2	132.3
82.5°	84.6	86.2	84.6	84.6
85°	52.3	50.8	47.7	49.2
87.5°	23.1	23.1	21.5	21.5
90°	11.5	8.8	6.0	3.3
92.5°	38.7	35.4	32.2	29.0
95°	73.7	71.4	69.2	67.0
97.5°	113.1	111.2	109.2	107.2
100°	159.3	158.3	157.3	156.3
102.5°	208.4	208.1	207.9	207.6
105°	260.8	260.6	260.3	260.1
107.5°	315.5	315.3	315.0	314.8
110°	372.1	371.6	371.1	370.6

TEST NUMBER: P1000918

CATALOG NUMBER: SA4XXDIP-B1195D1205UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	428.7	428.7	428.7	428.7
115°	486.7	486.7	486.7	486.7
117.5°	541.4	541.4	541.4	541.4
120°	599.1	598.1	597.1	596.1
122.5°	653.8	653.5	653.3	653.0
125°	708.9	708.9	708.9	708.9
127.5°	761.3	760.6	759.8	759.1
130°	814.9	814.2	813.4	812.7
132.5°	868.9	868.4	867.9	867.4
135°	918.8	917.3	915.8	914.3
137.5°	969.0	968.2	967.5	966.7
140°	1020.7	1020.2	1019.7	1019.2
142.5°	1068.7	1068.2	1067.7	1067.2
145°	1113.7	1112.7	1111.7	1110.7
147.5°	1159.1	1157.9	1156.6	1155.4
150°	1198.5	1197.6	1196.6	1195.6
152.5°	1235.0	1234.5	1234.0	1233.5
155°	1272.6	1272.6	1272.6	1272.6
157.5°	1304.6	1305.1	1305.6	1306.1
160°	1334.4	1334.6	1334.9	1335.1
162.5°	1359.7	1360.4	1361.2	1361.9
165°	1383.1	1383.9	1384.6	1385.4
167.5°	1401.4	1402.3	1403.3	1404.3
170°	1416.3	1417.5	1418.8	1420.0
172.5°	1428.2	1429.1	1430.1	1431.1
175°	1437.5	1438.7	1440.0	1441.2
177.5°	1441.9	1443.2	1444.4	1445.6
180°	1443.4	1443.4	1443.4	1443.4

(END OF REPORT)