

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001914

Luminaire Tested: SA4XXDIP-B795D590UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001914
REPORT IS A COMBINATION OF REPORTS P996539 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D590UB35-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5501.0 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001914

CATALOG NUMBER: SA4XXDIP-B795D590UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001914

CATALOG NUMBER: SA4XXDIP-B795D590UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	53	50	48
3	84	74	66	60	78	69	63	57	61	56	52	54	50	46	47	44	41
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	32	28	24	29	25	22
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	26	22	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10929	10929	10929
5°	10938	10615	10627
10°	10845	10320	10247
15°	10690	9969	9820
20°	10491	9591	9376
25°	10268	9190	8898
30°	9998	8757	8374
35°	9719	8314	7867
40°	9427	7837	7328
45°	9122	7359	6824
50°	8785	6895	6266
55°	8417	6353	5711
60°	8041	5760	5134
65°	7611	5148	4484
70°	7117	4409	3786
75°	6374	3555	3032
80°	5433	2570	2133
85°	4221	1430	1149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9122 cd/sqm

TEST NUMBER: P1001914

CATALOG NUMBER: SA4XXDIP-B795D590UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.3
10°-20°	355.9	6.5
20°-30°	523.8	9.5
30°-40°	608.9	11.1
40°-50°	608.8	11.1
50°-60°	532.5	9.7
60°-70°	395.3	7.2
70°-80°	224.3	4.1
80°-90°	65.8	1.2
90°-100°	48.4	0.9
100°-110°	144.9	2.6
110°-120°	246.2	4.5
120°-130°	324.7	5.9
130°-140°	364.7	6.6
140°-150°	358.4	6.5
150°-160°	301.4	5.5
160°-170°	200.6	3.6
170°-180°	70.2	1.3
0°-30°	1006.0	18.3
0°-40°	1614.9	29.4
0°-60°	2756.1	50.1
0°-90°	3441.6	62.6
90°-120°	439.5	8.0
90°-150°	1487.2	27.0
90°-180°	2059.0	37.4
0°-180°	5501.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1339	1335	1323	1335	1333	127
15°	1275	1270	1254	1261	1258	359
25°	1154	1147	1132	1133	1129	531
35°	993	986	971	963	958	621
45°	811	803	786	774	771	625
55°	613	610	595	582	576	549
65°	416	410	400	389	383	411
75°	221	216	210	206	205	235
85°	58	58	56	56	55	62
90°	2	8	13	16	17	6
95°	34	40	44	45	45	37
105°	134	134	137	138	140	142
115°	250	250	249	249	248	247
125°	364	364	364	363	362	325
135°	470	474	474	472	471	364
145°	571	574	574	574	572	358
155°	654	654	654	656	654	301
165°	712	711	710	713	711	201
175°	741	738	738	742	738	70
180°	742	742	742	742	742	

TEST NUMBER: P1001914

CATALOG NUMBER: SA4XXDIP-B795D590UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.2	1340.2	1340.2	1340.2	1340.2
2.5°	1344.5	1341.3	1329.5	1340.2	1339.2
5°	1339.2	1334.9	1323.1	1334.9	1332.7
7.5°	1329.5	1325.2	1312.3	1322.0	1320.9
10°	1315.5	1311.2	1297.3	1305.9	1303.7
12.5°	1297.3	1293.0	1278.0	1287.6	1284.4
15°	1274.7	1270.4	1254.3	1260.8	1257.6
17.5°	1249.0	1243.6	1228.6	1232.9	1230.7
20°	1220.0	1214.6	1198.5	1201.7	1199.6
22.5°	1188.8	1181.3	1165.2	1171.6	1167.3
25°	1154.5	1146.9	1131.9	1133.0	1128.7
27.5°	1115.8	1108.3	1094.3	1092.2	1086.8
30°	1077.1	1068.5	1054.6	1050.3	1044.9
32.5°	1036.3	1028.8	1013.8	1008.4	1003.0
35°	993.4	985.9	970.8	963.3	957.9
37.5°	948.3	941.8	925.7	918.2	910.7
40°	904.2	895.6	879.5	868.8	863.4
42.5°	857.0	852.7	834.4	821.5	818.3
45°	810.8	803.3	786.1	774.3	771.1
47.5°	762.5	757.1	741.0	728.1	719.5
50°	713.1	708.8	693.7	678.7	672.3
52.5°	664.8	659.4	643.3	630.4	621.8
55°	613.2	610.0	594.9	582.1	575.6
57.5°	564.9	561.7	546.6	533.7	527.3
60°	514.4	509.0	495.1	485.4	480.0
62.5°	465.0	460.7	445.7	437.1	431.7
65°	415.6	410.2	399.5	388.8	383.4
67.5°	365.1	360.8	350.1	339.4	338.3
70°	319.0	311.4	302.8	294.3	291.0
72.5°	269.6	262.0	255.6	249.1	245.9
75°	221.2	215.9	210.5	206.2	205.1
77.5°	174.0	171.8	166.5	165.4	162.2
80°	132.1	128.9	126.7	124.6	123.5
82.5°	91.3	90.2	90.2	89.1	88.1
85°	58.0	58.0	55.8	55.8	54.8
87.5°	27.9	26.8	25.8	25.8	25.8
90°	1.7	8.0	12.6	16.1	17.2
92.5°	14.9	22.4	25.3	27.0	27.6
95°	34.4	39.6	43.6	45.3	45.3
97.5°	55.1	59.7	64.3	66.6	66.6
100°	80.4	82.7	87.8	89.0	89.0
102.5°	106.8	107.3	111.9	113.7	114.2
105°	133.8	134.3	136.6	138.3	140.1
107.5°	161.9	162.5	163.0	165.3	164.7
110°	190.6	191.7	191.2	190.0	191.7

TEST NUMBER: P1001914

CATALOG NUMBER: SA4XXDIP-B795D590UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	220.4	220.4	219.3	219.3	219.3
115°	250.3	250.3	249.1	248.6	248.0
117.5°	278.4	278.4	277.8	276.1	274.4
120°	306.5	308.8	307.1	304.2	305.4
122.5°	335.8	336.4	335.8	334.1	331.2
125°	364.5	364.5	363.9	362.8	361.6
127.5°	390.3	392.1	390.9	389.8	389.2
130°	417.9	419.6	419.6	418.5	416.2
132.5°	446.0	447.2	446.6	445.5	444.9
135°	470.1	473.6	473.6	472.4	470.7
137.5°	497.1	498.8	500.0	498.3	498.8
140°	524.1	525.2	525.2	524.7	524.1
142.5°	548.8	549.9	549.4	549.4	549.4
145°	571.2	573.5	574.0	573.5	571.7
147.5°	594.1	597.0	596.4	595.8	595.3
150°	614.8	617.1	617.1	617.1	616.5
152.5°	634.3	635.5	636.0	637.8	636.0
155°	654.4	654.4	653.8	656.1	653.8
157.5°	671.6	670.5	670.5	672.2	670.5
160°	686.5	686.0	685.4	687.1	684.3
162.5°	700.3	698.6	698.0	701.5	698.6
165°	712.4	710.7	709.5	713.0	710.7
167.5°	722.1	719.8	719.8	723.3	719.8
170°	730.2	727.3	727.9	731.3	727.3
172.5°	735.9	733.6	733.6	737.6	733.6
175°	741.1	738.2	737.6	741.7	737.6
177.5°	743.4	740.5	740.5	744.5	739.9
180°	742.2	742.2	742.2	742.2	742.2

(END OF REPORT)