

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001921

Luminaire Tested: SA4XXDIP-B795D590UB40-4F0-XX-W2A-D4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001921
REPORT IS A COMBINATION OF REPORTS P996546 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D590UB40-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5349.3 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001921

CATALOG NUMBER: SA4XXDIP-B795D590UB40-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001921

CATALOG NUMBER: SA4XXDIP-B795D590UB40-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		74	74	74		62	62	62
1	98	93	89	85		91	87	83	79		74	71	69		63	61	59		53	51	50
2	89	81	74	68		82	75	69	64		64	60	56		55	51	48		46	43	41
3	81	71	63	56		75	66	59	53		56	51	47		48	44	40		40	37	34
4	74	62	54	47		68	58	50	45		50	44	39		42	38	34		36	32	29
5	67	55	47	40		62	52	44	38		45	38	34		38	33	29		32	28	25
6	62	49	41	35		57	46	39	33		40	34	29		34	29	26		29	25	22
7	57	45	36	30		53	42	34	29		36	30	26		31	26	23		26	22	20
8	53	40	32	27		49	38	31	25		33	27	23		28	24	20		24	20	17
9	50	37	29	24		46	35	28	23		30	24	20		26	21	18		22	18	16
10	46	34	26	21		43	32	25	20		28	22	18		24	20	16		21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7742	7742	7742
5°	7763	7541	7554
10°	7713	7392	7371
15°	7641	7225	7164
20°	7534	7044	6964
25°	7413	6845	6747
30°	7283	6648	6527
35°	7136	6446	6330
40°	7017	6253	6127
45°	6842	6071	5947
50°	6693	5865	5757
55°	6538	5665	5539
60°	6300	5418	5333
65°	6036	5152	5085
70°	5716	4846	4799
75°	5271	4507	4527
80°	4767	4162	4242
85°	4097	3813	4012

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6842 cd/sqm

TEST NUMBER: P1001921

CATALOG NUMBER: SA4XXDIP-B795D590UB40-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	1.7
10°-20°	257.7	4.8
20°-30°	389.7	7.3
30°-40°	471.5	8.8
40°-50°	498.4	9.3
50°-60°	469.1	8.8
60°-70°	389.3	7.3
70°-80°	273.2	5.1
80°-90°	155.1	2.9
90°-100°	306.6	5.7
100°-110°	504.9	9.4
110°-120°	435.1	8.1
120°-130°	352.9	6.6
130°-140°	284.2	5.3
140°-150°	210.7	3.9
150°-160°	146.6	2.7
160°-170°	86.2	1.6
170°-180°	28.0	0.5
0°-30°	737.4	13.8
0°-40°	1208.9	22.6
0°-60°	2176.5	40.7
0°-90°	2994.0	56.0
90°-120°	1246.7	23.3
90°-150°	2094.4	39.2
90°-180°	2355.0	44.0
0°-180°	5349.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	949	949	949	949	949	
5°	950	947	940	948	947	90
15°	911	912	909	919	918	257
25°	834	840	843	855	856	384
35°	729	742	753	768	771	457
45°	608	628	648	667	672	470
55°	476	499	530	552	558	424
65°	330	364	400	426	435	327
75°	183	222	267	297	306	194
85°	56	101	149	181	191	59
90°	18	64	116	148	156	13
95°	33	108	556	351	270	32
105°	76	127	443	900	905	82
115°	124	163	382	712	849	123
125°	167	197	361	594	669	149
135°	196	233	338	509	581	152
145°	224	256	326	413	458	141
155°	254	274	317	359	374	117
165°	277	285	304	322	327	78
175°	289	289	292	296	294	27
180°	289	289	289	289	289	

TEST NUMBER: P1001921

CATALOG NUMBER: SA4XXDIP-B795D590UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	949.4	949.4	949.4	949.4	949.4
2.5°	953.7	950.5	942.0	949.4	948.4
5°	950.5	947.3	939.9	948.4	947.3
7.5°	944.1	942.0	935.6	945.2	944.1
10°	935.6	934.5	929.2	938.8	937.7
12.5°	923.9	923.9	920.7	929.2	929.2
15°	911.2	912.2	909.0	918.6	917.5
17.5°	894.1	897.3	896.3	905.8	904.8
20°	876.1	879.3	880.3	891.0	891.0
22.5°	855.9	860.1	862.2	872.9	875.0
25°	833.5	839.9	843.1	854.8	855.9
27.5°	809.1	818.7	822.9	833.5	834.6
30°	784.6	793.1	800.6	812.3	814.4
32.5°	758.1	768.7	777.2	791.0	793.1
35°	729.4	742.1	752.7	767.6	770.8
37.5°	700.6	715.5	728.3	743.2	746.4
40°	673.0	686.8	701.7	717.7	721.9
42.5°	641.1	657.1	675.1	693.2	696.4
45°	608.1	628.3	648.5	666.6	671.9
47.5°	577.3	597.5	620.9	639.0	645.4
50°	543.3	566.7	590.1	611.3	617.7
52.5°	509.3	532.7	560.3	581.6	587.9
55°	476.3	498.6	530.5	551.8	558.2
57.5°	439.1	466.7	497.6	523.1	528.4
60°	403.0	430.6	465.7	490.1	498.6
62.5°	367.9	398.7	433.8	458.2	466.7
65°	329.6	363.6	399.8	426.3	434.8
67.5°	293.4	329.6	367.9	394.4	403.0
70°	256.2	292.4	332.8	361.5	368.9
72.5°	220.1	257.3	300.9	328.5	337.0
75°	182.9	222.2	266.9	296.6	306.2
77.5°	147.8	189.2	236.0	265.8	276.4
80°	115.9	158.4	205.2	237.1	245.6
82.5°	84.0	128.6	175.4	208.4	218.0
85°	56.3	101.0	148.8	180.7	191.4
87.5°	35.1	78.7	125.5	156.3	165.9
90°	17.6	64.0	115.5	147.5	156.5
92.5°	23.9	97.0	321.7	202.2	188.9
95°	32.6	108.0	555.7	350.6	269.5
97.5°	44.1	109.0	582.8	583.1	457.4
100°	54.9	113.2	537.7	757.4	638.1
102.5°	66.3	119.2	484.1	863.5	796.4
105°	76.1	127.2	443.0	899.6	904.9
107.5°	89.2	136.4	414.4	881.4	953.1
110°	101.1	144.8	399.3	829.6	948.9

TEST NUMBER: P1001921

CATALOG NUMBER: SA4XXDIP-B795D590UB40-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	112.5	154.0	388.9	767.5	909.0
115°	123.5	162.8	382.5	712.2	848.6
117.5°	136.0	172.0	376.6	666.6	790.4
120°	147.4	179.6	371.2	633.8	740.9
122.5°	158.7	188.0	365.3	611.1	700.4
125°	167.4	197.0	360.6	593.6	668.9
127.5°	176.5	207.2	354.1	575.6	647.7
130°	182.8	216.0	348.2	556.3	627.8
132.5°	190.2	224.6	343.4	534.6	607.1
135°	195.9	232.8	337.5	509.1	580.9
137.5°	202.7	238.9	333.2	483.4	551.2
140°	210.1	245.5	329.5	458.0	520.3
142.5°	217.1	251.4	327.4	435.4	487.6
145°	224.4	255.8	326.2	413.4	457.9
147.5°	233.0	260.8	324.5	394.1	429.8
150°	240.9	265.7	322.8	380.2	405.8
152.5°	247.2	270.2	320.0	369.4	388.7
155°	254.0	274.2	317.1	359.2	374.5
157.5°	260.9	277.9	314.3	349.5	361.5
160°	267.1	281.0	310.9	339.8	349.5
162.5°	272.8	283.6	307.5	330.5	338.2
165°	276.8	285.3	304.1	322.0	326.8
167.5°	281.3	286.7	300.6	314.5	317.7
170°	284.2	287.8	297.2	307.2	309.2
172.5°	287.0	288.7	293.8	300.6	300.6
175°	288.7	289.3	291.5	295.5	294.4
177.5°	289.8	289.3	289.8	291.8	289.8
180°	289.3	289.3	289.3	289.3	289.3

(END OF REPORT)