

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001932

Luminaire Tested: SA4XXDIP-B795D590UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001932
REPORT IS A COMBINATION OF REPORTS P996557 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D590UB50-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5266.0 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001932

CATALOG NUMBER: SA4XXDIP-B795D590UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001932

CATALOG NUMBER: SA4XXDIP-B795D590UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	53	50	48
3	84	74	66	60	78	69	63	57	61	56	52	54	50	46	47	44	41
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	32	28	24	29	25	22
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	26	22	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10462	10462	10462
5°	10470	10161	10174
10°	10382	9879	9810
15°	10233	9543	9399
20°	10043	9181	8975
25°	9829	8797	8518
30°	9571	8383	8016
35°	9303	7958	7531
40°	9025	7503	7014
45°	8733	7044	6532
50°	8409	6600	5998
55°	8058	6082	5467
60°	7697	5514	4915
65°	7285	4927	4292
70°	6811	4222	3625
75°	6104	3403	2904
80°	5199	2460	2042
85°	4039	1371	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8733 cd/sqm

TEST NUMBER: P1001932

CATALOG NUMBER: SA4XXDIP-B795D590UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	2.3
10°-20°	340.7	6.5
20°-30°	501.4	9.5
30°-40°	582.8	11.1
40°-50°	582.8	11.1
50°-60°	509.7	9.7
60°-70°	378.4	7.2
70°-80°	214.7	4.1
80°-90°	63.0	1.2
90°-100°	46.3	0.9
100°-110°	138.7	2.6
110°-120°	235.6	4.5
120°-130°	310.8	5.9
130°-140°	349.1	6.6
140°-150°	343.1	6.5
150°-160°	288.6	5.5
160°-170°	192.0	3.6
170°-180°	67.2	1.3
0°-30°	963.0	18.3
0°-40°	1545.9	29.4
0°-60°	2638.4	50.1
0°-90°	3294.5	62.6
90°-120°	420.7	8.0
90°-150°	1423.7	27.0
90°-180°	1971.0	37.4
0°-180°	5266.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1283	1283	1283	1283	1283	
5°	1282	1278	1266	1278	1276	122
15°	1220	1216	1201	1207	1204	344
25°	1105	1098	1084	1085	1080	509
35°	951	944	929	922	917	595
45°	776	769	752	741	738	598
55°	587	584	570	557	551	526
65°	398	393	382	372	367	394
75°	212	207	202	197	196	225
85°	56	56	54	54	52	60
90°	2	8	12	15	16	6
95°	33	38	42	43	43	36
105°	128	129	131	132	134	136
115°	240	240	238	238	237	236
125°	349	349	348	347	346	311
135°	450	453	453	452	451	348
145°	547	549	550	549	547	342
155°	626	626	626	628	626	288
165°	682	680	679	682	680	192
175°	709	707	706	710	706	67
180°	710	710	710	710	710	

TEST NUMBER: P1001932

CATALOG NUMBER: SA4XXDIP-B795D590UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1283.0	1283.0	1283.0	1283.0	1283.0
2.5°	1287.1	1284.0	1272.7	1283.0	1281.9
5°	1281.9	1277.8	1266.5	1277.8	1275.8
7.5°	1272.7	1268.6	1256.2	1265.5	1264.5
10°	1259.3	1255.2	1241.9	1250.1	1248.0
12.5°	1241.9	1237.7	1223.3	1232.6	1229.5
15°	1220.3	1216.2	1200.7	1206.9	1203.8
17.5°	1195.6	1190.5	1176.1	1180.2	1178.1
20°	1167.8	1162.7	1147.3	1150.4	1148.3
22.5°	1138.0	1130.8	1115.4	1121.6	1117.5
25°	1105.1	1097.9	1083.5	1084.6	1080.5
27.5°	1068.1	1060.9	1047.6	1045.5	1040.4
30°	1031.1	1022.9	1009.5	1005.4	1000.3
32.5°	992.0	984.8	970.5	965.3	960.2
35°	950.9	943.7	929.3	922.1	917.0
37.5°	907.7	901.6	886.2	879.0	871.8
40°	865.6	857.4	842.0	831.7	826.5
42.5°	820.4	816.3	798.8	786.4	783.4
45°	776.2	769.0	752.5	741.2	738.1
47.5°	729.9	724.8	709.3	697.0	688.8
50°	682.6	678.5	664.1	649.7	643.5
52.5°	636.3	631.2	615.8	603.4	595.2
55°	587.0	583.9	569.5	557.2	551.0
57.5°	540.7	537.7	523.3	510.9	504.8
60°	492.4	487.3	473.9	464.7	459.5
62.5°	445.1	441.0	426.6	418.4	413.3
65°	397.8	392.7	382.4	372.1	367.0
67.5°	349.5	345.4	335.1	324.9	323.8
70°	305.3	298.1	289.9	281.7	278.6
72.5°	258.0	250.8	244.7	238.5	235.4
75°	211.8	206.6	201.5	197.4	196.4
77.5°	166.5	164.5	159.3	158.3	155.2
80°	126.4	123.4	121.3	119.3	118.2
82.5°	87.4	86.4	86.4	85.3	84.3
85°	55.5	55.5	53.5	53.5	52.4
87.5°	26.7	25.7	24.7	24.7	24.7
90°	1.6	7.7	12.1	15.4	16.5
92.5°	14.3	21.4	24.2	25.8	26.4
95°	33.0	37.9	41.8	43.4	43.4
97.5°	52.8	57.2	61.5	63.7	63.7
100°	76.9	79.1	84.1	85.2	85.2
102.5°	102.2	102.8	107.2	108.8	109.4
105°	128.0	128.6	130.8	132.4	134.1
107.5°	155.0	155.5	156.1	158.3	157.7
110°	182.4	183.5	183.0	181.9	183.5

TEST NUMBER: P1001932

CATALOG NUMBER: SA4XXDIP-B795D590UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	211.0	211.0	209.9	209.9	209.9
115°	239.6	239.6	238.5	237.9	237.4
117.5°	266.5	266.5	266.0	264.3	262.7
120°	293.4	295.6	294.0	291.2	292.3
122.5°	321.5	322.0	321.5	319.8	317.1
125°	348.9	348.9	348.4	347.3	346.2
127.5°	373.7	375.3	374.2	373.1	372.6
130°	400.1	401.7	401.7	400.6	398.4
132.5°	427.0	428.1	427.5	426.4	425.9
135°	450.1	453.4	453.4	452.3	450.6
137.5°	475.9	477.5	478.6	477.0	477.5
140°	501.7	502.8	502.8	502.3	501.7
142.5°	525.3	526.4	525.9	525.9	525.9
145°	546.8	549.0	549.5	549.0	547.3
147.5°	568.8	571.5	571.0	570.4	569.9
150°	588.5	590.7	590.7	590.7	590.2
152.5°	607.2	608.3	608.9	610.5	608.9
155°	626.5	626.5	625.9	628.1	625.9
157.5°	642.9	641.8	641.8	643.5	641.8
160°	657.2	656.7	656.1	657.8	655.0
162.5°	670.4	668.8	668.2	671.5	668.8
165°	682.0	680.3	679.2	682.5	680.3
167.5°	691.3	689.1	689.1	692.4	689.1
170°	699.0	696.3	696.8	700.1	696.3
172.5°	704.5	702.3	702.3	706.1	702.3
175°	709.4	706.7	706.1	710.0	706.1
177.5°	711.6	708.9	708.9	712.7	708.3
180°	710.5	710.5	710.5	710.5	710.5

(END OF REPORT)