

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000934

Luminaire Tested: SA4XXDIP-B1195D365UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000934
REPORT IS A COMBINATION OF REPORTS P995547 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D365UB27-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6392.6 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000934

CATALOG NUMBER: SA4XXDIP-B1195D365UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000934

CATALOG NUMBER: SA4XXDIP-B1195D365UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	83	83	83	80
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	74	72	70	70	70	70	67
2	95	87	81	75	91	84	78	73	77	72	68	71	67	63	65	62	59	59	59	59	56
3	87	77	69	63	83	74	67	61	68	62	57	62	58	54	57	54	50	50	50	50	47
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43	43	43	43	41
5	73	61	52	46	70	59	51	45	54	48	42	50	45	40	46	42	38	38	38	38	35
6	68	55	46	40	64	53	45	39	49	42	37	45	40	35	42	37	33	33	33	33	31
7	63	50	41	35	60	48	40	35	45	38	33	41	36	31	38	34	30	30	30	30	28
8	58	45	37	32	56	44	36	31	41	34	29	38	32	28	35	30	27	27	27	27	25
9	54	41	34	28	52	40	33	28	37	31	27	35	29	25	33	28	24	24	24	24	22
10	51	38	31	26	49	37	30	25	35	28	24	32	27	23	30	26	22	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16146	16146	16146
5°	16159	15681	15700
10°	16022	15246	15139
15°	15792	14729	14506
20°	15499	14169	13850
25°	15168	13577	13145
30°	14770	12938	12371
35°	14357	12282	11622
40°	13928	11578	10826
45°	13476	10871	10081
50°	12977	10186	9257
55°	12435	9386	8438
60°	11879	8510	7585
65°	11244	7605	6624
70°	10512	6515	5593
75°	9418	5252	4480
80°	8024	3797	3151
85°	6236	2114	1696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13476 cd/sqm

TEST NUMBER: P1000934

CATALOG NUMBER: SA4XXDIP-B1195D365UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	2.9
10°-20°	525.8	8.2
20°-30°	773.8	12.1
30°-40°	899.5	14.1
40°-50°	899.4	14.1
50°-60°	786.6	12.3
60°-70°	584.0	9.1
70°-80°	331.4	5.2
80°-90°	95.6	1.5
90°-100°	133.3	2.1
100°-110°	271.2	4.2
110°-120°	241.7	3.8
120°-130°	203.0	3.2
130°-140°	169.4	2.7
140°-150°	129.4	2.0
150°-160°	91.0	1.4
160°-170°	53.5	0.8
170°-180°	17.4	0.3
0°-30°	1486.2	23.2
0°-40°	2385.7	37.3
0°-60°	4071.7	63.7
0°-90°	5082.7	79.5
90°-120°	646.2	10.1
90°-150°	1148.1	18.0
90°-180°	1310.0	20.5
0°-180°	6392.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1980	1980	1980	1980	1980	
5°	1978	1972	1955	1972	1969	188
15°	1883	1877	1853	1863	1858	531
25°	1706	1694	1672	1674	1667	785
35°	1468	1456	1434	1423	1415	918
45°	1198	1187	1161	1144	1139	923
55°	906	901	879	860	850	811
65°	614	606	590	574	566	608
75°	327	319	311	305	303	347
85°	86	86	82	82	81	92
90°	0	3	6	7	7	6
95°	12	37	287	142	86	13
105°	41	60	231	498	496	44
115°	73	91	206	396	476	72
125°	101	120	205	337	380	90
135°	120	143	204	299	340	93
145°	139	159	202	252	278	87
155°	158	170	197	223	232	73
165°	172	177	189	200	203	49
175°	179	180	181	183	183	17
180°	180	180	180	180	180	

TEST NUMBER: P1000934

CATALOG NUMBER: SA4XXDIP-B1195D365UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1980.0	1980.0	1980.0	1980.0	1980.0
2.5°	1986.3	1981.6	1964.1	1980.0	1978.4
5°	1978.4	1972.0	1954.6	1972.0	1968.9
7.5°	1964.1	1957.8	1938.7	1953.0	1951.4
10°	1943.5	1937.1	1916.5	1929.2	1926.0
12.5°	1916.5	1910.2	1888.0	1902.2	1897.5
15°	1883.2	1876.9	1853.1	1862.6	1857.8
17.5°	1845.1	1837.2	1815.0	1821.3	1818.2
20°	1802.3	1794.4	1770.6	1775.3	1772.1
22.5°	1756.3	1745.2	1721.4	1730.9	1724.5
25°	1705.5	1694.4	1672.2	1673.8	1667.4
27.5°	1648.4	1637.3	1616.7	1613.5	1605.6
30°	1591.3	1578.6	1558.0	1551.6	1543.7
32.5°	1531.0	1519.9	1497.7	1489.7	1481.8
35°	1467.5	1456.4	1434.2	1423.1	1415.2
37.5°	1400.9	1391.4	1367.6	1356.5	1345.4
40°	1335.9	1323.2	1299.4	1283.5	1275.6
42.5°	1266.0	1259.7	1232.7	1213.7	1208.9
45°	1197.8	1186.7	1161.3	1143.9	1139.1
47.5°	1126.4	1118.5	1094.7	1075.7	1063.0
50°	1053.4	1047.1	1024.9	1002.7	993.2
52.5°	982.1	974.1	950.3	931.3	918.6
55°	905.9	901.1	878.9	859.9	850.4
57.5°	834.5	829.8	807.5	788.5	779.0
60°	759.9	752.0	731.4	717.1	709.2
62.5°	687.0	680.6	658.4	645.7	637.8
65°	614.0	606.1	590.2	574.3	566.4
67.5°	539.4	533.1	517.2	501.3	499.8
70°	471.2	460.1	447.4	434.7	429.9
72.5°	398.2	387.1	377.6	368.1	363.3
75°	326.8	318.9	311.0	304.6	303.0
77.5°	257.0	253.8	245.9	244.3	239.6
80°	195.1	190.4	187.2	184.0	182.4
82.5°	134.9	133.3	133.3	131.7	130.1
85°	85.7	85.7	82.5	82.5	80.9
87.5°	41.2	39.7	38.1	38.1	38.1
90°	0.4	2.8	6.3	7.1	7.4
92.5°	4.9	27.2	138.2	45.7	32.1
95°	11.6	36.7	287.4	142.3	86.0
97.5°	19.4	40.6	307.5	290.6	206.6
100°	26.8	45.8	283.5	402.0	323.4
102.5°	33.9	52.2	253.5	471.8	424.9
105°	41.3	59.8	231.3	498.1	496.2
107.5°	49.4	67.5	216.9	490.2	530.0
110°	57.5	75.2	210.2	462.0	530.7



TEST NUMBER: P1000934

CATALOG NUMBER: SA4XXDIP-B1195D365UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.2	83.0	207.0	427.4	509.9
115°	72.6	91.2	206.3	396.4	476.4
117.5°	80.4	98.8	205.9	372.0	443.6
120°	88.2	106.2	205.9	355.6	416.8
122.5°	95.2	113.4	205.6	344.9	395.7
125°	101.2	120.2	205.2	337.3	380.1
127.5°	106.8	126.6	204.5	330.0	370.3
130°	111.4	132.8	204.2	321.5	361.8
132.5°	116.0	138.0	203.8	311.2	352.3
135°	120.2	143.2	203.5	299.4	339.9
137.5°	124.5	147.6	203.5	286.7	325.5
140°	129.1	151.6	203.1	274.4	309.6
142.5°	134.0	155.4	203.1	262.9	292.7
145°	138.6	158.7	202.4	252.5	277.5
147.5°	143.9	161.9	201.4	243.8	263.4
150°	148.8	164.8	200.3	235.9	251.8
152.5°	153.4	167.7	198.5	229.2	241.2
155°	157.6	170.2	196.8	222.9	232.4
157.5°	161.9	172.4	195.0	216.8	224.3
160°	165.7	174.4	192.9	210.9	216.9
162.5°	169.3	176.0	190.8	205.0	209.8
165°	171.7	177.0	188.7	199.8	202.8
167.5°	174.6	177.9	186.5	195.2	197.1
170°	176.3	178.6	184.4	190.6	191.8
172.5°	178.1	179.2	182.3	186.6	186.5
175°	179.1	179.5	180.9	183.4	182.7
177.5°	179.8	179.5	179.8	181.1	179.8
180°	179.5	179.5	179.5	179.5	179.5

(END OF REPORT)