

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001939

Luminaire Tested: SA4XXDIP-B795D810UB27-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001939
REPORT IS A COMBINATION OF REPORTS P996564 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB27-4F0-XX-W2A-D4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6041.7 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001939

CATALOG NUMBER: SA4XXDIP-B795D810UB27-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P1001939

CATALOG NUMBER: SA4XXDIP-B795D810UB27-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	97	92	88	84	89	85	81	78	71	69	66	59	57	55	48	46	45
2	88	80	73	68	80	73	68	63	62	58	54	51	48	45	41	39	37
3	80	70	62	56	73	64	58	52	54	49	45	45	41	38	36	33	31
4	73	61	53	47	67	57	49	44	48	42	38	40	36	32	32	29	26
5	67	55	46	40	61	50	43	37	43	37	32	36	31	28	29	26	23
6	61	49	40	34	56	45	38	32	38	33	28	32	27	24	26	23	20
7	57	44	36	30	52	41	33	28	35	29	25	29	25	21	24	20	18
8	52	40	32	26	48	37	30	25	32	26	22	27	22	19	22	18	16
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	17	14
10	46	33	26	21	42	31	24	20	27	21	17	22	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7721	7721	7721
5°	7742	7519	7533
10°	7692	7371	7350
15°	7619	7205	7144
20°	7513	7025	6944
25°	7393	6827	6729
30°	7263	6630	6508
35°	7116	6428	6313
40°	6997	6236	6110
45°	6824	6054	5931
50°	6674	5848	5741
55°	6520	5650	5523
60°	6281	5403	5319
65°	6020	5136	5071
70°	5700	4833	4786
75°	5256	4494	4514
80°	4754	4149	4230
85°	4090	3803	3999

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6824 cd/sqm

TEST NUMBER: P1001939

CATALOG NUMBER: SA4XXDIP-B795D810UB27-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.7	1.5
10°-20°	257.0	4.3
20°-30°	388.6	6.4
30°-40°	470.2	7.8
40°-50°	497.1	8.2
50°-60°	467.8	7.7
60°-70°	388.2	6.4
70°-80°	272.4	4.5
80°-90°	155.1	2.6
90°-100°	377.7	6.3
100°-110°	649.9	10.8
110°-120°	564.3	9.3
120°-130°	461.5	7.6
130°-140°	374.8	6.2
140°-150°	280.0	4.6
150°-160°	195.3	3.2
160°-170°	114.8	1.9
170°-180°	37.3	0.6
0°-30°	735.4	12.2
0°-40°	1205.6	20.0
0°-60°	2170.4	35.9
0°-90°	2986.1	49.4
90°-120°	1591.9	26.3
90°-150°	2708.1	44.8
90°-180°	3056.0	50.6
0°-180°	6041.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	948	945	937	946	945	90
15°	909	910	906	916	915	256
25°	831	838	841	852	854	383
35°	727	740	751	766	769	455
45°	606	627	647	665	670	469
55°	475	497	529	550	557	423
65°	329	363	399	425	434	326
75°	182	222	266	296	305	194
85°	56	101	148	180	191	59
90°	18	66	119	151	160	13
95°	39	128	709	426	315	38
105°	98	159	567	1166	1170	105
115°	162	212	493	924	1103	161
125°	222	261	470	774	872	198
135°	260	310	446	669	763	202
145°	299	341	434	548	606	188
155°	338	365	422	478	499	156
165°	369	380	405	429	435	104
175°	385	385	388	394	392	37
180°	385	385	385	385	385	

TEST NUMBER: P1001939

CATALOG NUMBER: SA4XXDIP-B795D810UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	946.8	946.8	946.8	946.8	946.8
2.5°	951.0	947.9	939.4	946.8	945.7
5°	947.9	944.7	937.2	945.7	944.7
7.5°	941.5	939.4	933.0	942.6	941.5
10°	933.0	931.9	926.6	936.2	935.1
12.5°	921.3	921.3	918.2	926.6	926.6
15°	908.6	909.7	906.5	916.0	915.0
17.5°	891.7	894.8	893.8	903.3	902.3
20°	873.6	876.8	877.9	888.5	888.5
22.5°	853.5	857.7	859.9	870.5	872.6
25°	831.2	837.6	840.8	852.4	853.5
27.5°	806.8	816.4	820.6	831.2	832.3
30°	782.5	790.9	798.4	810.0	812.1
32.5°	755.9	766.6	775.0	788.8	790.9
35°	727.3	740.0	750.6	765.5	768.7
37.5°	698.7	713.5	726.3	741.1	744.3
40°	671.1	684.9	699.8	715.7	719.9
42.5°	639.3	655.2	673.3	691.3	694.5
45°	606.5	626.6	646.7	664.8	670.1
47.5°	575.7	595.9	619.2	637.2	643.6
50°	541.8	565.1	588.4	609.6	616.0
52.5°	507.9	531.2	558.7	579.9	586.3
55°	475.0	497.3	529.1	550.3	556.6
57.5°	437.9	465.4	496.2	521.6	526.9
60°	401.8	429.4	464.4	488.8	497.3
62.5°	366.8	397.6	432.6	457.0	465.4
65°	328.7	362.6	398.6	425.2	433.6
67.5°	292.6	328.7	366.8	393.3	401.8
70°	255.5	291.6	331.9	360.5	367.9
72.5°	219.5	256.6	300.0	327.6	336.1
75°	182.4	221.6	266.1	295.8	305.3
77.5°	147.4	188.7	235.4	265.1	275.7
80°	115.6	158.0	204.6	236.4	244.9
82.5°	83.8	128.3	174.9	207.8	217.3
85°	56.2	100.7	148.4	180.2	190.8
87.5°	35.0	78.5	125.1	155.9	165.4
90°	17.8	65.5	118.6	150.8	160.1
92.5°	26.5	111.3	395.4	226.4	205.7
95°	38.8	127.5	709.2	426.4	315.1
97.5°	54.3	130.6	747.0	738.3	567.6
100°	69.2	137.6	689.3	972.2	810.8
102.5°	84.4	147.0	619.6	1115.8	1023.5
105°	98.1	159.0	566.6	1165.8	1170.2
107.5°	115.5	172.6	530.3	1143.5	1236.4
110°	131.9	184.9	511.6	1076.6	1232.6

TEST NUMBER: P1001939

CATALOG NUMBER: SA4XXDIP-B795D810UB27-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	147.5	198.4	499.5	996.0	1181.6
115°	162.4	211.6	492.7	924.2	1103.4
117.5°	179.0	224.7	486.6	865.5	1027.7
120°	194.6	236.4	481.3	823.9	963.7
122.5°	209.7	248.7	475.3	795.5	912.0
125°	221.5	261.3	470.3	773.9	872.3
127.5°	233.6	275.0	463.5	752.1	845.8
130°	242.4	287.1	457.4	728.2	821.2
132.5°	252.3	298.5	452.4	701.0	795.5
135°	260.3	309.5	446.3	669.2	762.7
137.5°	269.3	318.0	442.1	636.7	725.2
140°	279.2	326.6	438.2	604.9	685.9
142.5°	288.8	334.6	436.1	576.1	644.2
145°	298.6	340.6	434.5	548.4	606.4
147.5°	310.0	347.5	432.3	524.6	570.8
150°	320.6	353.9	430.0	506.4	540.5
152.5°	329.3	360.0	426.2	492.1	517.8
155°	338.4	365.3	422.4	478.4	498.9
157.5°	347.5	370.2	418.6	465.6	481.5
160°	355.8	374.4	414.1	452.7	465.6
162.5°	363.4	377.8	409.6	440.2	450.4
165°	368.7	380.0	405.0	428.9	435.3
167.5°	374.7	381.9	400.5	419.0	423.2
170°	378.5	383.5	395.9	409.2	411.8
172.5°	382.3	384.6	391.4	400.4	400.5
175°	384.6	385.3	388.4	393.7	392.1
177.5°	386.1	385.3	386.1	388.8	386.1
180°	385.3	385.3	385.3	385.3	385.3

(END OF REPORT)