

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001942

Luminaire Tested: SA4XXDIP-B795D810UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001942
REPORT IS A COMBINATION OF REPORTS P996567 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB27-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6209.7 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001942

CATALOG NUMBER: SA4XXDIP-B795D810UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001942

CATALOG NUMBER: SA4XXDIP-B795D810UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	94	90	87	92	88	84	81	75	73	71	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	31
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	27
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17
10	48	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10789	10789	10789
5°	10798	10479	10492
10°	10706	10188	10117
15°	10553	9842	9694
20°	10357	9468	9255
25°	10136	9072	8784
30°	9870	8645	8267
35°	9595	8208	7766
40°	9307	7737	7234
45°	9005	7265	6737
50°	8673	6807	6186
55°	8310	6272	5639
60°	7938	5686	5069
65°	7514	5082	4427
70°	7025	4354	3738
75°	6294	3509	2994
80°	5363	2537	2106
85°	4162	1412	1134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9005 cd/sqm

TEST NUMBER: P1001942

CATALOG NUMBER: SA4XXDIP-B795D810UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.7	2.0
10°-20°	351.3	5.7
20°-30°	517.1	8.3
30°-40°	601.1	9.7
40°-50°	601.0	9.7
50°-60°	525.7	8.5
60°-70°	390.3	6.3
70°-80°	221.4	3.6
80°-90°	64.9	1.0
90°-100°	286.2	4.6
100°-110°	582.2	9.4
110°-120°	518.9	8.4
120°-130°	435.9	7.0
130°-140°	363.7	5.9
140°-150°	277.8	4.5
150°-160°	195.3	3.1
160°-170°	114.8	1.8
170°-180°	37.3	0.6
0°-30°	993.1	16.0
0°-40°	1594.2	25.7
0°-60°	2720.9	43.8
0°-90°	3397.5	54.7
90°-120°	1387.3	22.3
90°-150°	2464.7	39.7
90°-180°	2812.0	45.3
0°-180°	6209.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1323	1323	1323	1323	1323	
5°	1322	1318	1306	1318	1316	125
15°	1258	1254	1238	1245	1242	355
25°	1140	1132	1117	1118	1114	524
35°	981	973	958	951	946	613
45°	800	793	776	764	761	617
55°	605	602	587	575	568	542
65°	410	405	394	384	378	406
75°	218	213	208	204	202	232
85°	57	57	55	55	54	62
90°	1	6	14	15	16	5
95°	25	79	617	305	185	27
105°	89	128	497	1069	1065	94
115°	156	196	443	851	1023	155
125°	217	258	441	724	816	194
135°	258	307	437	643	730	200
145°	298	341	434	542	596	187
155°	338	365	422	478	499	156
165°	369	380	405	429	435	104
175°	385	385	388	394	392	37
180°	385	385	385	385	385	

TEST NUMBER: P1001942

CATALOG NUMBER: SA4XXDIP-B795D810UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1323.1	1323.1	1323.1	1323.1	1323.1
2.5°	1327.3	1324.2	1312.5	1323.1	1322.0
5°	1322.0	1317.8	1306.1	1317.8	1315.7
7.5°	1312.5	1308.3	1295.5	1305.1	1304.0
10°	1298.7	1294.5	1280.7	1289.2	1287.1
12.5°	1280.7	1276.5	1261.6	1271.2	1268.0
15°	1258.4	1254.2	1238.3	1244.6	1241.5
17.5°	1233.0	1227.7	1212.8	1217.1	1215.0
20°	1204.4	1199.1	1183.2	1186.3	1184.2
22.5°	1173.6	1166.2	1150.3	1156.7	1152.4
25°	1139.7	1132.3	1117.4	1118.5	1114.2
27.5°	1101.5	1094.1	1080.3	1078.2	1072.9
30°	1063.4	1054.9	1041.1	1036.9	1031.6
32.5°	1023.1	1015.7	1000.8	995.5	990.2
35°	980.7	973.2	958.4	951.0	945.7
37.5°	936.1	929.8	913.9	906.5	899.0
40°	892.7	884.2	868.3	857.7	852.4
42.5°	846.0	841.8	823.8	811.0	807.9
45°	800.4	793.0	776.1	764.4	761.2
47.5°	752.7	747.4	731.5	718.8	710.3
50°	704.0	699.7	684.9	670.0	663.7
52.5°	656.3	650.9	635.0	622.3	613.8
55°	605.4	602.2	587.3	574.6	568.3
57.5°	557.7	554.5	539.6	526.9	520.5
60°	507.8	502.5	488.7	479.2	473.9
62.5°	459.1	454.8	440.0	431.5	426.2
65°	410.3	405.0	394.4	383.8	378.5
67.5°	360.5	356.2	345.6	335.0	334.0
70°	314.9	307.5	299.0	290.5	287.3
72.5°	266.1	258.7	252.3	246.0	242.8
75°	218.4	213.1	207.8	203.6	202.5
77.5°	171.7	169.6	164.3	163.3	160.1
80°	130.4	127.2	125.1	123.0	121.9
82.5°	90.1	89.1	89.1	88.0	86.9
85°	57.2	57.2	55.1	55.1	54.1
87.5°	27.6	26.5	25.4	25.4	25.4
90°	0.8	6.1	13.6	15.1	15.9
92.5°	10.6	58.3	296.8	98.0	68.9
95°	25.0	78.7	617.0	305.4	184.7
97.5°	41.6	87.1	660.1	623.8	443.6
100°	57.5	98.4	608.7	863.0	694.2
102.5°	72.7	112.0	544.3	1013.0	912.2
105°	88.6	128.3	496.6	1069.3	1065.2
107.5°	106.0	145.0	465.6	1052.3	1137.8
110°	123.4	161.6	451.2	991.8	1139.3



TEST NUMBER: P1001942

CATALOG NUMBER: SA4XXDIP-B795D810UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	140.1	178.3	444.4	917.6	1094.7
115°	156.0	195.7	442.9	851.0	1022.8
117.5°	172.6	212.0	442.1	798.7	952.4
120°	189.3	227.9	442.1	763.5	894.8
122.5°	204.4	243.4	441.4	740.4	849.4
125°	217.3	258.2	440.6	724.1	816.1
127.5°	229.4	271.8	439.1	708.6	794.9
130°	239.2	285.0	438.3	690.0	776.7
132.5°	249.1	296.4	437.6	668.1	756.3
135°	258.2	307.4	436.8	642.8	729.8
137.5°	267.2	316.8	436.8	615.5	698.7
140°	277.1	325.5	436.1	589.0	664.7
142.5°	287.7	333.5	436.1	564.4	628.3
145°	297.5	340.6	434.5	542.0	595.8
147.5°	308.9	347.5	432.3	523.5	565.5
150°	319.5	353.9	430.0	506.4	540.5
152.5°	329.3	360.0	426.2	492.1	517.8
155°	338.4	365.3	422.4	478.4	498.9
157.5°	347.5	370.2	418.6	465.6	481.5
160°	355.8	374.4	414.1	452.7	465.6
162.5°	363.4	377.8	409.6	440.2	450.4
165°	368.7	380.0	405.0	428.9	435.3
167.5°	374.7	381.9	400.5	419.0	423.2
170°	378.5	383.5	395.9	409.2	411.8
172.5°	382.3	384.6	391.4	400.4	400.5
175°	384.6	385.3	388.4	393.7	392.1
177.5°	386.1	385.3	386.1	388.8	386.1
180°	385.3	385.3	385.3	385.3	385.3

(END OF REPORT)