

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000963

Luminaire Tested: SA4XXDIP-B1195D365UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000963
REPORT IS A COMBINATION OF REPORTS P995579 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D365UB35-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6430.0 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000963

CATALOG NUMBER: SA4XXDIP-B1195D365UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1000963

CATALOG NUMBER: SA4XXDIP-B1195D365UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	100	100	100	92	92	92	84	84	84
1	104	100	96	92	100	96	92	89	88	85	82	81	78	76	74	72	71
2	95	87	81	75	91	84	78	73	77	72	68	71	67	64	65	62	60
3	87	77	69	63	83	74	67	61	68	62	57	63	58	54	58	54	51
4	80	68	60	53	76	66	58	52	61	54	49	56	51	46	52	47	44
5	73	61	52	46	70	59	51	45	54	48	43	50	45	40	47	42	38
6	68	55	46	40	64	53	45	39	49	42	37	46	40	35	42	37	34
7	63	50	41	35	60	48	40	35	45	38	33	42	36	31	39	34	30
8	58	45	37	32	56	44	36	31	41	34	30	38	32	28	36	31	27
9	54	42	34	28	52	40	33	28	38	31	27	35	30	25	33	28	24
10	51	38	31	26	49	37	30	25	35	28	24	33	27	23	31	26	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16355	16355	16355
5°	16369	15885	15904
10°	16230	15444	15336
15°	15998	14919	14694
20°	15700	14353	14031
25°	15366	13753	13316
30°	14962	13105	12531
35°	14544	12442	11773
40°	14109	11728	10966
45°	13652	11012	10212
50°	13146	10318	9377
55°	12597	9508	8547
60°	12034	8620	7684
65°	11391	7704	6709
70°	10648	6599	5666
75°	9542	5320	4539
80°	8131	3845	3192
85°	6316	2142	1719

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13652 cd/sqm

TEST NUMBER: P1000963

CATALOG NUMBER: SA4XXDIP-B1195D365UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	2.9
10°-20°	532.6	8.3
20°-30°	783.8	12.2
30°-40°	911.2	14.2
40°-50°	911.1	14.2
50°-60°	796.9	12.4
60°-70°	591.6	9.2
70°-80°	335.7	5.2
80°-90°	97.1	1.5
90°-100°	30.1	0.5
100°-110°	90.1	1.4
110°-120°	153.1	2.4
120°-130°	201.9	3.1
130°-140°	226.8	3.5
140°-150°	222.9	3.5
150°-160°	187.5	2.9
160°-170°	124.8	1.9
170°-180°	43.7	0.7
0°-30°	1505.5	23.4
0°-40°	2416.7	37.6
0°-60°	4124.6	64.1
0°-90°	5149.0	80.1
90°-120°	273.3	4.3
90°-150°	925.1	14.4
90°-180°	1281.0	19.9
0°-180°	6430.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2006	2006	2006	2006	2006	
5°	2004	1998	1980	1998	1994	190
15°	1908	1901	1877	1887	1882	538
25°	1728	1716	1694	1696	1689	795
35°	1487	1475	1453	1442	1434	930
45°	1213	1202	1176	1159	1154	935
55°	918	913	890	871	861	822
65°	622	614	598	582	574	616
75°	331	323	315	309	307	351
85°	87	87	84	84	82	93
90°	1	5	8	10	11	7
95°	21	25	27	28	28	23
105°	83	84	85	86	87	88
115°	156	156	155	155	154	154
125°	227	227	226	226	225	202
135°	292	295	295	294	293	226
145°	355	357	357	357	356	222
155°	407	407	407	408	407	187
165°	443	442	441	444	442	125
175°	461	459	459	461	459	44
180°	462	462	462	462	462	

TEST NUMBER: P1000963

CATALOG NUMBER: SA4XXDIP-B1195D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2005.7	2005.7	2005.7	2005.7	2005.7
2.5°	2012.1	2007.3	1989.6	2005.7	2004.1
5°	2004.1	1997.7	1980.0	1997.7	1994.4
7.5°	1989.6	1983.2	1963.9	1978.4	1976.8
10°	1968.7	1962.3	1941.4	1954.3	1951.1
12.5°	1941.4	1935.0	1912.5	1926.9	1922.1
15°	1907.7	1901.2	1877.1	1886.8	1881.9
17.5°	1869.1	1861.1	1838.6	1845.0	1841.8
20°	1825.7	1817.7	1793.6	1798.4	1795.2
22.5°	1779.1	1767.8	1743.7	1753.4	1746.9
25°	1727.7	1716.4	1693.9	1695.5	1689.1
27.5°	1669.8	1658.6	1637.7	1634.4	1626.4
30°	1611.9	1599.1	1578.2	1571.8	1563.7
32.5°	1550.9	1539.6	1517.1	1509.1	1501.1
35°	1486.6	1475.3	1452.8	1441.6	1433.6
37.5°	1419.1	1409.4	1385.3	1374.1	1362.8
40°	1353.2	1340.3	1316.2	1300.2	1292.1
42.5°	1282.5	1276.1	1248.7	1229.5	1224.6
45°	1213.4	1202.1	1176.4	1158.7	1153.9
47.5°	1141.1	1133.0	1108.9	1089.6	1076.8
50°	1067.1	1060.7	1038.2	1015.7	1006.1
52.5°	994.8	986.8	962.7	943.4	930.5
55°	917.7	912.8	890.3	871.1	861.4
57.5°	845.3	840.5	818.0	798.7	789.1
60°	769.8	761.8	740.9	726.4	718.4
62.5°	695.9	689.5	667.0	654.1	646.1
65°	622.0	613.9	597.9	581.8	573.7
67.5°	546.4	540.0	523.9	507.9	506.2
70°	477.3	466.1	453.2	440.4	435.5
72.5°	403.4	392.1	382.5	372.9	368.0
75°	331.1	323.0	315.0	308.6	307.0
77.5°	260.4	257.1	249.1	247.5	242.7
80°	197.7	192.9	189.6	186.4	184.8
82.5°	136.6	135.0	135.0	133.4	131.8
85°	86.8	86.8	83.6	83.6	82.0
87.5°	41.8	40.2	38.6	38.6	38.6
90°	1.1	5.0	7.9	10.0	10.7
92.5°	9.3	13.9	15.7	16.8	17.1
95°	21.4	24.6	27.1	28.2	28.2
97.5°	34.3	37.1	40.0	41.4	41.4
100°	50.0	51.4	54.6	55.3	55.3
102.5°	66.4	66.8	69.6	70.7	71.1
105°	83.2	83.6	85.0	86.1	87.1
107.5°	100.7	101.0	101.4	102.8	102.5
110°	118.5	119.3	118.9	118.2	119.3



TEST NUMBER: P1000963

CATALOG NUMBER: SA4XXDIP-B1195D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	137.1	137.1	136.4	136.4	136.4
115°	155.7	155.7	155.0	154.6	154.3
117.5°	173.2	173.2	172.8	171.7	170.7
120°	190.7	192.1	191.0	189.2	190.0
122.5°	208.9	209.2	208.9	207.8	206.0
125°	226.7	226.7	226.4	225.7	225.0
127.5°	242.8	243.9	243.2	242.4	242.1
130°	259.9	261.0	261.0	260.3	258.9
132.5°	277.4	278.2	277.8	277.1	276.7
135°	292.4	294.6	294.6	293.9	292.8
137.5°	309.2	310.3	311.0	309.9	310.3
140°	326.0	326.7	326.7	326.4	326.0
142.5°	341.4	342.1	341.7	341.7	341.7
145°	355.3	356.7	357.1	356.7	355.6
147.5°	369.6	371.3	371.0	370.6	370.3
150°	382.4	383.8	383.8	383.8	383.5
152.5°	394.6	395.3	395.6	396.7	395.6
155°	407.1	407.1	406.7	408.1	406.7
157.5°	417.8	417.1	417.1	418.1	417.1
160°	427.1	426.7	426.3	427.4	425.6
162.5°	435.6	434.6	434.2	436.3	434.6
165°	443.1	442.0	441.3	443.5	442.0
167.5°	449.2	447.8	447.8	449.9	447.8
170°	454.2	452.4	452.8	454.9	452.4
172.5°	457.8	456.3	456.3	458.8	456.3
175°	461.0	459.2	458.8	461.3	458.8
177.5°	462.4	460.6	460.6	463.1	460.3
180°	461.7	461.7	461.7	461.7	461.7

(END OF REPORT)