

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001965

Luminaire Tested: SA4XXDIP-B795D810UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001965
REPORT IS A COMBINATION OF REPORTS P996590 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB30-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6166.0 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001965

CATALOG NUMBER: SA4XXDIP-B795D810UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001965

CATALOG NUMBER: SA4XXDIP-B795D810UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56		
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	52	47		
2	90	83	76	71	83	77	72	67	66	62	59	57	54	51	48	45	43	39		
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	39	37	33		
4	75	64	56	50	70	60	53	47	52	47	42	45	40	37	38	35	32	28		
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25		
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24	22		
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19		
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17		
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16		
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10881	10881	10881
5°	10890	10568	10581
10°	10798	10275	10203
15°	10643	9926	9777
20°	10445	9549	9334
25°	10223	9150	8859
30°	9954	8719	8338
35°	9676	8278	7833
40°	9387	7803	7296
45°	9083	7327	6794
50°	8747	6865	6238
55°	8380	6326	5687
60°	8007	5735	5111
65°	7578	5126	4464
70°	7086	4390	3770
75°	6349	3540	3019
80°	5408	2559	2125
85°	4199	1425	1142

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9083 cd/sqm

TEST NUMBER: P1001965

CATALOG NUMBER: SA4XXDIP-B795D810UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.8	2.0
10°-20°	354.3	5.7
20°-30°	521.5	8.5
30°-40°	606.2	9.8
40°-50°	606.2	9.8
50°-60°	530.2	8.6
60°-70°	393.6	6.4
70°-80°	223.3	3.6
80°-90°	66.1	1.1
90°-100°	64.3	1.0
100°-110°	192.7	3.1
110°-120°	327.4	5.3
120°-130°	431.8	7.0
130°-140°	485.0	7.9
140°-150°	476.7	7.7
150°-160°	400.9	6.5
160°-170°	266.7	4.3
170°-180°	93.4	1.5
0°-30°	1001.6	16.2
0°-40°	1607.8	26.1
0°-60°	2744.1	44.5
0°-90°	3427.1	55.6
90°-120°	584.5	9.5
90°-150°	1977.9	32.1
90°-180°	2739.0	44.4
0°-180°	6166.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1334	1334	1334	1334	1334	
5°	1333	1329	1317	1329	1327	127
15°	1269	1265	1249	1255	1252	358
25°	1149	1142	1127	1128	1124	529
35°	989	982	967	959	954	618
45°	807	800	783	771	768	622
55°	610	607	592	580	573	547
65°	414	408	398	387	382	410
75°	220	215	210	205	204	234
85°	58	58	56	56	54	62
90°	2	11	17	21	23	7
95°	46	53	58	60	60	50
105°	178	179	182	184	186	189
115°	333	333	331	331	330	328
125°	485	485	484	482	481	432
135°	625	630	630	628	626	484
145°	760	763	763	763	760	475
155°	870	870	870	873	870	401
165°	947	945	944	948	945	267
175°	986	982	981	986	981	94
180°	987	987	987	987	987	

TEST NUMBER: P1001965

CATALOG NUMBER: SA4XXDIP-B795D810UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1334.4	1334.4	1334.4	1334.4	1334.4
2.5°	1338.7	1335.5	1323.7	1334.4	1333.3
5°	1333.3	1329.1	1317.3	1329.1	1326.9
7.5°	1323.7	1319.4	1306.6	1316.2	1315.2
10°	1309.8	1305.5	1291.6	1300.2	1298.0
12.5°	1291.6	1287.4	1272.4	1282.0	1278.8
15°	1269.2	1264.9	1248.9	1255.3	1252.1
17.5°	1243.5	1238.2	1223.2	1227.5	1225.3
20°	1214.6	1209.3	1193.3	1196.5	1194.3
22.5°	1183.6	1176.2	1160.1	1166.5	1162.3
25°	1149.4	1141.9	1127.0	1128.0	1123.8
27.5°	1110.9	1103.4	1089.5	1087.4	1082.1
30°	1072.4	1063.9	1050.0	1045.7	1040.4
32.5°	1031.8	1024.3	1009.4	1004.0	998.7
35°	989.0	981.6	966.6	959.1	953.8
37.5°	944.1	937.7	921.7	914.2	906.7
40°	900.3	891.7	875.7	865.0	859.7
42.5°	853.2	849.0	830.8	818.0	814.8
45°	807.3	799.8	782.7	770.9	767.7
47.5°	759.2	753.8	737.8	724.9	716.4
50°	710.0	705.7	690.7	675.8	669.3
52.5°	661.9	656.5	640.5	627.6	619.1
55°	610.5	607.3	592.4	579.5	573.1
57.5°	562.4	559.2	544.2	531.4	525.0
60°	512.2	506.8	492.9	483.3	477.9
62.5°	463.0	458.7	443.7	435.2	429.8
65°	413.8	408.4	397.8	387.1	381.7
67.5°	363.5	359.3	348.6	337.9	336.8
70°	317.6	310.1	301.5	293.0	289.8
72.5°	268.4	260.9	254.5	248.1	244.9
75°	220.3	214.9	209.6	205.3	204.2
77.5°	173.2	171.1	165.7	164.7	161.5
80°	131.5	128.3	126.2	124.0	123.0
82.5°	90.9	89.8	89.8	88.7	87.7
85°	57.7	57.7	55.6	55.6	54.5
87.5°	27.8	26.7	25.7	25.7	25.7
90°	2.3	10.7	16.8	21.4	22.9
92.5°	19.8	29.8	33.6	35.9	36.6
95°	45.8	52.7	58.0	60.3	60.3
97.5°	73.3	79.4	85.5	88.6	88.6
100°	106.9	109.9	116.8	118.3	118.3
102.5°	142.0	142.8	148.9	151.2	151.9
105°	177.9	178.6	181.7	184.0	186.3
107.5°	215.3	216.1	216.8	219.9	219.1
110°	253.5	255.0	254.2	252.7	255.0

TEST NUMBER: P1001965

CATALOG NUMBER: SA4XXDIP-B795D810UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	293.2	293.2	291.6	291.6	291.6
115°	332.9	332.9	331.3	330.6	329.8
117.5°	370.3	370.3	369.5	367.2	364.9
120°	407.7	410.7	408.4	404.6	406.1
122.5°	446.6	447.4	446.6	444.3	440.5
125°	484.8	484.8	484.0	482.5	481.0
127.5°	519.1	521.4	519.9	518.4	517.6
130°	555.8	558.1	558.1	556.5	553.5
132.5°	593.2	594.7	594.0	592.4	591.7
135°	625.3	629.8	629.8	628.3	626.0
137.5°	661.1	663.4	664.9	662.7	663.4
140°	697.0	698.5	698.5	697.8	697.0
142.5°	729.8	731.4	730.6	730.6	730.6
145°	759.6	762.7	763.4	762.7	760.4
147.5°	790.2	794.0	793.2	792.4	791.7
150°	817.6	820.7	820.7	820.7	819.9
152.5°	843.6	845.1	845.9	848.2	845.9
155°	870.3	870.3	869.5	872.6	869.5
157.5°	893.2	891.7	891.7	894.0	891.7
160°	913.1	912.3	911.5	913.8	910.0
162.5°	931.4	929.1	928.3	932.9	929.1
165°	947.4	945.1	943.6	948.2	945.1
167.5°	960.4	957.3	957.3	961.9	957.3
170°	971.1	967.3	968.0	972.6	967.3
172.5°	978.7	975.7	975.7	981.0	975.7
175°	985.6	981.8	981.0	986.4	981.0
177.5°	988.6	984.8	984.8	990.2	984.1
180°	987.1	987.1	987.1	987.1	987.1

(END OF REPORT)